



AC to DC SlimLine Wall Adapters

AC to DC Wall Adapters

Request a Large Quantity Quote

Jameco Part #	Manufacturer	Manufacturer Part #	Primary Output Voltage (VDC)	Output Current (A)	Maximum Output Power (W)	Input VAC @ Hz	Output Connector	Agency Approvals	Case Size (in)	Price 1	Price 10+
2138636	Emerson Network Power	SW013US-0500020US	5	0.2	1	100 to 240@50 to 60	USB Type A USB Female	TUV/FCC	0.8 x 1.5 x 2.5	\$2.95	\$2.59
2234097	Phihong	PLA02A-050-1.7	5	0.4	2	90 to 264@47 to 63	1.7mm x 3.0mm Right Angle Cylindrical Female Center Positive	UL,CUL	2 x 1.3 x 1	\$4.95	\$4.49
252701	Jameco Reliapro	S08AB050050G9270-R	5	0.5	2.5	100 to 240@47 to 63	2.1mm x 5.5mm Cylindrical Female Center Positive	UL/CUL/CE	1.7 x 1.1 x 2.9	\$6.95	\$6.59
2126125	Arndt	ADS0051-W050080	5	0.8	4	100 to 240@50 to 60	2.1mm x 5.5mm Cylindrical Female Center Positive	UL/CUL/CE/CEC	0.11 x 1.6 x 1.9	\$6.95	\$5.95
252720	Jameco Reliapro	HK-AP-050A100-US	5	1	7.5	100 to 240@50 to 60	2.1mm x 5.5mm Cylindrical Female Center Positive	UL/CUL/CEC	1.4 x 1 x 2.4	\$8.95	\$7.95
1940660	MEAN WELL	GS06U-1P1J	5	1	5	90 to 264@47 to 63	2.1mm x 5.5mm Cylindrical Female Center Positive	CB/CE/CUL/FCC/UL	1.11 x 1.6 x 2.6	\$9.40	\$8.15
2211098	Phihong	PLA05A-050-R	5	1	5	90 to 264@47 to 63	2.1mm x 5.5mm Cylindrical Female Center Positive	UL/CUL	3.1 x 1.3 x 1.6	\$5.49	\$4.49
2188537	CUI	EPAS-101W-05	5	2	10	100 to 240@50 to 60	2.5mm x 5.5mm Cylindrical Female Center Positive	UL/CUL	2.4 x 1.7 x 1	\$6.95	\$6.25
2209158	CUI	EPAS-101W-05-2.1	5	2	10	100 to 240@50 to 60	2.1mm x 5.5mm Cylindrical Female Center Positive	UL/CUL	2.4 x 1.7 x 1	\$7.95	\$6.95
2217772	Jameco Reliapro	KSAS0120500200VU	5	2	10	100 to 240@47 to 63	2.1mm x 5.5mm Cylindrical Female Center Positive	UL/CUL	3 x 1.6 x 1.2	\$11.95	\$10.95
2244359	Jameco Reliapro	XS-0502100FU	5	2.1	10.5	100 to 240@50 to 60	USB-A Sockets (2x)	UL	2 x 2 x 1.1	\$6.95	\$6.25
2217617	Seeed Studios	313990002	5	2.1	10	100 to 240@50 to 60	USB Type A USB Female	UL/FCC	2.2 x 1.2	\$9.95	\$8.95
2247091	MEAN WELL	SGA12U05-USB	5	2.4	12	90 to 264@47 to 63	2.1mm x 5.5mm Cylindrical Female Center Positive	CB/CUL/FCC/UL	2.45 x 1.08 x 1.56	\$9.50	\$7.75
2247082	MEAN WELL	SGA12U05-P1J	5	2.4	12	90 to 264@47 to 63	2.1mm x 5.5mm Cylindrical Female Center Positive	CB/CUL/FCC/UL	2.45 x 1.08 x 1.56	\$10.10	\$8.25
2138724	Jentec Technology	AF1805-A	5	2.5	12.5	100 to 120@50 to 60	2.1mm x 5.5mm Right Angle Cylindrical Female Center Positive	UL/CUL/CEC IV	1.3 x 1.9 x 2.4	\$5.95	\$4.95
2230336	Dee Van Enterprise Usa	DSA-15P-05 US	5	2.5	12.5	100 to 240@50 to 60	2.1mm x 5.5mm Cylindrical Female Center Positive	UL/CUL	2.7 x 1.7 x 1.1	\$10.95	\$9.95
2224016	Jameco Reliapro	KSAS0150500300VU-VI	5	3	15	100 to 240@47 to 63	2.1mm x 5.5mm Cylindrical Female Center Positive	UL/CUL	3.3 x 1.7 x 1.3	\$13.95	\$12.95
2247171	MEAN WELL	SGA18U05-P1J	5	3	15	90 to 264@47 to 63	2.1mm x 5.5mm Cylindrical Female Center Positive	CB/CUL/FCC/UL	2.97 x 1.26 x 1.87	\$12.80	\$10.49
2135451	OpenPeak	LFS054000D-8AS	5	4	20	90 to 132@50 to 60	2.1mm x 5.5mm Right Angle Cylindrical Female Center Positive	CE	1.7 x 2 x 3.6	\$9.95	\$8.95
2247242	MEAN WELL	SGA25U05-P1J	5	4	25	90 to 264@47 to 63	2.1mm x 5.5mm Cylindrical Female Center Positive	CB/CUL/FCC/UL	2.97 x 1.26 x 1.87	\$14.00	\$11.45
2225932	MEAN WELL	SGA40U05-P1J	5	5	25	90 to 264@47 to 63	2.1mm x 5.5mm Cylindrical Female Center Positive	CB/CUL/FCC/UL	2.97 x 1.26 x 1.87	\$18.00	\$14.75
2226003	MEAN WELL	SGA60U05-P1J	5	6	30	90 to 264@47 to 63	2.1mm x 5.5mm Cylindrical Female Center Positive	CB/CUL/FCC/UL	3.68 x 1.38 x 2.03	\$20.70	\$16.95
2145078	Arndt	MGT-6500SPS	6	0.5	3	90 to 264@50 to 60	2.1mm x 5.5mm Cylindrical Female Center Positive	UL/CUL/CEC	1.3 x 1.7 x 2.5	\$6.95	\$5.95
2230133	Jameco Reliapro	GQ05-060050-CU	6	0.5	3	100 to 240@47 to 63	2.1mm x 5.5mm Cylindrical Female Center Positive	UL/CUL	2.3 x 1.6 x 1.1	\$8.95	\$7.95
1940678	MEAN WELL	GS06U-11P1J	7.5	0.8	6	90 to 264@47 to 63	2.1mm x 5.5mm Cylindrical Female Center Positive	CB/CE/CUL/FCC/UL	2.1 x 1.3 x 2.6	\$9.40	\$8.15
2247103	MEAN WELL	SGA12U07-P1J	7.5	1.6	12	90 to 264@47 to 63	2.1mm x 5.5mm Cylindrical Female Center Positive	CB/CUL/FCC/UL	2.45 x 1.08 x 1.56	\$10.10	\$8.25
2247251	MEAN WELL	SGA25U07-P1J	7.5	2.9	25	90 to 264@47 to 63	2.1mm x 5.5mm Cylindrical Female Center Positive	CB/CUL/FCC/UL	2.97 x 1.26 x 1.87	\$14.00	\$11.45
2226011	MEAN WELL	SGA60U07-P1J	7.5	6	45	90 to 264@47 to 63	2.1mm x 5.5mm Cylindrical Female Center Positive	CB/CUL/FCC/UL	3.68 x 1.38 x 2.03	\$20.70	\$16.95
252753	Jameco Reliapro	S08AB09005001	9	0.5	4.5	100 to 240@47 to 63	2.1mm x 5.5mm Cylindrical Female Center Positive	CE/CEC/CUL/GS/UL	1.7 x 1.1 x 2.5	\$10.95	\$9.95
2236498	Jameco Reliapro	KSAS0050900050VUD	9	0.5	4.5	100 to 240@50 to 60	2.1mm x 5.5mm Cylindrical Female Center Positive	UL,CUL,CE	2.1 x 1.3 x 0.94	\$8.95	\$7.95
1940686	MEAN WELL	GS06U-2P1J	9	0.66	6	90 to 264@47 to 63	2.1mm x 5.5mm Cylindrical Female Center Positive	CB/CE/CUL/FCC/UL	1.11 x 1.3 x 2.6	\$9.40	\$8.15
2203741	Arndt	CYSC24-090100-P	9	1	9	100 to 120@50 to 60	2.5mm x 5.5mm Cylindrical Female Center Positive	UL/CUL/CEC	2.4 x 1.9 x 1.3	\$8.95	\$7.95
2228965	Arndt	CYSC24-090100-P-2.1	9	1	9	100 to 120@50 to 60	2.1mm x 5.5mm Cylindrical Female Center Positive	UL,CUL,CEC	2.4 x 1.9 x 1.3	\$8.95	\$7.95
2234100	Jameco Reliapro	MTR-16110	9	1	9	100 to 240@47 to 63	2.1mm x 5.5mm Cylindrical Female Center Positive	UL	1.5 x 1.1 x 1.7	\$10.95	\$9.95
252779	Jameco Reliapro	HK-AR-090A120-US	9	1.2	10.8	100 to 240@47 to 63	2.1mm x 5.5mm Cylindrical Female Center Positive	CE/CEC/CUL/GS/UL	1.7 x 1.1 x 2.9	\$11.95	\$10.95
2247111	MEAN WELL	SGA12U09-P1J	9	1.33	12	90 to 264@47 to 63	2.1mm x 5.5mm Cylindrical Female Center Positive	CB/CUL/FCC/UL	2.45 x 1.08 x 1.56	\$10.10	\$8.25
252786	Jameco Reliapro	HK-AW-090A150-US	9	1.5	13.5	100 to 240@47 to 63	2.1mm x 5.5mm Cylindrical Female Center Positive	CE/CEC/CUL/GS/UL	1.7 x 1.1 x 2.9	\$12.95	\$11.95
2247189	MEAN WELL	SGA18U09-P1J	9	2	18	90 to 264@47 to 63	2.1mm x 5.5mm Cylindrical Female Center Positive	CB/CUL/FCC/UL	2.97 x 1.26 x 1.87	\$12.80	\$10.49
2247269	MEAN WELL	SGA25U09-P1J	9	2.77	25	90 to 264@47 to 63	2.1mm x 5.5mm Cylindrical Female Center Positive	CB/CUL/FCC/UL	2.97 x 1.26 x 1.87	\$14.00	\$11.45
2225941	MEAN WELL	SGA40U09-P1J	9	4.44	40	90 to 264@47 to 63	2.1mm x 5.5mm Cylindrical Female Center Positive	CB/CUL/FCC/UL	2.97 x 1.26 x 1.87	\$18.00	\$14.75
2226020	MEAN WELL	SGA60U09-P1J	9	5.5	49.5	90 to 264@47 to 63	2.1mm x 5.5mm Cylindrical Female Center Positive	CB/CUL/FCC/UL	3.68 x 1.38 x 2.03	\$20.70	\$16.95
2236412	Jameco Reliapro	GQ05-120025-CU	12	0.25	3	100 to 240@47 to 63	2.1mm x 5.5mm Cylindrical Female Center Positive	UL,CUL	2.3 x 1.06 x 1.67	\$9.95	\$8.95
2150758	Arndt	MGT-12500SPS	12	0.5	6	90 to 264@50 to 60	2.1mm x 5.5mm Cylindrical Female Center Positive	UL/CUL/TUV/CE	1.3 x 1.7 x 2.5	\$7.95	\$6.95
252808	Jameco Reliapro	MPA-12005000	12	0.5	6	100 to 240@47 to 63	2.1mm x 5.5mm Cylindrical Female Center Positive	CE/CEC/CUL/GS/UL	1.7 x 1.1 x 2.5	\$8.95	\$7.95
1940694	MEAN WELL	GS06U-3P1J	12	0.5	6	90 to 264@47 to 63	2.1mm x 5.5mm Cylindrical Female Center Positive	CB/CE/CUL/FCC/UL	1.11 x 1.3 x 2.6	\$9.40	\$8.15
2265639	Arndt	PSU-C9	12	0.75	9	100 to 240@50 to 60	2.5mm x 5.5mm Cylindrical Female Center Positive	UL/CUL	2.7 x 1.7 x 1.7	\$6.95	\$6.25
2270847	Arndt	PSU-C9-ELEV6	12	0.75	9	100 to 240@50 to 60	2.5mm x 5.5mm Cylindrical Female Center Positive	UL/CUL/CEC	2.7 x 1.7 x 1.1	\$7.95	\$6.95
252824	Jameco Reliapro	HK-AR-120A100-US	12	1	12	100 to 240@47 to 63	2.1mm x 5.5mm Cylindrical Female Center Positive	CE/CEC/CUL/GS/UL	1.7 x 1.1 x 2.9	\$11.95	\$10.95
2227436	Arndt	DSA-12G-12AUS-120120	12	1	12	100 to 120@50 to 60	2.1mm x 5.5mm Cylindrical Female Center Positive	UL/CUL/CEC	2.7 x 1.6 x 1.1	\$7.95	\$6.95
2232825	Arndt	SPS121	12	1	12	100 to 240@50 to 60	2.1mm x 5.5mm Cylindrical Female Center Positive	UL/CUL	1.2 x 1.6 x 2.3	\$8.95	\$7.95
2233983	Arndt	DSA-12PFT-12FUS	12	1	12	100 to 240@47 to 63	2.1mm x 5.5mm Cylindrical Female Center Positive	UL	2.7 x 1.5 x 1.1	\$10.95	\$9.95
2247120	MEAN WELL	SGA12U12-P1J	12	1	12	90 to 264@47 to 63	2.1mm x 5.5mm Cylindrical Female Center Positive	CB/CUL/FCC/UL	2.45 x 1.08 x 1.56	\$10.10	\$8.25
252833	Jameco Reliapro	HK-AW-120A125-US	12	1.25	15	100 to 240@47 to 63	2.1mm x 5.5mm Cylindrical Female Center Positive	CE/CEC/CUL/GS/UL	1.7 x 1.1 x 2.9	\$12.95	\$11.95
2236501	Jameco Reliapro	KSA-24W-120150VU	12	1.5	18	100 to 240@50 to 60	2.1mm x 5.5mm Cylindrical Female Center Positive	UL/CUL	3.3 x 1.7 x 1.3	\$13.95	\$12.95

Jameco Pa Manufacturer		Manufacturer Part #	Primary Output Voltage (VDC)	Output Current (A)	Maximum Output Power (W)	Input VAC @ Hz	Output Connector	Agency Approvals	Case Size (in)	Price 1	Price 10+
2247197	MEAN WELL	SGA18U12-P1J	12	1.5	18	90 to 264@47 to 63	2.1mm x 5.5mm Cylindrical Female Center Positive	CB/CUL/FCC/UL	2.97 x 1.26 x 1.87	\$12.80	\$10.49
2228324	Arndt	CYSC24-120188P	12	1.88	22.56	100 to 120@60	2.5mm x 5.5mm Cylindrical Female Center Positive	UL,CEC	-	\$5.95	\$0.00
1950497	Jameco Reliapro	GQ30-120200-BU	12	2	24	100 to 240@50 to 60	2.1mm x 5.5mm Cylindrical Female Center Positive	BSMI/CB/CUL/FCC/PSE	2.3 x 1.3 x 2.9	\$15.95	\$14.49
2228922	Arndt	CAD2412	12	2	24	100 to 240@50 to 60	2.1mm x 5.5mm Cylindrical Female Center Positive	UL/CUL	2.9 x 1.25 x 2.1	\$10.95	\$9.95
2236738	Jameco Reliapro	GQ30-120200-BU-2.5	12	2	24	100 to 240@50 to 60	2.5mm x 5.5mm Cylindrical Female Center Positive	UL,CUL,CE	2.9 x 2.1 x 1.3	\$13.95	\$12.95
2247277	MEAN WELL	SGA25U12-P1J	12	2.08	25	90 to 264@47 to 63	2.1mm x 5.5mm Cylindrical Female Center Positive	CB/CUL/FCC/UL	2.97 x 1.26 x 1.87	\$14.00	\$11.45
2225959	MEAN WELL	SGA40U12-P1J	12	3.33	40	90 to 264@47 to 63	2.1mm x 5.5mm Cylindrical Female Center Positive	CB/CUL/FCC/UL	2.97 x 1.26 x 1.87	\$18.00	\$14.75
2229845	Arndt	AD898F20	12	3.5	42	100 to 240@50 to 60	2.1mm x 5.5mm Cylindrical Female Center Positive	UL/CUL	3.3 x 2.7 x 1.1	\$12.95	\$11.95
2226038	MEAN WELL	SGA60U12-P1J	12	5	60	90 to 264@47 to 63	2.1mm x 5.5mm Cylindrical Female Center Positive	CB/CUL/FCC/UL	3.68 x 1.38 x 2.03	\$20.70	\$16.95
2247138	MEAN WELL	SGA12U15-P1J	15	0.8	12	90 to 264@47 to 63	2.1mm x 5.5mm Cylindrical Female Center Positive	CB/CUL/FCC/UL	2.45 x 1.08 x 1.56	\$10.10	\$8.25
2247200	MEAN WELL	SGA18U15-P1J	15	1.2	18	90 to 264@47 to 63	2.1mm x 5.5mm Cylindrical Female Center Positive	CB/CUL/FCC/UL	2.97 x 1.26 x 1.87	\$12.80	\$10.49
2265647	Arndt	PS15V1300MA-003	15	1.3	19.5	100 to 240@50 to 60	2.1mm x 5.5mm Cylindrical Female Center Positive	UL/CUL/FCC	2.7 x 2.0 x 1.3	\$11.95	\$10.95
2247285	MEAN WELL	SGA25U15-P1J	15	1.66	25	90 to 264@47 to 63	2.1mm x 5.5mm Cylindrical Female Center Positive	CB/CUL/FCC/UL	2.97 x 1.26 x 1.87	\$14.00	\$11.45
2225967	MEAN WELL	SGA40U15-P1J	15	2.66	40	90 to 264@47 to 63	2.1mm x 5.5mm Cylindrical Female Center Positive	CB/CUL/FCC/UL	2.97 x 1.26 x 1.87	\$18.00	\$14.74
2226046	MEAN WELL	SGA60U15-P1J	15	4	60	90 to 264@47 to 63	2.1mm x 5.5mm Cylindrical Female Center Positive	CB/CUL/FCC/UL	3.68 x 1.38 x 2.03	\$20.70	\$16.95
2247146	MEAN WELL	SGA12U18-P1J	18	0.66	12	90 to 264@47 to 63	2.1mm x 5.5mm Cylindrical Female Center Positive	CB/CUL/FCC/UL	2.45 x 1.08 x 1.56	\$10.10	\$8.25
2247218	MEAN WELL	SGA18U18-P1J	18	1	18	90 to 264@47 to 63	2.1mm x 5.5mm Cylindrical Female Center Positive	CB/CUL/FCC/UL	2.97 x 1.26 x 1.87	\$12.80	\$10.49
2247293	MEAN WELL	SGA25U18-P1J	18	1.38	25	90 to 264@47 to 63	2.1mm x 5.5mm Cylindrical Female Center Positive	CB/CUL/FCC/UL	2.97 x 1.26 x 1.87	\$14.00	\$11.45
2225975	MEAN WELL	SGA40U18-P1J	18	2.22	40	90 to 264@47 to 63	2.1mm x 5.5mm Cylindrical Female Center Positive	CB/CUL/FCC/UL	2.97 x 1.26 x 1.87	\$18.00	\$14.75
2226054	MEAN WELL	SGA60U18-P1J	18	3.33	60	90 to 264@47 to 63	2.1mm x 5.5mm Cylindrical Female Center Positive	CB/CUL/FCC/UL	3.68 x 1.38 x 2.03	\$20.70	\$16.95
2229941	Jameco Reliapro	MTR-16109	24	0.5	12	100 to 240@47 to 63	2.1mm x 5.5mm Cylindrical Female Center Positive	UL/CUL/TUV/CE	2.9 x 1.3 x 2.2	\$11.95	\$10.95
2247154	MEAN WELL	SGA12U24-P1J	24	0.5	12	90 to 264@47 to 63	2.1mm x 5.5mm Cylindrical Female Center Positive	CB/CUL/FCC/UL	2.45 x 1.08 x 1.56	\$10.10	\$8.25
2076341	Jameco Reliapro	HK-AW-240A063-US	24	0.63	15.1	100 to 240@47 to 63	2.1mm x 5.5mm Cylindrical Female Center Positive	CEC/CUL/UL	1.7 x 1.1 x 2	\$11.95	\$10.95
2247226	MEAN WELL	SGA18U24-P1J	24	0.75	18	90 to 264@47 to 63	2.1mm x 5.5mm Cylindrical Female Center Positive	CB/CUL/FCC/UL	2.97 x 1.26 x 1.87	\$12.80	\$10.49
2208972	Jameco Reliapro	KSA-24W-240100VU	24	1	24	100 to 240@47 to 63	2.1mm x 5.5mm Cylindrical Female Center Positive	UL/CUL	3.5 x 1.7 x 1.3	\$12.95	\$11.49
2230416	Phihong	PDA024A-1A0S-R	24	1	24	110 to 120@50 to 60	2.1mm x 5.5mm Cylindrical Female Center Positive	IL,CUL	3.4 x 2.1 x 1.4	\$8.95	\$7.95
2247306	MEAN WELL	SGA25U24-P1J	24	1.04	25	90 to 264@47 to 63	2.1mm x 5.5mm Cylindrical Female Center Positive	CB/CUL/FCC/UL	2.97 x 1.26 x 1.87	\$14.00	\$11.45
2225983	MEAN WELL	SGA40U24-P1J	24	1.67	40	90 to 264@47 to 63	2.1mm x 5.5mm Cylindrical Female Center Positive	CB/CUL/FCC/UL	2.97 x 1.26 x 1.87	\$18.00	\$14.75
2226062	MEAN WELL	SGA60U24-P1J	24	2.5	60	90 to 264@47 to 63	2.1mm x 5.5mm Cylindrical Female Center Positive	CB/CUL/FCC/UL	3.68 x 1.38 x 2.03	\$20.70	\$16.95
2179391	Jameco Reliapro	PA1024-360HU-PF04	36	0.67	24.12	90 to 264@47 to 63	2.5mm x 5.5mm Cylindrical Female Center Positive	UL,CUL,CEC	2.8 x 1.9 x 1.3	\$10.39	\$9.39
2247162	MEAN WELL	SGA12U48-P1J	48	0.25	12	90 to 264@47 to 63	2.1mm x 5.5mm Cylindrical Female Center Positive	CB/CUL/FCC/UL	2.45 x 1.08 x 1.56	\$10.10	\$8.25
2247234	MEAN WELL	SGA18U48-P1J	48	0.375	18	90 to 264@47 to 63	2.1mm x 5.5mm Cylindrical Female Center Positive	CB/CUL/FCC/UL	2.97 x 1.26 x 1.87	\$12.80	\$10.49
2247314	MEAN WELL	SGA25U48-P1J	48	0.52	25	90 to 264@47 to 63	2.1mm x 5.5mm Cylindrical Female Center Positive	CB/CUL/FCC/UL	2.97 x 1.26 x 1.87	\$14.00	\$11.45
2225991	MEAN WELL	SGA40U48-P1J	48	0.84	40	90 to 264@47 to 63	2.1mm x 5.5mm Cylindrical Female Center Positive	CB/CUL/FCC/UL	2.97 x 1.26 x 1.87	\$18.00	\$14.75
2226071	MEAN WELL	SGA60U48-P1J	48	1.25	60	90 to 264@47 to 63	2.1mm x 5.5mm Cylindrical Female Center Positive	CB/CUL/FCC/UL	3.68 x 1.38 x 2.03	\$20.70	\$16.95