



AC to DC Wall Adapters

SlimLine AC to DC Wall Adapters

Request a Large Quantity Quote

Jameco Pa	Manufacturer	Manufacturer Part #	Primary Output Voltage (VDC)	Output Current (A)	Maximum Output Power (W)	Input VAC @ Hz	Output Connector	Agency Approvals	Case Size (in)	Price 1	Price 10+
2230408	Phihong	PSM04A-050-R	5	0.75	3.75	100 to 240@50 to 60	2.1mm x 5.5mm Cylindrical Female Center Positive	UL,CUL	2.7 x 1.8 x 0.95	\$6.95	\$6.25
2120090	Arndt	MU05-J050100-A1-2.1	5	1	5	100 to 240@50 to 60	2.1mm x 5.5mm Cylindrical Female Center Positive	UL,CUL	2.3 x 1.3 x 1.5	\$6.49	\$5.95
2234601	Arndt	MU05-050100-A1-10	5	1	5	100 to 240@50 to 60	2.1mm x 5.5mm Cylindrical Female Center Positive	UL,CUL	2.6 x 1.3 x 1.5	\$5.95	\$5.49
2151937	Velleman	PSSUSB4U	5	1	5	100 to 240@50 to 60	Multiple Connectors Included	UL	2.7 x 1.6 x 1.2	\$16.09	\$0.00
2229440	Arndt	TSA1-050120WA	5	1.2	6	100 to 240@50 to 60	Stripped & Tinned Pigtail Wires	UL,CUL	2.1 x 1.8 x 1.1	\$6.95	\$6.25
2229503	Arndt	YFAF22073001	5	1.2	6	100 to 240@50 to 60	Stripped & Tinned Pigtail Wires	UL,CUL	3.2 x 1.2 x 1.3	\$5.95	\$5.49
2227735	Arndt	EDF0500150A1BA	5	1.5	7.5	100-120@50-60	0.3mm x 3.5mm Cylindrical Female Center Positive	UL,CUL	8 x 1.6 x 1.3	\$7.95	\$6.95
2227786	Arndt	XA1005-2U	5	2	10	100 to 240@50 to 60	Multiple Connectors Included	UL,CUL,CE,CCC	2.7 x 1.7 x 1	\$4.95	\$4.49
2230361	Arndt	ADS6818-1505-WDB0530	5	3	15	100 to 240@50 to 60	2.5mm x 5.5mm Cylindrical Female Center Positive	UL,CUL	3.2 x 2.1 x 1.3	\$8.95	\$7.95
2234505	Arndt	BI20-050300-ADU	5	3	15	100 to 240@50 to 60	2.5mm x 5.5mm Right Angle Cylindrical Female Center Positive	UL,CUL	2.8 x 1.8 x 1.3	\$7.95	\$6.95
2225529	MEAN WELL	GST18U05-P1J	5	3	15	85 to 264@47 to 63	2.1mm x 5.5mm Cylindrical Female Center Positive	BSMI/CB/CUL/FCC/UL	3.1 x 2.1 x 1.3	\$11.50	\$9.39
2270919	Arndt	SA115B-05	5	3	15	100 to 240@50 to 60	2.1mm x 5.5mm Cylindrical Female Center Positive	UL,CUL,FCC	2.9 x 1.9 x 1.2	\$8.95	\$7.95
2270903	Arndt	UP0251P-05PA	5	3.5	17.5	100 to 240@50 to 60	2.1mm x 5.5mm Cylindrical Female Center Positive	UL,CUL,CE,FCC	2.9 x 2.2 x 1.2	\$7.95	\$6.95
2270911	Arndt	PA1030-050DUB	5	3.5	17.5	100 to 240@50 to 60	2.1mm x 5.5mm Cylindrical Female Center Positive	UL,CUL,FCC	3 x 1.9 x 1.3	\$8.95	\$7.95
379623	MEAN WELL	GS25U05-P1J	5	4	20	100 to 240@50 to 60	2.1mm x 5.5mm Cylindrical Female Center Positive	BSMI/CB/CUL/FCC/UL	1.4 x 2.1 x 3.1	\$11.95	\$10.95
2225650	MEAN WELL	GST25U05-P1J	5	4	20	85 to 264@47 to 63	2.1mm x 5.5mm Cylindrical Female Center Positive	BSMI/CB/CUL/FCC/UL	3.1 x 2.1 x 1.3	\$11.70	\$9.59
2225721	MEAN WELL	GST36U05-P1J	5	4.3	21.5	85 to 264@47 to 63	2.1mm x 5.5mm Cylindrical Female Center Positive	BSMI/CB/CUL/FCC/UL	3.1 x 2.1 x 1.3	\$13.30	\$10.89
2225596	MEAN WELL	GST18U07-P1J	7.5	2	15	85 to 264@47 to 63	2.1mm x 5.5mm Cylindrical Female Center Positive	BSMI/CB/CUL/FCC/UL	3.1 x 2.1 x 1.3	\$11.50	\$9.39
2225668	MEAN WELL	GST25U07-P1J	7.5	2.93	22	85 to 264@47 to 63	2.1mm x 5.5mm Cylindrical Female Center Positive	BSMI/CB/CUL/FCC/UL	3.1 x 2.1 x 1.3	\$11.70	\$9.59
1952847	MEAN WELL	GS18U09-P1J	9	2	18	90 to 264@50 to 60	2.1mm x 5.5mm Cylindrical Female Center Positive	BSMI/CB/CUL/FCC/UL/CE	1.3 x 2.1 x 3.1	\$11.75	\$10.49
2225609	MEAN WELL	GST18U09-P1J	9	2	18	85 to 264@47 to 63	2.1mm x 5.5mm Cylindrical Female Center Positive	BSMI/CB/CUL/FCC/UL	3.1 x 2.1 x 1.3	\$11.50	\$9.39
2225676	MEAN WELL	GST25U09-P1J	9	2.55	23	85 to 264@47 to 63	2.1mm x 5.5mm Cylindrical Female Center Positive	BSMI/CB/CUL/FCC/UL	3.1 x 2.1 x 1.3	\$11.70	\$9.59
380140	MEAN WELL	GS25U09-P1J	9	2.77	25	90 to 264@47 to 63	2.1mm x 5.5mm Cylindrical Female Center Positive	BSMI/CB/CUL/FCC/UL	1.3 x 2.1 x 3.1	\$13.95	\$11.49
2225730	MEAN WELL	GST36U09-P1J	9	3.11	28	85 to 264@47 to 63	2.1mm x 5.5mm Cylindrical Female Center Positive	BSMI/CB/CUL/FCC/UL	3.1 x 2.1 x 1.3	\$13.30	\$10.89
2121578	Jameco Reliapro	ST-12500	12	0.5	6	100 to 240@50 to 60	Screw Terminals	UL/CUL/CEC	1.8 x 2.1 x 3.8	\$10.95	\$9.95
2236463	Arndt	JOD-S-120050A	12	0.5	6	100 to 240@50 to 60	2.1mm x 5.5mm Cylindrical Female Center Positive	UL,CUL	2.3 x 1.5 x 1.3	\$4.95	\$4.49
1940774	MEAN WELL	GS12U12-P1I	12	1	12	90 to 264@47 to 63	2.1mm x 5.5mm Cylindrical Female Center Positive	BSMI/CB/CUL/FCC/UL	1.2 x 1.9 x 2.6	\$9.00	\$7.75
2121586	Jameco Reliapro	ST-121A	12	1	12	100 to 240@50 to 60	Screw Terminals	UL/CUL/CE	1.8 x 2.1 x 3.8	\$13.95	\$12.49
2230264	Arndt	EN-US12V1000	12	1	12	100 to 240@50 to 60	2.1mm x 5.5mm Cylindrical Female Center Positive	CE,FCC	3.3 x 1.7 x 1.2	\$7.95	\$6.95
2231662	Jameco Reliapro	GQ12-120100-AU	12	1	12	100 to 240@50 to 60	2.5mm x 5.5mm Cylindrical Female Center Positive	UL,CUL	2.7 x 1.6 x 1.1	\$10.95	\$9.95
2229765	Arndt	DSY12-120100W-1	12	1	12	100 to 240@50 to 60	2.1mm x 5.5mm Cylindrical Female Center Positive	UL,CUL	2.8 x 1.6 x 1.1	\$8.95	\$7.95
2270999	Arndt	DYS12-120100W	12	1	12	120@60	2.1mm x 5.5mm Cylindrical Female Center Positive	CE	-	\$6.95	\$6.25
1952855	MEAN WELL	GS18U12-P1J	12	1.5	18	90 to 264@47 to 63	2.1mm x 5.5mm Cylindrical Female Center Positive	BSMI/CB/CUL/FCC/UL	1.5 x 2.1 x 3.1	\$12.95	\$11.95
2209262	Asian Power Devices	WA-18G12U.	12	1.5	18	100 to 240@50 to 60	2.1mm x 5.5mm Cylindrical Female Center Positive	UL/CUL/CEC	3 x 1.9 x 1.3	\$9.95	\$8.95
2225537	MEAN WELL	GST18U12-P1J	12	1.5	18	85 to 264@47 to 63	2.1mm x 5.5mm Cylindrical Female Center Positive	BSMI/CB/CUL/FCC/UL	3.1 x 2.1 x 1.3	\$11.50	\$9.39
2231671	Jameco Reliapro	GQ15-120150-AU	12	1.5	18	100 to 240@50 to 60	2.5mm x 5.5mm Cylindrical Female Center Positive	UL,CUL	2.7 x 1.6 x 1.1	\$12.95	\$11.49
2082134	Jameco Reliapro	ST-122A	12	2	24	100 to 240@50 to 60	Screw Terminals Cylindrical Female Center Positive	UL/CUL/CEC	1.8 x 2.1 x 3.8	\$16.95	\$15.49
2234054	Arndt	YSU20120	12	2	24	100 to 240@50 to 60	2.1mm x 5.5mm Cylindrical Female Center Positive	UL,CUL	2.7 x 1.7 x 1.2	\$9.95	\$8.95
380156	MEAN WELL	GS25U12-P1J	12	2.08	25	90 to 264@47 to 63	2.1mm x 5.5mm Cylindrical Female Center Positive	BSMI/CB/CUL/FCC/UL	1.5 x 2.1 x 3.1	\$13.95	\$12.95
2225553	MEAN WELL	GST25U12-P1J	12	2.08	25	85 to 264@47 to 63	2.1mm x 5.5mm Cylindrical Female Center Positive	BSMI/CB/CUL/FCC/UL	3.1 x 2.1 x 1.3	\$11.70	\$9.59
2173116	Jameco Reliapro	KSAS0361200300HU-VI	12	3	36	100 to 240@50 to 60	2.1mm x 5.5mm Cylindrical Female Center Positive	UL,CUL,CEC	3.9 x 1.7 x 1.2	\$13.49	\$11.95
2230643	Jameco Reliapro	ST-123A	12	3	36	100 to 240@50 to 60	Screw Terminals	UL	3.8 x 2.1 x 1.6	\$17.95	\$16.49
2225570	MEAN WELL	GST36U12-P1J	12	3	36	85 to 264@47 to 63	2.1mm x 5.5mm Cylindrical Female Center Positive	BSMI/CB/CUL/FCC/UL	3.1 x 2.1 x 1.3	\$13.30	\$10.89
2239189	Jameco Reliapro	KSAS0361200300HU-2.5	12	3	36	100 to 240@50 to 60	2.5mm x 5.5mm Cylindrical Female Center Positive	UL	3.9 x 1.7 x 1.2	\$13.95	\$12.95
1952871	MEAN WELL	GS18U15-P1J	15	1.2	18	100 to 240@50 to 60	2.1mm x 5.5mm Cylindrical Female Center Positive	BSMI/CB/CUL/FCC/UL	1.4 x 2.1 x 3.1	\$13.95	\$12.49
2225617	MEAN WELL	GST18U15-P1J	15	1.2	18	85 to 264@47 to 63	2.1mm x 5.5mm Cylindrical Female Center Positive	BSMI/CB/CUL/FCC/UL	3.1 x 2.1 x 1.3	\$11.50	\$9.39
2225684	MEAN WELL	GST25U15-P1J	15	1.66	25	85 to 264@47 to 63	2.1mm x 5.5mm Cylindrical Female Center Positive	BSMI/CB/CUL/FCC/UL	3.1 x 2.1 x 1.3	\$11.70	\$9.59
380173	MEAN WELL	GS25U15-P1J	15	1.67	25	90 to 264@47 to 63	2.1mm x 5.5mm Cylindrical Female Center Positive	BSMI/CB/CUL/FCC/UL	1.3 x 2.1 x 3.1	\$11.95	\$9.95
2225625	MEAN WELL	GST18U18-P1J	18	1	18	85 to 264@47 to 63	2.1mm x 5.5mm Cylindrical Female Center Positive	BSMI/CB/CUL/FCC/UL	3.1 x 2.1 x 1.3	\$11.50	\$9.39
380191	MEAN WELL	GS25U18-P1J	18	1.38	25	100 to 240@50 to 60	2.1mm x 5.5mm Cylindrical Female Center Positive	BSMI/CB/CUL/FCC/UL	1.5 x 1.2 x 3.1	\$13.95	\$12.95
2225692	MEAN WELL	GST25U18-P1J	18	1.38	25	85 to 264@47 to 63	2.1mm x 5.5mm Cylindrical Female Center Positive	BSMI/CB/CUL/FCC/UL	3.1 x 2.1 x 1.3	\$11.70	\$9.59
1952898	MEAN WELL	GS18U24-P1J	24	0.75	18	90 to 264@47 to 63	2.1mm x 5.5mm Cylindrical Female Center Positive	BSMI/CB/CUL/FCC/UL	1.5 x 2.1 x 3.1	\$12.95	\$11.95
2225545	MEAN WELL	GST18U24-P1J	24	0.75	18	85 to 264@47 to 63	2.1mm x 5.5mm Cylindrical Female Center Positive	BSMI/CB/CUL/FCC/UL	3.1 x 2.1 x 1.3	\$11.50	\$9.39
2121594	Jameco Reliapro	ST-241A	24	1	24	100 to 240@50 to 60	Screw Terminals	UL/CUL/CEC	1.8 x 2.1 x 3.8	\$15.95	\$14.49

Jameco			Primary Output	Output	Maximum						
Part#	Manufacturer	Manufacturer Part #	Voltage (VDC)	Current (A)	Power (W)	Input VAC @ Hz	Output Connector	Agency Approvals	Case Size (in)	Price 1	Price 10+
1953671	Jameco Reliapro	MPC-2400107	24	1	24	120 to 240@50 to 60	2.5mm x 5.5mm Cylindrical Female Center Positive	UL/CSA	2.2 x 2.7 x 3.4	\$14.95	\$13.49
2229888	Jameco Reliapro	MPC2400107	24	1	24	100 to 240@50 to 60	2.1mm x 5.5mm Cylindrical Female Center Positive	UL,CUL,CEC	3.4 x 2.7 x 2.2	\$12.95	\$11.95
380202	MEAN WELL	GS25U24-P1J	24	1.04	25	100 to 240@50 to 60	2.1mm x 5.5mm Cylindrical Female Center Positive	BSMI/CB/CUL/FCC/UL	1.3 x 2.1 x 3.1	\$13.95	\$12.95
2225561	MEAN WELL	GST25U24-P1J	24	1.04	25	85 to 264@47 to 63	2.1mm x 5.5mm Cylindrical Female Center Positive	BSMI/CB/CUL/FCC/UL	3.1 x 2.1 x 1.3	\$11.70	\$9.59
2225588	MEAN WELL	GST36U24-P1J	24	1.5	36	85 to 264@47 to 63	2.1mm x 5.5mm Cylindrical Female Center Positive	BSMI/CB/CUL/FCC/UL	3.1 x 2.1 x 1.3	\$13.30	\$10.89
2167613	Jameco Reliapro	ST-242A	24	2	48	100 to 240@50 to 60	Screw Terminals	-	3.8 x 2.1 x 1.6	\$15.95	\$14.95
2224500	MEAN WELL	GSC18E-700	26	0.7	18.2	90 to 277@47 to 63	2.1mm x 5.5mm Cylindrical Female Center Positive	ENEC/DEKRA/CB/CE	3.1 x 2.1 x 1.3	\$14.00	\$11.39
2225633	MEAN WELL	GST18U28-P1J	28	0.64	18	85 to 264@47 to 63	2.1mm x 5.5mm Cylindrical Female Center Positive	BSMI/CB/CUL/FCC/UL	3.1 x 2.1 x 1.3	\$11.50	\$9.39
380220	MEAN WELL	GS25U28-P1J	28	0.89	25	100 to 240@50 to 60	2.1mm x 5.5mm Cylindrical Female Center Positive	BSMI/CB/CUL/FCC/UL	1.3 x 2.1 x 3.1	\$12.95	\$11.95
2225705	MEAN WELL	GST25U28-P1J	28	0.89	25	85 to 264@47 to 63	2.1mm x 5.5mm Cylindrical Female Center Positive	BSMI/CB/CUL/FCC/UL	3.1 x 2.1 x 1.3	\$11.70	\$9.59
2225641	MEAN WELL	GST18U48-P1J	48	0.375	18	85 to 264@47 to 63	2.1mm x 5.5mm Cylindrical Female Center Positive	BSMI/CB/CUL/FCC/UL	3.1 x 2.1 x 1.3	\$11.50	\$9.39
2225713	MEAN WELL	GST25U48-P1J	48	0.52	25	85 to 264@47 to 63	2.1mm x 5.5mm Cylindrical Female Center Positive	BSMI/CB/CUL/FCC/UL	3.1 x 2.1 x 1.3	\$11.70	\$9.59
2225748	MEAN WELL	GST36U48-P1J	48	0.75	36	90 to 264@47 to 63	2.1mm x 5.5mm Cylindrical Female Center Positive	BSMI/CB/CUL/FCC/UL	3.1 x 2.1 x 1.3	\$13.30	\$10.89