



1-800-831-4242 - www.Jameco.com

AC TUBEAXIAL FANS 115 - 220 VOLTS

Jameco SKU	Mfr Name	Mfr P/N	Voltage Rating AC	Length (mm)	Width (mm)	Height (mm)	Air Flow (CFM)	Bearing	Current (mA)	Power (Watts)	Agency Approvals	Noise (dBA)	Connection (Leads)	Price
213867	Fulltech Electric	UF-60D11HBWH-R	115	60	60	30	10.2	Ball	35	4	UL/CUL/VDE/CE	28	12	17.95
2290351	Common Wealth	FP-108AX(S-2)120BW	115	80	80	25	18	Ball	100	10	UL/CSA	29	12"	13.95
2231734	ADDA Corporation	AA8251HB-AT	115	80	80	25	21	Ball	70	5.8	UL/CUL/TUV/CE	27	Terminals	12.95
146078	Common Wealth	FP-108AX(S-1)120BW	115	80	80	25	23	Ball	140	14	UL/CE	29	12"	15.95
2230660	Thermocool Fans	G8025HAS	115	80	80	25	23	Sleeve	160	12	UL/CUL/TUV/CE	32	12"	10.95
2290343	Common Wealth	FP-108AX(S-1)120SW	115	80	80	25	23	Sleeve	170	14	UL/CSA	33	12"	13.95
2290359	Common Wealth	FP-108AX(S-1)120SW-14	115	80	80	25	23	Sleeve	170	14	UL/CSA	33	14" (14 AWG)	14.95
300557	Fulltech Electric	UF80B11SWH-R	115	80	80	25	24	Sleeve	140	14	UL/CUL/TUV/CE	35	12"	13.95
2133819	ADDA Corporation	AA8381MS-AT	115	80	80	38	24	Sleeve	75	8.6	UL/CUL/TUV/CE	26.2	Terminals	10.95
2228279	Mechatronics	80A12BWL	115	80	80	38	25	Ball	100	9	UL/CSA/CE	32	11"	11.95
300600	Fulltech Electric	UF80A11BWH-R	115	80	80	38	29	Ball	120	12	UL/CUL/TUV/CE	36	12"	15.95
2290375	Common Wealth	FP-108A(S-1)120BT*	115	80	80	38	30	Ball	120	12	UL/CSA/CE	35	72" (with AC power plug)	16.95
300389	Fulltech Electric	UF80A11BTH-R	115	80	80	38	30	Ball	120	12	UL/CUL/TUV/CE	36	Terminals	15.95
2234169	NMB Technologies	3610PS-12T-B20	115	92	92	25	28	Ball	90	11	CSA	35	Terminals	6.49
2230678	Thermocool Fans	G9225HAS	115	92	92	25	34	Sleeve	140	13	UL/CUL/TUV	40	Terminals	10.95
303467	Sunon	SF11592A-1092HBL-GN	115	92	92	25	37	Ball	110	12	UL/CSA/TUV/CE	40	12"	12.95
2271255	Common Wealth	FP-108JC(S-1)120BW	115	92	92	38	45	Ball	150	16	UL/CSA/CE	37	12" (with connector)	11.95
2135275	Common Wealth	FP-108JC(S-1)120SW	115	92	92	38	45	Sleeve	150	10	UL/CSA/CE	37	12"	13.95
2131830	ADDA Corporation	AA1251MB-AW	115	120	120	25	69	Ball	240	24.2	UL/CSA/TUV/CE	38.7	Terminals	13.55
1810048	Sunon	SP101AT1122HBL.GN	115	120	120	25	78	Ball	210	19	UL/CUL/TUV/CE	46	12"	16.95
124063	Sunon	SP101AT1122HBT-R	115	120	120	25	78	Ball	180	18	CSA/TUV/CE	46	Terminals	16.95
2290383	Common Wealth	FP-108-1(S-3)120BT	115	120	120	38	54	Ball	110	8	UL/CSA/CE	34	Terminals	13.95
2230379	EBM Papst	4800N	115	120	120	38	57.1	Sleeve	78	9	UL/CSA/CE	32	Terminals	11.95
303361	Fulltech Electric	UF12A11BTL1-R	115	120	120	38	64	Ball	200	14	UL/CSA/TUV/CE	37	Terminals	14.95
2290391	Common Wealth	FP-108-1(S-2)120BT	115	120	120	38	71	Ball	120	10	UL/CSA/CE	39	Terminals	14.95
2205405	ADDA Corporation	AA1281MB-AT(CF)	115	120	120	38	80	Ball	210	24.2	UL/CUL/TUV	41	Terminals	11.95
2230694	Thermocool Fans	G12038MAB	115	120	120	38	85	Ball	0.22	19	UL/CUL/TUV	44	Terminals	14.95
2231718	Sunon	SP102A-1123MBL.GN	115	120	120	38	88	Ball	160	15	UL/CUL/TUV/CE	40	12"	12.49
2100427	ADDA Corporation	AA1281HS-AW	115	120	120	38	91	Sleeve	250	19.8	UL/CUL/TUV/CE	42.6	12"	8.95
2134168	ADDA Corporation	AA1281HB-AWR2T	115	120	120	38	95	Hypro	190	16.5	UL/CUL/TUV/CE	40.1	4-10" (SMART)	9.95
2230686	Thermocool Fans	G12038HAS	115	120	120	38	95	Sleeve	0.34	25	UL/CUL/TUV	122	Terminals	9.95
16935	Common Wealth	FP108-1(S1)120BT*	115	120	120	38	105	Ball	240	18	UL/CSA	47	Terminals	13.95
2125931	Common Wealth	FP-108-1(S-1)120BT	115	120	120	38	105	Ball	250	19	UL/CSA/TUV/CE	45	Terminals	13.95
2290399	Common Wealth	FP-108-1(S-1)120BW	115	120	120	38	105	Ball	180	17	UL/CSA/CE	47	12"	13.95
106586	Common Wealth	FP-108-1(S-1)120ST	115	120	120	38	105	Sleeve	180	12	UL/CSA/CE	47	Terminals	12.95
1707163	Sunon	SP101A-1123HBL-GN	115	120	120	38	107	Ball	180	18	UL/CSA/TUV	50	12"	15.95
2292407	Sunon	SP100A/1123XST.GN	115	120	120	38	115	Sleeve	240	20	UL/CSA/TUV/CE	49	Terminals	12.95
2231726	Sunon	SP100A-1123XBL.GN	115	120	120	38	117	Ball	240	20	UL/CUL/TUV/CE	50	12"	13.95
102884	Sunon	SP100A-1123XBT.GN	115	120	120	38	117	Ball	240	22	UL/CUL/TUV/CE	50	Terminals	14.95
2290479	Common Wealth	EP-108-1(ULTRA)120TB	115	120	120	38	120	Ball	240	18	UL/CSA/CE	47	Terminals	15.95
2230141	Fulltech Electric	UF13A11BTH	115	127	127	38	120	Ball	160	12	UL/CUL/CE	50	Terminals	16.95
2290367	Common Wealth	FP-108-7(S-1)120BT	115	127	127	38	140	Ball	240	23	UL/CSA/TUV/CE	47	Terminals	19.95
2290295	Common Wealth	FP-108CX(120BW)	115	150	150	38	140	Ball	260	20	UL/CUL	31	8"	29.95
2290319	Common Wealth	FP-108EXM(120BW)	115	172	150	38	230	Ball	400	28	UL/CUL/TUV/CE	49	16"	29.95
2271263	Common Wealth	FP-108EX(S-2)120BW	115	172	150	51	170	Ball	370	30	UL/CSA/CE	33	12"	19.95
212582	Fulltech Electric	UF15PC11BWH-R	115	172	150	51	226	Ball	250	30	UL/CUL/TUV/CE	58	12" wires	29.95
189684	Fulltech Electric	UF15PC11BTH	115	172	150	51	226	Ball	250	30	UL/CUL/TUV/CE	58	Terminals	32.95
2230723	Thermocool Fans	G17050HASB	115	172	172	51	198	Ball	400	38	UL/CUL/TUV/CE/CCC	59	Terminals	27.95



1-800-831-4242 - www.Jameco.com

AC TUBEAXIAL FANS 115 - 220 VOLTS

Jameco SKU	Mfr Name	Mfr P/N	Voltage Rating AC	Length (mm)	Width (mm)	Height (mm)	Air Flow (CFM)	Bearing	Current (mA)	Power (Watts)	Agency Approvals	Noise (dBA)	Connection (Leads)	Price
2230117	ADDA Corporation	AA8252HB-AT	220	80	80	25	17	Ball	60	16.1	UL/CUL/CE/TUV	27.8	Terminals	12.95
2099471	ADDA Corporation	AA8382MX-AT	220	80	80	38	24	Hypro	50	6.8	UL/CUL/TUV	25.3	Terminals	7.95
2233457	ADDA Corporation	AA8382HS-AT	220	80	80	38	24	Sleeve	70	8.8	UL/CUL/TUV/CE	25.3	Terminals	7.95
355630	Fulltech Electric	UF-80A23-BTH-R	220	80	80	38	30	Ball	60	12	UL/CSA/VDE/CE	36	Terminals	12.95
100918	Sunon	SF23080A/2083HSL.GN	220	80	80	38	30	Sleeve	60	18	UL/CSA/CE/TUV	35	12"	15.95
2210837	Comair Rotron	SU3G1	220	80	80	38	32	Sleeve	70	10	UL/CSA	39	12"	4.95
2234177	NMB Technologies	3115FS-23T-B10-A00	220	80	80	38	33	Ball	87	6.5	UL/CSA	36	Terminals	8.95
2234636	NMB Technologies	3610PS-23T-B20	220	92	92	25	28	Ball	50	12	UL/CSA	35	Terminals	11.95
2231566	ADDA Corporation	AA1252MB-AT	220	120	120	25	65	Ball	100	21.6	UL/CUL/TUV/CE	38	Terminals	14.95
2133801	ADDA Corporation	AA1282UB-AT	220	120	120	38	96	Ball	60	8	UL/CUL/TUV/CE	39.2	Terminals	13.95
2290423	Common Wealth	FP-108-1(S-1)220BW	220	120	120	38	105	Ball	110	17	UL/CSA/TUV/CE	47	38"	14.95
2290415	Common Wealth	FP-108-1(S-1)220BT	220	120	120	38	105	Ball	110	17	UL/CSA/CE	47	Terminals	14.95
2290407	Common Wealth	FP-108-1(S-1)220ST	220	120	120	38	105	Sleeve	110	17	UL/CSA/CE	47	Terminals	13.95
2271015	ADDA Corporation	AA1282US-AT(CF)	220	120	120	38	107	Sleeve	170	37.4	UL/CUL/TUV/CE	46	Terminals	12.95
2293511	Thermactive Electronics	RAH1238B1	220	120	120	38	111	Ball	20	28	UL/CSA/TUV/CE	44	12"	12.95
303459	Sunon	DP200A-2123XBL-ROHS	220	120	120	38	117	Ball	120	22	UL/CSA/TUV/CE	50	12"	15.95
102892	Sunon	DP200A-2123XBT-R	220	120	120	38	117	Ball	140	22	UL/CSA/TUV	50	Terminals	17.95
2290311	Common Wealth	FP-108EXM(220BW)	220	172	150	38	230	Ball	280	38	UL/CUL/TUV/CE	49	16"	29.95
2265879	Orion Fans	OA172SAP-22-1TB	220	172	150	51	235	Ball	230	50	UL/CUL/TUV/CE	52	Terminals	24.95
2293503	Thermactive Electronics	RAH1751B1	220	172	150	51	250	Ball	200	46	UL/CUL/TUV/CE/VDE	56	12"	29.95
2292615	Thermactive Electronics	RAH1751B1-C-T	220	172	150	51	250	Ball	200	46	UL/CUL/TUV/CE	56	Terminals	29.95
2258419	Fulltech Electric	UF-12A1223BWH	115/220	120	120	38	92	Ball	260	30	UL/CUL/TUV/CE	42	4-12" (TACK + PWM + FG)	15.95