



[Click Here to Request a Large Quantity Quote](#)

[AC-to-DC Regulated Switching Wall Adapters](#)

Jameco Part #	Manufacturer	Manufacturer Part #	Primary Output Voltage (VDC)	Output Current (A)	Output Connector Diameters	Input Voltage (VAC)	Input Frequency	Output Connector Type	Polarity	Size (L" x W" x H")	Agency Approvals	Price 1
2230408	Phihong	PSM04A-050-R	5	0.75	2.1mm x 5.5mm	100 to 240	50 to 60	Cylindrical Female	Center Positive	2.7 x 1.8 x 0.95	UL/CUL	\$4.95
2227735	Arndt	EDF0500150A1BA	5	1.5	1.3mm x 3.5mm	100 to 120	50 to 60	Cylindrical Female	Center Positive	2.8 x 1.6 x 1.3	UL/CUL	\$7.95
2235381	Seed Studios	313990002RA	5	2.1	USB Type A	100 to 240	50 to 60	USB Port	N/A	2.3 x 1.6 x 1.3	UL/CUL/FCC	\$5.49
2289167	Globtek	WR92A2400CCP	5	2.4	2.1mm x 5.5mm	100 to 250	47 to 63	Cylindrical Female	Center Positive	3.3 x 2.1 x 1.6	UL/CSA	\$7.95
2270919	Arndt	SA115B-05	5	3	2.1mm x 5.5mm	100 to 240	50 to 60	Cylindrical Female	Center Positive	2.9 x 1.9 x 1.2	UL/CUL/FCC	\$6.95
2225529	MEAN WELL	GST18U05-P1J	5	3	2.1mm x 5.5mm	85 to 264	47 to 63	Cylindrical Female	Center Positive	3.1 x 2.1 x 1.3	UL/CUL/CB/FCC/EAC	\$12.20
2230361	Arndt	ADS6818-1505-WDB0530	5	3	2.5mm x 5.5mm	100 to 240	50 to 60	Cylindrical Female	Center Positive	3.2 x 2.1 x 1.3	UL/CUL	\$6.95
2234505	Arndt	BI20-050300-ADU	5	3	2.5mm x 5.5mm right angle	100 to 240	50 to 60	Cylindrical Female	Center Positive	2.8 x 1.8 x 1.3	UL/CUL	\$6.495
2270903	Arndt	UP0251P-05PA	5	3.5	2.1mm x 5.5mm	100 to 240	50 to 60	Cylindrical Female	Center Positive	2.9 x 2.2 x 1.12	UL/CUL/CE/FCC	\$6.49
2270911	Arndt	PA1030-050DUB	5	3.5	2.1mm x 5.5mm	100 to 240	50 to 60	Cylindrical Female	Center Positive	3 x 1.9 x 1.3	UL/CUL/FCC	\$6.95
2225650	MEAN WELL	GST25U05-P1J	5	4	2.1mm x 5.5mm	85 to 264	47 to 63	Cylindrical Female	Center Positive	3.1 x 2.1 x 1.3	UL/CUL/CB/FCC/EAC	\$12.40
2302511	Phihong	PLA02A-090R	9	0.22	2.5mm x 5.5mm	100 to 240	50 to 60	Cylindrical Female	Center Positive	1.98 x 0.98 x 1.38	UL/CUL/CEC	\$4.95
1940686	MEAN WELL	GS06U-2P1J	9	0.66	2.1mm x 5.5mm	90 to 264	47 to 63	Cylindrical Female	Center Positive	2.6 x 1.3 x 1.7	UL/CUL/FCC/EAC	\$9.90
2225609	MEAN WELL	GST18U09-P1J	9	2	2.1mm x 5.5mm	85 to 264	47 to 63	Cylindrical Female	Center Positive	3.1 x 2.1 x 1.3	UL/CUL/CB/FCC/EAC	\$12.20

Jameco Part #	Manufacturer	Manufacturer Part #	Primary Output Voltage (VDC)	Output Current (A)	Output Connector Diameters	Input Voltage (VAC)	Input Frequency	Output Connector Type	Polarity	Size (L" x W" x H")	Agency Approvals	Price 1
1952847	MEAN WELL	GS18U09-P1J	9	2	2.1mm x 5.5mm	90 to 264	47 to 63	Cylindrical Female	Center Positive	3.1 x 2.1 x 1.3	UL/CUL/TUV/CB/FCC	\$9.95
380140	MEAN WELL	GS25U09-P1J	9	2.77	2.1mm x 5.5mm	90 to 264	47 to 63	Cylindrical Female	Center Positive	3.1 x 2.1 x 1.3	UL/CUL/TUV/CB/FCC	\$11.95
1940694	MEAN WELL	GS06U-3P1J	12	0.5	2.1mm x 5.5mm	90 to 264	47 to 63	Cylindrical Female	Center Positive	2.6 x 1.3 x 1.7	UL/CUL/FCC/EAC	\$9.90
2121578	Jameco Reliapro	ST-12500	12	0.5	Screw Terminals	100 to 240	50 to 60	Screw Terminals	N/A	2 x 3.8 x 1.5	UL/CUL/CEC/FCC	\$10.95
2270999	Arndt	DYS12-120100W	12	1	2.1mm x 5.5mm	100 to 240	50 to 60	Cylindrical Female	Center Positive	2.8 x 2 x 1.5	CE	\$3.95
2231662	Jameco Reliapro	GQ12-120100-AU	12	1	2.5mm x 5.5mm	100 to 240	50 to 60	Cylindrical Female	Center Positive	2.7 x 1.6 x 1.1	UL/CUL	\$8.95
2121586	Jameco Reliapro	ST-121A	12	1	Screw Terminals	100 to 240	50 to 60	Screw Terminals	N/A	3.75 x 2 x 1.5	UL/CUL/CE	\$13.95
2225537	MEAN WELL	GST18U12-P1J	12	1.5	2.1mm x 5.5mm	85 to 264	47 to 63	Cylindrical Female	Center Positive	3.1 x 2.1 x 1.3	UL/CUL/CB/FCC/EAC	\$12.20
2231671	Jameco Reliapro	GQ15-120150-AU	12	1.5	2.5mm x 5.5mm	100 to 240	50 to 60	Cylindrical Female	Center Positive	2.7 x 1.6 x 1.1	UL/CUL	\$9.95
2234054	Arndt	YSU20120	12	2	2.1mm x 5.5mm	90 to 264	47 to 63	Cylindrical Female	Center Positive	2.7 x 1.7 x 1.2	UL/CUL	\$8.95
2082134	Jameco Reliapro	ST-122A	12	2	Screw Terminals	100 to 240	50 to 60	Screw Terminals	N/A	3.8 x 2.1 x 1.6	UL/CUL/CEC	\$13.95
2225553	MEAN WELL	GST25U12-P1J	12	2.08	2.1mm x 5.5mm	85 to 264	47 to 63	Cylindrical Female	Center Positive	3.1 x 2.1 x 1.3	UL/CUL/CB/FCC/EAC	\$12.40
380156	MEAN WELL	GS25U12-P1J	12	2.08	2.1mm x 5.5mm	90 to 264	47 to 63	Cylindrical Female	Center Positive	3.1 x 2.1 x 1.3	UL/CUL/TUV/CB/FCC	\$11.95
2303735	Jameco Reliapro	PS-2.1-12-25WTM	12	2.5	2.1mm x 5.5mm	100 to 240	50 to 60	Cylindrical Female	Center Positive	3.1 x 1.3 x 2.0	UL/CUL/FCC	\$10.95
2173116	Jameco Reliapro	KSAS0361200300HU-VI	12	3	2.1mm x 5.5mm	100 to 240	50 to 60	Cylindrical Female	Center Positive	3.9 x 1.7 x 1.2	UL/CUL/CECV	\$11.95
2225570	MEAN WELL	GST36U12-P1J	12	3	2.1mm x 5.5mm	85 to 264	47 to 63	Cylindrical Female	Center Positive	3.1 x 2.1 x 1.3	UL/CUL/CB/FCC/EAC	\$14.10
2239189	Jameco Reliapro	KSAS0361200300HU-2.5	12	3	2.5mm x 5.5mm	100 to 240	50 to 60	Cylindrical Female	Center Positive	3.9 x 1.7 x 1.2	UL/CUL/CEC	\$10.49

Jameco Part #	Manufacturer	Manufacturer Part #	Primary Output Voltage (VDC)	Output Current (A)	Output Connector Diameters	Input Voltage (VAC)	Input Frequency	Output Connector Type	Polarity	Size (L" x W" x H")	Agency Approvals	Price 1
2230643	Jameco Reliapro	ST-123A	12	3	Screw Terminals	100 to 240	50 to 60	Screw Terminals	N/A	3.8 x 2.1 x 1.6	UL	\$14.95
2225617	MEAN WELL	GST18U15-P1J	15	1.2	2.1mm x 5.5mm	85 to 264	47 to 63	Cylindrical Female	Center Positive	3.1 x 2.1 x 1.3	UL/CUL/CB/FCC/EAC	\$12.20
2225684	MEAN WELL	GST25U15-P1J	15	1.66	2.1mm x 5.5mm	85 to 264	47 to 63	Cylindrical Female	Center Positive	3.1 x 2.1 x 1.3	UL/CUL/CB/FCC/EAC	\$12.40
380173	MEAN WELL	GS25U15-P1J	15	1.67	2.1mm x 5.5mm	90 to 264	47 to 63	Cylindrical Female	Center Positive	3.1 x 2.1 x 1.3	UL/CUL/TUV/CB/FCC	\$10.49
2225545	MEAN WELL	GST18U24-P1J	24	0.75	2.1mm x 5.5mm	85 to 264	47 to 63	Cylindrical Female	Center Positive	3.1 x 2.1 x 1.3	UL/CUL/CB/FCC/EAC	\$12.20
1952898	MEAN WELL	GS18U24-P1J	24	0.75	2.1mm x 5.5mm	90 to 264	47 to 63	Cylindrical Female	Center Positive	3.1 x 2.1 x 1.3	UL/CUL/TUV/CB/FCC	\$14.95
2229888	Jameco Reliapro	CZH024240100USWM	24	1	2.1mm x 5.5mm	100 to 240	50 to 60	Cylindrical Female	Center Positive	3.4 x 2.7 x 2.2	UL/CUL/CEC	\$12.95
2121594	Jameco Reliapro	ST-241A	24	1	Screw Terminals	100 to 240	50 to 60	Screw Terminals	N/A	3.8 x 2 x 1.5	UL/CUL/CEC	\$13.95
2225561	MEAN WELL	GST25U24-P1J	24	1.04	2.1mm x 5.5mm	85 to 264	47 to 63	Cylindrical Female	Center Positive	3.1 x 2.1 x 1.3	UL/CUL/CB/FCC/EAC	\$12.40
380202	MEAN WELL	GS25U24-P1J	24	1.04	2.1mm x 5.5mm	90 to 264	47 to 63	Cylindrical Female	Center Positive	3.1 x 2.1 x 1.3	UL/CUL/TUV/CB/FCC	\$16.95
2225588	MEAN WELL	GST36U24-P1J	24	1.5	2.1mm x 5.5mm	85 to 264	47 to 63	Cylindrical Female	Center Positive	3.1 x 2.1 x 1.3	UL/CUL/CB/FCC/EAC	\$14.10
2167613	Jameco Reliapro	ST-242A	24	2	Screw Terminals	100 to 240	50 to 60	Screw Terminals	N/A	3.8 x 2.1 x 1.6	UL/CUL/CUS/FCC	\$15.95
2225633	MEAN WELL	GST18U28-P1J	28	0.64	2.1mm x 5.5mm	85 to 264	47 to 63	Cylindrical Female	Center Positive	3.1 x 2.1 x 1.3	UL/CUL/CB/FCC/EAC	\$12.20
2225705	MEAN WELL	GST25U28-P1J	28	0.89	2.1mm x 5.5mm	85 to 264	47 to 63	Cylindrical Female	Center Positive	3.1 x 2.1 x 1.3	UL/CUL/CB/FCC/EAC	\$12.40
380220	MEAN WELL	GS25U28-P1J	28	0.89	2.1mm x 5.5mm	90 to 264	47 to 63	Cylindrical Female	Center Positive	3.1 x 2.1 x 1.3	UL/CUL/TUV/CB/FCC	\$11.95
2225641	MEAN WELL	GST18U48-P1J	48	0.375	2.1mm x 5.5mm	85 to 264	47 to 63	Cylindrical Female	Center Positive	3.1 x 2.1 x 1.3	UL/CUL/CB/FCC/EAC	\$12.20