



Click Here to Request a Large Quantity Quote

RECHARGEABLE AND NON-RECHARGEABLE BATTERIES

Jameco Part#	Manufacturer	Manufacturer Part #	Cell Size	Volts (VDC)	Nominal Capacity (mAh)	Chemistry	Size	Termination	Features	Price
140783	Evergreen	S357ST	SR44	2	175.0	Silver-Oxide	0.45"Dia. x 0.21"Th	Pressure Fit	Non-Rechargeable	\$ 1.19
2237976	Evergreen	L1028FT	23A	12	55.0	Alkaline (Manganese Dry)	0.41"Dia. x 1.12"(H)	Button Top	Non-Rechargeable	\$ 0.95
151095	Evergreen	VINNICS9V/GP6F22MS	9V	9	330.0	Alkaline (Zinc-chloride)	1.04"L x 0.62"W x 1.91"H	Snaps	Non-Rechargeable	\$ 1.19
2112461	Evergreen	L6F22/VINNIC	9V	9	550.0	Alkaline (Zinc-Manganese Dioxide)	1.04"L x 0.62"W x 1.91"H	Snaps	Non-Rechargeable	\$ 1.95
198731	Energizer Batteries	ALK 9V 522	9V	9	600.0	Alkaline (Zinc-Manganese Dioxide)	1.04"L x 0.62"W x 1.91"H	Snaps	Non-Rechargeable	\$ 2.25
198791	Duracell	DURACELL PC1604	9V	9	600.0	Alkaline (Zinc-Manganese Dioxide)	1.04"L x 0.62"W x 1.91"H	Snaps	Non-Rechargeable	\$ 2.75
2158493	Micropower Battery	RS6	AA	1.5	940.0	Alkaline (Zinc-chloride)	0.57"Dia. x 1.99"L	Button Top	Non-Rechargeable	\$ 0.29
2112444	Evergreen	LR6AM3	AA	2	2450.0	Alkaline (Manganese Dry)	0.57"Dia. x 1.99"L	Button Top	Non-Rechargeable	\$ 0.49
198707	Energizer Batteries	ALK AA (EN91)	AA	2	2800.0	Alkaline (Zinc-Manganese Dioxide)	0.57"Dia. x 1.99"L	Button Top	Non-Rechargeable	\$ 0.79
2112436	Evergreen	LR03AM4	AAA	2	1200.0	Alkaline (Manganese Dry)	0.41"Dia. x 1.75"HL	Button Top	Non-Rechargeable	\$ 0.55
198715	Energizer Batteries	ALK AAA (EN92)	AAA	2	1200.0	Alkaline (Zinc-Manganese Dioxide)	0.41"Dia. x 1.75"L	Button Top	Non-Rechargeable	\$ 0.69
2112428	Evergreen	LR14AM2	C	2	6700.0	Alkaline (Zinc, EMD, HKO, Graphite)	0.98"Dia. x 1.90"L	Button Top	Non-Rechargeable	\$ 1.19
215845	Energizer Batteries	ALK D EN-95	D	2	18000.0	Alkaline (Zinc-Manganese Dioxide)	1.35"Dia. x 2.42"L	Button Top	Non-Rechargeable	\$ 1.75
2287279	Sanyou Electrical	CR14250SE	1/2 AA	3	850.0	Lithium Manganese Dioxide	0.55"Dia. x 0.99"L	Button Top	Non-Rechargeable	\$ 3.49
2123784	Jameco Reliapro	CR1220	CR1220	3	38.0	Lithium Manganese Dioxide	0.49"Dia. x 0.08"Th (12x2.0mm)	Pressure Fit	Non-Rechargeable	\$ 0.69
2210010	Jameco Reliapro	CR1220/WIRE LEADS	CR1220	3	40.0	Lithium Manganese Dioxide	0.77"L x 0.49"W x 0.10"Th	2" wire leads	Non-Rechargeable	\$ 0.89
240258	Jameco Reliapro	CR123A	CR123A	3	1300.0	Lithium Manganese Dioxide	0.65"Dia. x 1.36"L	Button Top	Non-Rechargeable	\$ 2.49
2238362	Jameco Reliapro	CR2025-LEADS	CR2025	3	160.0	Lithium Manganese Dioxide	0.79"Dia x 0.10"Th (20x2.5mm)	2" wire leads	Non-Rechargeable	\$ 1.29
2167509	Energizer Batteries	CR2025	CR2025	3	163.0	Lithium Manganese Dioxide	0.79"Dia. x 0.10"Th (20x2.5mm)	Pressure Fit	Non-Rechargeable	\$ 1.95
14162	Renata Batteries	CR2032	CR2032	3	210.0	Lithium Manganese Dioxide	0.79"Dia. x 0.13"Th (20x3.2mm)	Pressure Fit	Non-Rechargeable	\$ 0.89
2223443	Jameco Reliapro	CR2032-LEADS	CR2032	3	220.0	Lithium Manganese Dioxide	0.79"Dia. x 0.13"Th (20x3.2mm)	2" wire leads	Non-Rechargeable	\$ 1.49
11789	Jameco Reliapro	CR2325	CR2325	3	165.0	Lithium Manganese Dioxide	0.91"Dia. x 0.13"Th (23x2.5mm)	Pressure Fit	Non-Rechargeable	\$ 0.95
2280655	Laird	CR2430F2AW3	CR2430	3	290.0	Lithium Manganese Dioxide	1.00"Dia. x 0.12"Th (25x3.0mm)	PC mount, vertical	Non-Rechargeable	\$ 1.75
2238371	Jameco Reliapro	CR2450-LEADS	CR2450	3	540.0	Lithium Manganese Dioxide	0.95"Dia. x 0.2"Th (24x5.0mm)	2" wire leads	Non-Rechargeable	\$ 1.25
2280663	Laird	CR2450F2MX1HF	CR2450	3	550.0	Lithium Manganese Dioxide	1.00"Dia. x 0.22"Th (25x5.0mm)	PC mount	Non-Rechargeable	\$ 1.95
2158231	Arndt	CR927	CR927	3	30.0	Lithium Manganese Dioxide	0.37"Dia. x 0.10"Th	Pressure Fit	Non-Rechargeable	\$ 0.49
2284631	HCB Battery Co.	CP603146	Flat Pack	3	1950.0	Lithium Manganese Dioxide	1.81"L x 1.22"W x 0.24"Th	Solder Tab	Non-Rechargeable	\$ 9.95
33371	Tadiran	TL-5101/P	1/2 AA	4	950.0	Lithium-Thionyl Chloride	0.57"Dia x 0.99"L	Axial Leads	Non-Rechargeable	\$ 5.95
263898	Jameco Reliapro	ER14250 W/LEADS	1/2 AA	4	1200.0	Lithium-Thionyl Chloride	0.57"Dia. x 1.00"L	Axial Leads	Non-Rechargeable	\$ 5.95
33398	Tadiran	TL-5104/P	AA	4	2100.0	Lithium-Thionyl Chloride	0.57"Dia x 1.99"L	Axial Leads	Non-Rechargeable	\$ 7.29
146114	Tadiran	TL-5104/S	AA	4	2100.0	Lithium-Thionyl Chloride	0.57"Dia x 1.99"L	Button Top	Non-Rechargeable	\$ 6.95
2280743	SEIKO INSTRUMENTS	MS518SE-FL35E	MS518SE	3	3.4	Lithium (Manganese Silicon)	0.23"Dia. x 0.07"Th (5.8x1.8mm)	PC mount	Rechargeable	\$ 1.95
2275319	Jameco Reliapro	LJ503035	Flat Pack	4	500.0	Lithium Polymer	1.40"L x 1.15"W x 0.19"H	pin JST-PH connector (2mm pitch)	Rechargeable	\$ 6.95
2279415	Tenergy Corporation	31778	18650	4	2600.0	Lithium-Ion	0.75"Dia. x 2.76"L	Button Top	Rechargeable, protected type	\$ 24.95
2140349	Tenergy Corporation	30006	18650	4	2600.0	Lithium-Ion	0.75"Dia. x 2.76"L	Flat Top	Rechargeable, protected type	\$ 11.95
2279191	Jameco Reliapro		Pack	5	10000.0	Lithium Polymer		Dual USB-A port, with 3 cables	Rechargeable	\$ 19.95
2129351	MG Electronics	LBP-124500	Pack	12	4500.0	Lithium-Ion	2.00"L x 0.75"W x 3.00"H	1mm x 5.5mm female barrel plug	Rechargeable	\$ 49.95
261657	Jameco Reliapro	N700AA/BTN	AA	1	700.0	Nickel Cadmium	0.55"Dia. x 1.90"L	Button Top	Rechargeable	\$ 1.75
244515	Jameco Reliapro	20104	AA	1	1000.0	Nickel Cadmium	0.55"Dia. x 1.90"L	Button Top	Rechargeable	\$ 1.89
2286351	Evergreen	GP60BNK	Cylinder	4	60.0	Nickel Cadmium	0.64"Dia. x 0.74"L	PC mount, 3-pin	Rechargeable	\$ 2.95
244574	Jameco Reliapro	SC-1500	Sub-C	1	1500.0	Nickel Cadmium	0.87"Dia x 1.65"L	Flat Top	Rechargeable	\$ 3.29
244620	Tenergy Corporation	10005	9V	8	200.0	Nickel Metal Hydride	1.04"L x 0.62"W x 1.91"H	Snaps	Rechargeable	\$ 7.95
231087	Dantona Industries	AA-1800NM	AA	1	1800.0	Nickel Metal Hydride	0.56"Dia. x 1.97"L	Button Top	Rechargeable	\$ 2.95
2197492	Arndt	AA2300-2PKG	AA	1	2300.0	Nickel Metal Hydride	0.55"Dia. x 1.90"L	Button Top	Rechargeable	\$ 3.95
2127777	Tenergy Corporation	10320	AA	1	2500.0	Nickel Metal Hydride	0.57"Dia. x 1.99"L	Button Top	Rechargeable	\$ 3.95
231095	Tenergy Corporation	10405	AAA	1	1000.0	Nickel Metal Hydride	0.40"Dia x 1.79"L	Button Top	Rechargeable	\$ 2.75
2137473	Evergreen	NHB60H3A2H	Cylinder	4	80.0	Nickel Metal Hydride	0.63"Dia. x 0.75"L	PC mount, 2-pin	Rechargeable	\$ 4.95
2129342	Evergreen	COMP-16-3NMH	Cylinder	4	80.0	Nickel Metal Hydride	0.61"Dia. x 0.72"L	PC mount, 3-pin	Rechargeable	\$ 6.95
2285815	Tysonic	GP50NH	N	1	520.0	Nickel Metal Hydride	0.46"Dia. x 1.16"L	Button Top	Rechargeable	\$ 3.95
264014	Tysonic	TY-6-4.5	Rectangular	6	4500.0	Sealed Lead-acid	2.76"L x 1.85"W x 4.21"H	Faston F1, 0.187"	Rechargeable, Non-Spillable	\$ 10.95
318844	Tysonic	LA-TY-12-1.2	Rectangular	12	1200.0	Sealed Lead-acid	3.82"L x 1.87"W x 2.20"H	Faston F1, 0.187"	Rechargeable, Non-Spillable	\$ 14.95
264031	Tysonic	TY-12-2.3	Rectangular	12	2300.0	Sealed Lead-acid	7.01"L x 1.38"W x 2.64"H	Faston F1, 0.187"	Rechargeable, Non-Spillable	\$ 17.95
318924	Tysonic	LA-TY-12-3.4	Rectangular	12	3400.0	Sealed Lead-acid	5.28"L x 2.64"W x 2.64"H	Faston F1, 0.187"	Rechargeable, Non-Spillable	\$ 19.95
264049	Tysonic	TY-12-5	Rectangular	12	5000.0	Sealed Lead-acid	3.54"L x 2.76"W x 4.21"H	Faston F1, 0.187"	Rechargeable, Non-Spillable	\$ 17.95
2270863	EnerSys	NPX-25FR	Rectangular	12	5000.0	Sealed Lead-acid	3.54"L x 2.75"W x 4.21"H	Faston F2, 0.250"	Rechargeable, Non-Spillable	\$ 33.95
264057	Tysonic	TY-12-7.5	Rectangular	12	7500.0	Sealed Lead-acid	5.95"L x 2.56"W x 3.94"H	Faston F1, 0.187"	Rechargeable, Non-Spillable	\$ 24.95
264065	Tysonic	TY-12-12	Rectangular	12	12000.0	Sealed Lead-acid	5.95"L x 3.86"W x 3.94"H	Faston F1, 0.187"	Rechargeable, Non-Spillable	\$ 39.95
264073	Tysonic	TY-12-18	Rectangular	12	18000.0	Sealed Lead-acid	7.13"L x 2.29"W x 6.58"H	Bolt & nut, 0.472"	Rechargeable, Non-Spillable	\$ 49.95
318852	Tysonic	LA-TY-12-35	Rectangular	12	35000.0	Sealed Lead-acid	7.70"L x 5.12"W x 7.05"H	Bolt & nut, 0.65"	Rechargeable, Non-Spillable	\$ 109.95