



[Click Here to Request a Large Quantity Quote](#)

## BATTERY CHARGERS

Jameco Part#	Manufacturer	Manufacturer Part #	Description	Output Voltage (VDC)	Output Current (A)	Input Voltage	Battery Type	Price
<a href="#">2144366</a>	Adafruit Industries	259	USB Li-Ion/LiPoly Charger v1.2	4.2, 3.7	1	5 VDC	Li-Ion, LiPo	\$ 13.95
<a href="#">2228885</a>	DFRobot	FIT0398	7.4V Lipo Battery Charger	8.5	2	100-240 VAC @ 50-60 Hz	LiPo	\$ 19.95
<a href="#">2139006</a>	ENG Electric Company	3G-301DN13	Battery Charger Switch Mode 30W 13.5V@2.2A 100-240VAC UL/CUL	13.5	2	100-240 VAC @ 50-60 Hz	SLA	\$ 3.59
<a href="#">1954316</a>	MEAN WELL	PB-360N-24	360 Watt Single Output Lead-Acid Battery Charger 28.8 Volt @ 12.5 Amp	28.8	13	90-132 VAC @ 47-63 Hz	SLA	\$ 79.89
<a href="#">2197821</a>	MG Electronics	MG1261.5A	6V/12V Auxiliary Power Supply/Charger Auxiliary Power Supply/Charger	13.8, 12, 6	1.5, 0.13	12 VDC, 16.5 VAC	SLA	\$ 2.49