



[Click Here to Request a Large Quantity Quote](#)

[Alkaline Batteries](#)

Jameco Part #	Manufacturer	Manufacturer Part #	Cell Size	Volts (VDC)	Nominal Capacity (mAh)	Chemistry	Size	Termination	Features	Battery Type	Price 1
<a href="#">2237976</a>	Evergreen	L1028FT	23A	12	55	Alkaline (Manganese Dry)	0.41"Dia. x 1.12"(H)	Button Top	Non-Rechargeable	Primary	\$0.79
<a href="#">151095</a>	Evergreen	VINNICS9V/GP6F22MS	9V	9	330	Alkaline (Zinc-chloride)	1.04"L x 0.62"W x 1.91"H	Snaps	Non-Rechargeable	Primary	\$1.19
<a href="#">2112461</a>	Evergreen	L6F22/VINNIC	9V	9	550	Alkaline (Zinc-Manganese Dioxide)	1.04"L x 0.62"W x 1.91"H	Snaps	Non-Rechargeable	Primary	\$1.95
<a href="#">198731</a>	Energizer Batteries	ALK 9V 522	9V	9	600	Alkaline (Zinc-Manganese Dioxide)	1.04"L x 0.62"W x 1.91"H	Snaps	Non-Rechargeable	Primary	\$2.25
<a href="#">2158493</a>	Micropower Battery	R6S	AA	1.5	800	Zinc-chloride	0.57"(Dia) x 1.99"(H)	Button Top	Non-Rechargeable	Primary	\$0.29
<a href="#">2112444</a>	Evergreen	LR6AM3	AA	1.5	2450	Alkaline (Manganese Dry)	0.57"Dia. x 1.99"L	Button Top	Non-Rechargeable	Primary	\$0.49
<a href="#">198707</a>	Energizer Batteries	ALK AA (EN91)	AA	1.5	2800	Alkaline (Zinc-Manganese Dioxide)	0.57"Dia. x 1.99"L	Button Top	Non-Rechargeable	Primary	\$0.69
<a href="#">2112436</a>	Evergreen	LR03AM4	AAA	1.5	1200	Alkaline (Manganese Dry)	0.41"Dia.x 1.75"HL	Button Top	Non-Rechargeable	Primary	\$0.45
<a href="#">198715</a>	Energizer Batteries	ALK AAA (EN92)	AAA	1.5	1200	Alkaline (Zinc-Manganese Dioxide)	0.41"Dia. x 1.75"L	Button Top	Non-Rechargeable	Primary	\$0.69
<a href="#">2112428</a>	Evergreen	LR14AM2	C	1.5	6700	Alkaline (Zinc, EMD, HKO, Graphite)	0.98"Dia. x 1.90"L	Button Top	Non-Rechargeable	Primary	\$1.19
<a href="#">215845</a>	Energizer Batteries	ALK D EN-95	D	1.5	18000	Alkaline (Zinc-Manganese Dioxide)	1.35"Dia. x 2.42"L	Button Top	Non-Rechargeable	Primary	\$1.75
<a href="#">2309551</a>	Dantona Industries	VAL-357-5	SR44	1.55	155	Silver-Oxide	0.45"Dia. x 0.21"Th	Pressure Fit	Non-Rechargeable	Primary	\$7.95
<a href="#">140783</a>	Evergreen	S357ST	SR44	1.55	175	Silver-Oxide	0.45"Dia. x 0.21"Th	Pressure Fit	Non-Rechargeable	Primary	\$1.25



[Click Here to Request a Large Quantity Quote](#)

[Analog Panel Meters](#)

Jameco Part #	Manufacturer	Manufacturer Part #	Description	Meter Type	Measuring Range	Price 1
<a href="#">2282495</a>	Velleman	AIM601	Current Measuring Analog Panel Meter Class 2.5 (1 mA Range)	Ammeter (Current)	0 to 1 mA	\$8.95
<a href="#">316494</a>	Velleman	AIM6010A	Analog CURRENT PANEL METER 10A DC / 60 X 47MM	Ammeter (Current)	0 to 10 A	\$16.95
<a href="#">316486</a>	Velleman	AIM60100	Analog CURRENT PANEL METER 100MA DC / 2.4 X 1.9	Ammeter (Current)	0 to 100 mA	\$16.95
<a href="#">2131063</a>	Velleman	AIM603000	0 to 3 Amp Analog Current Meter (Ammeter)	Ammeter (Current)	0 to 3 A	\$16.95
<a href="#">316507</a>	Velleman	AIM6030A	Analog CURRENT PANEL METER 30A DC / 60 X 47MM	Ammeter (Current)	0 to 30 A	\$17.95
<a href="#">316566</a>	Velleman	AIM605000	Analog CURRENT PANEL METER 5A DC / 60 X 47MM	Ammeter (Current)	0 to 5 A	\$16.95
<a href="#">316523</a>	Velleman	AIM6050	Analog CURRENT PANEL METER 50MA DC / 60 X 47MM	Ammeter (Current)	0 to 50 mA	\$16.95
<a href="#">315301</a>	Velleman	AIM60005	Ammeter Analog Current Panel Meter 50uA DC 60x47mm	Ammeter (Current)	0 to 50 uA	\$16.95
<a href="#">316558</a>	Velleman	AIM60500	ANALOG CURRENT PANEL METER 500MA DC / 2.4 X 1.9	Ammeter (Current)	0 to 500 mA	\$16.95
<a href="#">316603</a>	Velleman	AVM6015	Analog Voltage Panel Meter 15 Volt DC 2.4 X 1.9	Voltmeter (Voltage)	0 to 15 VDC	\$15.95
<a href="#">316671</a>	Velleman	AVM7015	Analog Voltage Panel Meter 15 Volt DC 2.8 X 2.4	Voltmeter (Voltage)	0 to 15 VDC	\$15.95
<a href="#">316718</a>	Velleman	AVM60150	Analog Voltage Panel Meter 150 Volt AC 2.4 X 1.9	Voltmeter (Voltage)	0 to 150 VAC	\$15.95
<a href="#">2276639</a>	Jameco Benchpro	PM820222	Dual Range Analog DC Voltage Panel Meter 3V and 15V	Voltmeter (Voltage)	0 to 3 VDC, 0 to 15 VDC	\$6.95
<a href="#">316638</a>	Velleman	AVM6030	Analog VOLTAGE PANEL METER 30V DC / 60 X 47MM	Voltmeter (Voltage)	0 to 30 VDC	\$15.95
<a href="#">316654</a>	Velleman	AVM7030	Analog Voltage Panel Meter 30 Volt DC 2.8 X 2.4	Voltmeter (Voltage)	0 to 30 VDC	\$14.95
<a href="#">2289327</a>	Arndt	313-S-500VAC	0-500VAC Panel Meter	Voltmeter (Voltage)	0 to 500 VAC	\$9.95



[Click Here to Request a Large Quantity Quote](#)

[Battery Accessories, Holders & Clips](#)

Jameco Part #	Manufacturer	Manufacturer Part #	Cell Size	Number of Cells	Sides	Connector	Product Type	Size (L x W x H) (mm)	Features	Price 1
<a href="#">2146231</a>	Jameco Reliapro	BH-18650-2S-WG	18650	2	Single	Wires, 6"	Battery Holders (open)	75.7 x 41.5 x 20	No internal PCB, for flat top cells	\$1.95
<a href="#">105794</a>	Jameco Reliapro	GBH-1009-R	9V	1	Single	None	Battery Holder Clip	17 x 16 x 30	Side mount	\$0.49
<a href="#">2191891</a>	Jameco Reliapro	12BH079-GR-VP	9V	1	Single	None	Battery Holder Clip	26.4 x 16 x 19.3	Flat mount	\$0.69
<a href="#">2228447</a>	Memory Protection Devices	BC9VPC	9V	1	Single	PC Mount	Battery Holders (open)	54.9 x 30 x 21.4	Pins 0.51" apart	\$1.49
<a href="#">2203899</a>	Jameco Reliapro	9VSNAPOB6	9V	1	Single	Snaps	Battery Contact Clip	10.2 x 7 x 17	PC mount	\$0.49
<a href="#">101470</a>	Jameco Reliapro	G/S(A-102)-R	9V	1	Single	Wires, 10"	Battery Holders (open)	25.4 x 12.7 x 6.4	I-Type	\$0.49
<a href="#">11280</a>	Jameco Reliapro	A104-R	9V	1	Single	Wires, 3"	Battery Holders (open)	14.2 x 25.4 x 6.5	T-Type	\$0.39
<a href="#">1949488</a>	Jameco Reliapro	BAT-SNAP-4	9V	1	Single	Wires, 4"	Battery Holders (open)	25.4 x 12.7 x 6.5	I-Type	\$0.49
<a href="#">2191904</a>	Eagle Plastics	660279	9V	1	Single	Wires, 4", 2P connector	Battery Holders (open)	25.4 x 12.7 x 6.5	I-Type, JP2411-2P connector	\$1.25
<a href="#">2128067</a>	Jameco Reliapro	SBH-9VAS	9V	1	Single	Wires, 6"	Battery Holders (closed)	68.6 x 33 x 21.6	Cover and switch	\$1.49
<a href="#">109154</a>	Jameco Reliapro	BC6-R	9V	1	Single	Wires, 6"	Battery Holders (open)	25.4 x 13.8 x 6.1	I-Type	\$0.49
<a href="#">216452</a>	Jameco Reliapro	SBS-IR-1-R	9V	1	Single	Wires, 6"	Battery Holders (open)	26 x 13 x 8	I-Type, protected terminals	\$0.39
<a href="#">216427</a>	Jameco Reliapro	BH-9V-A-R	9V	1	Single	Wires, 6"	Battery Holders (open)	55 x 31 x 20	Flat mount	\$0.89
<a href="#">2207048</a>	Jameco Reliapro	1X9V-2.1 CS	9V	1	Single	Wires, 6", 2.1mm Plug	Battery Holders (closed)	53.6 x 30 x 16	Cover and switch, 2.1mm x 5.5mm barrel plug, center positive	\$3.25
<a href="#">2207056</a>	Jameco Reliapro	1X9V-2.1 SNAP	9V	1	Single	Wires, 6", 2.1mm Plug	Battery Holders (open)	25.4 x 12.7 x 6.5	I-Type, 2.1mm x 5.5mm barrel plug, center positive	\$1.75

Jameco Part #	Manufacturer	Manufacturer Part #	Cell Size	Number of Cells	Sides	Connector	Product Type	Size (L x W x H) (mm)	Features	Price 1
<a href="#">2207030</a>	Jameco Reliapro	1X9V-2.1	9V	1	Single	Wires, 6", 2.1mm Plug	Battery Holders (open)	54.5 x 30.5 x 20.9	2.1mm x 5.5mm barrel plug, center positive	\$1.75
<a href="#">2313167</a>	Keystone Electronics	228	A, AA, CR2	1	Single	Spring Contact	Battery Contact Clip	7.9 x 11.4 x 0.38	Contact clip for A, AA, CR2, 17-19mm	\$0.25
<a href="#">2222133</a>	Keystone Electronics	209	A, AA, CR2, CR123A	1	Single	Spring Contact, Snap-In	Battery Contact Clip	7.9 x 9.1 x 11.7	A/AA/CR2/CR123A	\$0.35
<a href="#">216072</a>	Jameco Reliapro	BH-311-2A-R	AA	1	Single	Wires, 6"	Battery Holders (open)	57 x 17 x 17	Holder is in-line with wires	\$0.75
<a href="#">216102</a>	Jameco Reliapro	SBH-321-2A-R	AA	2	Single	Wires, 6"	Battery Holders (closed)	68.4 x 35.4 x 18.6	Cover, no switch	\$1.25
<a href="#">216120</a>	Jameco Reliapro	SBH-321-1AS-S10	AA	2	Single	Wires, 6"	Battery Holders (closed)	68.5 x 34 x 18.2	Cover and switch	\$1.95
<a href="#">216081</a>	Jameco Reliapro	BH-321-2A-R	AA	2	Single	Wires, 6"	Battery Holders (open)	59 x 33 x 15		\$0.99
<a href="#">216099</a>	Jameco Reliapro	BH-321-4A-R	AA	2	Single	Wires, 6"	Battery Holders (open)	71 x 32 x 16	Mounting tabs	\$0.79
<a href="#">2295375</a>	Jameco Reliapro	BH-321-1ATH	AA	2	Single	Wires, 6", 2P connector	Battery Holders (open)	59 x 33 x 15	JST-PH connector	\$1.79
<a href="#">216144</a>	Jameco Reliapro	SBH-331-AS-R	AA	3	Single	Wires, 6"	Battery Holders (closed)	68.5 x 48 x 18.7	Cover and switch	\$1.65
<a href="#">216136</a>	Jameco Reliapro	BH-331-A-R	AA	3	Single	Wires, 6"	Battery Holders (open)	58 x 48 x 17		\$0.99
<a href="#">2191883</a>	Eagle Plastics	12BH341-GR	AA	4	Dual	Snaps	Battery Holders (open)	57 x 30 x 27	2x2, long	\$1.09
<a href="#">216179</a>	Jameco Reliapro	BH-343-1A-R	AA	4	Dual	Wires, 6"	Battery Holders (open)	57 x 30 x 27		\$1.19
<a href="#">2095453</a>	Jameco Reliapro	SBH-341-1A	AA	4	Single	Wires, 6"	Battery Holders (closed)	65 x 68 x 19	Cover, no switch	\$1.49
<a href="#">216187</a>	Jameco Reliapro	SBH-341-1AS-R	AA	4	Single	Wires, 6"	Battery Holders (closed)	68 x 64.4 x 19.3	Cover and switch	\$2.25
<a href="#">216152</a>	Jameco Reliapro	BH-341-2A-R	AA	4	Single	Wires, 6"	Battery Holders (open)	57 x 62 x 15		\$1.19
<a href="#">2207013</a>	Jameco Reliapro	4XAA-2.1	AA	4	Single	Wires, 6", 2.1mm Plug	Battery Holders (open)	63.2 x 57.7 x 15.6	2.1mm x 5.5mm barrel plug, center positive	\$1.95
<a href="#">2278463</a>	Jameco Reliapro	BAT. HOLDER-R WHT	AA	4	Single	Wires, 6", 2P connector	Battery Holders (open)	57 x 62 x 15	Molex 0050375023 connector	\$0.99



Jameco Part #	Manufacturer	Manufacturer Part #	Cell Size	Number of Cells	Sides	Connector	Product Type	Size (L x W x H) (mm)	Features	Price 1
<a href="#">105858</a>	Jameco Reliapro	BAT. HOLDER-R	AA	4	Single	Wires, 6", 4P Connector	Battery Holders (open)	58.4 x 63.5 x 16.3	4P connector with 0.1" pitch	\$0.99
<a href="#">216223</a>	Jameco Reliapro	BH-364-A	AA	6	Single	Wires, 6"	Battery Holders (open)	57 x 91 x 16	Holder is in-line with wires	\$1.69
<a href="#">2207021</a>	Jameco Reliapro	6XAA-2.1	AA	6	Single	Wires, 6", 2.1mm Plug	Battery Holders (open)	91.7 x 57.4 x 16	2.1mm x 5.5mm barrel plug, center positive	\$2.75
<a href="#">216259</a>	Jameco Reliapro	BH-382-B-R	AA	8	Dual	Snaps	Battery Holders (open)	108 x 31 x 29	4x2 cells long	\$1.39
<a href="#">216267</a>	Jameco Reliapro	BH-383-B-R	AA	8	Dual	Snaps	Battery Holders (open)	58 x 63 x 28	4x2 cells wide	\$1.09
<a href="#">216240</a>	Jameco Reliapro	BH-383-A	AA	8	Dual	Wires, 6"	Battery Holders (open)	57 x 30 x 27	4x2 cells wide	\$1.95
<a href="#">2197935</a>	Jameco Reliapro	BC-0302	AA, AAA	1	Single	Contact	Battery Contact Clip	9 x 14 x 15	PC Mount, 0.3" pitch, 2 required	\$0.39
<a href="#">2236981</a>	Jameco Reliapro	12-051	AAA	2	Single	Wires, 2.5", with crimped pins	Battery Holders (open)	53.3 x 24.6 x 13	Breadboard pins	\$1.09
<a href="#">216292</a>	Jameco Reliapro	SBH-421-AS-R	AAA	2	Single	Wires, 6"	Battery Holders (closed)	63 x 26 x 16	Cover and switch	\$1.39
<a href="#">216283</a>	Jameco Reliapro	BH-421-1A-R	AAA	2	Single	Wires, 6"	Battery Holders (open)	52 x 25 x 13		\$0.89
<a href="#">216312</a>	Jameco Reliapro	SBH-431-1AS-R	AAA	3	Single	Wires, 6"	Battery Holders (closed)	63.2 x 36.8 x 16	Cover and switch	\$1.15
<a href="#">2232833</a>	Jameco Reliapro	UM-4	AAA	4	Single	PC Mount	Battery Holders (open)	50.3 x 47.2 x 12.2	Pins 0.478" apart	\$0.99
<a href="#">216339</a>	Jameco Reliapro	SBH-441-AS-R	AAA	4	Single	Wires, 6"	Battery Holders (closed)	63 x 48 x 15	Cover and switch	\$1.59
<a href="#">2245546</a>	Jameco Reliapro	BH-482B	AAA	8	Dual	Snaps	Battery Holders (open)	97 x 23.8 x 24.4	4x2, long	\$0.99
<a href="#">216363</a>	Jameco Reliapro	BH-242-1A-R	C	4	Single	Wires, 6"	Battery Holders (open)	108 x 54 x 26		\$1.39
<a href="#">2246856</a>	Jameco Reliapro	WJ-CR1220-1	CR1216, CR1220	1	Coin Cell	PC Mount	Battery Holders (open)	13.4 x 11.7 x 2.3	Retaining clip, one side open	\$0.35
<a href="#">2258646</a>	Arndt	AAA-BAT-054	CR2012, CR2016, CR2020, CR2025, CR2032	1	Coin Cell	Surface Mount	Battery Holders (open)	31.9 x 23 x 4.2	For 20mm cells	\$0.99
<a href="#">355434</a>	Jameco Reliapro	17002-00603	CR2032	1	Coin Cell	PC Mount	Battery Holders (open)	23.7 x 22.5 x 8	For 20mm cells	\$0.65

Jameco Part #	Manufacturer	Manufacturer Part #	Cell Size	Number of Cells	Sides	Connector	Product Type	Size (L x W x H) (mm)	Features	Price 1
<a href="#">236996</a>	Keystone Electronics	103	CR2032	1	Coin Cell	PC Mount	Battery Holders (open)	28.5 x 22.7 x 8.3	For 20mm cells	\$1.49
<a href="#">38543</a>	Jameco Reliapro	GS025-021G	CR2325	1	Coin Cell	PC Mount	Battery Holders (open)	29.1 x 25.4 x 8.3	For 23mm cells	\$0.79
<a href="#">216371</a>	Jameco Reliapro	BH-111-1A	D	1	Single	Wires, 6"	Battery Holders (open)	69 x 37 x 27	Holder is in-line with wires	\$1.15
<a href="#">216390</a>	Jameco Reliapro	BH-121-1A-R	D	2	Single	Wires, 6"	Battery Holders (open)	71 x 73 x 31		\$1.09
<a href="#">216401</a>	Jameco Reliapro	BH-142-A-R	D	4	Single	Wires, 6"	Battery Holders (open)	133.5 x 74 x 31		\$1.09



[Click Here to Request a Large Quantity Quote](#)

### Battery Chargers

Jameco Part #	Manufacturer	Manufacturer Part #	Description	Price 1
<a href="#">2197821</a>	MG Electronics	MG1261.5A	6V or 12V Auxiliary Power Supply and Battery Charger	\$2.79
<a href="#">2139006</a>	ENG Electric Company	3G-301DN13	Battery Charger Switch Mode 30W 13.5V@2.2A 100-240VAC UL/CUL	\$3.59



[Click Here to Request a Large Quantity Quote](#)

[Lead Acid Batteries](#)

Jameco Part #	Manufacturer	Manufacturer Part #	Cell Size	Volts (VDC)	Nominal Capacity (mAh)	Chemistry	Size	Termination	Features	Price 1
<a href="#">264014</a>	Tysonic	TY-6-4.5	Rectangular	6	4500	Sealed Lead-acid	2.76"L x 1.85"W x 4.21"H	Faston F1, 0.187"	Rechargeable, Non-Spillable	\$11.95
<a href="#">318844</a>	Tysonic	LA-TY-12-1.2	Rectangular	12	1200	Sealed Lead-acid	3.82"L x 1.87"W x 2.20"H	Faston F1, 0.187"	Rechargeable, Non-Spillable	\$14.95
<a href="#">264031</a>	Tysonic	TY-12-2.3	Rectangular	12	2300	Sealed Lead-acid	7.01"L x 1.38"W x 2.64"H	Faston F1, 0.187"	Rechargeable, Non-Spillable	\$17.95
<a href="#">318924</a>	Tysonic	LA-TY-12-3.4	Rectangular	12	3400	Sealed Lead-acid	5.28"L x 2.64"W x 2.64"H	Faston F1, 0.187"	Rechargeable, Non-Spillable	\$18.95
<a href="#">2270863</a>	EnerSys	NPX-25FR	Rectangular	12	5000	Sealed Lead-acid	3.54"L x 2.75"W x 4.21"H	Faston F2, 0.250"	Rechargeable, Non-Spillable	\$33.95
<a href="#">264049</a>	Tysonic	TY-12-5	Rectangular	12	5000	Sealed Lead-acid	3.54"L x 2.76"W x 4.21"H	Faston F1, 0.187"	Rechargeable, Non-Spillable	\$19.95
<a href="#">264057</a>	Tysonic	TY-12-7.5	Rectangular	12	7500	Sealed Lead-acid	5.95"L x 2.56"W x 3.94"H	Faston F1, 0.187"	Rechargeable, Non-Spillable	\$24.95
<a href="#">264073</a>	Tysonic	TY-12-18	Rectangular	12	18000	Sealed Lead-acid	7.13"L x 2.29"W x 6.58"H	Bolt & nut, 0.472"	Rechargeable, Non-Spillable	\$49.95
<a href="#">318852</a>	Tysonic	LA-TY-12-35	Rectangular	12	35000	Sealed Lead-acid	7.70"L x 5.12"W x 7.05"H	Bolt & nut, 0.65"	Rechargeable, Non-Spillable	\$109.95





[Click Here to Request a Large Quantity Quote](#)

[Li-Ion & Li-Po Rechargeable Batteries](#)

Jameco Part #	Manufacturer	Manufacturer Part #	Cell Size	Volts (VDC)	Nominal Capacity (mAh)	Chemistry	Size	Termination	Features	Battery Type	Price 1
<a href="#">2291327</a>	Jameco Reliapro	NCR20700B	20700	3.6	2600	Lithium-Ion	0.78" Dia. x 2.76"L	Button Top	Rechargeable, protected type	Primary	\$5.95
<a href="#">2275319</a>	Jameco Reliapro	LJ503035	Flat Pack	3.7	500	Lithium Polymer	1.40"L x 1.15"W x 0.19"H	2-pin JST-PH connector (2mm pitch)	Rechargeable	Primary	\$6.95
<a href="#">2309567</a>	Dantona Industries	HS-503759-CON	Flat Pack	3.7	1400	Lithium Polymer	2.40"L x 1.50"W x 0.20"H	2-pin JST-PH connector (2mm pitch)	Rechargeable	Primary	\$9.95
<a href="#">2309575</a>	Dantona Industries	HS-785060-CON	Flat Pack	3.7	2500	Lithium Polymer	2.55"L x 2.00"W x 0.30"H	2-pin JST-PH connector (2mm pitch)	Rechargeable	Primary	\$14.95
<a href="#">2282647</a>	Jameco Reliapro	357095	Flat Pack	3.7	2800	Lithium Polymer	3.62"L x 2.78"W x 0.15"H	Wires	Rechargeable	Primary	\$5.00
<a href="#">2280743</a>	SEIKO INSTRUMENTS	MS518SE-FL35E	MS518SE	3	3.4	Lithium (Manganese Silicon)	0.23" Dia. x 0.07" Th (5.8x1.8mm)	PC mount	Rechargeable	Secondary	\$1.89
<a href="#">2279191</a>	Jameco Reliapro	P1013L	Pack	5	10000	Lithium-Ion	3.9"L x 2.6"W x 0.9"H	USB Type-C and USB micro-B	Rechargeable	Back-Up	\$17.95
<a href="#">2292135</a>	Jameco Reliapro	YS-163452	Pack	7.4	1300	Lithium Polymer	2.16"L x 1.29"W x 0.67"H	(2) female pin-header	Rechargeable	Primary	\$12.95
<a href="#">2292191</a>	Jameco Reliapro	12V4500MAH	Pack	12	4500	Lithium Polymer	3.35"L x 2.40"W x 0.75"H	2.1mm female barrel plug	Rechargeable	Primary	\$39.95
<a href="#">2129351</a>	MG Electronics	LBP-124500	Pack	12	4500	Lithium-Ion	2.00"L x 0.75"W x 3.00"H	2.1mm x 5.5mm female barrel plug	Rechargeable	Primary	\$49.95



[Click Here to Request a Large Quantity Quote](#)

Lithium batteries

Jameco Part #	Manufacturer	Manufacturer Part #	Cell Size	Volts (VDC)	Nominal Capacity (mAh)	Chemistry	Size	Termination	Features	Battery Type	Price 1
<a href="#">2287279</a>	Sanyou Electrical	CR14250SE	1/2 AA	3	850	Lithium Manganese Dioxide	0.55"Dia. x 0.99"L	Button Top	Non-Rechargeable	Primary	\$3.49
<a href="#">33371</a>	Tadiran	TL-5101/P	1/2 AA	3.6	950	Lithium-Thionyl Chloride	0.57"Dia. x 0.99"L	Axial Leads	Non-Rechargeable	Primary	\$5.95
<a href="#">263898</a>	Jameco Reliapro	ER14250 W/LEADS	1/2 AA	3.6	1200	Lithium-Thionyl Chloride	0.57"Dia. x 1.00"L	Axial Leads	Non-Rechargeable	Primary	\$5.95
<a href="#">33398</a>	Tadiran	TL-5104/P	AA	3.6	2100	Lithium-Thionyl Chloride	0.57"Dia. x 1.99"L	Axial Leads	Non-Rechargeable	Primary	\$7.29
<a href="#">146114</a>	Tadiran	TL-5104/S	AA	3.6	2100	Lithium-Thionyl Chloride	0.57"Dia. x 1.99"L	Button Top	Non-Rechargeable	Primary	\$6.95
<a href="#">2295711</a>	Renata Batteries	CR2032MFR-RV	CD2032	3	225	Lithium Manganese Dioxide	0.79"Dia. x 0.13"Th (20x3.2mm)	PC mount, vertical	Non-Rechargeable	Primary	\$1.95
<a href="#">2123784</a>	Jameco Reliapro	CR1220	CR1220	3	38	Lithium Manganese Dioxide	0.49"Dia. x 0.08"Th (12x2.0mm)	Pressure Fit	Non-Rechargeable	Primary	\$0.59
<a href="#">2210010</a>	Jameco Reliapro	CR1220/WIRE LEADS	CR1220	3	40	Lithium Manganese Dioxide	0.77"L x 0.49"W x 0.10"Th	2" wire leads	Non-Rechargeable	Primary	\$0.89
<a href="#">240258</a>	Jameco Reliapro	CR123A	CR123A	3	1300	Lithium Manganese Dioxide	0.65"Dia. x 1.36"L	Button Top	Non-Rechargeable	Primary	\$2.25
<a href="#">2309559</a>	Dantona Industries	LITH-8	CR123A	3	1500	Lithium Manganese Dioxide	0.65"Dia. x 1.36"L	Button Top	Non-Rechargeable	Primary	\$2.95
<a href="#">2238362</a>	Jameco Reliapro	CR2025-LEADS	CR2025	3	160	Lithium Manganese Dioxide	0.79"Dia. x 0.10"Th (20x2.5mm)	2" wire leads	Non-Rechargeable	Primary	\$1.19
<a href="#">14162</a>	Renata Batteries	CR2032	CR2032	3	210	Lithium Manganese Dioxide	0.79"Dia. x 0.13"Th (20x3.2mm)	Pressure Fit	Non-Rechargeable	Primary	\$0.79
<a href="#">2223443</a>	Jameco Reliapro	CR2032-LEADS	CR2032	3	220	Lithium Manganese Dioxide	0.79"Dia. x 0.13"Th (20x3.2mm)	2" wire leads	Non-Rechargeable	Primary	\$1.49
<a href="#">2280655</a>	Laird	CR2430F2AW3	CR2430	3	290	Lithium Manganese Dioxide	1.00"Dia. x 0.12"Th (25x3.0mm)	PC mount, vertical	Non-Rechargeable	Primary	\$1.95
<a href="#">2238371</a>	Jameco Reliapro	CR2450-LEADS	CR2450	3	540	Lithium Manganese Dioxide	0.95"Dia. x 0.2"Th (24x5.0mm)	2" wire leads	Non-Rechargeable	Primary	\$1.25

Jameco Part #	Manufacturer	Manufacturer Part #	Cell Size	Volts (VDC)	Nominal Capacity (mAh)	Chemistry	Size	Termination	Features	Battery Type	Price 1
<a href="#">2158231</a>	Arndt	CR927	CR927	3	30	Lithium Manganese Dioxide	0.37"Dia. x 0.10"Th	Pressure Fit	Non-Rechargeable	Primary	\$0.39
<a href="#">2284631</a>	HCB Battery Co.	CP603146	Flat Pack	3	1950	Lithium Manganese Dioxide	1.81"L x 1.22"W x 0.24"Th	Solder Tab	Non-Rechargeable	Primary	\$3.95



[Click Here to Request a Large Quantity Quote](#)

[NiCd & NiMH Rechargeable Batteries](#)

Jameco Part #	Manufacturer	Manufacturer Part #	Cell Size	Volts (VDC)	Nominal Capacity (mAh)	Chemistry	Size	Termination	Features	Battery Type	Price 1
<a href="#">244620</a>	Tenergy Corporation	10005	9V	8.4	200	Nickel Metal Hydride	1.04"L x 0.62"W x 1.91"H	Snaps	Rechargeable	Secondary	\$7.95
<a href="#">261657</a>	Jameco Reliapro	N700AA/BTN	AA	1.2	700	Nickel Cadmium	0.55"Dia. x 1.90"L	Button Top	Rechargeable	Primary	\$1.95
<a href="#">244515</a>	Jameco Reliapro	20104	AA	1.2	1000	Nickel Cadmium	0.55"Dia. x 1.90"L	Button Top	Rechargeable	Primary	\$1.89
<a href="#">2197492</a>	Arndt	AA2300-2PKG	AA	1.2	2300	Nickel Metal Hydride	0.55"Dia. x 1.90"L	Button Top	Rechargeable	Primary	\$2.95
<a href="#">2127777</a>	Tenergy Corporation	10320	AA	1.2	2500	Nickel Metal Hydride	0.57"Dia. x 1.99"L	Button Top	Rechargeable	Primary	\$3.95
<a href="#">231095</a>	Tenergy Corporation	10405	AAA	1.2	1000	Nickel Metal Hydride	0.40"Dia x 1.79"L	Button Top	Rechargeable	Primary	\$2.75
<a href="#">2129342</a>	Dantona Industries	COMP-16-3NMH	Cylinder	3.6	80	Nickel Metal Hydride	0.61"Dia. x 0.72"L	PC mount, 3-pin	Rechargeable	Secondary	\$7.95
<a href="#">2137473</a>	Evergreen	NHB60H3A2H	Cylinder	3.6	80	Nickel Metal Hydride	0.63"Dia. x 0.75"L	PC mount, 2-pin	Rechargeable	Secondary	\$4.95
<a href="#">2286351</a>	Evergreen	GP60BNK	Cylinder	3.6	60	Nickel Cadmium	0.64"Dia. x 0.74"L	PC mount, 3-pin	Rechargeable	Secondary	\$1.95
<a href="#">2285815</a>	Tysonic	GP50NH	N	1.2	520	Nickel Metal Hydride	0.46"Dia. x 1.16"L	Button Top	Rechargeable	Primary	\$1.95
<a href="#">244574</a>	Jameco Reliapro	SC-1500	Sub-C	1.2	1500	Nickel Cadmium	0.87"Dia x 1.65"L	Flat Top	Rechargeable	Primary	\$3.29