



[Click Here to Request a Large Quantity Quote](#)

[LCD Character Displays](#)

Jameco Part #	Manufacturer	Manufacturer Part #	Characters x Lines	Interface	Character / Background Color	Backlight (Y/N)	Character Format	Display Size (WxH) Inches	Input Current mA	Input Voltage-Max (V)	Price 1
2265751	Samsung Electronics	UC16130	16x1	Parallel 4/8 Bit	Black / Green	Y	5x8	2.54 x 0.54	2	5	\$2.75
2265919	Samsung Electronics	UC16116	16x1	Parallel 8 Bit	Black / None	N	5x8	2.54 x 0.51	2	5	\$1.95
2160374	DFRobot	FIT0127	16x2	Parallel	White / Blue	Y	5x8	2.6 x 0.63	3	5	\$10.95
2211071	Microtips Technology	MTC-S16204XFYHSAY-08	16x2	Parallel 4 Bit	Black / Yellow-Green	Y	5x7	2.45 x 0.70	3	4.5	\$6.95
2265951	Samsung Electronics	UC16231	16x2	Parallel 4/8 Bit	Black / None	N	5x8	2.5 x 0.62	2	5	\$3.59
2304023	Jameco Valuepro	SCL16012A_USB	16x2	Parallel 4/8 Bit	Black / Yellow-Green	Y	5x7	2.45 x 0.70		5	\$14.95
2295423	Jameco Valuepro	1602A	16x2	Parallel 4/8 Bit	Black / Yellow-Green	Y	5x8	2.56 x 0.55	100	5	\$4.95
2231030	Lumex Optoelectronics	LCM-SO1602DTR/M	16x2	Parallel 4/8 Bit	Grey / None	N	5x8	1.84 x 0.45	3	5	\$6.95
2303983	Jameco Valuepro	1602KYPD_ARD	16x2	Parallel 4/8 Bit	White / Blue	Y	5x7	2.45 x 0.70		5	\$7.95
2303991	Jameco Valuepro	1602KYPD_RPI	16x2	Parallel 4/8 Bit	White / Blue	Y	5x7	2.45 x 0.70		5	\$19.95
2160358	DFRobot	DFR0063	16x2	Parallel I2C/TWI	White / Blue	Y	5x8	2.5 x 0.58		5	\$11.95
2135638	Jameco Valuepro	LK162-12-WB-C166	16x2	Serial I2C	White / Blue	Y	5x8	2.5x.7	9	5	\$13.95
2304007	Jameco Valuepro	SCL1602J_BLWIT	16x2	Serial I2C, SPI	White / Blue	Y	5x8	2.54 x 0.57	2.2	5	\$7.95
210761	Jameco Valuepro	HC16401(HYUNDAI)	16x4	Parallel 4/8 Bit	Black / None	N	5x8	2.4 x 1.0	2.2	6.5	\$7.95
2265767	Samsung Electronics	UC20102	20x1	Parallel 8 Bit	Black / None	N	5x8	6.09 x 0.63	2	5	\$2.75
2265775	Samsung Electronics	SAM-20-2-EL	20x2	Parallel 4/8 Bit	Black / Yellow	Y	5x8	3.27 x 0.73	1	5	\$2.75

Jameco Part #	Manufacturer	Manufacturer Part #	Characters x Lines	Interface	Character / Background Color	Backlight (Y/N)	Character Format	Display Size (WxH) Inches	Input Current mA	Input Voltage-Max (V)	Price 1
2304015	Jameco Valuepro	SCL2004A-JP	20x4	Serial I2C, SPI	White / Blue	Y	5x7	3.03 x 0.99		5	\$9.95
2270959	Arndt	CCM0820	8x2	Parallel 4/8 Bit	Black / None	N	5x8	1.5 x 0.62	2	3.3	\$3.95
2303975	Jameco Valuepro	IICMODULE	Accessory	I2C	N/A	N	N/A	N/A		5	\$2.95
2133405	Scott Edwards Electronics	BPK-SOI	Accessory	Serial	N/A	N	N/A	N/A	0.5	5	\$9.95



[Click Here to Request a Large Quantity Quote](#)

[LCD Graphical Displays](#)

Jameco Part #	Manufacturer	Manufacturer Part #	Resolution	Interface	Display Mode	Color	Backlighting	Price 1
2211952	Adafruit Industries	326	128x64	SPI or IC	OLED	Y	N	\$19.49
2303999	Jameco Valuepro	SUR320240G028A	320x240	SPI	TFT	65K	LED	\$17.95
2215232	Adafruit Industries	1947	320x240	SPI or IC	TFT	262K	LED	\$44.49
2278271	Velleman	VMP400	480x320	SPI	TFT	Y	LED	\$37.95
2285247	Hantronix	HDA5001-GH1	800x480	Digital RGB 8 Bits/ Color	TFT	16.7M	Y	\$39.95
2255390	EarthLCD	OF-8.0-M5	800x600	VGA	TFT	262K	LED	\$209.95
2162898	Arndt	AB20811E	Custom Module	Serial	LCD	Black	LED	\$2.95



[Click Here to Request a Large Quantity Quote](#)

[Mounting Plates & Brackets](#)

Jameco Part #	Manufacturer	Manufacturer Part #	Product Type	Size Code	Material	Size	Color	Price 1
2310271	DELL COMPUTER	035D0N	Cable Management Arm	2U	Steel	-	Silver	\$29.95
2292879	Hammond Manufacturing	RASA22BK3	Fixed Side Support Bracket	1U	Steel	1.75"H x 20.95"D	Black	\$32.75
2273071	Arndt	532-356-2-LF-C	Mounting Bracket	1U	Steel	1.73"H x 1.73"D	Black	\$2.95
2292871	Hammond Manufacturing	PBPA19001BK2	Rack Spacer Panel Blank	1U	Aluminum	1.73"H	Black	\$10.19
2292863	Hammond Manufacturing	PBPS19001BK2	Rack Spacer Panel Blank	1U	Steel	1.73"H	Black	\$8.49
2292887	Hammond Manufacturing	RSLIDE22	Slide Rails	2U	Steel	24.90"D	Silver	\$55.25
2310279	DELL COMPUTER	0C212M	Slide Rails	2U-4U	Steel	-	Silver	\$69.95



[Click Here to Request a Large Quantity Quote](#)

[Parallel LCD Displays](#)

Jameco Part #	Manufacturer	Manufacturer Part #	AWG	Voltage Rating (DC)	Maximum Current Rating (A)	Length (FT)	Color	Price 1
2283287	Pomona Electronics	6733-0	18	10000	20	50	Black	\$27.89
2283295	Pomona Electronics	6733-2	18	10000	20	50	Red	\$27.89