



[Click Here to Request a Large Quantity Quote](#)

ELECTROMECHANICAL MAGNETIC BUZZERS

Jameco Part#	Manufacturer	Mfg PN	Frequency (Hz)	Operating Voltage (Vp-p/mA)	Voltage Range (Vp-p)	Sound (dB)	Size (H x Dia)"	Price 1
140695	Jameco Valuepro	63S1120-LA	400	12/25	9-15	75	.60 x 1.3	\$ 1.79
2231857	Speakers Unlimited	9000003613	2048	1.5/10	1.0-2.0	70	.21 x .47	\$ 0.25
2222408	Jameco Valuepro	DB111FLF-PN	2048	1.5/15	1.0 - 5.0	80	.33 x .47	\$ 0.65
2286407	CUI	CEM-1205C	2300	5/35	6.0-16	92	.37 x .47	\$ 1.75
2286415	CUI	CEM-1212C	2300	8/16	8.0-16	85	.37 x .47	\$ 1.95
2222387	Jameco Valuepro	TDB12LF-PN	2300	12/30	8.0-15	85	.37 x .47	\$ 1.39
76065	Jameco Valuepro	TDB05LFPN	2300	5.0/30	4.0 - 7.0	85	.35 x .46	\$ 1.75
138740	Jameco Valuepro	DBX05-PN	2400	5/40	3.0-8.0	85	.35 x .46	\$ 1.09
2222441	Jameco Valuepro	DBX12LF-PN	2400	12/40	6.0 - 15.0	85	.35 x .47	\$ 1.09
2159701	Arndt	CB-12HN	2700	2.4/100	1.1-3.0	85	.20 x .47	\$ 0.25
2222416	Jameco Valuepro	MDB03BFLF-PN	2700	3.0/30	2.0 - 5.0	80	.20 x .37	\$ 1.95
2222424	Jameco Valuepro	CDX094A3BOLF-PP	2731	3/100	2.0 - 5.0	85	.16 x .43	\$ 0.55