



[Click Here to Request a Large Quantity Quote](#)

### ELECTROMECHANICAL HARDWARE HEX NUTS

Jameco Part#	Manufacturer	Manufacturer Part #	Thread	Thick(	Outside Dia (	Material	Price 1
2183331	Jameco Valuepro	P-1150-1	1/4-32	0.062	0.377	Steel	\$ 0.35
2203119	Jameco Valuepro	3/8-32NUT	3/8-32	0.085	0.435	Steel	\$ 0.15
2182514	Keystone Electronics	1456	3/8-32	0.090	0.493	Steel	\$ 0.25
2185782	Bourns	H-38-2	3/8-32	0.093	0.495	Steel	\$ 0.15
2182581	Amphenol	31-10495-NA(BRASS)	3/8-32	0.096	0.525	Brass	\$ 0.29
2182784	Jameco Valuepro	P-2439	5/16-32	0.095	0.377	Steel	\$ 0.19
2233879	Keystone Electronics	1472	5/16-32	0.095	0.432	Steel	\$ 0.25
42420	Jameco Valuepro	6CNMS13	6-32	0.112	0.306	Steel	\$ 0.06
2192501	Jameco Valuepro	N-14018-ROHS	7/16-32	0.095	0.562	Steel	\$ 0.69
51553	Jameco Valuepro	#8-32HN	8-32	0.120	0.335	Steel	\$ 0.06
2183314	Jameco Valuepro	10-32HN	10/32	0.098	0.255	Steel	\$ 0.25
2182485	C&K	780701215	1/4-40	0.352	0.118	Steel	\$ 0.79
578321	C&K	700201201	1/4-40	0.062	0.355	Steel	\$ 0.25
2288111	Jameco Valuepro	38093	4-40	0.066	0.066	Steel	\$ 0.25
40943	Jameco Valuepro	14702	4-40	0.090	0.243	Steel	\$ 0.05
578110	C&K	464900201	10-48	0.047	0.324	Brass	\$ 0.25
2197450	Jameco Valuepro	2-56HES-SS	2-56	0.064	0.183	Stainless Steel	\$ 0.07
38165	Jameco Valuepro	36006	2-56	0.063	0.185	Steel	\$ 0.08
2203231	Dialight	4901-0000-03201	1-27	0.133	1.120	Steel	\$ 0.79
2276839	Amphenol	3/4-20HN	3/4-20	0.156	0.750	Steel	\$ 0.89
2235170	C&K	937C00000	3/4-24	0.125	0.875	Steel	\$ 0.69
2235188	C&K	531300201	3/4-24	0.250	1.000	Steel	\$ 0.89
2230900	Dialight	4901-000-002201	11/16-27	0.095	0.810	Steel	\$ 1.79
740914	TE Connectivity	1-329631-2	1/2-28	0.109	0.623	Steel	\$ 0.49
2235815	Fascomp	1/4-28HN	1/4-28	0.220	0.432	steel	\$ 0.19
2086282	Amphenol	31-5652	1/2-28 UNF	0.109	0.560	Steel	\$ 0.39
578371	C&K	10-137B	15/32-32	0.047	0.219	Brass	\$ 0.39
2235090	Dialight	17/32HN	17/32	0.091	0.624	Steel	\$ 0.35
2235090	Dialight	17/32HN	17/32-32	0.093	0.625	Steel	\$ 0.35