



[Click Here to Request a Large Quantity Quote](#)

ELECTROMECHANICAL HARDWARE WASHERS

Jameco Part#	Manufacturer	Manufacturer Part #	Description	Washer Type	Screw Size	Outside Dia(In.)	Price 1
2094725	Jameco Valuepro	33062	Flat Washer,#2 Zinc Plated Steel Flat Washer	Flat	#2	0.188	\$ 0.05
106826	Jameco Valuepro	149228	Flat Washer #4 Yellow Zinc Plated Steel	Flat	#4	0.281	\$ 0.05
2288119	Jameco Valuepro	149228	Flat Washer,#4 Zinc Finish Machine Screw	Flat	#4	0.276	\$ 0.25
2290607	Jameco Valuepro	#4FWZ	Flat Washer,#4 Zinc-plated Steel	Flat	#4	0.284	\$ 0.11
106833	Jameco Valuepro	960-6	Flat Washer #6 3/8 Zinc Plated Steel	Flat	#6	0.373	\$ 0.06
106842	Jameco Valuepro	960-8-3	Flat Washer, 8 3/8 OD RoHS Zinc Plated Steel (100 Pieces)	Flat	#8	0.375	\$ 0.06
2183381	Switchcraft	P-2061	Flat Washer1/4-32,.02" thick	Flat	1/4-32	0.406	\$ 0.29
2159963	Jameco Valuepro	P-1476-1	Flat Washer 15/32 Nickel Plate .468" ID	Flat	15/32"	0.468	\$ 0.39
2282543	Jameco Valuepro	90183A206	Flat Washer, 3/32" for Blind Rivets Zinc-Plated Steel	Flat	3/32"	0.312	\$ 0.25
2182522	Switchcraft	S1022-1	Flat Washer 3/8"ID x 5/8"OD x 0.02 Thick Nickel Plate	Flat	3/8"	0.625	\$ 0.29
2159971	Arndt	AN960-616L	Flat Washer, .382 ID x .625 OD AN960-616L	Flat	3/8"	0.625	\$ 0.19
2288671	Jameco Valuepro	5/16FW	Flat Washer,5/16 Zinc Plated 0.562"OD 0.334"ID	Flat	5/16"	0.334	\$ 0.25
211131	Jameco Valuepro	149248	Flat Washer #4 Yellow Zinc Plated Steel	Flat	4	0.237	\$ 0.05
2186187	Jameco Valuepro	P3031	Flat Washer 0.65"OD,0.445"ID, 0.02"THK,FOR 7/16-32 NUTS(10)	Flat	7/16-32	0.650	\$ 0.19
42463	Jameco Valuepro	#6LW	Split Lock Washer 6 Zinc Plated Steel Rohs (100 Pieces)	Split Lock	#6	0.240	\$ 0.08
51609	Jameco Valuepro	#8LW2	Split Lock Washer 8 Zinc Plated Steel (100 Pieces)	Split Lock	#8	0.290	\$ 0.09
2183411	Jameco Valuepro	M7LW	Lock Washer,M7 .04" Thick	Split Lock	M7	0.408	\$ 0.19
106789	Jameco Valuepro	33602	Split Lock Washer 2 Zinc Plated Steel (100 Pieces)	Split Lock	#2	0.172	\$ 0.07
40977	Jameco Valuepro	#S4LW	Split Lock Washer 4 .210 OD Zinc Plated Steel Rohs (100 Pieces)	Split Lock	#4	0.210	\$ 0.08
2183234	Jameco Valuepro	M6FW	Flat Washer M6 10mm (.394")OD 6.1mm (.240")ID .13mm (.005")TH	Flat	M6	0.393	\$ 0.15
2182637	Jameco Valuepro	M7FW	Flat Washer M8 12mm (.473")OD 7.1mm (.280")ID .4mm (.016")TH	Flat	M7	0.473	\$ 0.15
2182565	Jameco Valuepro	M8FW	Flat Washer M8 14mm (.5512")OD 8.1mm (.319")ID .4mm (.016")TH	Flat	M8	0.316	\$ 0.15
2182717	Jameco Valuepro	M9FW	Flat Washer M9 14mm (.5512")OD 9.1mm (.358")ID .4mm (.016")TH	Flat	M9	0.551	\$ 0.15
2183251	Jameco Valuepro	M10FW	Flat Washer M10 14.8mm (.586")OD 10.2mm (.400")ID .4mm (.016")TH	Flat	M10	0.586	\$ 0.15
2183306	Jameco Valuepro	M12FW	Flat Washer M8 17.9mm (.705")OD 12.2mm (.480")ID .4mm (.016")TH	Flat	M12	0.705	\$ 0.15
578380	C&K	707200201-VP	15/32-32 Key Lock Washer "O" Style Keyway	Keyway "O"-Style	15/32-32 NS	0.718	\$ 0.35
2182750	Jameco Valuepro	M12KLW	Keyway Washer "O" Style	Keyway "O"-Style	M12 x .75	0.724	\$ 0.29
578347	C&K	700701201	1/4-40 Key Lock Washer "O" Style Keyway	Keyway "O"-Style	1/4-40 UNS	0.468	\$ 0.15
2182493	C&K	757200201	Washer with Keylock	Keyway "D"-Style	1/4-40 UNS	0.468	\$ 0.15
2182590	C&K	465101201	10-48 Locking Ring Washer with O-Style Keyway	Keyway "O"-Style	10-48 UNS	0.468	\$ 0.25
2233861	Jameco Valuepro	M10KLCK	Washer "D"KEYLOCK #M10 & 3/8"HWRD,FOR ROTORY SWITCHES	Keyway "O"-Style	3/8-32 NEF	0.560	\$ 0.25
106850	Jameco Valuepro	4ITLW	Internal Tooth Washer 4 Zinc Plated Steel	Internal Tooth Lock	#4	0.258	\$ 0.03
2099745	Jameco Valuepro	TL#4	#4 Stud Terminal Lug Washer 0.465" Length	Terminal Lug	#4	0.230	\$ 0.19
2100208	Jameco Valuepro	TL-STUD4	#4 Stud Terminal Lug Washer Tin 0.470" Length	Terminal Lug	#4	0.260	\$ 0.19
106868	Jameco Valuepro	33707	Internal Tooth Washer 6 Zinc Plated Steel	Internal Tooth Lock	#6	0.277	\$ 0.04
1581572	Keystone Electronics	904	#6 Stud Lockwasher Terminal Lug 0.865 Inch Length	Lockwasher Terminal Lug	#6	0.312	\$ 0.19
106877	Jameco Valuepro	#81TLW	Internal Tooth Washer 8 Zinc Plated Steel Rohs (100 Pieces)	Internal Tooth Lock	#8	0.323	\$ 0.04
2203240	Dialight	8101-0000-03201	Internal Tooth Lockwasher 1.01" ID	Internal Tooth Lock	1.01"	1.390	\$ 0.39
578339	C&K	700303202	Internal Tooth Lock Washer for 1/4-40 sized screws,Nickel Plate	Internal Tooth Lock	1/4/-40	0.402	\$ 0.19



[Click Here to Request a Large Quantity Quote](#)

ELECTROMECHANICAL HARDWARE WASHERS

Jameco Part#	Manufacturer	Manufacturer Part #	Description	Washer Type	Screw Size	Outside Dia(In.)	Price 1
2182531	C&K	465200202	Internal Tooth Lock Washer.10-32 and 10-48,.018"Thick	Internal Tooth Lock	10/32	0.310	\$ 0.25
2230918	Dialight	8101-000-002201	Internal Tooth Washer, Lock ,11/16"ID,0.955"OD x 0.069"Thick	Internal Tooth Lock	11/16"	0.955	\$ 0.39
2182557	C&K	700302202	Internal Tooth Lock Washer 15/32-32	Internal Tooth Lock	15/32"	0.593	\$ 0.29
2235102	Dialight	17/32ITW	Internal Tooth Lock Washer 17/32,FOR SWITCHES AND LAMP HOLDER	Internal Tooth Lock	17/32"	0.700	\$ 0.29
2276847	Amphenol	3/4-ITLW	Internal Toothed Washer 3/4"	Internal Tooth Lock	3/4"	1.050	\$ 0.49
2159980	Jameco Valuepro	3/8-32HN	Internal Tooth Washer, 3/8-32,Nickel Plaing	Internal Tooth Lock	3/8	0.675	\$ 0.25
2185791	Arndt	3/8"ITW	Internal Tooth Lock Washer 3/8 32 Screws	Internal Tooth Lock	3/8"	0.500	\$ 0.25
101531	Amphenol	000-5579-NA	Internal Tooth Washer 3/8 Inch Internal Diameter	Internal Tooth Lock	3/8"	0.500	\$ 0.19
2201527	Jameco Valuepro	LW-11001-R	Internal Tooth Washer 5/16" ,.020 Thick	Internal Tooth Lock	5/16"	0.428	\$ 0.25
2203274	Dialight	9/16ITW	Internal Tooth Lockwasher,9/16 Inch ID	Internal Tooth Lock	9/16"	0.772	\$ 0.25
2089803	Amphenol	31-5653	Internal Tooth Lockwasher,1/2 Inch ID	Internal Tooth Lock	1/2"	0.625	\$ 0.25
527646	TE Connectivity	1-329632-2	Internal Tooth Lockwasher,1/2 Inch ID	Internal Tooth Lock	1/2"	0.625	\$ 0.35
2227161	Jameco Valuepro	M7ITW	Internal Tooth Washer, M7.03" Thick	Internal Tooth Lock	M7	0.470	\$ 0.17
2182741	Jameco Valuepro	M12ITW	Internal Tooth Washer, 12mm,Zinc Plating	Internal Tooth Lock	M12	0.629	\$ 0.25