



[Click Here to Request a Large Quantity Quote](#)

ELECTROMECHANICAL MOTORS GEARHEAD

Jameco Part#	Manufacturer	Manufacturer Part #	Rated Voltage (VDC)	Speed (RPM)	Current (mA)	Torque (g-cm)	Gear Ratio	Gear Case Size Dia x Length (")	Motor Size Dia x Length (")	Shaft Size Dia x Length (")	Price 1
2260834	Dagu HiTech Electronic	DG01D-W/LEADS	4.5	90	190.0	800	48-1	.88 x 1.9	.78 x .60	.08 x .38	\$ 9.95
2150432	Dagu HiTech Electronic	DG01D	4.5	90	190.0	800	47-1	.88 x 1.9	.78 x .60	.08 x .05	\$ 7.95
2146505	Jameco Reliapro	B32-6V3.1RPM	6	3	90.0	7350	340-1	1.90 x 0.41	1.3 x 0.9	0.28 x 0.87	\$ 14.95
253307	Jameco Reliapro	B32-6V9RPM	6	3	90.0	7350	340-1	1.90 x 0.41	1.3 x 0.9	0.30 x 0.70	\$ 14.95
400995	Solarbotics	GM8	6	78	57.0	5500	143-1	2.1 x .91	.78 x .55	.08 x .05	\$ 5.95
2150491	Dagu HiTech Electronic	RS003A	6	133	350.0	8800	75-1	.98 x .90	.97 x 1.2	.16 x .38	\$ 12.95
2150504	Dagu HiTech Electronic	RS003B	6	295	350.0	4000	34-1	.98 x .93	.96 x 1.2	.16 x .38	\$ 12.95
155013	Jameco Reliapro	HN-GH121926Y-R-M	12	2	250.0	6000	3000-1	1.30 x 0.90	1.5 x 1.1	0.23 x 0.90	\$ 24.95
155821	Jameco Reliapro	GH12-1830Y-P-R	12	5	220.0	4500	1000-1	1.40 x 0.90	1.3 x 1.0	0.23 x 0.90	\$ 24.95
155822	Jameco Reliapro	GH12-1830Y-P-R-M	12	5	250.0	4500	1000-	1.30 x 0.90	1.5 x 1.0	0.23 x 0.90	\$ 21.95
167039	Jameco Reliapro	HN-27GB,HNGH12-0953Y-R	12	9	90.0	1200	188-1	1.10 x 1.00	1.0 x 0.9	0.16 x 0.60	\$ 17.95
153438	Jameco Reliapro	GH27GM,HN-GH12-1045Y-R	12	12	90.0	800	200-1	1.10 x 0.60	0.9 x 1.0	0.16 x 0.70	\$ 15.95
155839	Jameco Reliapro	GH12-1641T-L-R	12	20	250.0	3000	270-	1.40 x 0.80	1.3 x 1.0	0.23 x 0.90	\$ 25.95
253534	Jameco Reliapro	38-010	12	24	97.0	7500	250-1	1.46 x 1.00	1.3 x 0.9	0.24 x 0.50	\$ 16.95
253518	Jameco Reliapro	38-008	12	40	87.5	4800	150-1	1.46 x 1.00	1.3 x 0.9	0.24 x 0.50	\$ 16.95
253518	Jameco Reliapro	38-008	12	40	87.5	4800	150-1	1.46 x 1.00	1.3 x 0.9	0.24 x 0.50	\$ 16.95
152911	Jameco Reliapro	HNGH12-1926Y,GH35GMA-R	12	40	172.0	2370	100-1	1.40 x 0.60	1.3 x 1.2	0.24 x 0.90	\$ 24.95
151442	Jameco Reliapro	HN-GH12-1632T-R-M	12	54	275.0	2200	100-1	1.30 x 0.90	1.5 x 0.7	0.23 x 0.30	\$ 23.95
253500	Jameco Reliapro	38-007	12	60	82.0	3200	100-1	1.46 x 0.70	1.3 x 0.9	0.24 x 0.50	\$ 15.95
2238101	Pololu	2827	12	80	250.0	18000	131-1	2.7 x 1.45	1.3 x .63	.24 x .60 (flat side)	\$ 34.95
253489	Jameco Reliapro	38-005	12	110	76.0	1300	56-1	1.46 x 0.70	1.3 x 0.9	0.24 x 0.50	\$ 14.95
253471	Jameco Reliapro	38-004	12	120	74.0	1100	50-1	1.46 x 0.70	1.3 x 0.9	0.24 x 0.50	\$ 15.95
161382	Jameco Reliapro	HN-GH12-1634T-R	12	145	293.0	850	30-1	1.40 x 0.70	1.3 x 1.0	0.23 x 0.90	\$ 25.95
164786	Jameco Reliapro	HN-GH12-1640Y,GH35GMB-R	12	220	120.0	180	1000-1	1.40 x 0.60	1.3 x 1.1	0.23 x 0.90	\$ 24.95
253446	Jameco Reliapro	38-001	12	600	61.8	350	10-1	1.46 x 0.70	1.3 x 0.9	0.20 x 0.50	\$ 16.95