



[Click Here to Request a Large Quantity Quote](#)

## ROCKER SWITCHES

Jameco PN	Manufacturer	Manufacturer Part #	Pins	Contact Form	Function ( ) Momentary	Current (A) @ 125VAC	Actuator Type	Color-Body	Color - Actuator/Cap	Termination Style	Length (in.)	Width (in.)	Depth (in.)	Price1
2276767	TE Connectivity	2-1571076-1	2	SPST	OFF-(ON)	16	Rocker	Black	Black	0.187" Quick Connect	0.845	0.584	0.444	\$ 1.95
2208198	Jameco Valuepro	RS-001G-A-BB-4	2	SPST	ON-OFF	6	Rocker	Black	Black	0.15" Quick Connect	0.59	0.41	0.75	\$ 0.75
2268199	Jameco Valuepro	R13-213A-03-BR	2	SPST	ON-OFF	6	Rocker	Black	Red	Solder Lug	0.799	0.566	0.374	\$ 1.49
621270	GC Electronics	35-1851-BU	2	SPST	ON-OFF	6	Rocker	Black	Black	Solder	2.51	0.82	1.21	\$ 3.95
2269791	Jameco Valuepro	112-R13-241A-05	2	SPST	ON-OFF	6	Round Rocker	Black	Black	Solder Lug	0.944	0.807	0.551	\$ 1.59
2267327	Mountain Switch	103-7062-EV	2	SPST	ON-OFF	8	Illuminated Rocker	Black	Red	0.187" Quick Connect	1.73	0.475	0.484	\$ 1.09
2267319	Mountain Switch	103-7061-EV	2	SPST	ON-OFF	8	Rocker	Black	Black	0.187" Quick Connect	1.73	0.475	0.484	\$ 0.89
316451	Jameco Valuepro	R13-243A-02	2	SPST	ON-OFF	8	Rocker	Black	Black	0.187" Quick Connect	0.83	0.374	0.854	\$ 0.99
2267303	Mountain Switch	103-7059-EVX	2	SPST	ON-OFF	8	Rocker	Black	Black with Raised Dot	Solder Lug	1.61	0.716	0.594	\$ 1.09
2276471	Marquardt Switch	1801.1908	2	SPST	ON-OFF	8	Rocker	Black	Black	0.187" Quick Connect	0.826	0.59	0.46	\$ 1.25
2267311	Mountain Switch	103-7060-EVX	2	SPST	ON-OFF	8	Rocker	Black	Black	Solder Lug	1.61	0.512	0.594	\$ 1.49
316048	Jameco Valuepro	R13-66B-G-02	2	SPST	ON-OFF	9	Illuminated Rocker	Black	Green	0.187" Quick Connect	1.093	0.512	0.594	\$ 1.49
2268127	Jameco Valuepro	R13-228B-05-BRR-N1	2	SPST	ON-OFF	10	Illuminated Rocker	Black	Red	Solder Lug	1.133	0.708	0.66	\$ 0.99
316128	Jameco Valuepro	R13-73B-R-02	2	SPST	ON-OFF	10	Illuminated Rocker	Black	Red	0.187" Quick Connect	0.83	0.59	0.866	\$ 1.49
2269847	Jameco Valuepro	R13-66B2S-02	2	SPST	ON-OFF	10	Illuminated Rocker	Black	Black with Green Neon	0.187" Quick Connect	0.826	0.59	0.464	\$ 1.49
2267183	Mountain Switch	103-7036-EV	2	SPST	ON-OFF	10	Illuminated Rocker	Black	Red	0.25" Quick Connect	1.18	0.551	0.551	\$ 1.59
2268015	Mountain Switch	R13-228B-05-BGG-N1	2	SPST	ON-OFF	10	Illuminated Rocker	Black	Green	Solder Lug	1.14	0.724	0.364	\$ 1.59
2269767	Jameco Valuepro	112-R13-73B-02-R	2	SPST	ON-OFF	10	Illuminated Rocker	Black	Red	0.187" Quick Connect	0.826	0.59	0.464	\$ 1.59
2269743	Jameco Valuepro	112-R13-73B-02-Y	2	SPST	ON-OFF	10	Illuminated Rocker	Black	Amber	0.187" Quick Connect	0.826	0.59	0.464	\$ 1.59
2268343	Jameco Valuepro	R13-66APA-02-BB	2	SPST	ON-OFF	10	Paddle	Black	Black	0.187" Quick Connect	0.826	0.59	0.464	\$ 1.25
2276759	C&K	8941K469	2	SPST	ON-OFF	10	Paddle	Black	Red	0.25" spade tab	1.93	0.745	1.185	\$ 1.95
316014	Jameco Valuepro	R13-66A-B-02-R	2	SPST	ON-OFF	10	Rocker	Black	Black	0.187" Quick Connect	0.826	0.59	0.54	\$ 0.99
316022	Jameco Valuepro	R13-66A-R-02-R	2	SPST	ON-OFF	10	Rocker	Black	Red	0.187" Quick Connect	0.826	0.59	0.54	\$ 0.99
2218839	Jameco Benchpro	RS-105A-BB-3-UL	2	SPST	ON-OFF	10	Rocker	Black	Black	0.187" Quick Connect	0.905	0.905	0.7	\$ 0.99
2234345	Jameco Valuepro	HM-RS-03	2	SPST	ON-OFF	10	Rocker	Black	Black	5.5" Wires	0.824	0.588	0.425	\$ 1.49
2267535	Mountain Switch	103-R13-211A-02-EV	2	SPST	ON-OFF	10	Rocker	Black	Black	0.187" Quick Connect	0.866	0.866	0.744	\$ 1.49
2269799	Jameco Valuepro	R13-89A-01	2	SPST	ON-OFF	10	Rocker	Black	Black	0.25" Quick Connect	1.18	0.551	0.551	\$ 1.59
2267199	Mountain Switch	103-7038-EV	2	SPST	ON-OFF	10	Rocker	Black	Black	0.25" Quick Connect	1.18	0.551	0.551	\$ 1.59
2277751	Carling Technologies	RSCA211-RB-B-E-N	2	SPST	ON-OFF	10	Rocker	Black	Black	0.25" Quick Connect	1.24	0.67	0.71	\$ 1.75
2276495	Apem Components	MR110-C5N-BRNWC	2	SPST	ON-OFF	10	Rocker	Black	Black	0.189 Quick Connect	0.83	0.59	0.56	\$ 1.75
2276487	Omron	A8L-11-12N1	2	SPST	ON-OFF	10	Rocker	Black	Black	PC terminal	0.83	0.59	0.65	\$ 1.75
577221	Cherry	RRA22H3BBBNN	2	SPST	ON-OFF	10	Round Rocker	Black	Black	0.187" Quick Connect	0.906	0.783	0.717	\$ 1.49
2267375	Mountain Switch	103-7072-EV	2	SPST	ON-OFF	15	Illuminated Rocker	Black	Green	0.25" Quick Connect	1.25	0.677	0.886	\$ 1.25
2268223	Mountain Switch	103-R13-72A-EV	2	SPST	ON-OFF	15	Rocker	Black	Black	0.25" Quick Connect	1.26	0.677	0.878	\$ 1.09
2267519	Mountain Switch	103-R13-112LP-02Y-E	2	SPST	ON-OFF	16	Illuminated Paddle	Black	Black with Yellow LED	0.187" Quick Connect + Solder	0.91	0.91	0.571	\$ 2.49
2267271	Mountain Switch	103-7052-EV	2	SPST	ON-OFF	16	Illuminated Rocker	Black	Orange	0.187" Quick Connect	0.905	0.905	0.327	\$ 0.79
2267279	Mountain Switch	103-7053-EV	2	SPST	ON-OFF	16	Illuminated Rocker	Black	Red	0.187" Quick Connect	0.905	0.905	0.327	\$ 0.95
2267287	Mountain Switch	103-7055-EV	2	SPST	ON-OFF	16	Illuminated Rocker	Black	Black with Green LED	0.187" Quick Connect	0.905	0.905	0.327	\$ 1.09
2267295	Mountain Switch	103-7056-EV	2	SPST	ON-OFF	16	Illuminated Rocker	Black	Black with Red LED	0.187" Quick Connect	0.905	0.905	0.327	\$ 1.25
2267359	Mountain Switch	103-7065-EV	2	SPST	ON-OFF	16	Illuminated Rocker	Black	Red	0.25" Quick Connect	1.637	1.005	0.63	\$ 1.25
2267351	Mountain Switch	103-7064-EV	2	SPST	ON-OFF	16	Illuminated Rocker	Black	Red	0.25" Quick Connect	1.637	1.005	0.63	\$ 1.25
2267447	Mountain Switch	103-7082-EV	2	SPST	ON-OFF	16	Illuminated Rocker	Black	Red	0.25" Quick Connect	1.38	0.551	0.709	\$ 1.59
2267463	Mountain Switch	103-7084-EV	2	SPST	ON-OFF	16	Illuminated Rocker	Black	Green	0.25" Quick Connect	1.38	0.551	0.709	\$ 1.59
2268207	Mountain Switch	103-R13-205L-01R-EV	2	SPST	ON-OFF	16	Illuminated Rocker	Black	Black with Red LED	0.25" Quick Connect	1.24	0.728	0.767	\$ 1.59
2267455	Mountain Switch	103-7083-EV	2	SPST	ON-OFF	16	Illuminated Rocker	Black	Yellow	0.25" Quick Connect	1.38	0.551	0.709	\$ 1.59
2267487	Mountain Switch	103-R13-205B-01R-EV	2	SPST	ON-OFF	16	Illuminated Rocker	Black	Red	0.25" Quick Connect	1.24	0.728	0.823	\$ 1.59
2269823	Jameco Valuepro	R13-91B-01-BR	2	SPST	ON-OFF	16	Illuminated Rocker	Black	Red	0.25" Quick Connect	1.3	0.551	0.709	\$ 1.59
2267247	Mountain Switch	103-7049-EV	2	SPST	ON-OFF	16	Illuminated Rocker	Black	Orange	0.25" Quick Connect	1.3	0.551	0.709	\$ 1.59
2267559	Mountain Switch	103-R13-238B-01G-EV	2	SPST	ON-OFF	16	Illuminated Rocker	Black	Green	0.25" Quick Connect	1.24	0.728	0.705	\$ 1.59
2267567	Mountain Switch	103-R13-238B-01R-EV	2	SPST	ON-OFF	16	Illuminated Rocker	Black	Red	0.25" Quick Connect	1.24	0.728	0.705	\$ 1.59
2269735	Jameco Valuepro	R13-91B-01-BG	2	SPST	ON-OFF	16	Illuminated Rocker	Black	Green	0.25" Quick Connect	1.3	0.551	0.709	\$ 1.59
2267231	Mountain Switch	103-7046-EV	2	SPST	ON-OFF	16	Illuminated Rocker	Black	Green	0.25" Quick Connect	1.3	0.551	0.709	\$ 1.59
2267999	Mountain Switch	103-R13-205L-01G-EV	2	SPST	ON-OFF	16	Illuminated Rocker	Black	Black with Green LED	0.25" Quick Connect	1.24	1.15	0.823	\$ 1.65



[Click Here to Request a Large Quantity Quote](#)

## ROCKER SWITCHES

Jameco PN	Manufacturer	Manufacturer Part #	Pins	Contact Form	Function ( ) Momentary	Current (A) @ 125VAC	Actuator Type	Color- Body	Color - Actuator/Cap	Termination Style	Length (in.)	Width (in.)	Depth (in.)	Price1
2267255	Mountain Switch	103-7050-EV	2	SPST	ON-OFF	16	Illuminated Rocker	Black	Red	0.25" Quick Connect	1.3	0.551	0.709	\$ 1.65
2268023	Mountain Switch	103-7047-EV	2	SPST	ON-OFF	16	Illuminated Rocker	Black	Red	0.25" Quick Connect	1.3	0.551	0.709	\$ 1.95
2267239	Mountain Switch	103-7048-EV	2	SPST	ON-OFF	16	Illuminated Rocker	Black	Green	0.25" Quick Connect	1.3	0.551	0.709	\$ 2.49
2267399	Mountain Switch	103-7075-EV	2	SPST	ON-OFF	16	Illuminated Rocker	Black	Red	0.25" Quick Connect	1.31	0.988	0.709	\$ 2.49
2267407	Mountain Switch	103-7076-EV	2	SPST	ON-OFF	16	Illuminated Rocker	Black	Yellow & Red	0.25" Quick Connect	1.31	0.988	0.709	\$ 3.29
2201914	Clarostat/Honeywell	028-01011-00	2	SPST	ON-OFF	16	Rocker	Black	Black	0.25" Quick Connect	1.18	0.547	0.585	\$ 0.55
2267263	Mountain Switch	103-7051-EV	2	SPST	ON-OFF	16	Rocker	Black	Black	0.187" Quick Connect	0.905	0.905	0.327	\$ 0.55
2267471	Mountain Switch	103-R13-91A-EV	2	SPST	ON-OFF	16	Rocker	Black	Black	0.25" Quick Connect	1.31	0.55	0.709	\$ 1.05
2268007	Mountain Switch	103-7081-EV	2	SPST	ON-OFF	16	Rocker	Black	Black	0.25" Quick Connect	1.38	0.551	0.709	\$ 1.09
2267343	Mountain Switch	103-7063-EVX	2	SPST	ON-OFF	16	Rocker	Black	Black	0.25" Quick Connect	1.637	1.005	0.63	\$ 1.09
2231355	Bulgin	R13-135A-02	2	SPST	ON-OFF	16	Rocker	Black	Black	0.187" Quick Connect	0.57	0.91	0.32	\$ 1.49
2267527	Mountain Switch	103-R13-205A2-01-EV	2	SPST	ON-OFF	16	Rocker	Black	Black/Red	0.25" Quick Connect	1.24	0.728	0.823	\$ 1.59
2267551	Mountain Switch	103-R13-238A-01W-EV	2	SPST	ON-OFF	16	Rocker	Black	White	0.25" Quick Connect	1.24	0.728	0.705	\$ 1.59
2267207	Mountain Switch	103-7043-EVX	2	SPST	ON-OFF	16	Rocker	Black	Black	0.25" Quick Connect	1.71	0.964	1.53	\$ 2.49
2276503	ZF	CRE22F2FBBNE	2	SPST	ON-OFF	20	Rocker	Black	Black	0.25" Quick Connect	1.24	0.645	0.715	\$ 1.25
2269831	Jameco Valuepro	R13-238A-01	2	SPST	ON-OFF	20	Rocker	Black	Black	0.25" Quick Connect	1.24	0.728	0.767	\$ 1.59
2268039	Jameco Valuepro	R13-66L-02-BBGG-L1	2	SPST	ON-ON	16	Illuminated Rocker	Black	Black with Green LED	Solder Lug	0.826	0.59	0.464	\$ 1.59
2290511	Bulgin	H8601VBBR	2	SPST-NO	OFF-(ON)	16	Curved Rocker	Black	Red	0.187" Quick Connect	0.83	0.59	0.76	\$ 1.95
2287175	Eaton	SMKMLLFAXXXXXX	10	SPDT	(ON)-NONE-ON	12 @ 24VDC	Rocker	Black	Illuminated Amber	Blade Contact	2.05	0.42	1.42	\$ 14.95
2287167	Eaton	SMEMKXDGXXXXXX	10	SPDT	(ON)-NONE-ON	12 @ 24VDC	Rocker	Black	Illuminated Green	Blade Contact	2.05	0.42	1.42	\$ 14.95
2180973	TE Connectivity	A105J1AV2B0	3	SPDT	(ON)-OFF-(ON)	5	Rocker	Red	Black	PC Pin	0.662	0.359	0.83	\$ 0.75
2267055	Mountain Switch	103-7010-EVX	3	SPDT	(ON)-OFF-(ON)	5	Rocker	Red	Black	PC terminal	1.1	0.37	0.4	\$ 2.49
2267111	Mountain Switch	103-7018-EVX	3	SPDT	(ON)-OFF-(ON)	5	Rocker	Red	Black	PC terminal	0.666	0.371	0.533	\$ 2.49
2181722	C&K	7105J1V3QE2	3	SPDT	(ON)-OFF-(ON)	5	Rocker	Red	Black	PC Pin	0.765	0.362	0.44	\$ 2.95
2268047	Mountain Switch	R13-66IPA-02BB	3	SPDT	(ON)-OFF-(ON)	16	Paddle	Black	Black	0.187" Quick Connect	0.826	0.59	0.464	\$ 1.25
617473	GC Electronics	35-695-BU	3	SPDT	(ON)-OFF-(ON)	16	Rocker	Black	Black	0.25" Quick Connect	1.236	0.659	0.6	\$ 3.95
2267039	Mountain Switch	103-7008-EVX	2	SPDT	ON-(ON)	5	Paddle	Red	Black	Solder Lug	1.16	0.365	0.376	\$ 1.59
2267095	Mountain Switch	103-7016-EVX	2	SPDT	ON-(ON)	5	Paddle	Red	Black	Solder Lug	1.75	0.357	0.83	\$ 1.95
2267087	Mountain Switch	103-7015-EVX	2	SPDT	ON-(ON)	5	Rocker	Red	Black	Solder Lug	1.166	0.373	0.415	\$ 2.49
2285503	C&K	7101J1ASE2	2	SPDT	ON-NONE-ON	4	Rocker	Red	Black	PC Terminal	0.5	0.275	0.37	\$ 4.95
2279159	Jameco Valuepro	RLS-102-A1	3	SPDT	ON-NONE-ON	6	Rocker	Blue	Black	Solder Lug	0.52	0.31	0.43	\$ 1.95
2287151	Eaton	SAEMKXDGXXXXXX	10	SPDT	ON-NONE-ON	12 @ 24VDC	Rocker	Black	Illuminated Green	Blade Contact	2.05	0.42	1.42	\$ 10.95
2172738	Jameco Valuepro	1901	2	SPDT	ON-OFF	6	Rocker	Black	Black	PC Pin	0.829	0.377	0.611	\$ 0.65
2267167	Mountain Switch	103-7032-EVX	3	SPDT	ON-OFF-(ON)	0.02	Rocker	White	Black	SMD	0.741	0.582	0.372	\$ 1.59
2277695	Apem Components	SY238CD6X-1179	3	SPDT	ON-OFF-(ON)	4	Rocker	Black	Black	PC terminal	0.633	0.436	0.56	\$ 2.95
2267063	Mountain Switch	103-7011-EVX	3	SPDT	ON-OFF-(ON)	5	Paddle	Red	Black	PC terminal RA	1.74	0.365	1.3	\$ 1.95
2267119	Mountain Switch	103-7019-EVX	3	SPDT	ON-OFF-(ON)	5	Paddle	Red	Black	Solder Lug	1.16	0.365	0.428	\$ 2.49
2277759	C&K	E107J2V31KE2	3	SPDT	ON-OFF-(ON)	7.5	Paddle	Red	Black	PC terminal	1.156	0.345	0.408	\$ 3.95
2268351	Jameco Valuepro	R13-66HPA-02-BB	2	SPDT	ON-OFF-(ON)	16	Paddle	Black	Black	0.187" Quick Connect	0.826	0.59	0.464	\$ 1.25
2267175	Mountain Switch	103-7034-EVX	3	SPDT	ON-OFF-ON	0.02	Rocker	White	Black	SMD	0.741	0.582	0.372	\$ 1.59
2182418	Dialight	570-12/574-1212-0104-007	3	SPDT	ON-OFF-ON	0.05	Rocker	Blue	Black	PC Pin	0.627	0.383	0.438	\$ 0.39
2267159	Mountain Switch	103-7027-EVX	3	SPDT	ON-OFF-ON	3	Rocker	Red	Black	PC terminal RA	0.736	0.32	0.357	\$ 3.95
2267047	Mountain Switch	103-7009-EVX	3	SPDT	ON-OFF-ON	5	Paddle	Red	Black	PC terminal	1.3	0.365	0.4	\$ 1.95
2276863	Eledis	3A11-BFST-SE22	2	SPDT	ON-OFF-ON	5	Rocker	Red	Black	Solder Lug	0.78	0.622	0.667	\$ 0.99
2268159	Jameco Valuepro	R13-241D05BB	2	SPDT	ON-OFF-ON	6	Rocker	Black	Black	Solder Lug	0.944	0.807	0.551	\$ 1.95
2267543	Mountain Switch	103-R13-211D-02-EV	2	SPDT	ON-OFF-ON	10	Rocker	Black	Black	0.187" Quick Connect	0.866	0.866	0.744	\$ 1.25
2267367	Mountain Switch	103-7066-EVX	3	SPDT	ON-OFF-ON	12	Illuminated Rocker	Black	Red	0.25" Quick Connect	1.81	0.976	1.551	\$ 1.25
2267495	Mountain Switch	103-R13-205D3-01-EV	3	SPDT	ON-OFF-ON	16	Rocker	Black	Black	0.25" Quick Connect	1.24	0.728	0.823	\$ 0.89
316072	Jameco Valuepro	R13-66D-02	3	SPDT	ON-OFF-ON	16	Rocker	Black	Black	0.187" Quick Connect	0.826	0.59	0.464	\$ 1.09
2268215	Mountain Switch	103-R13-238D-01W-EV	2	SPDT	ON-OFF-ON	16	Rocker	Black	White	0.25" Quick Connect	1.24	0.728	0.767	\$ 1.59
2267591	Mountain Switch	103-R13-238D-01B-EV	3	SPDT	ON-OFF-ON	16	Rocker	Black	Black	0.25" Quick Connect	1.24	0.728	0.705	\$ 1.59
1945241	Illinois Tool Works	163-009-029	2	SPDT	ON-OFF-ON	16	Rocker	Black	Black	0.25" Quick Connect	1.185	0.55	0.59	\$ 1.75
2287135	Eaton	SDKMKKFGXXGXXXX	10	SPDT	ON-OFF-ON	12 @ 24VDC	Rocker	Black	Illuminated Green	Blade Contact	2.05	0.42	1.42	\$ 12.95



[Click Here to Request a Large Quantity Quote](#)

## ROCKER SWITCHES

Jameco PN	Manufacturer	Manufacturer Part #	Pins	Contact Form	Function ( ) Momentary	Current (A) @ 125VAC	Actuator Type	Color-Body	Color - Actuator/Cap	Termination Style	Length (in.)	Width (in.)	Depth (in.)	Price1
2287159	Eaton	SDKMLLFAXXAXXXX	10	SPDT	ON-OFF-ON	12 @ 24VDC	Rocker	Black	Illuminated Amber	Blade Contact	2.05	0.42	1.42	\$ 19.95
2181255	C&K	7101J1V6BE2	2	SPDT	ON-ON	0.02	Rocker	Red	Black	PC Pin	0.765	0.362	0.44	\$ 2.49
2267079	Mountain Switch	103-7014-EVX	2	SPDT	ON-ON	5	Paddle	Red	Black	PC terminal RA	1.425	0.365	0.518	\$ 3.29
2267071	Mountain Switch	103-7013-EVX	2	SPDT	ON-ON	5	Rocker	Red	Black	Solder Lug	1.168	0.373	0.475	\$ 1.75
2267031	Mountain Switch	103-7005-EVX	2	SPDT	ON-ON	5	Rocker	Red	Black	Solder Lug	1.16	0.365	0.376	\$ 1.95
2269815	Jameco Valuepro	R13-213C-03-B	2	SPDT	ON-ON	6	Rocker	Black	Black	0.110" Quick Connect	0.799	0.566	0.374	\$ 1.25
2178566	CW Industries	GRS-4012-0050	2	SPDT	ON-ON	8	Rocker	Black	Red	0.187" Quick Connect	0.823	0.59	0.8	\$ 1.75
2269783	Jameco Valuepro	112-R13-136C-05-B	2	SPDT	ON-ON	10	Rocker	Black	Black	Solder Lug	1.18	0.787	0.44	\$ 1.25
2267191	Mountain Switch	103-7037-EV	2	SPDT	ON-ON	10	Rocker	Black	Red	0.25" Quick Connect	1.18	0.551	0.551	\$ 1.59
2268303	Jameco Valuepro	R13-136C-05-BB	2	SPDT	ON-ON	10	Rocker	Black	Black	Solder Lug	1.18	0.787	0.44	\$ 1.75
2268319	Jameco Valuepro	R13-136C-05-BR	2	SPDT	ON-ON	10	Rocker	Black	Red	Solder Lug	1.18	0.787	0.44	\$ 1.75
2268151	Mountain Switch	R13-228C-05-BB	2	SPDT	ON-ON	10	Rocker	Black	Black	Solder Lug	1.133	0.708	0.66	\$ 2.49
2280583	C&K	C121J13S205QF	2	SPDT	ON-ON	15	Rocker	Black	Black	0.25" Quick Conenct	0.82	0.68	0.375	\$ 3.95
2267391	Mountain Switch	103-7074-EVX	2	SPDT	ON-ON	16	Illuminated Rocker	Black	Yellow	0.25" Quick Connect	1.31	0.988	0.709	\$ 2.49
2276511	C&K	CR101J12S215QF	2	SPDT	ON-ON	16	Rocker	Black	Black	0.187" Quick Connect	0.78	0.78	0.571	\$ 1.39
2268183	Mountain Switch	103-R13-205C3-01-EV	2	SPDT	ON-ON	16	Rocker	Black	Black	0.25" Quick Connect	1.24	0.728	0.767	\$ 1.49
2267671	Mountain Switch	103T13238VO/WEV	2	SPDT	ON-ON	16	Rocker	Black	White	0.25" Quick Connect	1.24	0.728	0.767	\$ 1.59
2267623	Mountain Switch	103-R13-244A-02-EV	2	SPDT	ON-ON	16	Rocker	Black	Black	0.25" Quick Connect	0.925	0.925	0.622	\$ 1.59
2267575	Mountain Switch	103-R13-238C-01B-EV	2	SPDT	ON-ON	16	Rocker	Black	Black	0.25" Quick Connect	1.24	0.728	0.705	\$ 1.59
2267583	Mountain Switch	103-R13-238C-01W-EV	2	SPDT	ON-ON	16	Rocker	Black	White	0.25" Quick Connect	1.24	0.728	0.705	\$ 1.59
2267479	Mountain Switch	103-R13-135C-02-EV	2	SPDT	ON-ON	16	Rocker	Black	Black	0.25" Quick Connect	0.906	0.906	0.571	\$ 1.75
2267383	Mountain Switch	103-7073-EV	2	SPDT	ON-ON	16	Rocker	Black	Black	0.25" Quick Connect	1.31	0.988	0.709	\$ 2.49
2286103	C&K	E101J2V21BE9	3	SPDT	ON-ON	0.4 @ 20	Rocker	Red	Gray	PC Pins	1.15	0.345	0.408	\$ 6.95
2287119	Eaton	SM4MKKFGXGXGXXX	10	DPST	ON-NONE-(ON)	12 @ 24VDC	Rocker	Black	Illuminated Green	Blade Contact	2.05	0.42	1.42	\$ 14.95
2267647	Mountain Switch	103-R13-245B-02G-EV	2	DPST	ON-OFF	8	Illuminated Rocker	Black	Green	0.187" Quick Connect	1.18	1.18	0.512	\$ 1.49
2267655	Mountain Switch	103-R13-245B-02R-EV	2	DPST	ON-OFF	8	Illuminated Rocker	Black	Red	0.187" Quick Connect	1.18	1.18	0.512	\$ 1.49
2267639	Mountain Switch	103-R13-245A-02-EV	2	DPST	ON-OFF	8	Rocker	Black	Black	0.187" Quick Connect	1.18	1.18	0.512	\$ 1.09
316153	Jameco Valuepro	R13-73C-R-02-R	2	DPST	ON-OFF	10	Illuminated Rocker	Black	Red	0.187" Quick Connect	0.83	0.59	0.866	\$ 1.75
2269751	Jameco Valuepro	112-R13-73C-02-R	2	DPST	ON-OFF	10	Illuminated Rocker	Black	Red	0.187" Quick Connect	0.826	0.59	0.464	\$ 1.95
2269759	Jameco Valuepro	112-R13-73C-02-Y	2	DPST	ON-OFF	10	Illuminated Rocker	Black	Amber	0.187" Quick Connect	0.826	0.59	0.464	\$ 1.95
2181271	Otto	K2ABHLCADA	2	DPST	ON-OFF	10	Illuminated Rocker	Black	Black with Green LED	0.16" Quick Connect	0.65	1.06	1.05	\$ 12.95
2158522	Jameco Valuepro	GP1231100M00	2	DPST	ON-OFF	10	Rocker	Black	Black	0.25" Quick Connect	0.827	0.59	0.5	\$ 1.49
2093626	Marquardt Switch	1858.0103	4	DPST	ON-OFF	10	Rocker	Black	Black	Solder Lug	0.83	0.59	1.06	\$ 1.95
316111	Jameco Valuepro	R13-73A2-B-02-R	2	DPST	ON-OFF	12	Rocker	Black	Black	0.187" Quick Connect	0.83	0.594	0.866	\$ 1.75
2267415	Mountain Switch	103-7077-EV	2	DPST	ON-OFF	16	Illuminated Rocker	Black	Red	0.25" Quick Connect	1.22	1.18	1.16	\$ 1.59
2267631	Mountain Switch	103-R13-244B-02R-EV	2	DPST	ON-OFF	16	Illuminated Rocker	Black	Red	0.187" Quick Connect	0.925	0.925	0.622	\$ 1.59
2267607	Mountain Switch	103-R13-240B-01R-EV	2	DPST	ON-OFF	16	Illuminated Rocker	Black	Red	0.25" Quick Connect	1.24	1.15	0.823	\$ 1.95
2267503	Mountain Switch	103-R13-240B-01G-E	2	DPST	ON-OFF	16	Illuminated Rocker	Black	Green	0.25" Quick Connect	1.24	1.15	1.28	\$ 1.95
2267439	Mountain Switch	103-7080-EV	2	DPST	ON-OFF	16	Illuminated Rocker	Black	Green	0.25" Quick Connect	1.24	0.992	1.08	\$ 2.49
2267431	Mountain Switch	103-7079-EV	2	DPST	ON-OFF	16	Illuminated Rocker	Black	Red	0.25" Quick Connect	1.24	0.992	1.08	\$ 2.49
2267599	Mountain Switch	103-R13-240B-01R	2	DPST	ON-OFF	16	Illuminated Rocker	Black	Red	0.25" Quick Connect	1.24	1.15	0.823	\$ 2.49
2276479	Marquardt Switch	1555.3109-00	2	DPST	ON-OFF	16	Illuminated Rocker	Black	Black with Green Neon	0.25" Quick Connect	1.18	0.59	1.11	\$ 2.75
2267423	Mountain Switch	103-7078-EV	2	DPST	ON-OFF	16	Rocker	Black	Black	0.25" Quick Connect	1.24	0.992	1.08	\$ 1.59
2267223	Mountain Switch	103-7045-EVX	2	DPST	ON-OFF	16	Rocker	Black	Black	0.25" Quick Connect	1.71	0.964	1.53	\$ 3.29
2269695	Jameco Valuepro	R13-104A-01-BB	2	DPST	ON-OFF	16	Round Rocker	Black	Black	0.25" Quick Connect	1.18	1.18	1.16	\$ 1.59
2287143	Eaton	SR4MLLFAXXAXXXX	10	DPDT	(ON)-ON-(ON)	12 @ 24VDC	Rocker	Black	Illuminated Amber	Blade Contact	2.05	0.42	1.42	\$ 14.95
2267007	Mountain Switch	103-7001-EVX	2	DPDT	ON-(ON)	5	Rocker	Red	Black	PC terminal RA	0.5	0.45	0.45	\$ 2.49
2285295	C&K	7201J1ZSI	3	DPDT	ON-NONE-ON	5	Rocker	Red	Orange	Solder Lug	0.45	1.156	0.155	\$ 3.95
2267143	Mountain Switch	103-7023-EVX	3	DPDT	ON-OFF-ON	5	Rocker	Red	Black	PC terminal RA	1.27	0.372	0.82	\$ 2.49
2267919	Mountain Switch	1055-RA1165	3	DPDT	ON-OFF-ON	6	Rocker	Blue	Black	Solder Lug	1.16	0.472	0.362	\$ 1.49
2267991	Jameco Valuepro	R13-104-B-G	2	DPDT	ON-OFF-ON	16	Illuminated Rocker	Black	Green	0.25" Quick Connect	1.18	1.18	1.16	\$ 1.59
2267615	Mountain Switch	103-R13-240D-01-EV	3	DPDT	ON-OFF-ON	16	Rocker	Black	Black	0.25" Quick Connect	1.24	1.15	0.823	\$ 1.25
2267215	Mountain Switch	103-7044-EVX	3	DPDT	ON-OFF-ON	16	Rocker	Black	Black	0.25" Quick Connect	1.71	0.964	1.53	\$ 2.49



[Click Here to Request a Large Quantity Quote](#)

**ROCKER SWITCHES**

Jameco PN	Manufacturer	Manufacturer Part #	Pins	Contact Form	Function ( ) Momentary	Current (A) @ 125VAC	Actuator Type	Color-Body	Color - Actuator/Cap	Termination Style	Length (in.)	Width (in.)	Depth (in.)	Price1
<a href="#">2181183</a>	C&K	ET21J1ABE2	2	DPDT	ON-ON	0.02	Rocker	Red	Black	PC Pin	0.913	0.36	0.32	\$ 3.95
<a href="#">2267015</a>	Mountain Switch	103-7002-EVX	3	DPDT	ON-ON	5	Paddle	Red	Black	Solder Lug	1.16	0.365	0.376	\$ 1.59
<a href="#">2267127</a>	Mountain Switch	103-7021-EVX	2	DPDT	ON-ON	5	Paddle	Red	Black	PC terminal RA	1.565	0.662	0.668	\$ 2.95
<a href="#">2269871</a>	Mountain Switch	103-7012	2	DPDT	ON-ON	5	Rocker	Red	Black	Solder Lug	1.15	0.275	0.532	\$ 1.49
<a href="#">2267135</a>	Mountain Switch	103-7022-EVX	2	DPDT	ON-ON	5	Rocker	Red	Black	Solder Lug	1.168	0.372	0.415	\$ 2.95
<a href="#">2267663</a>	Mountain Switch	103-R13-245C-02-EV	2	DPDT	ON-ON	8	Rocker	Black	Black	0.187" Quick Connect	1.18	1.18	0.512	\$ 1.25
<a href="#">2268071</a>	Jameco Valuepro	R13-49B-05-BB	2	DPDT	ON-ON	10	Rocker	Black	Black	Solder Lug	1.18	0.787	0.44	\$ 1.25
<a href="#">2268031</a>	Mountain Switch	R13-136B-05-BR	2	DPDT	ON-ON	10	Rocker	Black	Red	Solder Lug	0.905	0.905	0.551	\$ 1.25
<a href="#">2268055</a>	Mountain Switch	R13-104C-01-BB	2	DPDT	ON-ON	16	Rocker	Black	Black	0.25" Quick Connect	1.18	1.18	1.16	\$ 1.59
<a href="#">2287127</a>	Eaton	SK4MLLFAXXAXXX	10	DPDT	ON-ON-ON	12 @ 24VDC	Rocker	Black	Illuminated Amber	Blade Contact	2.05	0.42	1.42	\$ 19.95
<a href="#">2267023</a>	Mountain Switch	103-7003-EVX	2	3PDT	ON-ON	5	Rocker	Red	Black	PC terminal	1.16	0.365	0.376	\$ 2.95
<a href="#">2268167</a>	Jameco Valuepro	R13-66C-10-BBNN	2	4PDT	ON-NONE-ON	16	Rocker	Black	Red	0.187" Quick Connect	0.826	0.59	0.464	\$ 1.59
<a href="#">2266991</a>	Jameco Valuepro	103-7000	2	4PDT	ON-ON	5	Rocker	Red	Black	PC terminal RA	0.85	0.5	0.565	\$ 3.29