



[Click Here to Request a Large Quantity Quote](#)

ELECTRONIC DESIGN METAL ENCLOSURES

Jameco Part#	Manufacturer	Manufacturer Part #	Product Type	Length (in.)	Width (in.)	Height (in.)	Material	Color	Additional Feature	Price 1
2292759	Hammond Manufacturing	1590LB	Box	2.0	2.0	1.3	Aluminum	Unpainted	Case Metal	\$ 6.49
2292695	Hammond Manufacturing	1550Q	Box	2.4	2.2	1.1	Aluminum	Clear Anodized	Diecast	\$ 5.75
2292663	Hammond Manufacturing	1455C801	Box	3.2	2.2	1	Aluminum	Clear Anodized	Extruded	\$ 12.95
2138169	Hammond Manufacturing	1550A	Box	3.5	1.4	1.2	Aluminum	Unpainted	Diecast	\$ 5.95
11957	Jameco Valuepro	03-125A	Box	3.9	2.0	1	Aluminum	Unpainted	Diecast	\$ 6.95
2157896	Jameco Valuepro	THN4	Box	3.9	2.5	0.9	Tin	Unpainted	Flip Top	\$ 2.39
11870	Jameco Valuepro	H2300-R	Box	4.0	2.0	2.8	Aluminum	Unpainted	U Shaped	\$ 5.49
208901	Jameco Valuepro	CMC 11914	Box	4.0	3.3	2.2	Aluminum	Ivory/Black	U Shaped	\$ 6.95
2138290	Hammond Manufacturing	1590B	Box	4.4	2.3	1.1	Aluminum	Unpainted	Diecast	\$ 7.25
2292687	Hammond Manufacturing	1550D	Box	4.6	2.6	2.1	Aluminum	Clear Anodized	Diecast	\$ 8.69
2138302	Hammond Manufacturing	1590BB	Box	4.7	3.7	1.2	Aluminum	Unpainted	Diecast	\$ 8.95
2292671	Hammond Manufacturing	1455J1202	Box	4.8	3.1	1.1	Aluminum	Clear Anodized	Extruded	\$ 13.69
2292679	Hammond Manufacturing	1455L1201	Box	4.8	4.1	1.2	Aluminum	Clear Anodized	Extruded	\$ 21.95
11886	Jameco Valuepro	H2320-R	Box	5.0	4.0	3	Aluminum	Unpainted	U Shaped	\$ 5.95
208911	Jameco Valuepro	CMC 11922-R	Box	5.9	5.3	3	Aluminum	Ivory/Black	U Shaped	\$ 8.95
209350	Jameco Valuepro	SY0206-R	Box	6.3	7.8	2.5	Aluminum	Ivory/Black	U Shaped	\$ 9.25
208929	Jameco Valuepro	CMC11949-R	Box	7.3	6.3	2.8	Aluminum	Ivory/Black	U Shaped	\$ 9.95
11973	Jameco Valuepro	03-125C	Box	7.5	4.3	2.4	Aluminum	Unpainted	Diecast	\$ 24.95
209358	Jameco Valuepro	SY0207-R	Box	7.5	9.8	3.2	Aluminum	Ivory/Black	U Shaped	\$ 15.95
2271423	Jameco Reliapro	TRC-E-LPV203560	Box	7.7	1.8	4.9	Steel	Black	NEMA with Vent and Knockouts	\$ 19.95
2271455	Jameco Reliapro	TRC-LRS-35-50	Box	8.5	1.9	4.8	Steel	Unpainted	NEMA with Vent and Knockouts	\$ 42.95
2271463	Jameco Reliapro	TRC-LRS-75100150	Box	10.8	1.8	5.5	Steel	Unpainted	NEMA with Vent and Knockouts	\$ 44.95
2271439	Jameco Reliapro	TRC-LRS-350	Box	12.5	1.9	6.2	Steel	Unpainted	NEMA with Vent and Knockouts	\$ 54.95
2271447	Jameco Reliapro	TRC-LRS-200	Box	12.5	1.9	6.2	Steel	Unpainted	NEMA with Vent and Knockouts	\$ 42.95
2271431	Jameco Reliapro	TRC-E-RSP750	Box	15.2	2.3	6.5	Steel	Unpainted	NEMA with Vent and Knockouts	\$ 79.95