



[Click Here to Request a Large Quantity Quote](#)

ELECTRONIC DESIGN - PROTOBOARDS

Jameco Part#	Manufacturer	Manufacturer Part #	Product Type	Plating	Centers (in.)	No. Of Holes	Length (in.)	Width (in.)	Hole Diameter (in.)	Thickness (in.)	No. of Mounting Holes x Dia. (in.)	Sided	Price 1
105100	Jameco Valuepro	(PCB228)	Protoboard	Epoxy Glass	0.1	288	2.7	1.6	0.035	0.0625	2 x 0.115	Single	\$ 3.95
105102	Jameco Valuepro	PCB-365-R	Protoboard	Epoxy Glass	0.1	365	3.5	1.5	0.038	0.0625	2 x 0.140	Single	\$ 3.95
645677	Jameco Valuepro	PB-456	Protoboard	Epoxy Glass	0.1	555	3.5	2.5	0.036/0.045	0.0625	4 x 0.140	Double	\$ 9.95
2191445	Busboard Prototype Systems	PAD1	Protoboard	Epoxy Glass	0.1	589	3.2	2	0.037	0.0625	4 x 0.125	Double	\$ 3.75
105111	Jameco Valuepro	PCB-102-R	Protoboard	Epoxy Glass	0.1	637	3.4	2.4	0.038	0.0625	2 x 0.140	Single	\$ 8.95
263215	Jameco Valuepro	PCB-858-R	Protoboard	Epoxy Glass	0.1	640	4.3	2.5	0.042	0.0625	4 x 0.120	Double	\$ 5.95
105129	Jameco Valuepro	2853PCB-R	Protoboard	Epoxy Glass	0.1	669	4.4	2	0.038	0.0625	4 x 0.140	Single	\$ 6.59
263207	Jameco Valuepro	PCB-463-R	Protoboard	Epoxy Glass	0.1	674	4.1	2.4	0.032	0.0625	4 x 0.130	Double	\$ 6.95
2191453	Busboard Prototype Systems	PAD2	Protoboard	Epoxy Glass	0.1	1209	4	3.2	0.037	0.0625	4 x 0.125	Double	\$ 5.95
105137	Jameco Valuepro	PCB-1266-R	Protoboard	Epoxy Glass	0.1	1266	4.5	3.3	0.035	0.0625	4 x 0.140	Single	\$ 4.95
262511	Jameco Valuepro	PB-1135	Protoboard	Epoxy Glass	0.1	1324	5	3.7	0.036/0.045	0.0625	4 x 0.140	Double	\$ 9.95
105153	Jameco Valuepro	2851PCB-R	Protoboard	Epoxy Glass	0.1	1450	5.5	3.1	0.035	0.0625	4 x 0.140	Single	\$ 5.49
206579	Jameco Valuepro	PCB-578-R	Protoboard	Epoxy Glass	0.1	1684	4.3	4.6	0.042	0.0625	4 x 0.140	Single	\$ 3.95
105162	Jameco Valuepro	2852PCB-R	Protoboard	Epoxy Glass	0.1	2225	7	3.6	0.035	0.0625	4 x 0.140	Single	\$ 9.95
2127241	Busboard Prototype Systems	PR3U	Protoboard	Epoxy Glass	0.1	2356	6.3	3.9	0.037	0.0625	2 x 0.100	Single	\$ 10.49
2127232	Busboard Prototype Systems	PR2H3U	Protoboard	Epoxy Glass	0.1	2356	6.3	3.9	0.037	0.0625	0	Single	\$ 9.95
21435	Jameco Valuepro	JE401-R	Protoboard	Epoxy Glass	0.1	2360	6.5	4.5	0.042	0.0625	0	Single	\$ 9.95
52943	Vector Electronics	#84P44WE	Protoboard	Epoxy Glass	0.1	2430	8.5	4.5	0.042	0.0625	0	Single	\$ 12.49
206587	Jameco Valuepro	PCB-586-R	Protoboard	Epoxy Glass	0.1	2550	6.8	4.3	0.042	0.0625	4 x 0.140	Single	\$ 7.95
105180	Jameco Valuepro	PCB-135-R	Protoboard	Epoxy Glass	0.1	2829	6.5	5	0.035	0.0625	8 x 0.120	Single	\$ 7.95
43140	Vector Electronics	#64P44XXXP	Protoboard	Epoxy Glass	0.1	2860	6.5	4.5	0.042	0.0625	0	Single	\$ 8.59
206594	Jameco Valuepro	PCB-594	Protoboard	Epoxy Glass	0.1	3906	8	5.5	0.042	0.0625	4 x 0.140	Single	\$ 9.95
105187	Jameco Valuepro	2507PCB	Protoboard	Epoxy Glass	0.1	4771	8.8	6.1	0.035	0.0625	8 x 0.140	Single	\$ 10.95
21478	Jameco Valuepro	JE407-R	Protoboard	Epoxy Glass	0.1	6063	13	5	0.038	0.0625	8 x 0.120	Double	\$ 26.95
37612	Vector Electronics	169P44XXXP	Protoboard	Epoxy Glass	0.1	7524	17	4.5	0.042	0.0625	0	Single	\$ 16.95
37621	Vector Electronics	169P84WE	Protoboard	Epoxy Glass	0.1	14448	17	8.5	0.042	0.0625	0	Single	\$ 29.95
2213421	DFRobot	FIT0099	Protoboard	Phenolic	0.1	572	2.3	3.1	0.038	0.0625	4 x 0.140	Single	\$ 1.49
262537	Jameco Valuepro	PB-1931	Protoboard	Phenolic	0.1	2192	6	4.9	0.036/0.045	0.0625	4 x 0.140	Double	\$ 10.95
616673	GC Electronics	22-512	Protoboard	Phenolic	0.2	800	6.8	3.4	0.03	0.0625	0	Single	\$ 5.19
616649	GC Electronics	22-508	Protoboard	Phenolic	0.3	684	6	2	0.03	0.0625	4 x 0.120	Single	\$ 10.95
169279	Jameco Valuepro	21-225	Protoboard Blank	Copper Plated			3	6		0.0625	0	Single	\$ 3.59
169288	Jameco Valuepro	21-226-R	Protoboard Blank	Copper Plated			5.9	5.9		0.0625	0	Single	\$ 3.95
616489	GC Electronics	22-260	Protoboard Blank	Copper Plated			6	4		0.0625	0	Single	\$ 2.45
169317	Jameco Valuepro	21-221-R	Protoboard Blank	Copper Plated			6	6		0.0625	0	Double	\$ 5.95
616500	GC Electronics	22-263	Protoboard Blank	Copper Plated			9	6		0.0625	0	Single	\$ 3.95
616518	GC Electronics	22-264	Protoboard Blank	Copper Plated			10	8		0.0625	0	Single	\$ 7.59
169296	Jameco Valuepro	21-227-R	Protoboard Blank	Copper Plated			12	2		0.0625	0	Single	\$ 10.95
169325	Jameco Valuepro	CIC 21-222-R	Protoboard Blank	Copper Plated			12	2		0.0625	0	Double	\$ 15.95
616534	GC Electronics	22-268	Protoboard Blank	Copper Plated			14	11		0.0625	0	Single	\$ 11.95
616690	GC Electronics	22-516	Protoboard Perforated	Phenolic	0.1	2565	6	4.5	0.042	0.0625	0	Single	\$ 4.19
2125042	Busboard Prototype Systems	SB300	Solderable Breadboard	Copper Plated	0.1	300	3	1.2	0.042	0.0625	0	Single	\$ 3.95
2191402	Busboard Prototype Systems	SB404	Solderable Breadboard	Epoxy Glass	0.1	628	3.8	1.9	0.042	0.0625	0	Single	\$ 4.95
2125034	Busboard Prototype Systems	BR1	Solderable Breadboard	Epoxy Glass	0.1	1226	7.1	1.9	0.042	0.0625	0	Single	\$ 6.49
2191411	Busboard Prototype Systems	SB830	Solderable Breadboard	Epoxy Glass	0.1	1258	7.3	1.9	0.042	0.0625	0	Single	\$ 6.49
2191429	Busboard Prototype Systems	SB1660	Solderable Breadboard	Epoxy Glass	0.1	2528	7.3	3.7	0.042	0.0625	6 x 0.125	Single	\$ 11.95
2125051	Busboard Prototype Systems	SB400	Solderable Breadboard	Phenolic	0.1	400	3	1.9	0.042	0.0625	0	Single	\$ 4.95
2191461	Busboard Prototype Systems	PR2H1	Stripboard	Copper Plated	0.1	589	3.2	2	0.037	0.0625	4 x 0.125	Single	\$ 3.15
2191470	Busboard Prototype Systems	PR2H2	Stripboard	Epoxy Glass	0.1	12.09	4	3.2	0.03	0.0625	4 x 0.125	Single	\$ 5.69
2127267	Busboard Prototype Systems	ST3U	Stripboard	Epoxy Glass	0.1	2356	6.3	3.9	0.037	0.0625	0	Single	\$ 9.95
2191488	Busboard Prototype Systems	ST1	Stripboard	Phenolic	0.1	589	2	3.2	0.037	0.0625	0	Single	\$ 3.15
2191496	Busboard Prototype Systems	ST2	Stripboard	Phenolic	0.1	899	4	3.2	0.037	0.0625	0	Single	\$ 5.69