



[Click Here to Request a Large Quantity Quote](#)

[Encapsulated Switching Power Supplies](#)

Jameco Part #	Manufacturer	Manufacturer Part #	Primary Output Voltage (VDC)	Output Current (A)	Maximum Output Power (W)	Family	Input Voltage (VAC)	Input Frequency	Maximum Input Current (A)	Output Connector Type	Number of Outputs	Size (L" x W" x H")	Price 1
2239752	MEAN WELL	IRM-01-3.3	3.3	0.3	1	IRM-01	85 to 305	47 to 63	0.025	PC Pin	1	1.33 x 0.87 x 0.59	\$4.90
2239939	MEAN WELL	IRM-02-3.3S	3.3	0.6	2	IRM-02	85 to 305	47 to 63	0.045	SMD	1	1.33 x 0.87 x 0.63	\$5.90
2239525	MEAN WELL	IRM-03-3.3	3.3	0.9	3	IRM-03	85 to 305	47 to 63	0.07	PC Pin	1	1.46 x 0.95 x 0.59	\$5.30
2193125	MEAN WELL	IRM-05-3.3	3.3	1.25	4.125	IRM-05	85 to 264	47 to 440	0.12	PC Pin	1	1.8 x 1 x 0.85	\$6.80
2193176	MEAN WELL	IRM-10-3.3	3.3	2.5	8.25	IRM-10	85 to 264	47 to 440	0.25	PC Pin	1	1.8 x 1 x 0.85	\$7.40
2193272	MEAN WELL	IRM-20-3.3	3.3	4.5	14.85	IRM-20	85 to 264	47 to 440	0.6	PC Pin	1	2.06 x 1.07 x 0.94	\$9.10
2239761	MEAN WELL	IRM-01-5	5	0.2	1	IRM-01	85 to 305	47 to 63	0.025	PC Pin	1	1.33 x 0.87 x 0.59	\$4.90
2239824	MEAN WELL	IRM-01-5S	5	0.2	1	IRM-01	85 to 305	47 to 63	0.025	SMD	1	1.33 x 0.87 x 0.63	\$5.70
2239883	MEAN WELL	IRM-02-5	5	0.4	2	IRM-02	85 to 305	47 to 63	0.045	PC Pin	1	1.33 x 0.87 x 0.59	\$5.10
2239947	MEAN WELL	IRM-02-5S	5	0.4	2	IRM-02	85 to 305	47 to 63	0.045	SMD	1	1.33 x 0.87 x 0.63	\$5.90

Jameco Part #	Manufacturer	Manufacturer Part #	Primary Output Voltage (VDC)	Output Current (A)	Maximum Output Power (W)	Family	Input Voltage (VAC)	Input Frequency	Maximum Input Current (A)	Output Connector Type	Number of Outputs	Size (L" x W" x H")	Price 1
2239509	MEAN WELL	IRM-03-5	5	0.6	3	IRM-03	85 to 305	47 to 63	0.07	PC Pin	1	1.46 x 0.95 x 0.59	\$5.30
2193133	MEAN WELL	IRM-05-5	5	1	5	IRM-05	85 to 264	47 to 440	0.12	PC Pin	1	1.8 x 1 x 0.85	\$6.80
2193230	MEAN WELL	IRM-15-5	5	3	15	IRM-15	85 to 264	47 to 440	0.35	PC Pin	1	1.8 x 1 x 0.85	\$8.60
2193281	MEAN WELL	IRM-20-5	5	4	20	IRM-20	85 to 264	47 to 440	0.6	PC Pin	1	2.06 x 1.07 x 0.94	\$9.10
2224737	MEAN WELL	IRM-45-5	5	8	40	IRM-45	85 to 264	47 to 440	1.5	PC Pin	1	3.43 x 2.05 x 1.16	\$13.10
2239779	MEAN WELL	IRM-01-9	9	0.111	1	IRM-01	85 to 305	47 to 63	0.025	PC Pin	1	1.33 x 0.87 x 0.59	\$4.90
2239517	MEAN WELL	IRM-03-9	9	0.333	3	IRM-03	85 to 305	47 to 63	0.07	PC Pin	1	1.46 x 0.95 x 0.59	\$5.30
2239787	MEAN WELL	IRM-01-12	12	0.083	1	IRM-01	85 to 305	47 to 63	0.025	PC Pin	1	1.33 x 0.87 x 0.59	\$4.90
2239904	MEAN WELL	IRM-02-12	12	0.167	2	IRM-02	85 to 305	47 to 63	0.045	PC Pin	1	1.33 x 0.87 x 0.59	\$5.10
2239488	MEAN WELL	IRM-03-12	12	0.25	2	IRM-03	85 to 305	47 to 63	0.07	PC Pin	1	1.46 x 0.95 x 0.59	\$5.30
2240024	MEAN WELL	IRM-03-12S	12	0.25	3	IRM-03	85 to 305	47 to 63	0.07	SMD	1	1.46 x 0.95 x 0.63	\$6.10
2193141	MEAN WELL	IRM-05-12	12	0.42	5.04	IRM-05	85 to 264	47 to 440	0.12	PC Pin	1	1.8 x 1 x 0.85	\$6.80
2193248	MEAN WELL	IRM-15-12	12	1.25	15	IRM-15	85 to 264	47 to 440	0.35	PC Pin	1	1.8 x 1 x 0.85	\$8.60

Jameco Part #	Manufacturer	Manufacturer Part #	Primary Output Voltage (VDC)	Output Current (A)	Maximum Output Power (W)	Family	Input Voltage (VAC)	Input Frequency	Maximum Input Current (A)	Output Connector Type	Number of Outputs	Size (L" x W" x H")	Price 1
2193299	MEAN WELL	IRM-20-12	12	1.8	21.6	IRM-20	85 to 264	47 to 440	0.6	PC Pin	1	2.06 x 1.07 x 0.94	\$9.10
2218610	MEAN WELL	IRM-30-12	12	2.5	30	IRM-30	85 to 264	47 to 440	0.75	PC Pin	1	2.74 x 1.54 x 0.94	\$12.50
2218661	MEAN WELL	IRM-30-12ST	12	2.5	30	IRM-30	85 to 264	47 to 440	0.75	Screw Terminal	1	3.58 x 1.56 x 1.12	\$14.40
2224745	MEAN WELL	IRM-45-12	12	3.8	45.6	IRM-45	85 to 264	47 to 440	1.5	PC Pin	1	3.43 x 2.05 x 1.16	\$13.10
2224796	MEAN WELL	IRM-45-12ST	12	3.8	45.6	IRM-45	85 to 264	47 to 440	1.5	Screw Terminal	1	4.29 x 2.05 x 1.32	\$15.00
2224841	MEAN WELL	IRM-60-12	12	5	60	IRM-60	85 to 264	47 to 440	1.8	PC Pin	1	3.43 x 2.05 x 1.16	\$14.60
2224892	MEAN WELL	IRM-60-12ST	12	5	60	IRM-60	85 to 264	47 to 440	1.8	Screw Terminal	1	4.29 x 2.05 x 1.32	\$16.50
2239912	MEAN WELL	IRM-02-15	15	0.133	2	IRM-02	85 to 305	47 to 63	0.045	PC Pin	1	1.33 x 0.87 x 0.59	\$5.10
2239533	MEAN WELL	IRM-03-15	15	0.2	3	IRM-03	85 to 305	47 to 63	0.07	PC Pin	1	1.46 x 0.95 x 0.59	\$5.30
2240032	MEAN WELL	IRM-03-15S	15	0.2	3	IRM-03	85 to 305	47 to 63	0.07	SMD	1	1.46 x 0.95 x 0.63	\$6.10
2193150	MEAN WELL	IRM-05-15	15	0.33	4.95	IRM-05	85 to 264	47 to 440	0.12	PC Pin	1	1.8 x 1 x 0.85	\$6.80
2193205	MEAN WELL	IRM-10-15	15	0.67	10.05	IRM-10	85 to 264	47 to 440	0.25	PC Pin	1	1.8 x 1 x 0.85	\$7.40
2193256	MEAN WELL	IRM-15-15	15	1	15	IRM-15	85 to 264	47 to 440	0.35	PC Pin	1	1.8 x 1 x 0.85	\$8.60

Jameco Part #	Manufacturer	Manufacturer Part #	Primary Output Voltage (VDC)	Output Current (A)	Maximum Output Power (W)	Family	Input Voltage (VAC)	Input Frequency	Maximum Input Current (A)	Output Connector Type	Number of Outputs	Size (L" x W" x H")	Price 1
2218628	MEAN WELL	IRM-30-15	15	2	30	IRM-30	85 to 264	47 to 440	0.75	PC Pln	1	2.74 x 1.54 x 0.94	\$12.50
2239808	MEAN WELL	IRM-01-24	24	0.042	1	IRM-01	85 to 305	47 to 63	0.025	PC Pin	1	1.33 x 0.87 x 0.59	\$4.90
2239921	MEAN WELL	IRM-02-24	24	0.086	2	IRM-02	85 to 305	47 to 63	0.045	PC Pin	1	1.33 x 0.87 x 0.59	\$5.10
2239496	MEAN WELL	IRM-03-24	24	0.125	3	IRM-03	85 to 305	47 to 63	0.07	PC Pin	1	1.46 x 0.95 x 0.59	\$5.30
2240041	MEAN WELL	IRM-03-24S	24	0.125	3	IRM-03	85 to 305	47 to 63	0.07	SMD	1	1.46 x 0.95 x 0.63	\$6.10
2193168	MEAN WELL	IRM-05-24	24	0.23	5.52	IRM-05	85 to 264	47 to 440	0.12	PC Pin	1	1.8 x 1 x 0.85	\$6.80
2193310	MEAN WELL	IRM-20-24	24	0.9	21.6	IRM-20	85 to 264	47 to 440	0.6	PC Pin	1	2.06 x 1.07 x 0.94	\$9.10
2218636	MEAN WELL	IRM-30-24	24	1.3	31	IRM-30	85 to 264	47 to 440	0.75	PC Pln	1	2.74 x 1.54 x 0.94	\$12.50
2218687	MEAN WELL	IRM-30-24ST	24	1.3	31	IRM-30	85 to 264	47 to 440	0.75	Screw Terminal	1	3.58 x 1.56 x 1.12	\$14.40
2224761	MEAN WELL	IRM-45-24	24	1.9	45.6	IRM-45	85 to 264	47 to 440	1.5	PC Pln	1	3.43 x 2.05 x 1.16	\$13.10
2224817	MEAN WELL	IRM-45-24ST	24	1.9	45.6	IRM-45	85 to 264	47 to 440	1.5	Screw Terminal	1	4.29 x 2.05 x 1.32	\$15.00
2224868	MEAN WELL	IRM-60-24	24	2.5	60	IRM-60	85 to 264	47 to 440	1.8	PC Pln	1	3.43 x 2.05 x 1.16	\$14.60

Jameco Part #	Manufacturer	Manufacturer Part #	Primary Output Voltage (VDC)	Output Current (A)	Maximum Output Power (W)	Family	Input Voltage (VAC)	Input Frequency	Maximum Input Current (A)	Output Connector Type	Number of Outputs	Size (L" x W" x H")	Price 1
2224913	MEAN WELL	IRM-60-24ST	24	2.5	60	IRM-60	85 to 264	47 to 440	1.8	Screw Terminal	1	4.29 x 2.05 x 1.32	\$16.50
2224770	MEAN WELL	IRM-45-48	48	0.94	45.1	IRM-45	85 to 264	47 to 440	1.5	PC Pln	1	3.43 x 2.05 x 1.16	\$13.10