



[Click Here to Request a Large Quantity Quote](#)

SEMICONDUCTORS: MEMORY EEPROM

| Jameco Part# | Manufacturer | Manufacturer Part # | Description | Package Type | Configuration | Nanoseconds | Price 1 |
|-------------------------|---------------------|---------------------|--|--------------|---------------|-------------|---------|
| 74691 | Major Brands | 28C16A-25 | IC 28C16A-25 EEPROM 16K-Bit CMOS Parallel | DIP-24 | 2Kx8 | 200 | \$ 4.95 |
| 74843 | Major Brands | 28C256-15 | IC 28C256-16 EEPROM 256K-Bit CMOS Parallel | DIP-28 | 32Kx8 | 150 | \$ 5.95 |
| 74878 | Major Brands | 28C256-25 | IC 28C256-25IC EEPROM 256K-Bit CMOS Parallel | DIP-28 | 32Kx8 | 250 | \$ 4.95 |
| 74827 | Major Brands | 28C64A-25 | IC 28C64A-25 EEPROM 64k-Bit CMOS | DIP-28 | 8Kx8 | 250 | \$ 4.95 |
| 200580 | Major Brands | AT24C256PC | IC 24C256PC EEPROM 256K-Bit CMOS 2-Wire Serial | DIP-8 | 32Kx8 | 300 | \$ 1.95 |
| 2286151 | Atmel (Microchip) | AT25128-10PC | IC AT25128-10PC EEPROM 128K-Bit SPI Serial 3MHz 4.5-5.5V | DIP-8 | 16Kx8- | 100 | \$ 2.49 |
| 2286231 | Atmel (Microchip) | AT25128-10PC2.7 | IC AT25128-10PC2.7EEPROM 128K-Bit SPI Serial 3MHz 2.7-5.5V | DIP-8 | 16Kx8 | 200 | \$ 2.49 |
| 2286159 | Atmel (Microchip) | AT25128-10PI-1.8 | IC AT25128-10PI-1.8 EEPROM 128K-Bit SPI Serial 2.1MHz 1.8-3.6V | DIP-8 | 16Kx8 | 300 | \$ 2.49 |
| 2290671 | STMicroelectronics | M24128-BW | IC M24128-BW EEPROM Memory 128Kb I2C 1MHz | DIP-8 | 16Kx8 | 450 | \$ 0.39 |
| 2288055 | Mitsubishi Electric | M5L27512K | IC 27512 EEPROM 524,288-Bit 250ns Erasable and Electrically Reprogrammable ROM | DIP-28 | 64Kx8 | 250 | \$ 5.95 |