



[Click Here to Request a Large Quantity Quote](#)

TERMINAL BLOCK BARRIER TERMINALS

Jameco Part#	Manufacturer	Manufacturer Part #	Description	Maximum Current Rating (A)	Maximum Voltage Rating (V)	Number of Positions	Wire Size (AWG)	Top Termination	Bottom Termination	Mounting	Price 1
2172682	Adam Technologies	TDA-02-V2	Dual Row Barrier Strip	10	300	2	18-12	Screw, M3.5	Open Bottom	Chassis, Panel	\$ 1.75
2272863	Jameco Valuepro	GGE-10-2P	Dual Row Barrier Strip	10	600	2	22-12	Screw, M3.5	Open Bottom with Flange	Chassis, Panel	\$ 0.59
208857	Jameco Valuepro	GGE-10-4P-R	Dual Row Barrier Strip	10	600	4	22-14	Screw, M3.5	Open Bottom	Chassis, Panel	\$ 1.39
208865	Jameco Valuepro	GGE-10-6P-R	Dual Row Barrier Strip	10	600	6	22-12	Screw, M3.5	Open Bottom	Chassis, Panel	\$ 1.75
2272871	Jameco Valuepro	GGE-10-8P	Dual Row Barrier Strip	10	600	8	22-12	Screw, M3.5	Open Bottom with Flange	Chassis, Panel	\$ 1.95
208900	Jameco Valuepro	GGE-10-10P-R	Dual Row Barrier Strip	10	600	10	22-12	Screw, M3.5	Open Bottom	Chassis, Panel	\$ 2.75
208882	Jameco Valuepro	GGE-10-12P-R	Dual Row Barrier Strip	10	600	12	22-12	Screw, M3.5	Open Bottom	Chassis, Panel	\$ 2.95
230973	Cinch Connectors	2-140	Dual Row Barrier Strip	15	250	2	16	Screw, 6-32	Open Bottom with Flange	Panel Mount	\$ 2.25
230990	Cinch Connectors	4-140	Dual Row Barrier Strip	15	250	4	16	Screw, 6-32	Open Bottom with Flange	Panel Mount	\$ 2.49
659411	Molex	38770-0104	Dual Row Barrier Strip	15	250	4	22-12	Screw, 6-32	Closed Bottom with Flange	Panel Mount	\$ 2.75
2273047	Molex	5-140	Dual Row Barrier Strip	15	250	5	16	Screw, 6-32	Open Bottom with Flange	Chassis, Panel	\$ 2.49
231010	Cinch Connectors	6-140	Dual Row Barrier Strip	15	250	6	16	Screw, 6-32	Open Bottom with Flange	Panel Mount	\$ 3.39
231036	Cinch Connectors	8-140	Dual Row Barrier Strip	15	250	8	16	Screw, 6-32	Open Bottom with Flange	Panel Mount	\$ 4.25
659454	Molex	38770-0108	Dual Row Barrier Strip	15	250	8	22-12	Screw, 6-32	Closed Bottom with Flange	Panel Mount	\$ 3.49
231052	Cinch Connectors	10-140	Dual Row Barrier Strip	15	250	10	16	Screw, 6-32	Open Bottom with Flange	Panel Mount	\$ 4.95
2273023	Cinch Connectors	20-140	Dual Row Barrier Strip	15	250	20	16	Screw, 6-32	Open Bottom with Flange	Chassis, Panel	\$ 8.95
2272831	Molex	38770-0102	Dual Row Barrier Strip	15	300	2	22-14	Screw, M3.5	Closed Bottom with Flange	Chassis, Panel	\$ 1.95
2272839	Molex	38770-0106	Dual Row Barrier Strip	15	300	6	22-14	Screw, 6-32	Closed Bottom with Flange	Chassis, Panel	\$ 3.95
2272847	Molex	38770-0110	Dual Row Barrier Strip	15	300	10	22-14	Screw, 6-32	Closed Bottom with Flange	Chassis, Panel	\$ 3.95
2272855	Molex	38770-0112	Dual Row Barrier Strip	15	300	12	22-14	Screw, 6-32	Closed Bottom with Flange	Chassis, Panel	\$ 5.29
231351	Cinch Connectors	2-141	Dual Row Barrier Strip	20	250	2	14	Screw, 6-32	Closed Bottom with Flange	Panel Mount	\$ 1.95
231378	Cinch Connectors	4-141	Dual Row Barrier Strip	20	250	4	14	Screw, 6-32	Closed Bottom with Flange	Panel Mount	\$ 2.75
231394	Cinch Connectors	6-141	Dual Row Barrier Strip	20	250	6	14	Screw, 6-32	Closed Bottom with Flange	Panel Mount	\$ 3.75
231431	Cinch Connectors	10-141	Dual Row Barrier Strip	20	250	10	14	Screw, 6-32	Closed Bottom with Flange	Panel Mount	\$ 5.95
441228	Cinch Connectors	20-141	Dual Row Barrier Strip	20	250	20	14	Screw, 6-32	Open Bottom with Flange	Panel Mount	\$ 8.95
2293327	Molex	38760-0103	Dual Row Barrier Strip	20	300	3	22-14	Screw, M3.5	Closed Bottom with Flange	Chassis, Panel	\$ 2.25
2278167	On Shore Technology	DB-95MNV-25	Dual Row Barrier Strip	20	300	25	22-12	Screw, 6-32	Open Bottom with Flange	Chassis, Panel	\$ 6.95
2272879	Jameco Valuepro	GGE-20-2P	Dual Row Barrier Strip	20	600	2	22-12	Screw, M3.5	Closed Bottom with Flange	Chassis, Panel	\$ 0.89
237083	On Shore Technology	41296.2	Dual Row Barrier Strip	20	600	2	22-14	DIN Rail	DIN Rail	Cable Mount	\$ 0.99
2272887	Jameco Valuepro	GGE-20-4P	Dual Row Barrier Strip	20	600	4	22-14	Screw, M3.5	Closed Bottom with Flange	Chassis, Panel	\$ 1.25
207547	Jameco Valuepro	GGE-20-6P-R	Dual Row Barrier Strip	20	600	6	22-12	Screw, M3.5	Closed Bottom with Flange	Chassis, Panel	\$ 1.59
2272903	Jameco Valuepro	GGE-20-8P	Dual Row Barrier Strip	20	600	8	22-12	Screw, M3.5	Closed Bottom with Flange	Chassis, Panel	\$ 2.29
2272911	Jameco Valuepro	GGE-20-10P	Dual Row Barrier Strip	20	600	10	22-12	Screw, M3.5	Closed Bottom with Flange	Chassis, Panel	\$ 2.49
207572	Jameco Valuepro	GGE-20-12P-R	Dual Row Barrier Strip	20	600	12	22-12	Screw, M3.5	Open Bottom with Flange	Chassis, Panel	\$ 2.95
441210	Cinch Connectors	2-142	Dual Row Barrier Strip	30	250	2	10	Screw, 6-32	Open Bottom with Flange	Chassis, Panel	\$ 2.95
440858	Cinch Connectors	4-142	Dual Row Barrier Strip	30	250	4	10	Screw, 6-32	Open Bottom with Flange	Chassis, Panel	\$ 3.75
440874	Cinch Connectors	6-142	Dual Row Barrier Strip	30	250	6	10	Screw, 6-32	Open Bottom with Flange	Chassis, Panel	\$ 6.75
440891	Cinch Connectors	8-142	Dual Row Barrier Strip	30	250	8	10	Screw, 6-32	Open Bottom with Flange	Chassis, Panel	\$ 8.49
2281103	Jameco Valuepro	672RZ18CRES	Dual Row Barrier Strip	30	600	18	14-12	Screw, 8-32	Closed Bottom with Flange	Panel Mount	\$ 12.95
2275375	On Shore Technology	ES0800/02DSFB	Dual Row Eurostyle Barrier Strip	15	300	2	22-14	Screw, M2.5	None	Chassis, Panel	\$ 0.39
2275391	On Shore Technology	ES0800/03DSFB	Dual Row Eurostyle Barrier Strip	15	300	3	22-14	Screw, M2.5	None	Chassis, Panel	\$ 0.75
2275431	On Shore Technology	ES0800/04DSFB	Dual Row Eurostyle Barrier Strip	15	300	4	22-14	Screw, M2.5	None	Chassis, Panel	\$ 0.75
2275463	On Shore Technology	ES0800/06DSFB	Dual Row Eurostyle Barrier Strip	15	300	6	22-14	Screw, M2.5	None	Chassis, Panel	\$ 1.25
2275471	On Shore Technology	ES0800/08DSFB	Dual Row Eurostyle Barrier Strip	15	300	8	22-14	Screw, M2.5	None	Chassis, Panel	\$ 1.25
2275479	On Shore Technology	ES0800/10DSFB	Dual Row Eurostyle Barrier Strip	15	300	10	22-14	Screw, M2.5	None	Chassis, Panel	\$ 1.75
2259260	On Shore Technology	ES0800/12DSFB	Dual Row Eurostyle Barrier Strip	15	300	12	22-14	Screw, M2.5	None	Chassis, Panel	\$ 1.49
215011	Jameco Valuepro	PA7DS	Dual Row Eurostyle Barrier Strip	18	450	12	22-12	Screw, M2.6	None	Chassis, Panel	\$ 1.75
2275487	On Shore Technology	ES1000/02DSFB	Dual Row Eurostyle Barrier Strip	20	300	2	20-12	Screw, M3	None	Chassis, Panel	\$ 0.75
2275735	On Shore Technology	ES1000/03DSFB	Dual Row Eurostyle Barrier Strip	20	300	3	20-12	Screw, M3	None	Chassis, Panel	\$ 0.75
2275743	On Shore Technology	ES1000/04DSFB	Dual Row Eurostyle Barrier Strip	20	300	4	20-12	Screw, M3	None	Chassis, Panel	\$ 1.09
2275751	On Shore Technology	ES1000/06DSFB	Dual Row Eurostyle Barrier Strip	20	300	6	20-12	Screw, M3	None	Chassis, Panel	\$ 1.49
2275759	On Shore Technology	ES1000/08DSFB	Dual Row Eurostyle Barrier Strip	20	300	8	20-12	Screw, M3	None	Chassis, Panel	\$ 1.95
2275767	On Shore Technology	ES1000/10DSFB	Dual Row Eurostyle Barrier Strip	20	300	10	20-12	Screw, M3	None	Chassis, Panel	\$ 1.95
2275775	On Shore Technology	ES1000/12DSFB	Dual Row Eurostyle Barrier Strip	20	300	12	20-12	Screw, M3	None	Chassis, Panel	\$ 2.49
2120170	On Shore Technology	ES1000/12DS	Dual Row Eurostyle Barrier Strip	20	300	12	20-12	Screw, M3	None	Chassis, Panel	\$ 1.75



[Click Here to Request a Large Quantity Quote](#)

TERMINAL BLOCK BARRIER TERMINALS

Jameco Part#	Manufacturer	Manufacturer Part #	Description	Maximum Current Rating (A)	Maximum Voltage Rating (V)	Number of Positions	Wire Size (AWG)	Top Termination	Bottom Termination	Mounting	Price 1
215029	Jameco Valuepro	PA9DS	Dual Row Eurostyle Barrier Strip	24	450	12	22-12	Screw, M3	None	Chassis, Panel	\$ 2.25
2275791	On Shore Technology	ES1200/03DSFB	Dual Row Eurostyle Barrier Strip	30	300	3	20-10	Screw, M3	None	Chassis, Panel	\$ 1.09
2275799	On Shore Technology	ES1200/04DSFB	Dual Row Eurostyle Barrier Strip	30	300	4	20-10	Screw, M3	None	Chassis, Panel	\$ 1.25
2275807	On Shore Technology	ES1200/06DSFB	Dual Row Eurostyle Barrier Strip	30	300	6	20-10	Screw, M3	None	Chassis, Panel	\$ 1.75
2275815	On Shore Technology	ES1200/08DSFB	Dual Row Eurostyle Barrier Strip	30	300	8	20-10	Screw, M3	None	Chassis, Panel	\$ 2.25
2275823	On Shore Technology	ES1200/10DSFB	Dual Row Eurostyle Barrier Strip	30	300	10	20-10	Screw, M3	None	Chassis, Panel	\$ 2.49
2275831	On Shore Technology	ES1200/12DSFB	Dual Row Eurostyle Barrier Strip	30	300	12	20-10	Screw, M3	None	Chassis, Panel	\$ 3.29
215037	Jameco Valuepro	PA12HDS	Dual Row Eurostyle Barrier Strip	35	450	12	22-12	Screw, M3.5	None	Chassis, Panel	\$ 2.95
2275335	Jameco Valuepro	HI-202-02PH-S-D40	Single Row Barrier Strip	10	250	2	22-14	Screw, M3.5	Insulated Solder Turret with Flange	Chassis, Panel	\$ 0.89
2275231	Jameco Valuepro	HI-201-02PH-S-D40	Single Row Barrier Strip	10	250	2	22-14	Screw, M3.5	PC Pin with Flange	Through Hole	\$ 1.95
2275439	Jameco Valuepro	HI-201-02P	Single Row Barrier Strip	10	250	2	22-14	Screw, M3.5	PC Pin, w/o Flange	Chassis, Panel	\$ 1.09
2275175	Jameco Valuepro	HI-200-03PH-S-D40	Single Row Barrier Strip	10	250	3	22-14	Screw, M3.5	Closed Bottom with Flange	Chassis, Panel	\$ 2.09
2275343	Jameco Valuepro	HI-202-03PH-S-D40	Single Row Barrier Strip	10	250	3	22-14	Screw, M3.5	Insulated Solder Turret with Flange	Chassis, Panel	\$ 1.25
2275239	Jameco Valuepro	HI-201-03PH-S-D40	Single Row Barrier Strip	10	250	3	22-14	Screw, M3.5	PC Pin with Flange	Through Hole	\$ 2.15
2275287	Jameco Valuepro	HI-201-03P	Single Row Barrier Strip	10	250	3	22-14	Screw, M3.5	PC Pin, w/o Flange	Through Hole	\$ 1.95
2275183	Jameco Valuepro	HI-200-04PH-S-D40	Single Row Barrier Strip	10	250	4	22-14	Screw, M3.5	Closed Bottom with Flange	Chassis, Panel	\$ 2.39
2275351	Jameco Valuepro	HI-202-04PH-S-D40	Single Row Barrier Strip	10	250	4	22-14	Screw, M3.5	Insulated Solder Turret with Flange	Chassis, Panel	\$ 1.95
2275247	Jameco Valuepro	HI-201-04PH-S-D40	Single Row Barrier Strip	10	250	4	22-14	Screw, M3.5	PC Pin with Flange	Through Hole	\$ 2.29
2275295	Jameco Valuepro	HI-201-04P	Single Row Barrier Strip	10	250	4	22-14	Screw, M3.5	PC Pin,w/o Flange	Through Hole	\$ 2.09
2275191	Jameco Valuepro	HI-200-05PH-S-D40	Single Row Barrier Strip	10	250	5	22-14	Screw, M3.5	Closed Bottom with Flange	Chassis, Panel	\$ 2.69
2275359	Jameco Valuepro	HI-202-05PH-S-D40	Single Row Barrier Strip	10	250	5	22-14	Screw, M3.5	Insulated Solder Turret with Flange	Chassis, Panel	\$ 2.95
2275255	Jameco Valuepro	HI-201-05PH-S-D40	Single Row Barrier Strip	10	250	5	22-14	Screw, M3.5	PC Pin with Flange	Through Hole	\$ 2.59
2275303	Jameco Valuepro	HI-201-05P	Single Row Barrier Strip	10	250	5	22-14	Screw, M3.5	PC Pin, w/o Flange	Through Hole	\$ 2.19
2275199	Jameco Valuepro	HI-200-06PH-S-D40	Single Row Barrier Strip	10	250	6	22-14	Screw, M3.5	Closed Bottom with Flange	Chassis, Panel	\$ 2.95
2275367	Jameco Valuepro	HI-202-06PH-S-D40	Single Row Barrier Strip	10	250	6	22-14	Screw, M3.5	Insulated Solder Turret with Flange	Chassis, Panel	\$ 2.25
2275263	Jameco Valuepro	HI-201-06PH-S-D40	Single Row Barrier Strip	10	250	6	22-14	Screw, M3.5	PC Pin with Flange	Through Hole	\$ 2.95
2275311	Jameco Valuepro	HI-201-06P	Single Row Barrier Strip	10	250	6	22-14	Screw, M3.5	PC Pin, w/o Flange	Through Hole	\$ 2.59
2275207	Jameco Valuepro	HI-200-08PH-S-D40	Single Row Barrier Strip	10	250	8	22-14	Screw, M3.5	Closed Bottom with Flange	Chassis, Panel	\$ 3.49
2275383	Jameco Valuepro	HI-202-08PH-S-D40	Single Row Barrier Strip	10	250	8	22-14	Screw, M3.5	Insulated Solder Turret with Flange	Chassis, Panel	\$ 3.29
2275271	Jameco Valuepro	HI-201-08PH-S-D40	Single Row Barrier Strip	10	250	8	22-14	Screw, M3.5	PC Pin with Flange	Through Hole	\$ 3.49
2275447	Jameco Valuepro	HI-201-08P	Single Row Barrier Strip	10	250	8	22-14	Screw, M3.5	PC Pin, w/o Flange	Chassis, Panel	\$ 3.09
2275215	Jameco Valuepro	HI-200-10PH-S-D40	Single Row Barrier Strip	10	250	10	22-14	Screw, M3.5	Closed Bottom with Flange	Chassis, Panel	\$ 4.49
2275399	Jameco Valuepro	HI-202-10PH-S-D40	Single Row Barrier Strip	10	250	10	22-14	Screw, M3.5	Insulated Solder Turret with Flange	Chassis, Panel	\$ 4.75
2275279	Jameco Valuepro	HI-201-10PH-S-D40	Single Row Barrier Strip	10	250	10	22-14	Screw, M3.5	PC Pin with Flange	Through Hole	\$ 3.75
2275455	Jameco Valuepro	HI-201-10P	Single Row Barrier Strip	10	250	10	22-14	Screw, M3.5	PC Pin, w/o Flange	Chassis, Panel	\$ 3.95
2275223	Jameco Valuepro	HI-200-12PH-S-D40	Single Row Barrier Strip	10	250	12	22-14	Screw, M3.5	Closed Bottom with Flange	Chassis, Panel	\$ 4.95
2275407	Jameco Valuepro	HI-202-12PH-S-D40	Single Row Barrier Strip	10	250	12	22-14	Screw, M3.5	Insulated Solder Turret with Flange	Chassis, Panel	\$ 4.95
2275423	Jameco Valuepro	HI-201-12PH-S-D40	Single Row Barrier Strip	10	250	12	22-14	Screw, M3.5	PC Pin with Flange	Chassis, Panel	\$ 4.39
2275415	Jameco Valuepro	HI-201-12P	Single Row Barrier Strip	10	250	12	22-14	Screw, M3.5	PC Pin, w/o Flange	Chassis, Panel	\$ 4.95
2277015	Molex	38720-6303	Single Row Barrier Strip	15	300	3	22-14	Screw, 6-32	PC Pin,w/o Flange	Through Hole	\$ 1.95
797849	Molex	38720-6305	Single Row Barrier Strip	15	300	5	14-22	Screw, 6-32	PC Pin, w/o Flange	Through Hole	\$ 2.49
2272927	Eaton	A102203	Single Row Barrier Strip	20	250	3	22-14	Screw, 6-32	PC Pin,Offset, w/o Flange	Through Hole	\$ 0.89
2272983	Eaton	A102204	Single Row Barrier Strip	20	250	4	22-14	Screw, 6-32	PC Pin,Offset, w/o Flange	Chassis, Panel	\$ 1.49
2272975	Eaton	A104204R26	Single Row Barrier Strip	20	250	4	22-14	Screw, 6-32	PC Pin,Offset,R/A, w/o Flange	Through Hole	\$ 1.95
2273055	Magnum	A20220604	Single Row Barrier Strip	30	300	6	22-12	Screw, 6-32	PC Pin, w/o Flange	Through Hole	\$ 2.49
2272943	Eaton	A207108R42	Single Row Barrier Strip	30	300	8	22-12	Screw, 6-32	PC Pin Right Angle with Flange	Through Hole	\$ 2.95
2272959	Eaton	A303102	Single Row Barrier Strip	30	600	2	22-12	Screw, 6-32	Closed Bottom with Flange	Through Hole	\$ 0.99
2272967	Eaton	A382207	Single Row Barrier Strip	30	600	7	22-12	Screw, 6-32	PC Pin, w/o Flange	Through Hole	\$ 2.95
2281111	TYCO Power Systems	SSB7TM100102	Single Row Barrier Strip	30	600	10	10	Screw, 6-32	Open Bottom with Flange	Through Hole	\$ 4.95
2162628	Arndt	HB951-08P	Single Row Tri-Barrier Strip	10	250	8	22-14	Screw, M3.5	PC Pin,Offset, w/o Flange	Through Hole	\$ 2.95
2276559	Cooper Industries	CB10111S1968	Single Row Tri-Barrier Strip	15	300	10	22-14	Screw, 6-32	Insulated Solder Turret with Flange	Through Hole	\$ 3.95
2273031	TE Connectivity	4PCV-05-006	Single Row Tri-Barrier Strip	20	150	5	22-12	Screw, 6-32	PC Pin,Offset, w/o Flange	Through Hole	\$ 1.25
2277895	TE Connectivity	4PCV-06-006	Single Row Tri-Barrier Strip	20	150	6	22-12	Screw, 6-32	PC Pin,Offset, w/o Flange	Through Hole	\$ 1.49
2277903	TE Connectivity	4PCV-08-006	Single Row Tri-Barrier Strip	20	150	8	22-14	Screw, 6-32	PC Pin,Offset, w/o Flange	Through Hole	\$ 1.95
2277911	Dinkle	DT35-B01W-02	Single Row Tri-Barrier Strip	20	300	2	22-12	Screw, M3.5	PC Pin,Offset, w/o Flange	Through Hole	\$ 1.09



[Click Here to Request a Large Quantity Quote](#)

TERMINAL BLOCK BARRIER TERMINALS

Jameco Part#	Manufacturer	Manufacturer Part #	Description	Maximum Current Rating (A)	Maximum Voltage Rating (V)	Number of Positions	Wire Size (AWG)	Top Termination	Bottom Termination	Mounting	Price 1
2133616	Dinkle	DT39-B01W-06	Single Row Tri-Barrier Strip	20	300	6	22-12	Screw, M3.5	PC Pin,Offset, w/o Flange	Through Hole	\$ 1.25
2133624	Dinkle	DT39-B01W-08	Single Row Tri-Barrier Strip	20	300	8	22-12	Screw, M3.5	PC Pin,Offset, w/o Flange	Through Hole	\$ 1.95
2277919	Dinkle	DT35-B01W-09	Single Row Tri-Barrier Strip	20	300	9	22-12	Screw, M3.5	PC Pin,Offset, w/o Flange	Through Hole	\$ 2.49
2277927	Dinkle	DT35-B01W-10	Single Row Tri-Barrier Strip	20	300	10	22-12	Screw, M3.5	PC Pin,Offset, w/o Flange	Through Hole	\$ 2.95
2277935	Dinkle	DT35-B01W-14	Single Row Tri-Barrier Strip	20	300	14	22-12	Screw, M3.5	PC Pin,Offset, w/o Flange	Through Hole	\$ 3.49
2272951	TE Connectivity	6PCR-03	Single Row Tri-Barrier Strip	25	300	3	22-12	Screw, 6-32	PC Pin Right Angle w/o Flange	Through Hole	\$ 0.99
2277087	TE Connectivity	6PCV-04	Single Row Tri-Barrier Strip	25	300	4	22-12	Screw, 6-32	PC Pin Right Angle w/o Flange	Through Hole	\$ 1.49
2277079	TE Connectivity	6PCV-06	Single Row Tri-Barrier Strip	25	300	6	22-12	Screw, 6-32	PC Pin,Offset, w/o Flange	Through Hole	\$ 1.95
2273039	Eaton	CB20221107	Single Row Tri-Barrier Strip	30	300	11	22-12	Screw, 6-32	PC Pin,Offset, w/o Flange	Through Hole	\$ 2.95
2272919	Eaton	CB20221207	Single Row Tri-Barrier Strip	30	300	12	22-12	Screw, 6-32	PC Pin,Offset, w/o Flange	Through Hole	\$ 3.95
2277071	Molex	386608803	Single Row Tri-Barrier Strip	45	600	3	18-8	Screw, 6-32	PC Pin, Zig Zag, w/o Flange	Through Hole	\$ 3.29