



[Click Here to Request a Large Quantity Quote](#)

INTERCONNECTS RF CONNECTORS

Jameco Part#	Manufacturer	Manufacturer Part #	Family	Gender	Body Orientation	Impedance	Contact Plating	Contact Material	Body Plating	Body Material	Price 1
2116365	Pomona Electronics	72934	Assorted Adapters	Female/Male	Assorted	50 Ohm	Gold	Brass/Beryllium Copper	Gold/Nickel	Brass	\$ 489.95
2116040	Pomona Electronics	5698	Assorted Adapters	Female/Male	Assorted	50 Ohm	Gold	Brass/Phosphor Bronze	Silver	Brass	\$ 244.95
2077618	Jameco Valuepro	BNC-CR	BNC	Female	Right Angle	75 Ohm	Tin	Tin	Nickel	Brass	\$ 0.75
111561	Steren Electronics	200-148	BNC	Female	Straight	50 Ohm	Gold	Brass	Nickel	Brass/Zinc	\$ 2.25
71590	Jameco Valuepro	G1B235-R	BNC	Female	Straight	50 Ohm	Gold	Brass	Nickel	Steel	\$ 1.75
2161297	Jameco Valuepro	B-235-1-R	BNC	Female	Straight	50 Ohm	Gold	Phosphor Bronze	Nickel	Brass	\$ 1.09
421331	TE Connectivity	227726-3	BNC	Female	Straight	50 Ohm	Gold	Phosphor Bronze	Nickel	Brass	\$ 4.25
658427	Amphenol	112424	BNC	Female	Straight	50 Ohm	Gold	Phosphor Bronze	Nickel	Brass	\$ 3.49
223360	Amphenol	31-5	BNC	Female	Straight	50 Ohm	Gold	Silver	Nickel	Brass	\$ 3.95
355178	Jameco Valuepro	31-221-VP	BNC	Female	Straight	50 Ohm	Gold Over Nickel	Phosphor Bronze	Nickel	Brass	\$ 1.75
223520	Amphenol	31-236-RFX	BNC	Female	Straight	50 Ohm	Silver	Silver	Nickel	Brass	\$ 1.49
2280239	Amphenol	112495	BNC	Female	Straight	75 Ohm	Gold	Phosphor Bronze	Nickel	Zinc	\$ 2.95
174290	Jameco Valuepro	TBC-090-R	BNC	Female	Straight		Gold	Bass	Nickel	Brass	\$ 1.25
2225924	Jameco Valuepro	MCI-7062 50OHM	BNC	Female/Female	Straight	50 Ohm	Gold	Brass	Nickel	Zinc	\$ 2.49
658451	Amphenol	112437	BNC	Female/Female	Straight	50 Ohm	Gold	Phosphor Bronze	Nickel	Brass	\$ 3.79
355152	Jameco Valuepro	31-219-RFX-VP-R	BNC	Female/Female	Straight	50 Ohm	Silver	Beryllium Copper	Nickel	Brass	\$ 2.95
2185811	Amphenol	31-5500	BNC	Female/Female	Straight		Gold	Brass	Nickel	Brass	\$ 0.29
71909	Steren Electronics	200-160	BNC	Female/Female	Straight		Gold	Brass/Zinc	Nickel	Brass/Zinc	\$ 1.19
2258611	Jameco Valuepro	FFF-T-BNC	BNC	Female/Female/Female	Tee Style	50 Ohm	Gold	Brass	Nickel	Brass	\$ 0.79
72629	Steren Electronics	200-150	BNC	Female/Female/Female	Tee Style	50 Ohm	Gold	Brass/Zink	Nickel	Brass/Zinc	\$ 1.25
118594	Steren Electronics	200-155	BNC	Female/Male/Female	Tee Style	50 Ohm	Gold	Brass/Zinc	Nickel	Brass/Zinc	\$ 1.75
2084341	Amphenol	MX-554A/U-100	BNC	Male	Straight	100 Ohm	Silver	Brass	Nickel	Brass	\$ 0.79
188306	Amphenol	31-320-RFX	BNC	Male	Straight	50 Ohm	Gold	Brass	Nickel	Brass	\$ 2.49
2185731	Amphenol	31-347	BNC	Male	Straight	50 Ohm	Gold	Brass	Nickel	Brass	\$ 0.39
2185820	Amphenol	31-332	BNC	Male	Straight	50 Ohm	Gold	Brass	Nickel	Brass	\$ 0.39
71458	Jameco Valuepro	B-611T	BNC	Male	Straight	50 Ohm	Gold	Brass	Nickel	Brass	\$ 1.25
2185694	Amphenol	31-321-1002	BNC	Male	Straight	50 Ohm	Gold	Brass	Nicle	Brass	\$ 1.09
71482	Steren Electronics	200-145	BNC	Male	Straight	50 Ohm	Gold	Brass/Zinc	Nickel	Brass/Zinc	\$ 1.09
2185723	Amphenol	31-206	BNC	Male	Straight	50 Ohm	Silver	Beryllium Copper	Silver	Brass	\$ 6.95
223394	Amphenol	31-212	BNC	Male	Straight	50 Ohm	Silver	Brass	Nickel	Brass	\$ 3.95
2258620	Jameco Valuepro	RG-6U-BNC	BNC	Male	Straight	75 Ohm	Gold	Brass	Nickel	Brass	\$ 0.79
2258638	Jameco Valuepro	RG-59U-BNC	BNC	Male	Straight	75 Ohm	Gold	Brass	Nickel	Brass	\$ 0.99
2085052	Amphenol	31-71013	BNC	Male	Straight	75 Ohm	Gold	Brass	Nickel	Brass	\$ 1.25
71271	Steren Electronics	200-143	BNC	Male	Straight	75 Ohm	Gold	Brass/Zink	Nickel	Brass/Zinc	\$ 1.25
2185993	Amphenol	MX554A/U	BNC	Male	Straight	91 Ohm	Gold	Brass	Nickel	Brass	\$ 1.49
2277023	Amphenol	31-6-RFX	BNC	Male Cap	Straight				Nickel	Zinc	\$ 1.49
127352	Jameco Valuepro	B-412-R	BNC	Male/Female	Right Angle	50 Ohm	Gold	Brass	Nickel	Brass	\$ 3.59
2115901	Pomona Electronics	4108-20DB	BNC	Male/Female	Straight	50 Ohm	Gold	Brass	Tarnish Resistant	Brass	\$ 94.95
2115899	Pomona Electronics	4108-10DB	BNC	Male/Female	Straight	50 Ohm	Gold	Brass	Tarnish Resistant	Brass	\$ 94.95
2115928	Arndt	MX575A/U	BNC	Male/Female	Straight	75 Ohm	Gold	Brass	Tarnish Resistant	Brass	\$ 1.49
2258603	Jameco Valuepro	MF-RA-BNC	BNC	Male/Male	Right Angle	50 Ohm	Gold	Brass	Nickel	Brass	\$ 0.79
127343	Jameco Valuepro	B-311	BNC	Male/Male	Straight	50 Ohm	Gold	Brass	Nickel	Brass	\$ 2.49
2205448	Amphenol	31-71032	BNC	Plug	Straight	75 Ohm	Gold	Brass	Nickel	Brass	\$ 1.25
2284807	Pomona Electronics	1452	BNC/Binding Post	Female/Male	Straight	50 Ohm	Nickel	Brass	Nickel	Brass	\$ 16.49
2284799	Pomona Electronics	1296	BNC/Binding Post	Male/Female	Straight	50 Ohm	Nickel	Brass	Nickel	Brass	\$ 18.49
2284791	Pomona Electronics	1269	BNC/Double Banana	Female/Male	Straight		Nickel	Brass	Nickel	Brass	\$ 10.29
114753	Jameco Valuepro	RB312	BNC-RCA	Male/Female	Straight		Nickel	Brass	Nickel	Brass	\$ 1.49
114789	Jameco Valuepro	BR312-R	BNC-RCA	Male/Male	Straight		Nickel	Brass	Nickel	Zinc	\$ 1.95



[Click Here to Request a Large Quantity Quote](#)

INTERCONNECTS RF CONNECTORS

Jameco Part#	Manufacturer	Manufacturer Part #	Family	Gender	Body Orientation	Impedance	Contact Plating	Contact Material	Body Plating	Body Material	Price 1
2272079	Kobiconn	17PF059	F Type	Female	Straight		Nickel	Brass	Nickel	Brass	\$ 0.29
2276943	Amphenol	172300	F Type	Male	Straight	50 Ohm	Gold	Phosphor Bronze	Nexcote	Brass	\$ 12.95
2276951	Amphenol	17312	F Type	Male	Straight	50 Ohm	Gold	Phosphor Bronze	Nickel	Brass	\$ 9.95
2272143	Jameco Valuepro	SNS1P6-VP	F Type Seal	Male	Straight	75 Ohm	POM		Brass	Brass	\$ 0.49
1121110	Jameco Valuepro	G7409-R	G7409-R	Male	Straight	50 Ohm	Gold Over Nickel	Brass	Nickel Over Copper	Brass	\$ 1.25
2277047	Huber & Suhner	32 N-716-50-2/133 WE	N Type	Male	Straight	50 Ohm	Sucoplate	Brass	Sucoplate	Brass	\$ 119.95
145382	Jameco Valuepro	S-P215-10A-HI-R GGT	SMA	Female	Straight	50 Ohm	Gold	Beryllium Copper	Gold	Brass	\$ 2.25
2091541	Amphenol	132119RP	SMA	Female	Straight	50 Ohm	Gold	Beryllium Copper	Gold	Brass	\$ 4.95
159531	Jameco Valuepro	S-2454-GGT	SMA	Female	Straight		Gold	Brass	Gold	Brass	\$ 2.95
659041	Amphenol	132169	SMA	Female/Female	Straight	50 Ohm	Gold	Beryllium Copper	Gold	Brass	\$ 4.95
659059	Amphenol	132170	SMA	Female/Female	Straight	50 Ohm	Gold	Beryllium Copper	Gold	Brass	\$ 7.49
160013	Jameco Valuepro	CH-7818-N-R	SMA	Female/Female	Straight	50 Ohm	Gold	Brass	Nickel	Brass	\$ 3.29
153294	Jameco Valuepro	SMA-7817-R	SMA	Female/Female	Straight		Gold	Brass	Gold	Brass	\$ 2.15
153366	Jameco Valuepro	4804-R	SMA	Male	Straight	50 Ohm	Gold	Brass	Nickel	Brass	\$ 2.95
153286	Jameco Valuepro	SMA-7813-R	SMA	Male	Straight	50 Ohm	Gold Over Nickel	Phosphor Bronze	Gold Over Nickel	Brass	\$ 2.95
161307	Jameco Valuepro	S-412-G-R	SMA	Male/Female	Right Angle		Gold	Brass	Gold	Brass	\$ 4.49
161294	Jameco Valuepro	S-311-G-R	SMA	Male/Male	Straight		Gold	Brass	Gold	Brass	\$ 2.75
2185985	Amphenol	95625	SMA to BNC	Female/Male	Right Angle		Gold	Brass	Nickel	Brass	\$ 0.29
159469	Jameco Valuepro	CH7830-N-R	SMA-BNC	Female/Female	Straight		Gold	Brass	Nickel	Brass	\$ 2.95
153454	Jameco Valuepro	SB-321-R	SMA-BNC	Female/Male	Straight		Gold	Brass	Nickel	Brass	\$ 2.25
159477	Jameco Valuepro	CH-7820-N-R	SMA-BNC	Male/Female	Straight		Gold	Brass	Nickel	Brass	\$ 2.95
153593	Jameco Valuepro	4288-R	SMA-BNC	Male/Male	Straight		Gold	Brass	Gold	Brass	\$ 2.95
2085204	Amphenol	82-5590	Twinax	Female	Straight		Gold	Phosphor Bronze	Nickel	Brass	\$ 5.95