



[Click Here to Request a Large Quantity Quote](#)

INTERCONNECTS RECTANGULAR CONNECTORS IDC

Jameco Part#	Manufacturer	Manufacturer Part #	Gender	Number of Contacts	Number of Rows	Maximum Voltage Rating	Maximum Current Rating (A)	Maximum Contact Resistance	Contact Plating	Contact Material	Housing Material	Body Orientation	Housing Color	Pitch	Product Length	Price 1
2276959	TE Connectivity	3-641435-2	Plug	2	1	250VDC/250VAC	1	20mOhm	Tin	Tin	Nylon	Right Angle	Orange	3.96mm	11.89mm	\$ 0.49
42658	Jameco Valuepro	8200-14-R	Plug	14	2	250VDC/250VAC	1	30mOhm	Phosphor Bronze	Phosphor Bronze	Polybutylene Terephthalate	Right Angle	Black	2.54mm	22.74mm	\$ 0.89
42674	Jameco Valuepro	8200-16-R	Plug	16	2	250VDC/250VAC	1	30mOhm	Gold	Phosphor Bronze	Polybutylene Terephthalate	Straight	Black	2.54mm	25.12mm	\$ 0.99
104097	Jameco Valuepro	8200-20-R	Plug	20	2	250VDC/250VAC	1	30mOhm	Phosphor Bronze	Phosphor Bronze	Polybutylene Terephthalate	Straight	Black	2.54mm	29.74mm	\$ 1.09
2271415	Arndt	IDC-24-0.1	Plug	24	2	250VDC/250VAC	1	20mOhm	Gold	Brass	Polybutylene Terephthalate	Right Angle	Black	2.54mm	35.75mm	\$ 1.19
42691	Jameco Valuepro	8200-24-R	Plug	24	2	250VDC/250VAC	1	20mOhm	Gold Over Nickel	Brass	Polybutylene Terephthalate	Right Angle	Black	2.54mm	35.75mm	\$ 1.25
42712	Jameco Valuepro	8200-40-R	Plug	40	2	250VDC/250VAC	1	30mOhm	Phosphor Bronze	Phosphor Bronze	Polybutylene Terephthalate	Straight	Black	2.54mm	55.2mm	\$ 1.39
742215	TE Connectivity	1658621-1	Receptacle	10	2	250VDC/250VAC	1	20mOhm	Gold Over Nickel	Phosphor Bronze	Thermoplastic	Right Angle	Black	2.54mm	17.27mm	\$ 0.79
138376	Jameco Valuepro	8000-10NE	Receptacle	10	2	250VDC/250VAC	3	20mOhm	Gold	Copper Alloy	Polybutylene Terephthalate	Right Angle	Black	2.54mm	17.27mm	\$ 0.39
153948	Jameco Valuepro	8000-14-R	Receptacle	14	2	250VDC/250VAC	1	30mOhm	Phosphor Bronze	Phosphor Bronze	Polybutylene Terephthalate	Right Angle	Black	2.54mm	22.35mm	\$ 0.49
525325	TE Connectivity	746285-3	Receptacle	16	2	250VDC/250VAC	1	20mOhm	Gold Over Nickel	Phosphor Bronze	Thermoplastic	Right Angle	Black	2.54mm	24.89mm	\$ 0.99
901722	TE Connectivity	1658622-3	Receptacle	16	2	250VDC/250VAC	1	20mOhm	Gold Over Nickel	Phosphor Bronze	Thermoplastic	Right Angle	Black	2.54mm	17.78mm	\$ 1.25
119467	Jameco Valuepro	8000-16-R	Receptacle	16	2	250VDC/250VAC	3	20mOhm	Gold	Copper Alloy	Polybutylene Terephthalate	Right Angle	Black	2.54mm	24.94mm	\$ 0.55
525333	TE Connectivity	746285-4	Receptacle	20	2	250VDC/250VAC	1	20mOhm	Gold Over Nickel	Phosphor Bronze	Thermoplastic	Right Angle	Black	2.54mm	29.97mm	\$ 1.39
901600	TE Connectivity	1658621-9	Receptacle	20	2	250VDC/250VAC	1	20mOhm	Gold Over Nickel	Phosphor Bronze	Thermoplastic	Right Angle	Black	2.54mm	55.37mm	\$ 2.09
32522	Jameco Valuepro	8000-20-R	Receptacle	20	2	250VDC/250VAC	3	20mOhm	Gold	Copper Alloy	Polybutylene Terephthalate	Right Angle	Black	2.54mm	30mm	\$ 0.59
2218134	TE Connectivity	622-2630-B	Receptacle	26	2	250VDC/250VAC	1	20mOhm	Gold	Beryllium Copper	Thermoplastic	Right Angle	Blue	2.54mm	37.4mm	\$ 0.89
525413	TE Connectivity	746288-6	Receptacle	26	2	250VDC/250VAC	1	20mOhm	Gold Over Nickel	Phosphor Bronze	Thermoplastic	Right Angle	Black	2.54mm	37.59mm	\$ 1.49
901642	TE Connectivity	1658622-1	Receptacle	26	2	250VDC/250VAC	1	20mOhm	Gold Over Nickel	Phosphor Bronze	Thermoplastic	Right Angle	Black	2.54mm	10.16mm	\$ 0.75
32564	Jameco Valuepro	8000-26-R	Receptacle	26	2	250VDC/250VAC	3	20mOhm	Gold	Copper Alloy	Polybutylene Terephthalate	Right Angle	Black	2.54mm	37.59mm	\$ 0.69
32644	Jameco Valuepro	8000-34-R	Receptacle	34	2	250VDC/250VAC	3	20mOhm	Gold	Copper Alloy	Polybutylene Terephthalate	Right Angle	Black	2.54mm	47.8mm	\$ 0.79
32679	Jameco Valuepro	8000-40-R	Receptacle	40	2	250VDC/250VAC	1	30mOhm	Phosphor Bronze	Phosphor Bronze	Polybutylene Terephthalate	Right Angle	Black	2.54mm	55.37mm	\$ 0.85
1963124	TE Connectivity	1-746610-5	Receptacle	40	2	250VDC/250VAC	4	20mOhm	Gold Over Nickel	Brass	Nylon	Straight	White	2.54mm	17.78mm	\$ 1.49
32708	Jameco Valuepro	8000-50-R	Receptacle	50	2	250VDC/250VAC	3	20mOhm	Gold	Copper Alloy	Polybutylene Terephthalate	Right Angle	Black	2.54mm	68.18mm	\$ 0.89