

[Click Here to Request a Large Quantity Quote](#)



INTERCONNECTS RECTANGULAR CONNECTORS-SHUNTS AND SHORTING BLOCKS

Jameco Part#	Manufacturer	Manufacturer Part #	Number of Contacts	Number of Rows	Type	Maximum Current Rating (A)	Maximum Contact Resistance	Contact Plating	Contact Material	Housing Material	Column1	Pitch (mm)	Product Depth (mm)	Product Length (mm)	Price 1
152671	Jameco Valuepro	2012JH-R	2	1	Top Closed	1	30mOhm	Gold	Brass	Polyamide66	Black Tab	2.54	6.47	5	\$ 0.15
19141	Jameco Valuepro	7600A-R	2	1	Top Closed	3	20mOhm	Gold Over Nickel	Phosphor Bronze	Polybutylene Terephthalate	Black	2.54	6.4	5	\$ 0.15
112432	Jameco Valuepro	2012J-CR	2	1	Top Closed	3	20mOhm	Gold Over Nickel	Phosphor Bronze	Polybutylene Terephthalate	Red	2.54	6.4	5	\$ 0.15
112442	Jameco Valuepro	GJWCL-B-R	2	1	Top Closed	3	20mOhm	Gold Over Nickel	Phosphor Bronze	Polybutylene Terephthalate	Blue	2.54	4.95	6.5	\$ 0.15
112425	Jameco Valuepro	JOPENB-R	2	1	Top Open	3	20mOhm	Gold	Phosphor Bronze	Polybutylene Terephthalate	Blue	2.54	5	6	\$ 0.15
112417	Jameco Valuepro	2012J-OR-R	2	1	Top Open	3	20mOhm	Gold	Phosphor Bronze	Polybutylene Terephthalate	Red	2.54	5	6	\$ 0.15
22024	Jameco Valuepro	7600-B-R	2	1	Top Open	3	20mOhm	Gold Over Nickel	Phosphor Bronze	Polybutylene Terephthalate	Black	2.54	6	5	\$ 0.15
119264	Jameco Valuepro	2.0 MINI JUMPER OPEN-R	2	1	Top Open	3	20mOhm	Gold	Phosphor Bronze	Polybutylene Terephthalate	Black	2.54	3.5	4	\$ 0.09