



[Click Here to Request a Large Quantity Quote](#)

INTERCONNECTS - SCREW TERMINAL BLOCKS

Jameco Part#	Manufacturer	Manufacturer Part #	Description	Pitch (Inches)	Number of Positions	Maximum Current Rating (A)	Maximum Voltage Rating (V)	Top Termination	Gender	Body Orientation	Mounting	Number of Rows	Price 1
2280751	Molex	44764-2401	Header	0.118	24	7	250	Press-Fit	Male	Right Angle	Through Hole	2	\$ 4.95
2279855	Phoenix Contact	1772618	Plug	0.138	2	8	300	Screwless, Leg Spring	Female	180°	Cable Mount	2	\$ 2.95
2094506	On Shore Technology	OSTTE020161	Header	0.138	2	10	125	Screw, Leaf Spring, Wire Guard	Female	Straight	Through Hole	1	\$ 0.49
2094514	On Shore Technology	OSTTE030161	Header	0.138	3	10	125	Screw, Leaf Spring, Wire Guard	Female	Straight	Through Hole	1	\$ 0.79
2279871	Amphenol	TS04110B0000G	Plug	0.138	4	8	300	Screw, Leaf Spring, Wire Guard	Female	270°	Cable Mount	1	\$ 2.95
2279863	Phoenix Contact	1772634	Plug	0.138	4	8	300	Screwless, Leg Spring	Female	180°	Cable Mount	2	\$ 5.95
2124411	On Shore Technology	OSTTE040161	Header	0.138	4	10	125	Screw, Leaf Spring, Wire Guard	Female	Straight	Through Hole	1	\$ 0.89
2277063	TE Connectivity	2-796694-0	Header	0.138	20	11	300	Screwless	Male	Vertical	Through Hole	1	\$ 1.95
2279831	Phoenix Contact	1851041	Plug	0.150	2	8	300	Screwless, Leg Spring	Female	Straight	Cable Mount	1	\$ 2.95
2235751	Phoenix Contact	1850673	Plug	0.150	3	8	300	Screw, Pressure Clip	Female	Straight	Cable Mount	1	\$ 3.95
2279839	Phoenix Contact	1851054	Plug	0.150	3	8	300	Screwless, Leg Spring	Female	180°	Cable Mount	1	\$ 4.95
2273143	Phoenix Contact	1827884	Header	0.150	4	8	300	Screwless	Male	Right Angle	Through Hole	1	\$ 3.25
2279847	Phoenix Contact	1851067	Plug	0.150	4	8	300	Screwless, Leg Spring	Female	180°	Cable Mount	1	\$ 6.95
2235743	Phoenix Contact	1850699	Plug	0.150	5	8	300	Screw, Pressure Clip	Female	Straight	Cable Mount	1	\$ 8.95
2280071	Phoenix Contact	1827897	Header	0.150	5	8	300	Screwless	Male	Right Angle	Through Hole	1	\$ 3.49
2280079	Phoenix Contact	1879324	Header	0.150	6	8	300	Press-Fit	Male	Vertical	Through Hole	1	\$ 4.95
2273151	Phoenix Contact	1827907	Header	0.150	6	8	300	Screwless	Male	Right Angle	Through Hole	1	\$ 3.79
2280191	Phoenix Contact	1827907	Header	0.150	6	8	300	Screwless	Male	Right Angle	Through Hole	1	\$ 3.95
2280199	Phoenix Contact	1827910	Header	0.150	7	8	300	Screwless	Male	Right Angle	Through Hole	1	\$ 3.95
2273119	Phoenix Contact	1803633	Plug	0.150	8	8	300	Screw, Clamping Yoke	Female	Straight	Cable Mount	1	\$ 6.95
2280207	Phoenix Contact	1830127	Header	0.150	8	8	300	Screwless	Male	Right Angle	Through Hole	2	\$ 6.95
2285127	Phoenix Contact	1850932	Plug	0.150	10	8	160	Screw	Female	Vertical	Cable Mount	1	\$ 14.95
2287447	Phoenix Contact	1827949	Header	0.150	10	8	160	Screw	Male	Right Angle	Through Hole	1	\$ 4.95
2280231	Phoenix Contact	1879366	Header	0.150	10	8	300	Press-Fit	Male	Vertical	Through Hole	1	\$ 6.95
2235727	Phoenix Contact	1850767	Plug	0.150	12	8	300	Screw, Pressure Clip	Female	Straight	Cable Mount	1	\$ 19.95
2280215	Phoenix Contact	1830143	Header	0.150	12	8	300	Screwless	Male	Right Angle	Through Hole	2	\$ 8.95
2280223	Phoenix Contact	1830169	Header	0.150	16	8	300	Screwless	Male	Right Angle	Through Hole	2	\$ 9.95
2285015	Phoenix Contact	1844948	Header	0.150	18	8	250	Screw	Male	Vertical	Through Hole	1	\$ 6.95
2273135	Phoenix Contact	1851397	Plug	0.150	18	8	300	Screwless, Leg Spring, Push-In Spring	Female	Straight	Cable Mount	1	\$ 29.95
2287199	Phoenix Contact	1844951	Header	0.150	19	8	160	Screw	Male	Vertical	Through Hole	1	\$ 6.95
99427	Dinkle	TERM BLK-R	Header	0.197	2	10	300	Screw	Female	Right Angle	Through Hole	1	\$ 0.65
2159656	Phoenix Contact	1869062	Header	0.197	2	10	300	Screw, Rising Cage Clamp	Female	55° (125°)	Through Hole	1	\$ 1.05
189676	On Shore Technology	OSTTC020162	Header	0.197	2	15	300	Screw, Leaf Spring, Wire Guard	Female	Straight	Through Hole	1	\$ 0.55
164794	On Shore Technology	OSTTH020160	Header	0.197	2	15	300	Screw, Leaf Spring, Wire Guard	Female	Straight	Cable Mount	1	\$ 0.65
2094485	On Shore Technology	OSTTA020161	Header	0.197	2	16	250	Screw, Leaf Spring, Wire Guard	Female	Straight	Through Hole	1	\$ 0.59
161067	Dinkle	EK500A-02P-R	Header	0.197	2	20	300	Screw	Female	45° (135°)	Through Hole	1	\$ 0.79
160785	Dinkle	EK500V-02P-R	Header	0.197	2	20	300	Screw	Female	Straight	Through Hole	1	\$ 0.69
99398	Dinkle	DT128V3P-R	Header	0.197	3	10	300	Screw	Female	Straight	Through Hole	1	\$ 0.99
2120655	On Shore Technology	OSTTC032162	Header	0.197	3	15	300	Screw, Leaf Spring, Wire Guard	Female	Right Angle	Through Hole	1	\$ 0.69
189668	On Shore Technology	OSTTC030162	Header	0.197	3	15	300	Screw, Leaf Spring, Wire Guard	Female	Straight	Through Hole	1	\$ 0.69
164806	On Shore Technology	OSTTH030160	Header	0.197	3	15	300	Screw, Leaf Spring, Wire Guard	Female	Straight	Cable Mount	1	\$ 0.85
2281135	On Shore Technology	OSTTAXX0101	Header	0.197	3	16	250	Screw	Female	Vertical	Through Hole	1	\$ 0.65
2094493	On Shore Technology	OSTTA030161	Header	0.197	3	16	250	Screw, Leaf Spring, Wire Guard	Female	Straight	Through Hole	1	\$ 0.69
2273087	Phoenix Contact	1935174	Header	0.197	3	18	300	Screw	Female	Right Angle	Through Hole	1	\$ 0.55
161059	Dinkle	EK500A-03P-R	Header	0.197	3	20	300	Screw	Female	45° (135°)	Through Hole	1	\$ 1.09
160793	Dinkle	EK500V-03P-R	Header	0.197	3	20	300	Screw	Female	Straight	Through Hole	1	\$ 0.79
2281119	Weidmuller	1640880000	Header	0.197	3	28	250	Press-Fit	Female	Vertical	Through Hole	1	\$ 1.25
2288439	TYCO Power Systems	1-282830-3	Plug	0.197	4	16	250	Screw	Female	Vertical	Cable Mount	1	\$ 1.95
2124429	On Shore Technology	OSTTA040161	Header	0.197	4	16	250	Screw, Leaf Spring, Wire Guard	Female	Straight	Through Hole	1	\$ 0.79
2280623	TYCO Power Systems	787441-1	Plug	0.197	5	7	50	Press-Fit	Male	Right Angle	Through Hole	1	\$ 3.95
2280135	TE Connectivity	207530-2	Header	0.197	18	7.5	600	Press-Fit	Female	Vertical	Through Hole	3	\$ 9.95
2120567	On Shore Technology	OSTYC022150	Header	0.200	2	10	300	Screw, Leaf Spring, Wire Guard	Female	Right Angle	Through Hole	1	\$ 0.69
2285487	Phoenix Contact	1759017	Header	0.200	2	12	250	Press-Fit	Male	Right Angle	Through Hole	1	\$ 0.59
2280087	Phoenix Contact	1758018	Header	0.200	2	12	300	Screwless	Male	Vertical	Through Hole	1	\$ 0.59
2120647	On Shore Technology	OSTTC022162	Header	0.200	2	15	300	Screw, Leaf Spring, Wire Guard	Female	Right Angle	Through Hole	1	\$ 0.49
152347	On Shore Technology	OSTTA024163	Header	0.200	2	15	300	Screw, Leaf Spring, Wire Guard	Female	Straight	Through Hole	1	\$ 0.65



[Click Here to Request a Large Quantity Quote](#)

INTERCONNECTS - SCREW TERMINAL BLOCKS

Jameco Part#	Manufacturer	Manufacturer Part #	Description	Pitch (Inches)	Number of Positions	Maximum Current Rating (A)	Maximum Voltage Rating (V)	Top Termination	Gender	Body Orientation	Mounting	Number of Rows	Price 1
2094581	On Shore Technology	OSTTJ025153	Plug	0.200	2	20	300	Screw, Leaf Spring, Wire Guard	Female	Right Angle	Cable Mount	1	\$ 0.89
2120575	On Shore Technology	OSTYC032150	Header	0.200	3	10	300	Screw, Leaf Spring, Wire Guard	Female	Right Angle	Through Hole	1	\$ 0.85
2280591	Phoenix Contact	1759020	Header	0.200	3	12	250	Press-Fit	Male	Right Angle	Through Hole	1	\$ 0.89
2285319	Phoenix Contact	1758021	Header	0.200	3	12	250	Press-Fit	Male	Vertical	Through Hole	1	\$ 0.89
2285087	Phoenix Contact	1779987	Plug	0.200	3	12	250	Screw	Female	Vertical	Cable Mount	1	\$ 2.75
2276975	Weidmuller	1627250000	Plug	0.200	3	14	300	Screw, Clamping Yoke	Male	Straight	Cable Mount	1	\$ 1.95
152355	On Shore Technology	OSTTA034163	Header	0.200	3	15	300	Screw, Leaf Spring, Wire Guard	Female	Straight	Through Hole	1	\$ 0.85
2094590	On Shore Technology	OSTTJ035153	Header	0.200	3	20	300	Screw, Leaf Spring, Wire Guard	Female	Right Angle	Cable Mount	1	\$ 1.25
2280855	Phoenix Contact	1762062	Header	0.200	4	10	250	Press-Fit	Male	Right Angle	Through Hole	2	\$ 1.75
2285095	Phoenix Contact	1759033	Header	0.200	4	12	250	Press-Fit	Male	Right Angle	Through Hole	1	\$ 1.19
2229685	TE Connectivity	332520004	Plug	0.200	4	15	250	Screw, Push-In	Female	Straight	Cable Mount	1	\$ 0.89
2124445	On Shore Technology	OSTTA044163	Header	0.200	4	15	300	Screw, Leaf Spring, Wire Guard	Female	Straight	Through Hole	1	\$ 0.95
2273095	Phoenix Contact	1733596	Header	0.200	4	15	300	Screw, Rising Cage Clamp	Female	35° (145°)	Through Hole	1	\$ 2.49
2235364	Wiecon	25.340.0653.0	Plug	0.200	6	15	300	Screw, Push-In	Female	Straight	Cable Mount	1	\$ 3.95
2276983	Weidmuller	1644760000	Plug	0.200	10	10	300	Screw, Clamping Yoke	Female	90° & 270°	Cable Mount	2	\$ 4.95
2280863	Phoenix Contact	1759091	Header	0.200	10	12	250	Press-Fit	Male	Right Angle	Through Hole	1	\$ 2.95
2280983	Phoenix Contact	1758092	Header	0.200	10	12	250	Press-Fit	Male	Vertical	Through Hole	1	\$ 2.95
2280599	Phoenix Contact	1776605	Header	0.200	10	12	250	Screw	Male	Right Angle	Through Hole	1	\$ 9.95
2280975	Phoenix Contact	1776582	Header	0.200	10	12	250	Screw	Male	Right Angle	Through Hole	1	\$ 7.95
2281335	Phoenix Contact	1777206	Header	0.200	10	12	250	Screw	Male	Vertical	Cable Mount	1	\$ 5.95
2277239	Weco	99-AEG-FB/11-NZ-C	Plug	0.200	11	15	300	Screw	Female	Straight	Cable Mount	1	\$ 3.95
2281367	Weco	231-312/026-000	Plug	0.200	12	16	630	Press-Fit	Female	Vertical	Cable Mount	1	\$ 6.95
2287415	Phoenix Contact	203250	Bridge	0.242	10			Screw	Female	Vertical	-	1	\$ 9.95
2276967	Weidmuller	1623050000	Plug	0.300	2	15	300	Screw, Clamping Yoke	Female	Straight	Cable Mount	1	\$ 1.95
2273127	Phoenix Contact	1720017	Header	0.375	2	30	300	Screw, Rising Cage Clamp	Female	35° (145°)	Through Hole	1	\$ 1.49
2273103	Phoenix Contact	1720020	Header	0.375	3	30	300	Screw, Rising Cage Clamp	Female	35° (145°)	Through Hole	1	\$ 2.25
2285959	Phoenix Contact	3208746	Connector	0.390	1	60	600	Push in, Spring	Female	Vertical	Cable Mount	1	\$ 6.95
2279927	Phoenix Contact	MKDSP10N/3-10.16	Header	0.400	3	60	600	Screw	Female	Right Angle	Through Hole	1	\$ 2.95