



[Click Here to Request a Large Quantity Quote](#)

INTERCONNECTS TERMINALS

Jameco Part#	Manufacturer	Manufacturer Part #	Product Type	Product Depth (inch)	Product Length (inch)	Wire Size (AWG)	Gender	Insulation	Color	Stud Size	Plating	Body Material	Price 1
303247	TE Connectivity	640923-1	Quick Connect	0.11	0.8	22-18	Female	Nylon	Red	—	Tin	Brass	\$ 0.25
459188	Molex	19003-0107	Quick Connect	0.19	0.8	22-18	Female	Nylon	Red	—	Tin	Brass	\$ 0.25
106922	Jameco Valuepro	FDV1-187(8)-R	Quick Connect	0.19	0.7	22-16	Female	Vinyl	Red	—	Tin	Brass	\$ 0.12
2276991	Molex	19007-0001	Quick Connect	0.24	0.6	22-18	Female	Nylon	Red	—	Tin	Brass	\$ 0.39
103668	Jameco Valuepro	FDV1-250-R	Quick Connect	0.25	0.8	22-16	Female	Vinyl	Red	—	Tin	Brass	\$ 0.15
2284943	TYCO Power Systems	42100-2	Quick Connect	0.25	0.8	18-14	Female	Non-Insulated	Natural	—	Tin	Brass	\$ 0.25
109112	Jameco Valuepro	GFF1250-R	Quick Connect	0.30	0.9	22-16	Female	Vinyl	Red	—	Tin	Brass	\$ 0.12
303327	TE Connectivity	640905-1	Quick Connect	0.30	0.9	16-14	Female	Nylon	Blue	—	Tin	Brass	\$ 0.25
489643	Molex	19003-0017	Quick Connect	0.32	0.8	22-18	Female	Nylon 6/6	Red	—	Tin	Brass	\$ 0.29
489635	Molex	19003-0011	Quick Connect	0.32	0.8	22-18	Female	Nylon 6/6	Salmon	—	Tin	Brass	\$ 0.19
489694	Molex	19003-0050	Quick Connect	0.32	0.8	16-14	Female	Nylon 6/6	Blue	—	Tin	Brass	\$ 0.29
460040	Molex	19002-0024	Quick Connect	0.32	0.8	16-14	Female	Nylon	Blue	—	Tin	Brass	\$ 0.25
524197	TE Connectivity	2-520182-2	Quick Connect	0.34	0.9	22-18	Female	Nylon	Red	—	Tin	Brass	\$ 0.19
489627	Molex	19003-0001	Quick Connect	0.38	0.9	22-18	Female	Nylon 6/6	Red	—	Tin	Brass	\$ 0.19
489678	Molex	19003-0040	Quick Connect	0.38	0.9	16-14	Female	Nylon 6/6	Blue	—	Tin	Brass	\$ 0.19
489766	Molex	19005-0005	Quick Connect	0.38	0.9	16-14	Female	Nylon	Blue/Natural	—	Tin	Brass	\$ 0.25
489774	Molex	19005-0010	Quick Connect	0.38	1.0	12-10	Female	Nylon	Yellow	—	Tin	Brass	\$ 0.39
489723	Molex	19004-0001	Quick Connect	0.45	1.0	22-18	Male	Nylon	Red	—	Zinc Chromate	Copper	\$ 0.25
489731	Molex	19004-0005	Quick Connect	0.45	1.0	16-14	Male	Nylon	Blue	—	Zinc Chromate	Copper	\$ 0.35
459188	Molex	19003-0107	Quick Connect	0.78	0.3	22-18	Female	Nylon	Red	—	Tin	Brass	\$ 0.25
460040	Molex	19002-0024	Quick Connect	0.89	0.4	16-14	Female	Nylon	Blue	—	Tin	Brass	\$ 0.25
2284951	TYCO Power Systems	63860-1	Quick Connect PCB	0.25	0.5	—	Male	Non-Insulated	Natural	—	Tin	Brass	\$ 0.25
752464	TE Connectivity	42822-2	Quick Connect PCB	0.29	0.4	—	Male	Non-Insulated	Natural	8-6	Tin	Steel	\$ 0.15
2150897	TE Connectivity	1217056-1	Quick Connect PCB	0.31	0.6	—	Male	Non-Insulated	Natural	—	Tin	Brass	\$ 0.25
103684	Jameco Valuepro	RVS1-3.7-R	Ring Tongue	0.22	0.7	22-16	N/A	Vinyl	Red	6	Tin	Copper	\$ 0.21
844254	TE Connectivity	34105	Ring Tongue	0.22	0.4	22-16	N/A	Non-Insulated	Natural	6	Tin	Copper	\$ 0.15
302720	TE Connectivity	320619	Ring Tongue	0.25	0.7	16-14	N/A	Nylon	Blue	6	Tin	Copper	\$ 0.25
844289	TE Connectivity	34107	Ring Tongue	0.28	0.6	22-16	N/A	Non-Insulated	Natural	6	Tin	Copper	\$ 0.25
302666	TE Connectivity	36152	Ring Tongue	0.28	0.8	22-16	N/A	Nylon	Red	6	Tin	Copper	\$ 0.29
2144681	Panduit Corporation	PV10-8R-D	Ring Tongue	0.31	1.1	12-10	N/A	Non-Insulated	Yellow	8	Tin	Copper	\$ 0.25
302674	TE Connectivity	31890	Ring Tongue	0.31	0.8	22-16	N/A	Nylon	Red	8	Tin	Copper	\$ 0.19
302738	TE Connectivity	320565	Ring Tongue	0.34	0.9	16-14	N/A	Nylon	Blue	8	Tin	Copper	\$ 0.25
2285527	Panduit Corporation	PN10-10R-D	Ring Tongue	0.38	1.1	12-10	N/A	Nylon	Yellow	10	Tin	Copper	\$ 0.29
103588	Jameco Valuepro	SVS1-3.7-R	Spade Tongue	0.22	0.8	22-16	Male	Vinyl	Red	6	Tin	Copper	\$ 0.15
2129764	ETCO	PS55-130-THB	Spade Tongue	0.24	0.5	26-22	Male	Non-Insulated	Natural	6	Tin	Brass	\$ 0.25
2160577	Jameco Valuepro	SNYDL1-3.7/34541	Spade Tongue	0.25	0.9	22-16	Male	Nylon	Red	6	Tin	Copper	\$ 0.15
302877	TE Connectivity	34541	Spade Tongue	0.25	0.8	22-16	Male	Nylon	Red	6	Tin	Copper	\$ 0.25
2160631	Jameco Valuepro	SNBL1-3.7/323127	Spade Tongue	0.25	0.6	22-16	Male	Non-Insulated	Natural	6	Tin	Copper	\$ 0.12
103596	Jameco Valuepro	SVM2-4-R	Spade Tongue	0.28	0.8	16-14	Male	Vinyl	Blue	8	Tin	Copper	\$ 0.15
2160585	Jameco Valuepro	SNYDLL2-3.7/35559	Spade Tongue	0.28	0.9	16-14	Male	Nylon	Blue	8	Tin	Copper	\$ 0.15
303010	TE Connectivity	320862	Spade Tongue	0.29	0.7	16-14	Male	Nylon	Blue	8	Tin	Copper	\$ 0.15
302906	TE Connectivity	35559	Spade Tongue	0.30	0.8	16-14	Male	Nylon	Blue	6	Tin	Copper	\$ 0.22
502879	Molex	19144-0001	Spade Tongue	0.32	0.9	22-18	Male	Polyvinyl Chloride	Red	6	Tin	Copper	\$ 0.25

[Click Here to Request a Large Quantity Quote](#)



INTERCONNECTS TERMINALS

Jameco Part#	Manufacturer	Manufacturer Part #	Product Type	Product Depth (inch)	Product Length (inch)	Wire Size (AWG)	Gender	Insulation	Color	Stud Size	Plating	Body Material	Price 1
2234151	Arndt	4FRJ6	Spade Tongue	0.32	0.9	16-14	Male	Vinyl	Blue	10	Tin	Copper	\$ 0.25
2231881	Panduit Corporation	PV10-10LFB-2K	Spade Tongue	0.34	1.0	12-10	Male	Vinyl	Yellow	10	Tin	Copper	\$ 0.25
2234151	Arndt	4FRJ6	Spade Tongue	0.86	0.3	16-14	Male	Vinyl	Blue	10	Tin	Copper	\$ 0.25
303183	TE Connectivity	320562	Splice	0.14	1.3	16-14	Female	Nylon	Blue	—	Tin	Copper	\$ 0.59
303175	TE Connectivity	320559	Splice	0.21	1.3	22-16	Female	Nylon	Red	—	Tin	Copper	\$ 0.49
844107	TE Connectivity	34070	Splice	0.21	1.1	22-16	Female	Nylon	Red	—	Tin	Copper	\$ 0.25
169747	Excel Cell Electronics	ECT UYZ	Splice	0.34	0.5	26-22	Female	Polypropylene	Yellow	—	Tin	—	\$ 0.25
2239154	Jameco Valuepro	878101	Splice	0.37	0.8	18-14	Female	Polypropylene	Blue	—	Tin	Brass	\$ 0.15