

- Operating Temperature: -30 - +85
- Style: Encapsulated
- Mounting Style: Through-Hole
- Load Regulation: Regulated
- Frame: Enclosed
- Color: Black



• See Datasheet for Agency Approvals

Request a Large Quantity Quote

Jameco Part #	Manufacturer Part #	Primary Output Voltage (VDC)	Output Current (A)	Maximum Output Power (W)	Input Voltage (VAC)	Input Voltage (VDC)	Input Frequency	Maximum Input Current (A)	Output Connector Type	Efficiency (%)	Length (inch)	Width (inch)	Height (inch)	Price 1	Price 10
2239752	IRM-01-3.3	3.3	0.3	1	85 to 305		47 to 63	0.025	PC Pin	66	1.33	0.87	0.59	\$4.70	\$3.79
2239816	IRM-01-3.3S	3.3	0.3	1	85 to 305	120 to 430	47 to 63	0.025	SMD	66	1.33	0.87	0.63	\$5.40	\$4.65
2239761	IRM-01-5	5	0.2	1	85 to 305	120 to 430	47 to 63	0.025	PC Pin	70	1.33	0.87	0.59	\$4.70	\$3.79
2239824	IRM-01-5S	5	0.2	1	85 to 305	120 to 430	47 to 63	0.025	SMD	70	1.33	0.87	0.63	\$5.40	\$4.39
2239779	IRM-01-9	9	0.111	1	85 to 305	120 to 430	47 to 63	0.025	PC Pin	72	1.33	0.87	0.59	\$4.70	\$3.79
2239832	IRM-01-9S	9	0.111	1	85 to 305		47 to 63	0.025	SMD	72	1.33	0.87	0.63	\$5.40	\$4.65
2239787	IRM-01-12	12	0.083	1	85 to 305	120 to 430	47 to 63	0.025	PC Pin	74	1.33	0.87	0.59	\$4.70	\$3.79
2239841	IRM-01-12S	12	0.083	1	85 to 305		47 to 63	0.025	SMD	74	1.33	0.87	0.63	\$5.40	\$4.39
2237950	IRM-01-15	15	0.067	1	85 to 305	120 to 430	47 to 63	0.025	PC Pin	75	1.33	0.87	0.59	\$4.70	\$3.79
2239859	IRM-01-15S	15	0.067	1	85 to 305		47 to 63	0.025	SMD	75	1.33	0.87	0.63	\$5.40	\$4.39
2239808	IRM-01-24	24	0.042	1	85 to 305	120 to 430	47 to 63	0.025	PC Pin	77	1.33	0.87	0.59	\$4.70	\$3.79
2239867	IRM-01-24S	24	0.042	1	85 to 305	120 to 430	47 to 63	0.025	SMD	77	1.33	0.87	0.63	\$5.40	\$4.39
2239875	IRM-02-3.3	3.3	0.6	2	85 to 305	120 to 430	47 to 63	0.045	PC Pin	66	1.33	0.87	0.59	\$4.90	\$3.95
2239939	IRM-02-3.3S	3.3	0.6	2	85 to 305		47 to 63	0.045	SMD	66	1.33	0.87	0.63	\$5.60	\$4.55
2239883	IRM-02-5	5	0.4	2	85 to 305		47 to 63	0.045	PC Pin	70	1.33	0.87	0.59	\$4.90	\$3.95
2239947	IRM-02-5S	5	0.4	2	85 to 305		47 to 63	0.045	SMD	70	1.33	0.87	0.63	\$5.60	\$4.55
2239891	IRM-02-9	9	0.222	2	85 to 305		47 to 63	0.045	PC Pin	72	1.33	0.87	0.59	\$4.90	\$3.95
2239955	IRM-02-9S	9	0.222	2	85 to 305		47 to 63	0.045	SMD	72	1.33	0.87	0.63	\$5.60	\$4.55
2239904	IRM-02-12	12	0.167	2	85 to 305		47 to 63	0.045	PC Pin	74	1.33	0.87	0.59	\$4.90	\$3.95
2239963	IRM-02-12S	12	0.167	2	85 to 305		47 to 63	0.045	SMD	74	1.33	0.87	0.63	\$5.60	\$4.55
2239912	IRM-02-15	15	0.133	2	85 to 305		47 to 63	0.045	PC Pin	75	1.33	0.87	0.59	\$4.90	\$3.95
2239971	IRM-02-15S	15	0.133	2	85 to 305		47 to 63	0.045	SMD	75	1.33	0.87	0.63	\$5.60	\$4.55
2239921	IRM-02-24	24	0.086	2	85 to 305		47 to 63	0.045	PC Pin	77	1.33	0.87	0.59	\$4.90	\$3.95
2239980	IRM-02-24S	24	0.086	2	85 to 305		47 to 63	0.045	SMD	77	1.33	0.87	0.63	\$5.60	\$4.55
2239525	IRM-03-3.3	3.3	0.9	3	85 to 305		47 to 63	0.07	PC Pin	68	1.46	0.95	0.59	\$5.00	\$4.15
2239998	IRM-03-3.3S	3.3	0.9	3	85 to 305		47 to 63	0.07	SMD	68	1.46	0.95	0.63	\$5.80	\$4.69
2239509	IRM-03-5	5	0.6	3	85 to 305		47 to 63	0.07	PC Pin	72	1.46	0.95	0.59	\$5.00	\$4.15
2240008	IRM-03-5S	5	0.6	3	85 to 305	120 to 430	47 to 63	0.07	SMD	72	1.46	0.95	0.63	\$5.80	\$4.69
2239517	IRM-03-9	9	0.333	3	85 to 305		47 to 63	0.07	PC Pin	77	1.46	0.95	0.59	\$5.00	\$4.15
2240016	IRM-03-9S	9	0.333	3	85 to 305	120 to 430	47 to 63	0.07	SMD	77	1.46	0.95	0.63	\$5.80	\$4.69
2239488	IRM-03-12	12	0.25	2	85 to 305	120 to 430	47 to 63	0.07	PC Pin	78	1.46	0.95	0.59	\$5.00	\$4.15
2240024	IRM-03-12S	12	0.25	3	85 to 305	120 to 430	47 to 63	0.07	SMD	78	1.46	0.95	0.63	\$5.80	\$4.69
2239533	IRM-03-15	15	0.2	3	85 to 305		47 to 63	0.07	PC Pin	78	1.46	0.95	0.59	\$5.00	\$4.15
2240032	IRM-03-15S	15	0.2	3	85 to 305	120 to 430	47 to 63	0.07	SMD	78	1.46	0.95	0.63	\$5.80	\$4.69
2239496	IRM-03-24	24	0.125	3	85 to 305	120 to 430	47 to 63	0.07	PC Pin	80	1.46	0.95	0.59	\$5.00	\$4.15
2240041	IRM-03-24S	24	0.125	3	85 to 305	120 to 430	47 to 63	0.07	SMD	80	1.46	0.95	0.63	\$5.80	\$4.69
2193125	IRM-05-3.3	3.3	1.25	4.125	85 to 264	120 to 370	47 to 440	0.12	PC Pin	68	1.8	1	0.85	\$6.50	\$5.45
2193133	IRM-05-5	5	1	5	85 to 264	120 to 370	47 to 440	0.12	PC Pin	71	1.8	1	0.85	\$6.50	\$5.45
2193141	IRM-05-12	12	0.42	5.04	85 to 264	120 to 370	47 to 440	0.12	PC Pin	75	1.8	1	0.85	\$6.50	\$5.45
2193150	IRM-05-15	15	0.33	4.95	85 to 264	120 to 370	47 to 440	0.12	PC Pin	75	1.8	1	0.85	\$6.50	\$5.45
2193168	IRM-05-24	24	0.23	5.52	85 to 264	120 to 370	47 to 440	0.12	PC Pin	77	1.8	1	0.85	\$6.50	\$5.45
2193176	IRM-10-3.3	3.3	2.5	8.25	85 to 264	120 to 370	47 to 440	0.25	PC Pin	74	1.8	1	0.85	\$7.00	\$5.69
2193184	IRM-10-5	5	2	10	85 to 264	120 to 370	47 to 440	0.25	PC Pin	77	1.8	1	0.85	\$7.00	\$5.69
2193192	IRM-10-12	12	0.85	10.2	85 to 264	120 to 370	47 to 440	0.25	PC Pin	82	1.8	1	0.85	\$7.00	\$5.69
2193205	IRM-10-15	15	0.67	10.05	85 to 264	120 to 370	47 to 440	0.25	PC Pin	82	1.8	1	0.85	\$7.00	\$5.69
2193213	IRM-10-24	24	0.42	10.08	85 to 264	120 to 370	47 to 440	0.25	PC Pin	82	1.8	1	0.85	\$7.00	\$5.95
2193221	IRM-15-3.3	3.3	3.5	11.55	85 to 264	120 to 370	47 to 440	0.35	PC Pin	74	2	1.0	0.94	\$8.10	\$6.85
2193230	IRM-15-5	5	3	15	85 to 264	120 to 370	47 to 440	0.35	PC Pin	78	1.8	1	0.85	\$8.10	\$6.59
2193248	IRM-15-12	12	1.25	15	85 to 264	120 to 370	47 to 440	0.35	PC Pin	82	1.8	1	0.85	\$8.10	\$6.85
2193256	IRM-15-15	15	1	15	85 to 264	120 to 370	47 to 440	0.35	PC Pin	82	1.8	1	0.85	\$8.10	\$6.59
2193264	IRM-15-24	24	0.63	15.12	85 to 264	120 to 370	47 to 440	0.35	PC Pin	83	1.8	1	0.85	\$8.10	\$6.85
2193272	IRM-20-3.3	3.3	4.5	14.85	85 to 264	120 to 370	47 to 440	0.6	PC Pin	76	2.06	1.07	0.94	\$8.60	\$7.05
2193281	IRM-20-5	5	4	20	85 to 264	120 to 370	47 to 440	0.6	PC Pin	79	2.06	1.07	0.94	\$8.60	\$7.05
2193299	IRM-20-12	12	1.8	21.6	85 to 264	120 to 370	47 to 440	0.6	PC Pin	84	2.06	1.07	0.94	\$8.60	\$7.05
2193301	IRM-20-15	15	1.4	21	85 to 264	120 to 370	47 to 440	0.6	PC Pin	84	2.06	1.07	0.94	\$8.60	\$7.35
2193310	IRM-20-24	24	0.9	21.6	85 to 264	120 to 370	47 to 440	0.6	PC Pin	85	2.06	1.07	0.94	\$8.60	\$7.05
2218601	IRM-30-5	5	6	30	85 to 264		47 to 440	0.75	PC Pin	83	2.74	1.54	0.94	\$11.90	\$9.75
2218652	IRM-30-5ST	5	6	30	85 to 264		47 to 440	0.75	Screw Terminal	83	3.58	1.56	1.12	\$13.70	\$11.19
2218610	IRM-30-12	12	2.5	30	85 to 264		47 to 440	0.75	PC Pin	88	2.74	1.54	0.94	\$11.90	\$9.75
2218661	IRM-30-12ST	12	2.5	30	85 to 264		47 to 440	0.75	Screw Terminal	88	3.58	1.56	1.12	\$13.70	\$11.19
2218628	IRM-30-15	15	2	30	85 to 264		47 to 440	0.75	PC Pin	88	2.74	1.54	0.94	\$11.90	\$9.75
2218679	IRM-30-15ST	15	2	30	85 to 264		47 to 440	0.75	Screw Terminal	88	3.58	1.56	1.12	\$13.70	\$11.19
2218636	IRM-30-24	24	1.3	31	85 to 264		47 to 440	0.75	PC Pin	88.5	2.74	1.54	0.94	\$11.90	\$9.75
2218687	IRM-30-24ST	24	1.3	31	85 to 264		47 to 440	0.75	Screw Terminal	88.5	3.58	1.56	1.12	\$13.70	\$11.19
2218644	IRM-30-48	48	0.63	30	85 to 264		47 to 440	0.75	PC Pin	90	2.74	1.54	0.94	\$11.90	\$9.75
2218695	IRM-30-48ST	48	0.63	30	85 to 264		47 to 440	0.75	Screw Terminal	90	3.58	1.56	1.12	\$13.70	\$11.19
2224737	IRM-45-5	5	8	40	85 to 264		47 to 440	1.5	PC Pin	83.5	3.43	2.05	1.16	\$12.40	\$10.09
2224788	IRM-45-5ST	5	8	40	85 to 264		47 to 440	1.5	Screw Terminal	83.5	4.29	2.05	1.32	\$14.20	\$11.85
2224745	IRM-45-12	12	3.8	45.6	85 to 264		47 to 440	1.5	PC Pin	87.5	3.43	2.05	1.16	\$12.40	\$10.09
2224796	IRM-45-12ST	12	3.8	45.6	85 to 264		47 to 440	1.5	Screw Terminal	87.5	4.29	2.05	1.32	\$14.20	\$11.59

Jameco Part#	Manufacturer Part #	Primary Output Voltage (VDC)	Output Current (A)	Maximum Output Power (W)	Input Voltage (VAC)	Input Voltage (VDC)	Input Frequency	Maximum Input Current (A)	Output Connector Type	Efficiency (%)	Length (inch)	Width (inch)	Height (inch)	Price 1	Price 10
2224753	IRM-45-15	15	3	45	85 to 264		47 to 440	1.5	PC Pin	88.5	3.43	2.05	1.16	\$12.40	\$10.35
2224809	IRM-45-15ST	15	3	45	85 to 264		47 to 440	1.5	Screw Terminal	88.5	4.29	2.05	1.32	\$14.20	\$11.85
2224761	IRM-45-24	24	1.9	45.6	85 to 264		47 to 440	1.5	PC Pin	89.5	3.43	2.05	1.16	\$12.40	\$10.09
2224817	IRM-45-24ST	24	1.9	45.6	85 to 264		47 to 440	1.5	Screw Terminal	89.5	4.29	2.05	1.32	\$14.20	\$11.59
2224770	IRM-45-48	48	0.94	45.1	85 to 264		47 to 440	1.5	PC Pin	90.5	3.43	2.05	1.16	\$12.40	\$10.09
2224825	IRM-45-48ST	48	0.94	45.1	85 to 264		47 to 440	1.5	Screw Terminal	90.5	4.29	2.05	1.32	\$14.20	\$11.85
2224833	IRM-60-5	5	10	50	85 to 264		47 to 440	1.8	PC Pin	84	3.43	2.05	1.16	\$13.90	\$11.39
2224884	IRM-60-5ST	5	10	50	85 to 264		47 to 440	1.8	Screw Terminal	84	4.29	2.05	1.32	\$15.70	\$12.75
2224841	IRM-60-12	12	5	60	85 to 264		47 to 440	1.8	PC Pin	87.5	3.43	2.05	1.16	\$13.90	\$11.39
2224892	IRM-60-12ST	12	5	60	85 to 264		47 to 440	1.8	Screw Terminal	87.5	4.29	2.05	1.32	\$15.70	\$12.75
2224850	IRM-60-15	15	4	60	85 to 264		47 to 440	1.8	PC Pin	89	3.43	2.05	1.16	\$13.90	\$11.39
2224905	IRM-60-15ST	15	4	60	85 to 264		47 to 440	1.8	Screw Terminal	89	4.29	2.05	1.32	\$15.70	\$12.75
2224868	IRM-60-24	24	2.5	60	85 to 264		47 to 440	1.8	PC Pin	90	3.43	2.05	1.16	\$13.90	\$11.39
2224913	IRM-60-24ST	24	2.5	60	85 to 264		47 to 440	1.8	Screw Terminal	90	4.29	2.05	1.32	\$15.70	\$12.75
2224876	IRM-60-48	48	1.25	60	85 to 264		47 to 440	1.8	PC Pin	91	3.43	2.05	1.16	\$13.90	\$11.39
2224921	IRM-60-48ST	48	1.25	60	85 to 264		47 to 440	1.8	Screw Terminal	91	4.29	2.05	1.32	\$15.70	\$12.75