



[Click Here to Request a Large Quantity Quote](#)

[Multiple Output Enclosed Switching Power Supplies](#)

Jameco Part #	Manufacturer	Manufacturer Part #	Primary Output Voltage (VDC)	Output Current (A)	Maximum Output Power (W)	Family	Additional Output Voltages (VDC)	Input Voltage (VAC)	Input Frequency	Maximum Input Current (A)	Output Connector Type	Number of Outputs	Price 1
323380	MEAN WELL	RD-35B	5	2.2	51.2	RD-35	24	88 to 264	47 to 63	0.8	Screw Terminal Block	2	\$14.95
323476	MEAN WELL	RT-50D	5	3	51	RT-50	24, 12	88 to 264	47 to 63	1.3	Screw Terminal Block	3	\$14.95
323492	MEAN WELL	RQ-50D	5	3	53.4	RQ-50	12, 24, -12	88 to 264	47 to 63	1.3	Screw Terminal Block	4	\$17.49
323362	MEAN WELL	RD-35A	5	4	32	RD-35	12	88 to 264	47 to 63	0.8	Screw Terminal Block	2	\$11.95
323460	MEAN WELL	RT-50B	5	4	50	RT-50	12, -12	88 to 264	47 to 63	1.3	Screw Terminal Block	3	\$14.95
323468	MEAN WELL	RT-50C	5	4	50	RT-50	15, -15	88 to 264	47 to 63	1.3	Screw Terminal Block	3	\$14.95
323433	MEAN WELL	RD-50B	5	4	53.6	RD-50	24	88 to 264	47 to 63	1.3	Screw Terminal Block	2	\$14.95
323513	MEAN WELL	RD-65B	5	4	68	RD-65	24	88 to 264	47 to 63	2	Screw Terminal Block	2	\$16.95
323572	MEAN WELL	RQ-65D	5	4	68	RQ-65	12, 24, -12	88 to 264	47 to 63	2	Screw Terminal Block	4	\$19.95
323555	MEAN WELL	RT-65D	5	4	68	RT-65	24, 12	88 to 264	47 to 63	2	Screw Terminal Block	3	\$17.95
323759	MEAN WELL	RD-125B	5	4.6	133.4	RD-125	24	88 to 264	47 to 63	3	Screw Terminal Block	2	\$25.49
323484	MEAN WELL	RQ-50B	5	5	45.5	RQ-50	12, -5, -12	88 to 264	47 to 63	1.3	Screw Terminal Block	4	\$17.49
323540	MEAN WELL	RT-65B	5	5	64.6	RT-65	12, -12	88 to 264	47 to 63	2	Screw Terminal Block	3	\$17.95
323548	MEAN WELL	RT-65C	5	5	65.5	RT-65	15, -15	88 to 264	47 to 63	2	Screw Terminal Block	3	\$17.95

Jameco Part #	Manufacturer	Manufacturer Part #	Primary Output Voltage (VDC)	Output Current (A)	Maximum Output Power (W)	Family	Additional Output Voltages (VDC)	Input Voltage (VAC)	Input Frequency	Maximum Input Current (A)	Output Connector Type	Number of Outputs	Price 1
2108912	MEAN WELL	RQ-50C	5	6	50	RQ-50	15, -5, -15	88 to 264	47 to 63	1.3	Screw Terminal Block	4	\$19.49
323425	MEAN WELL	RD-50A	5	6	54	RD-50	12	88 to 264	47 to 63	1.3	Screw Terminal Block	2	\$16.29
323564	MEAN WELL	RQ-65B	5	6	62.5	RQ-65	12, -5, -12	88 to 264	47 to 63	2	Screw Terminal Block	4	\$19.95
323505	MEAN WELL	RD-65A	5	6	66	RD-65	12	88 to 264	47 to 63	2	Screw Terminal Block	2	\$16.95
323522	MEAN WELL	RT-65A	5	6	66.1	RT-65	12, -5	88 to 264	47 to 63	2	Screw Terminal Block	3	\$17.95
323695	MEAN WELL	RQ-85D	5	6	84	RQ-85	12, 24, -12	88 to 264	47 to 63	2.5	Screw Terminal Block	4	\$27.95
2149802	MEAN WELL	RQ-85C	5	7	82.5	RQ-85	15, -5, -15	88 to 264	47 to 63	2.5	Screw Terminal Block	4	\$27.95
323741	MEAN WELL	RD-125A	5	7.7	130.9	RD-125	12	88 to 264	47 to 63	3	Screw Terminal Block	2	\$25.49
323812	MEAN WELL	RQ-125D	5	8	124	RQ-125	12, 24, -12	88 to 132, 176 to 264	47 to 63	3	Screw Terminal Block	4	\$31.49
323792	MEAN WELL	RT-125D	5	8	136	RT-125	24, 12	88 to 264	47 to 63	3	Screw Terminal Block	3	\$28.49
323783	MEAN WELL	RT-125C	5	10	132.5	RT-125	15, -15	88 to 264	47 to 63	3	Screw Terminal Block	3	\$28.49
323775	MEAN WELL	RT-125B	5	12	132	RT-125	12, -12	88 to 264	47 to 63	3	Screw Terminal Block	3	\$28.49
213752	MEAN WELL	QP-200D	5	15	204.9	QP-200	12, 24, -12	88 to 264	47 to 63	3.5	Screw Terminal Block	4	\$88.95
668764	MEAN WELL	QP-320D	5	20	316	QP-320	12, 24, -12	88 to 264	47 to 63	4	Screw Terminal Block	4	\$104.95
2106124	MEAN WELL	RD-125-1224	12	3.7	133.2	RD-125	24	88 to 264	47 to 63	3	Screw Terminal Block	2	\$25.49
2290503	MEAN WELL	RD-125-1224-UNBOXED	12	3.7	133.2	RD-125	24	88 to 264	47 to 63	3	Screw Terminal Block	2	\$22.95
2106167	MEAN WELL	RD-3513	13.5	2	35.1	RD-35	-13.5	88 to 264	47 to 63	0.8	Screw Terminal Block	2	\$12.95
2105439	MEAN WELL	AD-155A	13.8	11.5	151.55	AD-155	13.3	88 to 264	47 to 63	2.5	JST RCY Male	2	\$48.95

Jameco Part #	Manufacturer	Manufacturer Part #	Primary Output Voltage (VDC)	Output Current (A)	Maximum Output Power (W)	Family	Additional Output Voltages (VDC)	Input Voltage (VAC)	Input Frequency	Maximum Input Current (A)	Output Connector Type	Number of Outputs	Price 1
2106141	MEAN WELL	RD-125-2412	24	3.7	133.2	RD-125	12	88 to 132, 176 to 264	47 to 63	3	Screw Terminal Block	2	\$25.49
2146118	MEAN WELL	AD-155B	27.6	5	151.55	AD-155	27.1	88 to 264	47 to 63	2.5	Screw Terminal Block	2	\$48.95