



[Click Here to Request a Large Quantity Quote](#)

DISCRETE LEDS - MULTI-COLOR

Jameco Part#	Manufacturer	Manufacturer Part #	Type	Color	Lens Type	Package	Wavelength	Luminous Intensity - Iv (mcd)	Angle (deg)	Voltage - Vf (Typ.)	Current - If (Typ.)	Height (mm)	Mounting	Pin Count	Price 1
104889	Jameco Valuepro	LEG5292	Rectangular	Green/Orange	Non Diffused	2mm x 5mm	565 nm, 635 nm	6	116	1.7	30 mA	7	0.1"	2	\$ 0.25
2186419	Lite-On Electronics	LTL-2H3VYKNT	Bi-Color	Amber/Yellow	Clear	3mm, T-1	595 nm	3400	22	1.9	50 mA	8.7	0.1"	2	\$ 0.09
94553	Jameco Valuepro	LHG2062	Bi-Color	Green/Red	Diffused White	3mm, T-1	565 nm, 697 nm	2.0/5.0	70	2.6	30 mA	5.2	0.1"	2	\$ 0.19
2283151	Jameco Valuepro	LHG2062B	Bi-Color	Green/Red	Diffused	3mm, T-1	565 nm, 697 nm	2.0/5.0	70	2.0/5.0	30 mA	5.2	0.1"	2	\$ 0.19
2278855	Jameco Valuepro	LED-3mmRDGRN	Bi-Color	Green/Red	White Diffused	3mm, T-1	565 nm, 697 nm	2.0/5.0	36	1.7	30 mA	5.2	0.1"	2	\$ 0.25
2186371	Lite-On Electronics	LTL-1BEWJ	Bi-Color	Green/Red	White Diffused	3mm, T-1	565 nm, 660 nm	12.6/5.6	140	1.8/2.1	0 mA, 30 mA	5.15	0.1"	2	\$ 0.25
2224163	Kingbright Corporation	WP115WEGW	Bi-Color	Green/Red	White Diffused	3mm, T-1	568 nm, 617 nm	40	60	2.0/2.2	0 mA, 25 mA	5	0.1"	2	\$ 0.25
156946	Jameco Valuepro	UT0362-21-D61-R	Bi-Color	Green/Red	White Diffused	3mm, T-1	567 nm, 670 nm	2.7/13.3	50	2.1	30 mA		0.1"	2	\$ 0.39
1995935	Lite-On Electronics	LTL-14CHJ	Bi-Color	Green/Red Orange	White Diffused	3mm, T-1	565 nm, 630 nm	4.8	200	2.6	30 mA	4.45	0.1"	2	\$ 0.29
2186451	Lite-On Electronics	LTL-1BEHKVMP1	Bi-Color	Green/Red	Water Clear	3mm, T-1 RA	565 nm, 650 nm	19/29	55	2.0/2.1	30 mA	4.05	0.1"	3	\$ 0.25
2006772	Lite-On Electronics	LTL-2H3VYKNT1	Bi-Color	Amber/Yellow	Water Clear	5mm, T-1 3/4	595 nm	3400	15	2	50 mA	8.7	0.1"	2	\$ 0.25
334182	Jameco Valuepro	GDG-5MMSURCSYGC	Bi-Color	Green/Red	Diffused White	5mm, T-1 3/4	565 nm, 697 nm	2.0/8.0	30	2.6	30 mA	8.6	0.1"	2	\$ 0.19
34673	Jameco Valuepro	LHG3392	Bi-Color	Green/Red	Diffused White	5mm, T-1 3/4	565 nm, 697 nm	3.0/12.0	70	2.8	30 mA		0.1"	3	\$ 0.19
697557	Lite-On Electronics	LTL-30EFJ	Bi-Color	Green/Red	White Diffused	5mm, T-1 3/4	565 nm, 697 nm	5.6/19	30	2.6	30 mA	8.6	0.05"	2	\$ 0.25
1109260	Vishay	TLUV5300	Bi-Color	Green/Red	White Diffused	5mm, T-1 3/4	545 nm, 630 nm	2.5	60	3	30 mA	8.6	0.1"	2	\$ 0.25
2186460	Lite-On Electronics	LTL-30WJNF	Bi-Color	Green/Red	Diffused	5mm, T-1 3/4	565 nm, 660 nm	19/87	60	2.1	0 mA, 30 mA	8.7	0.1"	2	\$ 0.25
2266591	Jameco Valuepro	5ARG9HWB	Bi-Color	Green/Red	White Diffused	5mm, T-1 3/4	565 nm, 697 nm	2.6				8.6	0.1"	3	\$ 0.35
2236439	Sunled Corporation	XLMDKDG59MW3.15	Bi-Color	Green/Red	Diffused	5mm, T-1 3/4	515 nm, 660 nm	1195/1495	60	3.3	20 mA	8.6	3" Leads	3	\$ 1.29
1995960	Lite-On Electronics	LTL-30EHJ-002	Bi-Color	Green/Red Orange	White Diffused	5mm, T-1 3/4	565 nm, 630 nm	29/40	30	2.1	30 mA	8.6	0.05"	3	\$ 0.25
2228957	Jameco Valuepro	RGB-LED-CC-5-WC	Super Bright	RGB	Water Clear	5mm, T-1 3/4	625 nm, 525 nm, 470 nm	5000/9000/6000	20	2.0/3.2/3.2	30 mA	8.7	0.05"	4	\$ 0.39
2211119	Jameco Valuepro	MSL-504RGB-4P-	Super Bright	RGB	Water Clear	5mm, T-1 3/4	625 nm, 525 nm, 470 nm	2000/3000/1200	25	2.0/3.4/3.4	30 mA	7.9	0.1"	4	\$ 1.19
2211127	Jameco Valuepro	MSL-504RGB-4P+	Super Bright	RGB	Water Clear	5mm, T-1 3/4	625 nm, 525 nm, 470 nm	2000/3000/1200	25	2.0/3.4/3.4	25 mA	7.9	0.05"	2	\$ 1.19
2219559	Jameco Valuepro	RGB LED CC-5	Super Bright	RGB	Diffused	5mm, T-1 3/4	620 nm, 520 nm, 465 nm	1700/5000/4000	25	1.9/3.0/3.0	20 mA	8.7	0.05"	4	\$ 1.25
2210829	MCD Electronics	MCDL-5T8R6G5B6C-CA	Super Bright	RGB	Water Clear	5mm, T-1 3/4	624 nm, 525 nm, 470 nm	3500/4000/2000	20	2.25/3.5/3.5	30 mA	8.7	0.05"	2	\$ 1.75
2125181	Jameco Valuepro	MCDL-5T8R6G5B6C	Super Bright	RGB	Water Clear	5mm, T-1 3/4	624 nm, 525 nm, 470 nm	3500/4000/2000	20	2.25/3.5/3.5	30 mA	8.7	0.1"	4	\$ 2.25
2128500	Jameco Valuepro	MCDL-5013RGBC-TL-A	Super Bright	RGB	Water Clear	5mm, T-1 3/4	628 nm, 525 nm, 470 nm	3000/5000/1000	25	2.0/3.5/3.5	30 mA	8.7	0.05"	4	\$ 2.25
2219575	Jameco Valuepro	RGB LED CC-10	Super Bright	RGB	Clear	10mm, T-3 3/4	625 nm, 525 nm, 470 nm			2.0/3.4/3.4	20 mA	10.9	0.05"	4	\$ 0.49
2219567	Jameco Valuepro	RGB LED CA-10	Super Bright	RGB	Diffused	10mm, T-3 3/4	625 nm, 525 nm, 470 nm			2.0/3.2/3.2	20 mA	10.9	0.05"	4	\$ 0.59