

Panel Mount Indicators



Jameco Part#	Manufacturer	Manufacturer Part #	Fig.	Color	Illumination Type	Voltage (V)	Mounting Hole (mm)	Mounting Hole (inch)	Mounting Style	Termination	Type	Additional Feature	Price 1	Price 10
141111	Jameco Valuepro	L-922S-RD	4	Red	LED	2	6	0.235	nut and washer	Terminals	T1	Chrome housing	\$1.09	\$0.99
141129	Jameco Valuepro	L-913-RD	5	Red	LED	2	6	0.235	nut and washer	Terminals	T1	Chrome housing	\$1.25	\$1.15
141137	Jameco Valuepro	L-917-RD	5	Red	LED	2	8	0.312	nut and washer	Terminals	T1-3/4	Chrome housing	\$1.25	\$1.09
2099788	Solico	970S00146	14	Red	LED	2.7	8	0.312	snap in	6" wires	Flush Round		\$0.59	\$0.49
2181360	Jameco Valuepro	N792-12V-12CM-RED	1	Red	Incandescent	12	7	0.281	nut and washer	4.7" wires	Cylinder		\$1.49	\$1.25
2181378	Jameco Valuepro	N792-12V-12CM-GRN	1	Green	Incandescent	12	7	0.281	nut and washer	4.7" wires	Cylinder		\$1.49	\$1.25
215715	Jameco Valuepro	R9-71B-05-12V-RED-R	2	Red	Incandescent	12	16	0.625	nut and washer	0.196" solder terminals	Dome		\$2.25	\$1.95
637183	Jameco Valuepro	UT2U1G-H113-R801-W05	6	Green	LED	12	7	0.25	snap in	5.5" wires	T1-3/4		\$1.09	\$0.99
2158936	Jameco Valuepro	UT2U1W-H113-R801-1739	6	White	LED	12	6	0.25	snap in	5.5" wires	T1-3/4		\$0.89	\$0.79
2158506	Inter Market	F151-12G	13	Green	Incandescent	12	7	0.281	nut and washer	0.196" solder terminals	High Flat Dome		\$0.79	\$0.69
2129457	Sorenson Lighted Controls	3335-4-50-183-A-1001	3	Red	Incandescent	14	9.5 x 31.8	0.375 x 1.28	snap in	0.25" quick connect	Rectangle	With thermometer stencil, 0.375 x 1.28 hole	\$0.99	\$0.89
2228463	Solico	2435-1-10-20110	14	Red	Incandescent	14	8	0.31	snap in	6" wires	Flush Round		\$1.19	\$1.09
2230563	Jameco Valuepro	XPG1LCWD01M12VW6	6	White	LED	14	14	0.55	snap in	6" wires	T3		\$3.95	\$3.49
2230571	Jameco Valuepro	XPG1LCBD01D12VW6	6	Blue	LED	14	14	0.55	snap in	6" wires	T3		\$3.95	\$3.49
2126387	Sorenson Lighted Controls	KE12-4-03-050P0	7	Pure White	LED	14	16	0.625	nut and washer	0.25" quick connect	T3		\$1.19	\$1.05
2126395	Sorenson Lighted Controls	KE12-4-03-01060	7	White	LED	14	16	0.625	nut and washer	0.25" quick connect	T3		\$0.99	\$0.89
2126408	Sorenson Lighted Controls	KE12-4-03-01050	7	Blue	LED	14	16	0.625	nut and washer	0.25" quick connect	T3	Translucent LED	\$0.99	\$0.89
2126424	Sorenson Lighted Controls	KE12-4-03-01020	7	Amber	LED	14	16	0.625	nut and washer	0.25" quick connect	T3	Translucent LED	\$0.99	\$0.89
2230580	Jameco Valuepro	XPG1LMD01D12VW6	6	Red	LED	14	14	0.55	snap in	6" wires	T3		\$3.95	\$3.49
2183488	Dialight	249-7872-3335-504	15	Red	LED	28	9.525	0.375	nut and washer	Turret lugs	Cylinder		\$2.95	\$2.59
2202651	Amdt	120VNEON	10	Assorted	Neon	120	16	0.625	nut and washer	0.196" solder terminals	Dome	2x red, 1x yellow, 1x green	\$5.95	\$5.39
2236025	Xicon	361-7672	9	Amber	Neon	120	11	0.453	nut and washer	0.12" tabs	High Flat Cone		\$1.75	\$1.49
215803	Jameco Valuepro	R9-71N-05-120V-RED-R	10	Red	Neon	120	16	0.625	nut and washer	0.196" solder terminals	Dome		\$1.95	\$1.75
215812	Jameco Valuepro	R9-71N-05-120V-YELLOW-R	10	Yellow	Neon	120	16	0.625	nut and washer	0.196" solder terminals	Dome		\$1.95	\$1.75
215830	Jameco Valuepro	R9-71N-05-120V-GREEN-R	10	Green	Neon	120	16	0.625	nut and washer	0.196" solder terminals	Dome		\$1.95	\$1.75
1585485	Jameco Valuepro	32501001714	11	Green	Neon	120	21.6 x 7.9	0.85 x 0.31	snap in	6" wires	Rectangle	Rectangular body, 0.38 x 0.91 hole	\$0.25	\$0.12
2276615	Dialight	533-0601-304-1873Y	8	Yellow	LED	125	20.6502	0.813 square	snap in	0.196" solder terminals	Midflange	Lamp Holder with cap and LED	\$4.95	\$4.49
2276623	Dialight	533-0601-304-1875R	8	Red	LED	125	20.6502	0.813 square	snap in	0.196" solder terminals	Midflange	Lamp Holder with cap and LED	\$4.95	\$4.49
2276631	Dialight	533-0601-304-1875G	8	Green	LED	125	20.6502	0.813 square	snap in	0.196" solder terminals	Midflange	Lamp Holder with cap and LED	\$4.95	\$4.49
2179737	Philmore	11-2062B	12	Red	Neon	125	8	0.312	snap in	6" wires	Cylinder		\$3.49	\$2.95
2129545	Sorenson Lighted Controls	4416-12-0-010-1	6	Red	LED	250	6	0.25	snap in	9" wires	T1-3/4		\$1.09	\$0.99
2126512	Sorenson Lighted Controls	2954-X-11-373-10	16	Red	Neon	480	13	0.5	snap in	15" wires	Flush Round		\$1.09	\$0.99
2276583	CML	2150QA1	17	Red	Neon	125	8	0.312	snap in	0.187" quick connect	T1-3/4		\$2.49	\$1.95