


[Click Here to Request a Large Quantity Quote](#)

PASSIVE COMPONENTS - CAPACITORS ALUMINUM ELECTROLYTIC AXIAL

Jameco Part#	Manufacturer	Manufacturer Part #	Capacitance (uF)	Construction	Voltage (VDC)	Tolerance (%)	Size	Operating Temperature- Max (Cel)	Mounting	Price 1
10866	Jameco Valuepro	A1/50	1	Axial	50	20	5 x 12 mm	85	Through Hole	\$ 0.59
93569	Jameco Valuepro	A2.2/50	2.2	Axial	50	20	6 x 13 mm	85	Through Hole	\$ 0.59
11076	Jameco Valuepro	A4.7/50	4.7	Axial	50	20	6 x 13 mm	85	Through Hole	\$ 0.59
2235786	NIC Components	R6.8/50	6.8	Axial	50	20	5 x 11	85	Through Hole	\$ 0.10
1946199	Jameco Valuepro	A10/16	10	Axial	16	20	4 x 7 mm	85	Through Hole	\$ 0.59
10882	Jameco Valuepro	A10/50	10	Axial	50	20	6 x 12 mm	85	Through Hole	\$ 0.75
2296559	Cornell Dubilier	600D106F250DG4	10	Axial	250	-10/+50	9.5 x 35	125	Through Hole	\$ 4.95
331425	Jameco Valuepro	AB10/450-R	10	Axial	450	20	13 x 25 mm	85	Through Hole	\$ 1.75
199268	Jameco Valuepro	EA2225H613-R	22	Axial	25	20	6 x 12.5 mm	85	Through Hole	\$ 0.59
2202520	Spectrol/Vishay Corporation	A22/35/105	22	Axial	35	20	6.5 x 10.5 mm	105	Through Hole	\$ 0.75
10997	Illinois Capacitor	A22/50	22	Axial	50	20	6 x 12	85	Through Hole	\$ 0.75
331433	Jameco Valuepro	AB22/450-R	22	Axial	450	20	16 x 26 mm	85	Through Hole	\$ 1.75
135319	Jameco Valuepro	A47/25	47	Axial	25	20	6.5 x 17 mm	85	Through Hole	\$ 0.75
11105	Jameco Valuepro	A47/50	47	Axial	50	20	8 x 16 mm	85	Through Hole	\$ 0.69
199188	Jameco Valuepro	EA10016H613-R	100	Axial	16	20	6 x 12.5 mm	85	Through Hole	\$ 0.75
93551	Jameco Valuepro	A100/35	100	Axial	35	20	8 x 16 mm	85	Through Hole	\$ 0.79
10911	Jameco Valuepro	A100/50	100	Axial	50	20	8 x 20 mm	85	Through Hole	\$ 0.89
331417	Jameco Valuepro	AB100/250-R	100	Axial	250	20	16 x 32 mm	85	Through Hole	\$ 2.95
11019	Jameco Valuepro	A220/50-VP-R	220	Axial	50	20	10 x 17 mm	85	Through Hole	\$ 0.79
2234943	Illinois Capacitor	A330/50	330	Axial	50	20	10 x 25.5 mm	85	Through Hole	\$ 0.39
2235794	Matsushita Electronic Comp.	A470/16	470	Axial	16	20	8 x 21	85	Through Hole	\$ 0.25
199381	Jameco Valuepro	EA47035H1321-R	470	Axial	35	20	10 x 21 mm	85	Through Hole	\$ 1.39
11123	Jameco Valuepro	A470/50-VP-R	470	Axial	50	20	13 x 21 mm	85	Through Hole	\$ 1.35
2215689	Jameco Valuepro	T200V680UF	680	Axial	200	20	25 x 51	85	Through Hole	\$ 2.95
10954	Jameco Valuepro	A1000/25	1000	Axial	25	20	13 x 26 mm	85	Through Hole	\$ 1.25
93649	Jameco Valuepro	A1000/35	1000	Axial	35	20	13 x 31.5 mm	85	Through Hole	\$ 1.75
147256	Jameco Valuepro	A1000/50	1000	Axial	50	20	16 x 32 mm	85	Through Hole	\$ 3.49
11033	Jameco Valuepro	A2200/16	2200	Axial	16	20	16 x 30 mm	105	Through Hole	\$ 1.95
93658	Jameco Valuepro	A2200/35-R	2200	Axial	35	20	16 x 30 mm	85	Through Hole	\$ 1.49
2229520	Jameco Valuepro	A220UF-50V	2200	Axial	50	20	16 x 31	85	Through Hole	\$ 0.89
199479	Jameco Valuepro	EA220050H1836-R	2200	Axial	50	20	18 x 33 mm	85	Through Hole	\$ 3.95
2144972	Jameco Valuepro	A3300/16	3300	Axial	16	20	16 x 26	85	Through Hole	\$ 2.49
199487	Jameco Valuepro	EA330050H2042-R	3300	Axial	50	20	22 x 43 mm	85	Through Hole	\$ 3.59
2229538	Jameco Valuepro	A4700/16	4700	Axial	16	20	16 x 36	85	Through Hole	\$ 2.95
93673	Jameco Valuepro	140-TEA472M1EBK1837	4700	Axial	25	20	18 x 37	85	Through Hole	\$ 3.25
158650	Jameco Valuepro	HONJU A4700A25	4700	Axial	25	20	22 x 40	85	Through Hole	\$ 3.69
158811	Jameco Valuepro	A4700A50-R	4700	Axial	50	20	25 x 43 mm	85	Through Hole	\$ 2.95
93681	Jameco Valuepro	A10000/16	10000	Axial	16	20	22 x 21 mm	85	Through Hole	\$ 3.95
2215671	Jameco Valuepro	16V22000	22000	Axial	16	20	25 x 61	85	Through Hole	\$ 6.95
135394	Jameco Valuepro	GB102LB	Assorted	Axial	—	20	—	85	Through Hole	\$ 19.95
130340	Jameco Valuepro	130340 (refill)	Assorted	Axial	—	20	—	85	Through Hole	\$ 29.95



[Click Here to Request a Large Quantity Quote](#)

PASSIVE COMPONENTS - CAPACITORS ALUMINUM ELECTROLYTIC AXIAL

Jameco Part#	Manufacturer	Manufacturer Part #	Capacitance (uF)	Construction	Voltage (VDC)	Tolerance (%)	Size	Operating Temperature- Max (Cel)	Mounting	Price 1
81875	Jameco Valuepro	81875 (kit)	Assorted	Axial	—	20	—	85	Through Hole	\$ 44.95