



[Click Here to Request a Large Quantity Quote](#)

FUSES 0.25" X 1.25"

Jameco Part#	Manufacturer	Manufacturer Part #	Family	Blow characteristic	Rated Breaking Capacity (A)	Rated Voltage (VAC)	Fuse Material	Body Diameter (in.)	Body Length (in.)	Price 1
69404	Jameco Valuepro	AGC-1/4-R-VP	AGC	Fast Acting	0.25	250	Glass	0.25	1.25	\$ 0.49
10410	Jameco Valuepro	AGC-1/2-VP	AGC	Fast Acting	0.5	250	Glass	0.25	1.25	\$ 0.35
652949	Littelfuse	0312001.HXP	312	Fast Acting	1	250	Glass	0.25	1.25	\$ 0.39
10373	Jameco Valuepro	AGC-1-R-VP	AGC	Fast Acting	1	250	Glass	0.25	1.25	\$ 0.35
10382	Jameco Valuepro	AGC-2-R-VP	AGC	Fast Acting	2	250	Glass	0.25	1.25	\$ 0.39
1709960	Littelfuse	0225003.H	225	Fast Acting	3	250	Glass	0.25	1.25	\$ 0.59
69439	Jameco Valuepro	FUSE 3A-R	AGC	Fast Acting	3	250	Glass	0.25	1.25	\$ 0.39
69535	Jameco Valuepro	TSA-3A	MDL	Fast Acting	3	250	Glass	0.25	1.25	\$ 0.79
197544	Jameco Valuepro	MFA1-4	MFA	Fast Acting	4	250	Glass	0.25	1.25	\$ 0.35
10402	Jameco Valuepro	FUSE 5A-R	AGC	Fast Acting	5	250	Glass	0.25	1.25	\$ 0.39
2287479	Littelfuse	020200H5	202	Fast Acting	5	250	Thermo Plastic	0.37	0.16	\$ 1.25
2258427	Schurter	F6.3A/125V	F	Fast Acting	6.3	125	Glass	0.25	1.25	\$ 0.29
2280535	Littelfuse	312008.MPX	AGC	Fast Acting	8	250	Glass	0.25	1.25	\$ 0.25
69462	Jameco Valuepro	FUSE 10A	AGC	Fast Acting	10	250	Glass	0.25	1.25	\$ 0.49
656974	Littelfuse	0314015.HXP	314	Fast Acting	15	250	Ceramic	0.25	1.25	\$ 0.49
1711445	Littelfuse	0324015P	3AB	Fast Acting	15	250	Ceramic	0.25	1.25	\$ 0.29
186301	Jameco Valuepro	FUSE 16A	MDL	Fast Acting	16	250	Glass	0.25	1.25	\$ 0.29
653319	Littelfuse	0313.125HXP	313	Slow Blow	0.125	250	Glass	0.25	1.25	\$ 1.09
25655	Jameco Valuepro	GFSL250MA-R	MDL	Slow Blow	0.25	250	Glass	0.25	1.25	\$ 0.79
25639	Jameco Valuepro	G1SA1A-R	MDL	Slow Blow	1	250	Glass	0.25	1.25	\$ 0.79
25646	Jameco Valuepro	TSA-2A	MDL	Slow Blow	2	250	Glass	0.25	1.25	\$ 0.79
25672	Jameco Valuepro	MDL-5A-R	MDL	Slow Blow	5	250	Glass	0.25	1.25	\$ 0.79
653589	Littelfuse	0313008.HXP	313	Slow Blow	8	250	Glass	0.25	1.25	\$ 1.49
69570	Jameco Valuepro	G1SF10A-R	MDL	Slow Blow	10	250	Glass	0.25	1.25	\$ 0.79
1711656	Littelfuse	0326020.HXP	326	Slow Blow	20	250	Ceramic	0.25	1.25	\$ 0.99
1710451	Littelfuse	0251.125MXL	251	Very Fast	0.125	125	Epoxy Coated	0.25	1.25	\$ 0.49
1712106	Littelfuse	0451002.MRL	451	Very Fast	2	125	Ceramic	0.25	1.25	\$ 0.75