

[Click Here to Request a Large Quantity Quote](#)



PASSIVE COMPONENTS CRYSTALS

Jameco Part#	Manufacturer	Manufacturer Part #	Case	Frequency (MHz)	Impedance	Frequency Calibration Tol.	Frequency Stability Tol.	Price 1
14584	Jameco Valuepro	CY32.76	AT39 Tunning Fork	32.768	10.5pF	±50ppm @ 25°C	±50ppm @ -10 ⁰ to 25°C	\$ 0.19
325244	Jameco Valuepro	JVP-325243-R	AT39 Tunning Fork	32.768	12.5pF	±50ppm @ 25°C	±50ppm @ -10 ⁰ to 25°C	\$ 0.19
137859	Jameco Valuepro	CY8LP	HC49/S Low Profile	8.0	Series	±50ppm @ 25°C	±50ppm @ -10 ⁰ to 25°C	\$ 0.49
137875	Jameco Valuepro	CY11.05LP	HC49/S Low Profile	11.0592	Series	±50ppm @ 25°C	±50ppm @ -10 ⁰ to 25°C	\$ 0.29
137891	Jameco Valuepro	CY16LP	HC49/S Low Profile	16.0	Series	±50ppm @ 25°C	±50ppm @ -10 ⁰ to 25°C	\$ 0.29
102613	Jameco Valuepro	CY1.8432	HC49/U (HC18/U)	1.8432	18pF	±50ppm @ 25°C	±50ppm @ -10 ⁰ to 25°C	\$ 0.29
14533	Jameco Valuepro	CY3.57	HC49/U (HC18/U)	3.579545	18pF	±50ppm @ 25°C	±50ppm @ -10 ⁰ to 25°C	\$ 0.49
14592	Jameco Valuepro	CY4A	HC49/U (HC18/U)	4.0	20pF	±50ppm @ 25°C	±50ppm @ -10 ⁰ to 25°C	\$ 0.49
324364	Jameco Valuepro	TQR49U4M0000AS10-R	HC49/U (HC18/U)	4.0	Series	±50ppm @ 25°C	±50ppm @ -10 ⁰ to 25°C	\$ 0.49
14728	Jameco Valuepro	CY8	HC49/U (HC18/U)	8.0	Series	±50ppm @ 25°C	±50ppm @ -10 ⁰ to 25°C	\$ 0.49
14381	Jameco Valuepro	CY10	HC49/U (HC18/U)	10.0	Series	±50ppm @ 25°C	±50ppm @ -10 ⁰ to 25°C	\$ 0.49
324110	Jameco Valuepro	TQR49U11M0592A3210	HC49/U (HC18/U)	11.0592	32pF	±50ppm @ 25°C	±50ppm @ -10 ⁰ to 25°C	\$ 0.39
2159630	Arndt	12MOOHC49U	HC49/U (HC18/U)	12.0	20pF	±50ppm @ 25°C	±50ppm @ -10 ⁰ to 25°C	\$ 0.19
14453	Jameco Valuepro	CY16	HC49/U (HC18/U)	16.0	Series	±50ppm @ 25°C	±50ppm @ -10 ⁰ to 25°C	\$ 0.29
14517	Jameco Valuepro	CY20	HC49/U (HC18/U)	20.0	Series	±50ppm @ 25°C	±50ppm @ -10 ⁰ to 25°C	\$ 0.29
324398	Jameco Valuepro	JVP-324398	HC49/U (HC18/U)	49.860	20pF	±50ppm @ 25°C	±50ppm @ -10 ⁰ to 25°C	\$ 0.29
537799	Jameco Valuepro	XTAL-14.31818MHZ-HC49U	HC49/UA	14.31818	Series	±50ppm @ 25°C	±50ppm @ -10 ⁰ to 25°C	\$ 0.19
324187	Jameco Valuepro	TQR49U14M7456A2010	HC49/UA	14.7456	20pF	±50ppm @ 25°C	±50ppm @ -10 ⁰ to 25°C	\$ 0.25
324233	Jameco Valuepro	CY18.432	HC49/UA	18.432	20pF	±50ppm @ 25°C	±50ppm @ -10 ⁰ to 25°C	\$ 0.39
2281063	Jameco Valuepro	1L.5561.001.04	HC49/US Low Profile	3.579545	16pF	±5ppm @ 25°C	±5ppm @ -10 ⁰ to 25°C	\$ 0.39
324962	Jameco Valuepro	TQR49S4M00000A2010-R	HC49/US Low Profile	4.0	20pF	±50ppm @ 25°C	±50ppm @ -10 ⁰ to 25°C	\$ 0.49
324929	Jameco Valuepro	TQR49S5M0000A2010	HC49/US Low Profile	5.0	20pF	±50ppm @ 25°C	±50ppm @ -10 ⁰ to 25°C	\$ 0.49
325198	Jameco Valuepro	TQR49S12M0000A2040	HC49/US Low Profile	12.0	20pF	±50ppm @ 25°C	±50ppm @ -10 ⁰ to 25°C	\$ 0.19
325139	Jameco Valuepro	TQR49S16M0000A2010	HC49/US Low Profile	16.0	20pF	±50ppm @ 25°C	±50ppm @ -10 ⁰ to 25°C	\$ 0.49
325068	Jameco Valuepro	TQR49S20M0000A2010-R	HC49/US Low Profile	20.0	20pF	±50ppm @ 25°C	±50ppm @ -10 ⁰ to 25°C	\$ 0.49
325024	Jameco Valuepro	TQR49S24M0000A2010	HC49/US Low Profile	24.0	20pF	±50ppm @ 25°C	±50ppm @ -10 ⁰ to 25°C	\$ 0.39