



[Click Here to Request a Large Quantity Quote](#)

PASSIVE COMPONENTS - INDUCTORS

Jameco Part#	Manufacturer	Manufacturer Part #	Description	Inductance (µH)	Rated Current (mA)	Price 1
2295975	Major Brands	0805CS-270XJBC	Chip Inductor 0805CS SMD 0.027uH 500mA 5% 250MHz	0.027	500	\$ 0.49
372285	Jameco Valuepro	9230-94-VP	Choke Axial Molded RF 0.1uH 1.1A 10%	0.1	1100	\$ 0.79
372293	Jameco Valuepro	9230-00-VP	Choke Axial Molded RF 0.15uH 1.1A 10%	0.15	1100	\$ 0.79
372306	Jameco Valuepro	9230-04-VP	Choke Axial Molded RF 0.22uH 935mA 10%	0.22	935	\$ 0.79
372314	Jameco Valuepro	9230-10-VP	Choke Axial Molded RF 0.39uH 640mA 10%	0.39	640	\$ 0.79
372322	Jameco Valuepro	9230-12-VP	Choke Axial Molded RF 0.47uH 590mA 10%	0.47	590	\$ 0.79
372331	Jameco Valuepro	9230-14-VP	Choke Axial Molded RF 0.56uH 495mA 10%	0.56	495	\$ 0.79
372349	Jameco Valuepro	9230-16-VP	Choke Axial Molded RF 0.68uH 450mA 10%	0.68	450	\$ 0.79
372373	Jameco Valuepro	9230-34-VP	Choke Axial Molded RF 3.9uH 350mA 10%	3.9	350	\$ 0.99
2296615	Jameco Valuepro	LHL10NB822J	Fixed Inductor 8.2MH 150 mA 5% 12 Ohm 11mm Radial Vertical Cylinder	8.2	150	\$ 0.59
372171	Jameco Valuepro	78F100K-VP	Choke Axial Conformal 10uH 370mA 10%	10	370	\$ 0.45
2296135	Major Brands	DO3316P-103	Power Inductor SMD 10uH 3900mA 20% 0.038 Ohms	10	3900	\$ 1.49
2296199	Major Brands	DC5022P103	Power Inductor SMD 10uH 4300mA 20% 0.031 Ohms	10	4300	\$ 1.95
2296463	Major Brands	DHC-7342-100R	Power Inductor SMD High Current 10uH 7100mA 10% 0.0157 Ohms	10	7100	\$ 2.95
2296207	Major Brands	CO3321P-153	Power Inductor SMD 15uH 3100mA 20% 0.046 Ohms	15	3100	\$ 1.59
372402	Jameco Valuepro	9230-52-VP	Choke Axial Molded RF 22uH 190mA 10%	22	190	\$ 0.79
372411	Jameco Valuepro	9230-56-VP	Choke Axial Molded RF 33uH 187mA 10%	33	187	\$ 0.99
371581	Jameco Valuepro	2109-H-VP	Inductor Toroid Horizontal 47uH 3.6A 15%	47	3600	\$ 1.79
372429	Jameco Valuepro	9230-64-VP	Choke Axial Molded RF 68uH 135mA 10%	68	135	\$ 0.99
2296359	Major Brands	PVC-0-823-03	Power Choke 82uH 2800mA 10% 0.11 Ohms Vertical Mount	82	2800	\$ 1.95
208194	Jameco Valuepro	CEC-101J	Choke Axial Conformal 100uH 240mA 5%	100	240	\$ 0.99
371856	Jameco Valuepro	2112-V-VP	Inductor Toroid Vertical 100uH 240mA 15%	100	240	\$ 1.95
2295887	Jameco Valuepro	CT67F-101K	High Power Toroid Inductor 100uH 2.5A(DC) 10% Vertical 1.0kHz	100	2500	\$ 1.95
372445	Jameco Valuepro	9230-70-VP	Choke Axial Molded RF120uH 97mA 10%	120	97	\$ 0.99
372269	Jameco Valuepro	78F221J-VP	Choke Axial Conformal 220uH 130mA 5%	220	130	\$ 0.39
387268	Jameco Valuepro	2316-V-VP	Inductor Toroid Vertical 220uH 5.8A 15%	220	5800	\$ 2.49
208240	Jameco Valuepro	CEC-102J	Choke Axial Conformal 1000uH 160mA 5%	1000	160	\$ 0.39
371979	Jameco Valuepro	2124-V-VP	Inductor Toroid Vertical 1000uH 250mA 15%	1000	250	\$ 2.29
2287095	Yageo Corporation	SL0608T-472K-B-N	Choke Radial Molded 4700uH 52mA 10%	4700	52	\$ 0.59
372453	Jameco Valuepro	MCGSB-1501-1R0K	Choke Axial Molded RF 10000uH 24mA 10%	10000	24	\$ 1.95
2233959	Jameco Valuepro	VC1019-104K-UL	Choke Axial High Current RF 100,000uH 65mA 10%	10000	65	\$ 1.29
642741	Jameco Valuepro	VC0513-103K-UL	Chokes Axial High Current 10000uH 125mA 10%	10000	125	\$ 0.89
2279935	Jameco Valuepro	VC1019-103K-UL	Choke Axial High Current RF 10000uH 266mA 10%	10000	266	\$ 0.99
642927	Jameco Valuepro	GSPCU1020-103K08	Chokes Axial High Current RF 10000uH 350mA 10%	10000	350	\$ 1.29
2233967	Jameco Valuepro	VC1019-503K-UL	Choke Axial High Current RF 50,000uH 100mA 10%	50000	100	\$ 1.29