

[Click Here to Request a Large Quantity Quote](#)



**WIREWOUND PRECISION POTENTIOMETERS (-55°C to +125°C)**

Jameco SKU	Mfr Name	MFG Series	Mfr P/N	Resistance (Ohms)	Power Rating	Tolerance (%)	Number of Turns	Shaft Type	Shaft Length (mm)	Termination Style	Body Dia. (mm)	Ganging Number	Price 1	Price 10+
2231312	Vishay	536	536-11203	20,000	2 W	5	10	Round Slotted	19	Solder, Panel Mount	22	1	\$9.95	\$8.95
2199404	BI Technologies	3371	3371R2K-L.25	2,000	0.75 W	10	1	Round	22	Solder, Panel Mount	22	1	\$4.95	\$4.49
2201519	BI Technologies	5120	5127R1K-L.50	1,000	1 W	5	1	Round Slotted	21	Solder, Panel Mount	22	1	\$5.95	\$5.39
2198663	BI Technologies	7276	7276R500L.25	500	2 W	5	5	Round Slotted	19	Solder, Panel Mount	22	1	\$6.95	\$6.25
2194806	BI Technologies	8140	8146R2K-L.25CT	2,000	2 W	10	10	Round Slotted	20	Solder, Panel Mount	22	1	\$5.95	\$4.95
2111880	Jameco Valuepro	3540S	3540S-1-502-VP	5,000	2 W	5	10	Round Slotted	20	Solder, Panel Mount	22	2	\$9.95	\$8.95
183521	Bourns	3540S	3540S-1-103L	10,000	2 W	5	10	Round Slotted	20	Solder, Panel Mount	22	2	\$24.95	\$22.49
2177854	Jameco Valuepro	3540S	3540S-1-103-VP	10,000	2 W	5	10	Round Slotted	20	Solder, Panel Mount	22	2	\$9.95	\$8.95
855818	Bourns	3590S	3590S-2-502L	5,000	2 W	5	10	Round Slotted	20	Solder, Panel Mount	22	1	\$13.95	\$12.49
2200145	BI Technologies	AR30	AR30K-L.25	30,000	5 W	3	10	Round	19	Solder, Panel Mount	46	1	\$6.95	\$6.25