



[Click Here to Request a Large Quantity Quote](#)

[Slim Line Regulated Switching Wall Adapters](#)

Jameco Part #	Manufacturer	Manufacturer Part #	Primary Output Voltage (VDC)	Output Current (A)	Output Connector Diameters	Input Voltage (VAC)	Input Frequency	Output Connector Type	Polarity	Size (L" x W" x H")	Agency Approvals	Price 1
<a href="#">2138636</a>	Emerson Network Power	SW013US-0500020US	5	0.2	USB Type A	100 to 240	50 to 60	USB Port	N/A	2.5 x 0.8 x 1.5	TUV/FCC	\$1.95
<a href="#">2234097</a>	Phihong	PLA02A-050-1.7	5	0.4	1.7mm x 3.0mm right angle	90 to 264	47 to 63	Cylindrical Female	Center Positive	2 x 1 x 1.4	UL/CUL	\$3.25
<a href="#">2126125</a>	Arndt	ADS0051-W050080	5	0.8	2.1mm x 5.5mm	100 to 240	50 to 60	Cylindrical Female	Center Positive	1.9 x 1.6 x 0.9	UL/CUL/FCC	\$5.95
<a href="#">2289127</a>	Arndt	DSC-6PFA-05FU	5	1	1.3mm x 3.5mm	100 to 240	50 to 60	Cylindrical Female	Center Positive	2.4 x 1.0 x 1.6	UL/CUL/TUV/FCC	\$5.95
<a href="#">252720</a>	Jameco Reliapro	HK-AP-050A100-US	5	1	2.1mm x 5.5mm	100 to 240	50 to 60	Cylindrical Female	Center Positive	2.3 x 1.1 x 1.7	UL/CUL/CEC	\$8.95
<a href="#">2120090</a>	Arndt	MU05-J050100-A1-2.1	5	1	2.1mm x 5.5mm	100 to 240	50 to 60	Cylindrical Female	Center Positive	2.3 x 1.3 x 1.5	UL/CUL/CEC	\$4.95
<a href="#">2234601</a>	Arndt	MU05-050100-A1-10	5	1	2.1mm x 5.5mm	100 to 240	50 to 60	Cylindrical Female	Center Positive	2.6 x 1.3 x 1.5	UL/CUL	\$3.95
<a href="#">1940660</a>	MEAN WELL	GS06U-1P1J	5	1	2.1mm x 5.5mm	90 to 264	47 to 63	Cylindrical Female	Center Positive	2.6 x 1.3 x 1.7	UL/CUL/FCC/EAC	\$9.90
<a href="#">2211098</a>	Phihong	PLA05A-050-R	5	1	2.1mm x 5.5mm	90 to 264	47 to 63	Cylindrical Female	Center Positive	3.1 x 1.3 x 1.6	UL/CUL	\$4.95
<a href="#">2289807</a>	Jameco Reliapro	TC006	5	1	USB Type A	100 to 240	50 to 60	USB Port	N/A	1.0 x 1.0 x 1.1		\$3.95
<a href="#">2210888</a>	Arndt	1128	5	1	USB Type A	100 to 240	50 to 60	USB Port	N/A	2.6 x 1.3 x 1.5	UL/CUL	\$2.49
<a href="#">2217772</a>	Jameco Reliapro	HK-AR-050A200-US	5	2	2.1mm x 5.5mm	100 to 240	47 to 63	Cylindrical Female	Center Positive	3 x 1.6 x 1.2	UL/CUL/CEC	\$10.95
<a href="#">2244359</a>	Jameco Reliapro	US2018	5	2.1	USB Type A	100 to 240	50 to 60	USB Port	N/A	2 x 1.1 x 2	UL	\$6.95
<a href="#">2217617</a>	Seed Studios	313990002	5	2.1	USB Type A	100 to 240	50 to 60	USB Port	N/A	2.3 x 1.3 x 1.6	UL/FCC	\$9.95
<a href="#">2230336</a>	Dee Van Enterprise Usa	DSA-15P-05 US	5	2.5	2.1mm x 5.5mm	100 to 240	50 to 60	Cylindrical Female	Center Positive	2.7 x 1.1 x 1.7	UL/CUL	\$9.95

Jameco Part #	Manufacturer	Manufacturer Part #	Primary Output Voltage (VDC)	Output Current (A)	Output Connector Diameters	Input Voltage (VAC)	Input Frequency	Output Connector Type	Polarity	Size (L" x W" x H")	Agency Approvals	Price 1
<a href="#">2292431</a>	Arndt	FJ-SW0503000U	5	3	2.1mm x 5.5mm	100 to 240	50 to 60	Cylindrical Female	Center Positive	3.2 x 1.7 x 1.4	UL/CUL	\$6.49
<a href="#">2224016</a>	Jameco Reliapro	KSAS0180500300VU-VI	5	3	2.1mm x 5.5mm	100 to 240	50 to 60	Cylindrical Female	Center Positive	3.3 x 1.3 x 1.7	UL/CUL/CEC	\$11.95
<a href="#">2135451</a>	MG Electronics	SPS-054000D	5	4	2.1mm x 5.5mm right angle	90 to 132	47 to 63	Cylindrical Female	Center Positive	3.0 x 1.3 x 1.8	UL/CUL/CE	\$10.95
<a href="#">2225932</a>	MEAN WELL	SGA40U05-P1J	5	5	2.1mm x 5.5mm	90 to 264	47 to 63	Cylindrical Female	Center Positive	2.97 x 1.26 x 1.87	UL/CUL/CB/FCC/EAC	\$19.00
<a href="#">2226003</a>	MEAN WELL	SGA60U05-P1J	5	6	2.1mm x 5.5mm	90 to 264	47 to 63	Cylindrical Female	Center Positive	3.68 x 1.38 x 2.03	UL/CUL/CB/FCC/EAC	\$21.90
<a href="#">2230133</a>	Jameco Reliapro	GQ05-060050-CU	6	0.5	2.1mm x 5.5mm	100 to 240	50 to 60	Cylindrical Female	Center Positive	2.3 x 1.1 x 1.6	UL/CUL	\$5.49
<a href="#">2145078</a>	Arndt	MGT-6500SPS	6	0.5	2.1mm x 5.5mm	90 to 264	50 to 60	Cylindrical Female	Center Positive	2.5 x 1.1 x 1.8	UL/CUL/CEC	\$6.95
<a href="#">2236498</a>	Jameco Reliapro	KSAS0050900050VUD	9	0.5	2.1mm x 5.5mm	100 to 240	50 to 60	Cylindrical Female	Center Positive	2.1 x 0.9 x 1.3	UL/CUL/CE	\$8.95
<a href="#">2234100</a>	Jameco Reliapro	MTR-16110	9	1	2.1mm x 5.5mm	100 to 240	47 to 63	Cylindrical Female	Center Positive	2.5 x 1.1 x 1.7	UL	\$9.95
<a href="#">2203741</a>	Arndt	CYSC24-090100-P	9	1	2.5mm x 5.5mm	100 to 120	50 to 60	Cylindrical Female	Center Positive	2.4 x 1.3 x 1.9	UL/CUL	\$7.95
<a href="#">252779</a>	Jameco Reliapro	HK-AR-090A120-US	9	1.2	2.1mm x 5.5mm	100 to 240	47 to 63	Cylindrical Female	Center Positive	2.9 x 1.3 x 2.2	UL/CUL/CE/CEC	\$10.95
<a href="#">252786</a>	Jameco Reliapro	HK-AW-090A150-US	9	1.5	2.1mm x 5.5mm	100 to 240	47 to 63	Cylindrical Female	Center Positive	2.9 x 1.3 x 2.2	UL/CUL/TUV	\$11.95
<a href="#">2236412</a>	Jameco Reliapro	GQ05-120025-CU	12	0.25	2.1mm x 5.5mm	100 to 240	47 to 63	Cylindrical Female	Center Positive	2.2 x 1 x 1.7	UL/CUL	\$7.95
<a href="#">252808</a>	Jameco Reliapro	HK-AP-120A050-US	12	0.5	2.1mm x 5.5mm	100 to 240	47 to 63	Cylindrical Female	Center Positive	2.5 x 1.1 x 1.7	UL/CUL/CE/CEC	\$8.95
<a href="#">2150758</a>	Arndt	MGT-12500SPS	12	0.5	2.1mm x 5.5mm	100 to 240	50 to 60	Cylindrical Female	Center Positive	2.5 x 1.1 x 1.7	UL/CUL/TUV/CE	\$6.95
<a href="#">2270847</a>	Arndt	PSU-C9-ELEV6	12	0.75	2.5mm x 5.5mm	100 to 240	50 to 60	Cylindrical Female	Center Positive	2.7 x 1.1 x 1.7	UL/CUL/CEC	\$5.95

Jameco Part #	Manufacturer	Manufacturer Part #	Primary Output Voltage (VDC)	Output Current (A)	Output Connector Diameters	Input Voltage (VAC)	Input Frequency	Output Connector Type	Polarity	Size (L" x W" x H")	Agency Approvals	Price 1
<a href="#">2233983</a>	Arndt	DSA-12PFT-12FUS	12	1	2.1mm x 5.5mm	100 to 240	47 to 63	Cylindrical Female	Center Positive	2.7 x 1.1 x 1.5	UL	\$7.95
<a href="#">252824</a>	Jameco Reliapro	HK-AR-120A100-US	12	1	2.1mm x 5.5mm	100 to 240	47 to 63	Cylindrical Female	Center Positive	2.9 x 1.1 x 1.6	UL/CUL/TUV	\$9.95
<a href="#">2232825</a>	Arndt	SPS121	12	1	2.1mm x 5.5mm	100 to 240	50 to 60	Cylindrical Female	Center Positive	2.3 x 1.2 x 1.6	UL/CUL	\$6.95
<a href="#">2303159</a>	Jameco Valuepro	PEA-120100VA	12	1	2.1mm x 5.5mm	100 to 240	50 to 60	Cylindrical Female	Center Positive	2.9 x 1.2 x 1.7	UL/CUL	\$7.95
<a href="#">252833</a>	Jameco Reliapro	HK-AW-120A125-US	12	1.25	2.1mm x 5.5mm	100 to 240	47 to 63	Cylindrical Female	Center Positive	2.9 x 1.3 x 2.2	UL/CUL/TUV	\$10.95
<a href="#">2236501</a>	Jameco Reliapro	KSA-24W-120150VU	12	1.5	2.1mm x 5.5mm	100 to 240	50 to 60	Cylindrical Female	Center Positive	3.3 x 1.3 x 1.7	UL/CUL	\$11.95
<a href="#">1950497</a>	Jameco Reliapro	GQ30-120200-BU	12	2	2.1mm x 5.5mm	100 to 240	50 to 60	Cylindrical Female	Center Positive	2.9 x 1.3 x 2.2	UL/CUL/FCC	\$13.95
<a href="#">2236738</a>	Jameco Reliapro	GQ30-120200-BU-2.5	12	2	2.5mm x 5.5mm	100 to 240	50 to 60	Cylindrical Female	Center Positive	2.9 x 1.3 x 2.1	UL/CUL	\$10.95
<a href="#">2295471</a>	Jameco Reliapro	KSA-24W-120200VU(ROHS)	12	2	2.5mm x 5.5mm	100 to 240	50 to 60	Cylindrical Female	Center Positive	3.3 x 1.3 x 1.7	UL/CUL/CEC	\$10.95
<a href="#">2247277</a>	MEAN WELL	SGA25U12-P1J	12	2.08	2.1mm x 5.5mm	90 to 264	47 to 63	Cylindrical Female	Center Positive	2.97 x 1.26 x 1.87	UL/CUL/CB/FCC/EAC	\$12.95
<a href="#">2280167</a>	Arndt	PS-2.1-12-24WTM	12	2.5	2.1mm x 5.5mm	100 to 240	50 to 60	Cylindrical Female	Center Positive	3.1 x 2.1 x 1.3	UL/CSA/CEC	\$8.95
<a href="#">2295551</a>	Jameco Reliapro	KSA-30W-120250VU	12	2.5	2.5mm x 5.5mm	100 to 240	50 to 60	Cylindrical Female	Center Positive	2.8 x 1.2 x 1.7	UL/CUL	\$12.95
<a href="#">2225959</a>	MEAN WELL	SGA40U12-P1J	12	3.33	2.1mm x 5.5mm	90 to 264	47 to 63	Cylindrical Female	Center Positive	2.97 x 1.26 x 1.87	UL/CUL/CB/FCC/EAC	\$19.00
<a href="#">2229845</a>	Arndt	AD898F20	12	3.5	2.1mm x 5.5mm	100 to 240	50 to 60	Cylindrical Female	Center Positive	3.3 x 1.1 x 2.7	UL/CUL	\$9.95
<a href="#">2226038</a>	MEAN WELL	SGA60U12-P1J	12	5	2.1mm x 5.5mm	90 to 264	47 to 63	Cylindrical Female	Center Positive	3.68 x 1.38 x 2.03	UL/CUL/CB/FCC/EAC	\$21.90
<a href="#">2265647</a>	Arndt	PS15V1300MA-003	15	1.3	2.1mm x 5.5mm	100 to 240	50 to 60	Cylindrical Female	Center Positive	2.8 x 1.4 x 2.2	UL/CUL/FCC	\$7.95

Jameco Part #	Manufacturer	Manufacturer Part #	Primary Output Voltage (VDC)	Output Current (A)	Output Connector Diameters	Input Voltage (VAC)	Input Frequency	Output Connector Type	Polarity	Size (L" x W" x H")	Agency Approvals	Price 1
<a href="#">2229941</a>	Jameco Reliapro	HK-AW-240A050-US	24	0.5	2.1mm x 5.5mm	100 to 240	47 to 63	Cylindrical Female	Center Positive	2.9 x 1.3 x 2.2	UL/CUL/TUV/CE	\$8.95
<a href="#">2247154</a>	MEAN WELL	SGA12U24-P1J	24	0.5	2.1mm x 5.5mm	90 to 264	47 to 63	Cylindrical Female	Center Positive	2.45 x 1.08 x 1.56	UL/CUL/CB/FCC/EAC	\$10.60
<a href="#">2076341</a>	Jameco Reliapro	HK-AW-240A063-US	24	0.63	2.1mm x 5.5mm	100 to 240	47 to 63	Cylindrical Female	Center Positive	2.9 x 1.3 x 2.2	UL/CUL/CEC	\$9.95
<a href="#">2230416</a>	Phihong	PDA024A-1A0S-R	24	1	2.1mm x 5.5mm	100 to 120	60	Cylindrical Female	Center Positive	3.4 x 1.4 x 2.1	UL/CUL	\$8.95
<a href="#">2208972</a>	Jameco Reliapro	KSA-24W-240100VU	24	1	2.1mm x 5.5mm	100 to 240	47 to 63	Cylindrical Female	Center Positive	3.5 x 1.3 x 1.7	UL/CUL/CECV	\$10.95
<a href="#">2271063</a>	Jameco Reliapro	MTR-18028	24	1	2.5mm x 5.5mm	100 to 240	47 to 63	Cylindrical Female	Center Positive	2.9 x 1.3 x 2.3	UL/CUL/CEC	\$12.95
<a href="#">2247306</a>	MEAN WELL	SGA25U24-P1J	24	1.04	2.1mm x 5.5mm	90 to 264	47 to 63	Cylindrical Female	Center Positive	2.97 x 1.26 x 1.87	UL/CUL/CB/FCC/EAC	\$14.80
<a href="#">2226062</a>	MEAN WELL	SGA60U24-P1J	24	2.5	2.1mm x 5.5mm	90 to 264	47 to 63	Cylindrical Female	Center Positive	3.68 x 1.38 x 2.03	UL/CUL/CB/FCC/EAC	\$21.90
<a href="#">2226071</a>	MEAN WELL	SGA60U48-P1J	48	1.25	2.1mm x 5.5mm	90 to 264	47 to 63	Cylindrical Female	Center Positive	3.68 x 1.38 x 2.03	UL/CUL/CB/FCC/EAC	\$21.90