

[Click Here to Request a Large Quantity Quote](#)



WALL TRANSFORMER & TABLE-TOP POWER SUPPLIES

Jameco Part#	Manufacturer	Manufacturer Part #	BODY TYPE	Primary Output Voltage (VDC)	Output Current (A)	Maximum Output Power (W)	Output Connector Type	Output Connector Diameters	Polarity	Input Voltage (VAC)	Input Frequency	Agency Approvals	Price
2224059	Sparkle Power	AD025DGAA1-J25	TABLE-TOP	5	5.0	25	Cylindrical Female	2.5mm x 5.5mm	Center Positive	90 to 264	47 to 63	UL/CUL/TUV/CE	\$13.95
2203821	Arndt	AD6550LF	TABLE-TOP	5	4.0	20	Cylindrical Female	2.1mm x 5.5mm	Center Positive	100 to 120	50 to 60	UL/CUL/CECV	\$7.95
2179577	Delta Electronics	ADP-12GB-2.5	TABLE-TOP	5	2.5	12	Cylindrical Female	2.5mm x 5.5mm	Center Positive	100 to 240	50 to 60	UL/CUL	\$4.95
2202870	Arndt	EADP-20NB	TABLE-TOP	5	4.0	20	Cylindrical Female	2.1mm x 5.5mm	Center Positive	100 to 120	50 to 60	UL/CUL/CEC	\$7.95
2234249	Arndt	FY0506000	TABLE-TOP	5	6.0	30	Cylindrical Female	2.5mm x 5.5mm	Center Positive	100 to 240	50 to 60	UL/CUL/TUV/CE/FCC	\$9.95
2203848	Arndt	G32DD-050400-A	TABLE-TOP	5	4.0	20	Cylindrical Female	2.1mm x 5.5mm	Center Positive	100 to 120	50/60	UL/CUL	\$7.95
1940387	MEAN WELL	GS18A05-P1J	TABLE-TOP	5	3.0	15	Cylindrical Female	2.1mm x 5.5mm	Center Positive	90 to 264	47 to 63	UL/CUL/TUV/CE/CEC	\$11.95
1940571	MEAN WELL	GS25A05-P1J	TABLE-TOP	5	5.0	20	Cylindrical Female	2.1mm x 5.5mm	Center Positive	90 to 264	47 to 63	UL/CUL/TUV/CE/CEC	\$12.95
1952337	MEAN WELL	GS40A05-P1J	TABLE-TOP	5	4.0	25	Cylindrical Female	2.1mm x 5.5mm	Center Positive	90 to 264	47 to 63	UL/CSA/RUV/CEC	\$12.95
2289159	Globtek	GT21089-1005T	TABLE-TOP	5	2.0	10	Cylindrical Female	2.1mm x 5.5mm	Center Positive	100 to 240	50 to 60	UL/CSA/TUV/CE	\$8.95
2235760	Globtek	GT-21089-1305	TABLE-TOP	5	2.6	13	Cylindrical Female	2.1mm x 5.5mm	Center Positive	100 to 240	50 to 60	UL/CUL/CCC/CE	\$8.95
2292423	Globtek	GT-41062-1805-T3	TABLE-TOP	5	3.4	17	Cylindrical Female	2.1mm x 5.5mm	Center Positive	100 to 240	50 to 60	UL/CUL/CE/CCC	\$8.95
2202626	Arndt	PS-2.1-5-4DAC	TABLE-TOP	5	4.0	20	Cylindrical Female	2.1mm x 5.5mm	Center Positive	100 to 120	50 to 60	UL/CUL/CEC	\$7.95
2227807	Sceptre Power	PS-5050APL05	TABLE-TOP	5	5.0	25	Cylindrical Female	2.1mm x 5.5mm	Center Positive	100 to 240	50 to 60	UL/CUL/TUV/CE	\$13.95
2270887	Arndt	SQ15W5P-10	TABLE-TOP	5	3.0	15	Cylindrical Female	2.1mm x 5.5mm	Center Positive	100 to 240	50 to 60	UL	\$8.95
196218	Globtek	TR9CA2000C12CP-Y(R)	TABLE-TOP	5	2.0	10	Cylindrical Female	2.1mm x 5.5mm	Center Positive	90 to 264	47 to 63	UL/CUL/TUV/CE	\$16.95
2227815	Globtek	TR9CA2000LLP-Y-D	TABLE-TOP	5	2.6	13	Cylindrical Female	2.5mm x 5.5mm	Center Positive	100 to 240	50 to 60	UL/CUL/TUV/CCC/CE	\$9.95
2217617	Seeed Studios	313990002	WALL	5	2.1	10	USB Port	USB Type A	—	100 to 240	50 to 60	UL/FCC	\$9.95
2235381	Seeed Studios	313990002RA	WALL	5	2.1	10.5	USB Port	USB Type A	—	100 to 240	50 to 60	UL	\$6.95
2126125	Arndt	ADS0051-W050080	WALL	5	0.8	4	Cylindrical Female	2.1mm x 5.5mm	Center Positive	100 to 240	50 to 60	UL/CUL/CE/CEC	\$6.95
2230361	Arndt	ADS6818-1505-WDB0530	WALL	5	3.0	15	Cylindrical Female	2.5mm x 5.5mm	Center Positive	100 to 240	50 to 60	UL,CUL	\$8.95
2234505	Arndt	BI20-050300-ADU	WALL	5	3.0	15	Cylindrical Female	2.5mm x 5.5mm RA	Center Positive	100 to 240	50 to 60	UL,CUL	\$7.95
2230336	Dee Van Enterprise Usa	DSA-15P-05 US	WALL	5	2.5	12.5	Cylindrical Female	2.1mm x 5.5mm	Center Positive	100 to 240	50 to 60	UL/CUL	\$10.95
2289127	Arndt	DSC-6PFA-05FU	WALL	5	1.0	5	Cylindrical Female	1.3mm x 3.5mm	Center Positive	100 to 240	50 to 60	UL/CUL/TUV/FCC	\$6.95
2227735	Arndt	EDF0500150A1BA	WALL	5	1.5	7.5	Cylindrical Female	1.3mm x 3.5mm	Center Positive	100 to 120	50 to 60	UL/CUL	\$7.95
2188537	CUI	EPAS-101W-05	WALL	5	2.0	10	Cylindrical Female	2.5mm x 5.5mm	Center Positive	100 to 240	50 to 60	UL,CUL	\$5.95
1940660	MEAN WELL	GS06U-1P1J	WALL	5	1.0	5	Cylindrical Female	2.1mm x 5.5mm	Center Positive	90 to 264	47 to 63	CB/CE/CUL/FCC/UL	\$9.40
379623	MEAN WELL	GS25U05-P1J	WALL	5	4.0	20	Cylindrical Female	2.1mm x 5.5mm	Center Positive	100 to 240	50 to 60	BSMI/CB/CUL/FCC/UL	\$11.95
2270967	Globtek	GTM41076-0605	WALL	5	1.2	6	USB micro-B	—	—	100 to 240	50 to 60	UL	\$8.95
252720	Jameco Reliapro	HK-AP-050A100-US	WALL	5	1.0	7.5	Cylindrical Female	2.1mm x 5.5mm	Center Positive	100 to 240	50 to 60	UL/CUL/CEC	\$8.95
2217772	Jameco Reliapro	HK-AR-050A200-US	WALL	5	2.0	10	Cylindrical Female	2.1mm x 5.5mm	Center Positive	100 to 240	47 to 63	UL/CUL/CECV	\$11.95
2289479	Jameco Reliapro	JTA0302A	WALL	5	2.0	10	Cylindrical Female	2.1mm x 5.5mm RA	Center Positive	100 to 120	50 to 60	UL/CUL/TUV	\$9.95
2224016	Jameco Reliapro	KSAS0150500300VU-VI	WALL	5	3.0	15	Cylindrical Female	2.1mm x 5.5mm	Center Positive	100 to 240	47 to 63	UL/CUL	\$11.95
2135451	OpenPeak	LFS054000D-8AS	WALL	5	4.0	20	Cylindrical Female	2.1mm x 5.5mm RA	Center Positive	90 to 132	50 to 60	CE	\$10.95
2234601	Arndt	MU05-050100-A1-10	WALL	5	1.0	5	Cylindrical Female	2.1mm x 5.5mm	Center Positive	100 to 240	50 to 60	UL,CUL	\$4.49
2120090	Arndt	MU05-J050100-A1-2.1	WALL	5	1.0	5	Cylindrical Female	2.1mm x 5.5mm	Center Positive	100 to 240	50 to 60	UL/CUL/CEC	\$6.49
2270911	Arndt	PA1030-050DUB	WALL	5	3.5	17.5	Cylindrical Female	2.1mm x 5.5mm	Center Positive	100 to 240	50 to 60	UL,CUL,FCC	\$8.95
2234097	Phihong	PLA02A-050-1.7	WALL	5	0.4	2	Cylindrical Female	1.7mm x 3.0mm RA	Center Positive	90 to 264	47 to 63	UL,CUL	\$3.95
2211098	Phihong	PLA05A-050-R	WALL	5	1.0	5	Cylindrical Female	2.1mm x 5.5mm	Center Positive	90 to 264	47 to 63	UL/CUL	\$5.49
2202829	Phihong	PSA08R-050-1.3	WALL	5	1.0	5	Cylindrical Female	1.3mm x 3.5mm	Center Positive	100 to 240	47 to 63	UL/CUL/CE	\$5.49
2230408	Phihong	PSM04A-050-R	WALL	5	0.8	3.75	Cylindrical Female	2.1mm x 5.5mm	Center Positive	100 to 240	50 to 60	UL,CUL	\$4.95
2158240	Phihong	PSM11R-050-USB	WALL	5	2.0	10	USB Mini-B	—	—	90 to 264	47 to 63	UL/TUV/SAA/CE	\$4.95
252701	Jameco Reliapro	S08AB050050G9270-R	WALL	5	0.5	2.5	Cylindrical Female	2.1mm x 5.5mm	Center Positive	100 to 240	47 to 63	UL/CUL/CE	\$6.95
2270919	Arndt	SA115B-05	WALL	5	3.0	15	Cylindrical Female	2.1mm x 5.5mm	Center Positive	100 to 240	50 to 60	UL,CUL,FCC	\$8.95
2225932	MEAN WELL	SGA40U05-P1J	WALL	5	5.0	25	Cylindrical Female	2.1mm x 5.5mm	Center Positive	90 to 264	47 to 63	CB/CUL/FCC/UL	\$18.00
2138636	Emerson Network Power	SW013US-0500020US	WALL	5	0.2	1	USB Port	USB Type A	—	100 to 240	50 to 60	TUV/FCC	\$1.95
2289807	Jameco Reliapro	TC006	WALL	5	1.0	5	USB Port	USB Type A	—	100 to 240	50 to 60	—	\$4.95
2197812	Cincon Electronics Company	TR10R050	WALL	5	1.6	10	Cylindrical Female	2.5mm x 5.5mm RA	Center Positive	90 to 264	47 to 63	UL/CUL/TUV/FCC	\$3.95
2202790	Cincon Electronics Company	TR10R050-1	WALL	5	1.6	8	Cylindrical Female	2.1mm x 5.5mm	Center Positive	100 to 240	47 to 63	UL/CUL/TUV/CE	\$4.95
2229440	Arndt	TSA1-050120WA	WALL	5	1.2	6	Stripped & Tinned Pigtail Wire	—	—	100 to 240	50 to 60	UL,CUL	\$5.49
2270903	Arndt	UP0251P-05PA	WALL	5	3.5	17.5	Cylindrical Female	2.1mm x 5.5mm	Center Positive	100 to 240	50 to 60	UL,CUL,CE,FCC	\$7.95
2244359	Jameco Reliapro	US2018	WALL	5	2.1	10.5	USB Port	—	—	100 to 240	50 to 60	UL	\$6.95
2289167	Globtek	WR92A2400CCP	WALL	5	2.4	12	Cylindrical Female	2.1mm x 5.5mm	Center Positive	100 to 250	47 to 63	UL/CSA	\$9.95
2229503	Arndt	YFAF22073001	WALL	5	1.2	6	Stripped & Tinned Pigtail Wire	—	—	100 to 240	50 to 60	UL,CUL	\$5.95
2292431	Arndt	FJ-SW0503000U	WALL	5	3.0	15	Cylindrical Female	2.1mm x 5.5mm	Center Positive	100 to 240	50 to 60	UL/CUL/CCC/CE/CB/GS/FCC/EK/SAA/CSA/PSE	\$7.95
2144956	Jameco Reliapro	GQ65-060330-E1	TABLE-TOP	6	3.3	19.8	Cylindrical Female	2.1mm x 5.5mm	Center Positive	90 to 264	47 to 63	UL/TUV/CE	\$12.95
2230133	Jameco Reliapro	GQ05-060050-CU	WALL	6	0.5	3	Cylindrical Female	2.1mm x 5.5mm	Center Positive	100 to 240	47 to 63	UL/CUL	\$7.95
2145078	Arndt	MGT-6500SPS	WALL	6	0.5	3	Cylindrical Female	2.1mm x 5.5mm	Center Positive	90 to 264	50 to 60	UL/CUL/CEC	\$6.95
2231435	Arndt	094-0224-000	TABLE-TOP	9	1.1	10	Cylindrical Female	2.1mm x 5.5mm RA	Center Positive	100 to 240	50 to 60	UL/CUL/TUV/CE/CCC	\$6.95
1940408	MEAN WELL	GS18A09-P1J	TABLE-TOP	9	2.0	18	Cylindrical Female	2.1mm x 5.5mm	Center Positive	90 to 264	47 to 63	UL/CUL/TUV/CEC	\$12.95
2173036	Phihong	PSA18U-090	TABLE-TOP	9	2.0	18	Cylindrical Female	2.1mm x 5.5mm	Center Positive	90 to 264	47 to 63	UL/CUL/CE	\$7.95
2203741	Arndt	CYSC24-090100-P	WALL	9	1.0	9	Cylindrical Female	2.5mm x 5.5mm	Center Positive	100 to 120	50 to 60	UL/CUL	\$8.95

[Click Here to Request a Large Quantity Quote](#)



WALL TRANSFORMER & TABLE-TOP POWER SUPPLIES

Jameco Part#	Manufacturer	Manufacturer Part #	BODY TYPE	Primary Output Voltage (VDC)	Output Current (A)	Maximum Output Power (W)	Output Connector Type	Output Connector Diameters	Polarity	Input Voltage (VAC)	Input Frequency	Agency Approvals	Price
2082311	MEAN WELL	GE18I09-P1J	WALL	9	2.0	18	Cylindrical Female	2.1mm x 5.5mm	Center Positive	90 to 264	47 to 63	CSA/EN/UL	\$13.30
1940686	MEAN WELL	GS06U-2P1J	WALL	9	0.7	6	Cylindrical Female	2.1mm x 5.5mm	Center Positive	90 to 264	47 to 63	CB/CE/CUL/FCC/UL	\$9.40
1952847	MEAN WELL	GS18U09-P1J	WALL	9	2.0	18	Cylindrical Female	2.1mm x 5.5mm	Center Positive	90 to 264	50 to 60	BSMI/CB/CUL/FCC/UL/CEC	\$10.95
380140	MEAN WELL	GS25U09-P1J	WALL	9	2.8	25	Cylindrical Female	2.1mm x 5.5mm	Center Positive	90 to 264	47 to 63	BSMI/CB/CUL/FCC/UL	\$11.95
252779	Jameco Reliapro	HK-AR-090A120-US	WALL	9	1.2	10.8	Cylindrical Female	2.1mm x 5.5mm	Center Positive	100 to 240	47 to 63	CE/CEC/CUL/GS/UL	\$10.95
252786	Jameco Reliapro	HK-AW-090A150-US	WALL	9	1.5	13.5	Cylindrical Female	2.1mm x 5.5mm	Center Positive	100 to 240	47 to 63	CE/CEC/CUL/GS/UL	\$11.95
2236498	Jameco Reliapro	KSAS0050900050VUD	WALL	9	0.5	4.5	Cylindrical Female	2.1mm x 5.5mm	Center Positive	100 to 240	50 to 60	UL,CUL,CE	\$8.95
2234100	Jameco Reliapro	MTR-16110	WALL	9	1.0	9	Cylindrical Female	2.1mm x 5.5mm	Center Positive	100 to 240	47 to 63	UL	\$10.95
2202896	Phihong	PSA21R-090	WALL	9	1.7	10	Cylindrical Female	2.1mm x 5.5mm	Center Positive	100 to 240	47 to 63	UL/CUL/TUV/CE	\$9.95
2230045	Phihong	PSC12R-090	WALL	9	1.1	10	Cylindrical Female	2.1mm x 5.5mm	Center Positive	90 to 264	47 to 63	CEC	\$9.95
2227401	Arndt	ADA017	TABLE-TOP	12	3.0	36	Cylindrical Female	2.1mm x 5.5mm	Center Positive	100 to 240	50 to 60	UL/CUL	\$8.95
2229491	Dee Van Enterprise Usa	DSA-0151D-12-2.1	TABLE-TOP	12	1.5	18	Cylindrical Female	2.1mm x 5.5mm	Center Positive	100 to 125	50 to 60	UL/CSA/TUV/CE	\$8.95
2229482	Dee Van Enterprise Usa	DSA-0151D-12-2.5	TABLE-TOP	12	1.5	18	Cylindrical Female	2.5mm x 5.5mm	Center Positive	100 to 125	50 to 60	UL/CSA/TUV/CE	\$11.95
2272991	EDAC	EA1050A-120	TABLE-TOP	12	5.0	60	DIN Male	4-pin DIN	—	100 to 240	50 to 60	UL/CUL/TUV/CE/FCC/CCC	\$15.95
2227381	Delta Electronics	EADP-24MB	TABLE-TOP	12	2.0	24	Cylindrical Female	2.5mm x 5.5mm	Center Positive	100 to 240	50 to 60	UL/CUL/CCC/CE	\$7.95
2230168	Arndt	EADP-36FB	TABLE-TOP	12	3.0	36	Cylindrical Female	2.1mm x 5.5mm	Center Positive	100 to 240	50 to 60	UL/CUL	\$6.95
2271239	Jameco Reliapro	G99-KPL060F-L253	TABLE-TOP	12	5.0	60	Cylindrical Female	2.5mm x 5.5mm	Center Positive	100 to 240	47 to 63	UL/CUL/TUV/CE/FCC/CCC	\$14.95
1954244	MEAN WELL	GS15A-3P1J	TABLE-TOP	12	1.3	15	Cylindrical Female	2.1mm x 5.5mm RA	Center Positive	90 to 264	47 to 63	UL/CUL/TUV/CEC	\$14.20
1940416	MEAN WELL	GS18A12-P1JU	TABLE-TOP	12	1.5	18	Cylindrical Female	2.1mm x 5.5mm	Center Positive	90 to 264	47 to 63	UL/CUL/TUV/CEC	\$13.95
2079357	MEAN WELL	GS40A12-P1M	TABLE-TOP	12	3.3	40	Cylindrical Female	2.5mm x 5.5mm	Center Positive	90 to 264	47 to 63	UL/CUL/TUV/CEC	\$12.95
1952370	MEAN WELL	GS60A12-P1J	TABLE-TOP	12	5.0	60	Cylindrical Female	2.1mm x 5.5mm	Center Positive	90 to 264	47 to 63	UL/CUL/TUV/CEC	\$14.95
2167445	Jameco Reliapro	K36V120300E2	TABLE-TOP	12	3.0	36	Cylindrical Female	2.1mm x 5.5mm	Center Positive	100 to 240	47 to 63	UL/CSA/EN	\$13.95
2208956	Jameco Reliapro	KPL-060F-VI	TABLE-TOP	12	5.0	60	Cylindrical Female	2.1mm x 5.5mm	Center Positive	100 to 240	50 to 60	UL/CUL/TUV/CE	\$13.95
2234661	Jameco Reliapro	MP65-120350-E11	TABLE-TOP	12	3.5	42	Cylindrical Female	2.1mm x 5.5mm	Center Positive	100 to 240	50 to 60	UL/CUL/CE	\$12.95
2188570	Arndt	MPGS-U0241202000D2	TABLE-TOP	12	2.0	24	Cylindrical Female	2.5mm x 5.5mm	Center Positive	100 to 240	50 to 60	UL/CUL/FCC	\$7.95
2236543	Lite-On Electronics	PA-1600-2A-LF	TABLE-TOP	12	5.0	60	Cylindrical Female	2.5mm x 5.5mm	Center Positive	100 to 240	50 to 60	UL/CUL/TUV/CE	\$11.95
2236754	Arndt	PS-2.1-12-3-DC-S1	TABLE-TOP	12	3.0	36	Cylindrical Female	2.1mm x 5.5mm	Center Positive	100 to 120	50 to 60	UL/CUL/FCC	\$6.95
2270895	Phihong	PSA18U-120	TABLE-TOP	12	1.5	18	DIN Male	4-Pin DIN	—	100 to 240	50 to 60	UL/CUL/TUV/CE	\$11.95
2230230	Arndt	RX-SP5012-6	TABLE-TOP	12	6.0	72	Cylindrical Female	2.1mm x 5.5mm	Center Positive	100 to 240	50 to 60	CE/FCC	\$17.95
2289471	Jameco Reliapro	SA06-15S12R-U	TABLE-TOP	12	1.3	15	Cylindrical Female	2.1mm x 5.5mm	Center Positive	100 to 240	50 to 60	UL/CUL/TUV/CB/CE/FCC	\$8.95
2227823	Globtek	TR9CE1250LCP-Y	TABLE-TOP	12	1.3	15	Cylindrical Female	2.5mm x 5.5mm	Center Positive	100 to 240	50 to 60	UL/CUL/TUV/CCC/CE	\$15.95
2265599	Globtek	TR9CE4000LCP-Y	TABLE-TOP	12	4.2	50	Cylindrical Female	2.5mm x 5.5mm	Center Positive	100 to 240	50 to 60	UL/CUL/TUV/CE	\$11.95
2229239	ENG Electric Company	3A-181WP12	WALL	12	1.5	18	Cylindrical Female	2.5mm x 5.5mm	Center Positive	90 to 255	50 to 60	UL/CUL	\$11.95
2229845	Arndt	AD898F20	WALL	12	3.5	42	Cylindrical Female	2.1mm x 5.5mm	Center Positive	100 to 240	50 to 60	UL/CUL	\$11.95
2233983	Arndt	DSA-12PFT-12FUS	WALL	12	1.0	12	Cylindrical Female	2.1mm x 5.5mm	Center Positive	100 to 240	47 to 63	UL	\$7.95
2227532	Dee Van Enterprise Usa	DSA-24CA-12	WALL	12	2.0	24	Cylindrical Female	2.5mm x 5.5mm	Center Positive	90 to 264	47 to 63	CECV	\$14.95
2270999	Arndt	DYS12-120100W	WALL	12	1.0	12	Cylindrical Female	2.1mm x 5.5mm	Center Positive	100 to 240	50 to 60	CE	\$4.95
2154986	Arndt	FW75550/12	WALL	12	1.3	15	Cylindrical Female	2.1mm x 5.5mm	Center Positive	100 to 240	50 to 60	UL/CUL/CE	\$10.95
2236412	Jameco Reliapro	GQ05-120025-CU	WALL	12	0.3	3	Cylindrical Female	2.1mm x 5.5mm	Center Positive	100 to 240	47 to 63	UL,CUL	\$9.95
2231662	Jameco Reliapro	GQ12-120100-AU	WALL	12	1.0	12	Cylindrical Female	2.5mm x 5.5mm	Center Positive	100 to 240	50 to 60	UL,CUL	\$10.95
2231671	Jameco Reliapro	GQ15-120150-AU	WALL	12	1.5	18	Cylindrical Female	2.5mm x 5.5mm	Center Positive	100 to 240	50 to 60	UL,CUL	\$12.95
1950497	Jameco Reliapro	GQ30-120200-BU	WALL	12	2.0	24	Cylindrical Female	2.1mm x 5.5mm	Center Positive	100 to 240	50 to 60	BSMI/CB/CUL/FCC/PSE	\$13.95
2236738	Jameco Reliapro	GQ30-120200-BU-2.5	WALL	12	2.0	24	Cylindrical Female	2.5mm x 5.5mm	Center Positive	100 to 240	50 to 60	UL,CUL,CE	\$10.95
1940694	MEAN WELL	GS06U-3P1J	WALL	12	0.5	6	Cylindrical Female	2.1mm x 5.5mm	Center Positive	90 to 264	47 to 63	CB/CE/CUL/FCC/UL	\$9.40
1940774	MEAN WELL	GS12U12-P1I	WALL	12	1.0	12	Cylindrical Female	2.1mm x 5.5mm	Center Positive	90 to 264	47 to 63	BSMI/CB/CUL/FCC/UL	\$9.00
380156	MEAN WELL	GS25U12-P1J	WALL	12	2.1	25	Cylindrical Female	2.1mm x 5.5mm	Center Positive	90 to 264	47 to 63	BSMI/CB/CUL/FCC/UL	\$12.95
2173984	MEAN WELL	GS36U12-P1J	WALL	12	3.0	36	Cylindrical Female	2.1mm x 5.5mm	Center Positive	90 to 264	47 to 63	UL/CUL/CB/FCC	\$8.95
2271047	MEAN WELL	GSM25U12-E13-MOD-2.1	WALL	12	2.1	25	Cylindrical Female	2.1mm x 5.5mm	Center Positive	90 to 264	47 to 63	UL/TUV/CEC	\$7.49
2271055	MEAN WELL	GSM36U12-E13-MOD-2.1	WALL	12	3.0	36	Cylindrical Female	2.1mm x 5.5mm	Center Positive	100 to 240	50 to 60	UL/TUV/CEC	\$7.95
252808	Jameco Reliapro	HK-AP-120A050-US	WALL	12	0.5	6	Cylindrical Female	2.1mm x 5.5mm	Center Positive	100 to 240	47 to 63	CE/CEC/CUL/GS/UL	\$8.95
252824	Jameco Reliapro	HK-AR-120A100-US	WALL	12	1.0	12	Cylindrical Female	2.1mm x 5.5mm	Center Positive	100 to 240	47 to 63	CE/CEC/CUL/GS/UL	\$9.95
252833	Jameco Reliapro	HK-AW-120A125-US	WALL	12	1.3	15	Cylindrical Female	2.1mm x 5.5mm	Center Positive	100 to 240	47 to 63	CE/CEC/CUL/GS/UL	\$10.95
2236501	Jameco Reliapro	KSA-24W-120150VU	WALL	12	1.5	18	Cylindrical Female	2.1mm x 5.5mm	Center Positive	100 to 240	50 to 60	UL/CUL	\$11.95
2239189	Jameco Reliapro	KSAS0361200300HU-2.5	WALL	12	3.0	36	Cylindrical Female	2.5mm x 5.5mm	Center Positive	100 to 240	50 to 60	UL/CUL/CEC	\$11.95
2173116	Jameco Reliapro	KSAS0361200300HU-VI	WALL	12	3.0	36	Cylindrical Female	2.1mm x 5.5mm	Center Positive	100 to 240	50 to 60	UL/CUL/CECV	\$11.95
2150758	Arndt	MGT-12500SPS	WALL	12	0.5	6	Cylindrical Female	2.1mm x 5.5mm	Center Positive	90 to 264	50 to 60	UL/CUL/TUV/CE	\$7.95
2227831	Phihong	PLA12R-120	WALL	12	1.0	12	Cylindrical Female	2.1mm x 5.5mm	Center Positive	100 to 240	50 to 60	UL/CUL/CE	\$9.95
2280167	Arndt	PS-2.1-12-24WTM	WALL	12	2.5	30	Cylindrical Female	2.1mm x 5.5mm	Center Positive	100 to 240	50 to 60	UL/CSA/CEC	\$10.95
228849	Phihong	PSA21R-120	WALL	12	1.7	20	Cylindrical Female	2.1mm x 5.5mm	Center Positive	90 to 264	47 to 63	UL/CUL/CE/TUV	\$10.95
2261061	Phihong	PSAA20R-120L6-R	WALL	12	1.7	20.04	Cylindrical Female	2.1mm x 5.5mm	Center Positive	90 to 264	47 to 63	UL/CUL/CE	\$18.95
2258689	Phihong	PSAC12R-120-R	WALL	12	1.0	12	Cylindrical Female	2.1mm x 5.5mm	Center Positive	90 to 264	47 to 63	UL/CUL/CE	\$15.95
2270847	Arndt	PSU-C9-ELEV6	WALL	12	0.8	9	Cylindrical Female	2.5mm x 5.5mm	Center Positive	100 to 240	50 to 60	UL,CUL,CEC	\$5.95
2247277	MEAN WELL	SGA25U12-P1J	WALL	12	2.1	25	Cylindrical Female	2.1mm x 5.5mm	Center Positive	90 to 264	47 to 63	CB/CUL/FCC/UL	\$14.00

[Click Here to Request a Large Quantity Quote](#)



WALL TRANSFORMER & TABLE-TOP POWER SUPPLIES

Jameco Part#	Manufacturer	Manufacturer Part #	BODY TYPE	Primary Output Voltage (VDC)	Output Current (A)	Maximum Output Power (W)	Output Connector Type	Output Connector Diameters	Polarity	Input Voltage (VAC)	Input Frequency	Agency Approvals	Price
2225959	MEAN WELL	SGA40U12-P1J	WALL	12	3.3	40	Cylindrical Female	2.1mm x 5.5mm	Center Positive	90 to 264	47 to 63	CB/CUL/FCC/UL	\$18.00
2226038	MEAN WELL	SGA60U12-P1J	WALL	12	5.0	60	Cylindrical Female	2.1mm x 5.5mm	Center Positive	90 to 264	47 to 63	CB/CUL/FCC/UL	\$20.70
2232825	Arndt	SPS121	WALL	12	1.0	12	Cylindrical Female	2.1mm x 5.5mm	Center Positive	100 to 240	50 to 60	UL/CUL	\$6.95
2121586	Jameco Reliapro	ST-121A	WALL	12	1.0	12	Screw Terminals	Screw Terminals	—	100 to 240	50 to 60	UL/CUL/CE	\$13.95
2082134	Jameco Reliapro	ST-122A	WALL	12	2.0	24	Screw Terminals	Screw Terminals	—	100 to 240	50 to 60	UL/CUL/CEC	\$13.95
2230643	Jameco Reliapro	ST-123A	WALL	12	3.0	36	Screw Terminals	Screw Terminals	—	100 to 240	50 to 60	UL	\$14.95
2121578	Jameco Reliapro	ST-12500	WALL	12	0.5	6	Screw Terminals	Screw Terminals	—	100 to 240	50 to 60	UL/CUL/CEC	\$10.95
2210693	Asian Power Devices	WA-18H12	WALL	12	1.5	18	Cylindrical Female	2.1mm x 5.5mm	Center Positive	100 to 240	50 to 60	UL	\$7.95
2234054	Arndt	YSU20120	WALL	12	2.0	24	Cylindrical Female	2.1mm x 5.5mm	Center Positive	100 to 240	50 to 60	UL,CUL	\$9.95
2151101	Arndt	CNR2260	WALL	12	0.5	6	Cylindrical Female	2.1mm x 5.5mm	Center Positive	100 to 240	50 to 60	UL/CUL	\$5.95
2292919	Phihong	PSAA30R-120R	WALL	12	2.5	30	Cylindrical Female	2.1mm x 5.5mm	Center Positive	90 to 264	47 to 63	UL CUL CE C-Tick	\$13.95
2271223	Jameco Reliapro	G99-KPL060H-L035	TABLE-TOP	15	4.0	60	Cylindrical Female	2.1mm x 5.5mm	Center Positive	100 to 240	47 to 63	UL/CUL/TUV/CE/FCC/CCC	\$13.95
1940619	MEAN WELL	GS25A15-P1J	TABLE-TOP	15	1.7	25	Cylindrical Female	2.1mm x 5.5mm	Center Positive	90 to 264	47 to 63	ULCUL/TUV/CEC	\$12.95
1954295	MEAN WELL	GS60A15-P1J	TABLE-TOP	15	4.0	60	Cylindrical Female	2.1mm x 5.5mm	Center Positive	90 to 264	47 to 63	UL/CUL/TUV/CE	\$15.95
380173	MEAN WELL	GS25U15-P1J	WALL	15	1.7	25	Cylindrical Female	2.1mm x 5.5mm	Center Positive	90 to 264	47 to 63	BSMI/CB/CUL/FCC/UL	\$11.49
2265647	Arndt	PS15V1300MA-003	WALL	15	1.3	19.5	Cylindrical Female	2.1mm x 5.5mm	Center Positive	100 to 240	50 to 60	UL/CUL/FCC	\$7.95
2292327	Arndt	PA1030-180T1A	TABLE-TOP	18	1.7	30.06	Stripped & Tinned	18 AWG SPT-1	—	100 to 240	50 to 60	UL/CUL/CE/FCC	\$10.95
2225975	MEAN WELL	SGA40U18-P1J	WALL	18	2.2	40	Cylindrical Female	2.1mm x 5.5mm	Center Positive	90 to 264	47 to 63	CB/CUL/FCC/UL	\$18.00
2271231	Jameco Reliapro	G99-ABU120M-N039	TABLE-TOP	24	5.0	120	Cylindrical Female	2.5mm x 5.5mm	Center Positive	100 to 240	47 to 63	UL/CUL/TUV/CE/FCC/CCC	\$31.95
2271311	Jameco Reliapro	GM95-240375-F	TABLE-TOP	24	3.8	90	Cylindrical Female	2.5mm x 5.5mm	Center Positive	100 to 240	50 to 60	UL/CUL/TUV/CE/CCC	\$22.95
2099286	MEAN WELL	GS220A24-R7B	TABLE-TOP	24	9.2	220	DIN Male	4-pin DIN	—	90 to 264	47 to 63	UL/CUL/TUV/CE/PFC	\$57.95
2190346	MEAN WELL	GS25A24-P1J	TABLE-TOP	24	1.0	25	Cylindrical Female	2.1mm x 5.5mm	Center Positive	90 to 264	47 to 63	UL/CUL/TUV/CB/CE/FCC/CCC	\$10.95
1940635	MEAN WELL	GS25A24-P1JU	TABLE-TOP	24	1.0	25	Cylindrical Female	2.1mm x 5.5mm	Center Positive	90 to 264	47 to 63	UL/CUL/TUV/CEC	\$12.95
1940547	MEAN WELL	GS25B24-P1J	TABLE-TOP	24	1.0	25	Cylindrical Female	2.1mm x 5.5mm	Center Positive	90 to 264	47 to 63	UL/CSA/TUV/CE/CEC	\$10.95
1952214	MEAN WELL	GS60A24-P1J	TABLE-TOP	24	2.5	60	Cylindrical Female	2.1mm x 5.5mm	Center Positive	90 to 264	47 to 63	UL/CUL/TUV/CEC	\$14.95
2229984	Jameco Reliapro	KPL-060M-2.1-VI	TABLE-TOP	24	2.5	60	Cylindrical Female	2.1mm x 5.5mm	Center Positive	100 to 240	50 to 60	UL/CUL/TUV/CEC	\$14.95
2229992	Jameco Reliapro	KPL-060M-2.5-VI	TABLE-TOP	24	2.5	60	Cylindrical Female	2.5mm x 5.5mm	Center Positive	100 to 240	50 to 60	UL/CUL/TUV/CEC	\$12.95
2271159	Arndt	CPS024240100	WALL	24	1.0	24	Cylindrical Female	2.1mm x 5.5mm	Center Positive	100 to 240	50 to 60	UL/TUV/CE	\$10.95
2082345	MEAN WELL	GE12I24-P1J	WALL	24	0.6	15	Cylindrical Female	2.1mm x 5.5mm	Center Positive	90 to 264	47 to 63	CSA/EN/UL	\$9.70
1952898	MEAN WELL	GS18U24-P1J	WALL	24	0.8	18	Cylindrical Female	2.1mm x 5.5mm	Center Positive	90 to 264	47 to 63	BSMI/CB/CUL/FCC/UL	\$11.95
380202	MEAN WELL	GS25U24-P1J	WALL	24	1.0	25	Cylindrical Female	2.1mm x 5.5mm	Center Positive	100 to 240	50 to 60	BSMI/CB/CUL/FCC/UL	\$12.95
2229941	Jameco Reliapro	HK-AW-240A050-US	WALL	24	0.5	12	Cylindrical Female	2.1mm x 5.5mm	Center Positive	100 to 240	47 to 63	UL/CUL/TUV/CE	\$10.95
2076341	Jameco Reliapro	HK-AW-240A063-US	WALL	24	0.6	15.1	Cylindrical Female	2.1mm x 5.5mm	Center Positive	100 to 240	47 to 63	CEC/CUL/UL	\$10.95
2208972	Jameco Reliapro	KSA-24W-240100VU	WALL	24	1.0	24	Cylindrical Female	2.1mm x 5.5mm	Center Positive	100 to 240	47 to 63	UL/CUL/CECV	\$11.95
2229888	Jameco Reliapro	MPC2400107	WALL	24	1.0	24	Cylindrical Female	2.1mm x 5.5mm	Center Positive	100 to 240	50 to 60	UL,CUL,CEC	\$12.95
2271063	Jameco Reliapro	MTR-18028	WALL	24	1.0	24	Cylindrical Female	2.5mm x 5.5mm	Center Positive	100 to 240	50 to 60	UL/CUL/CEC	\$14.95
2230416	Phihong	PDA024A-1A0S-R	WALL	24	1.0	24	Cylindrical Female	2.1mm x 5.5mm	Center Positive	90 to 132	50 to 60	UL/CUL	\$8.95
2247306	MEAN WELL	SGA25U24-P1J	WALL	24	1.0	25	Cylindrical Female	2.1mm x 5.5mm	Center Positive	90 to 264	47 to 63	CB/CUL/FCC/UL	\$14.00
2225983	MEAN WELL	SGA40U24-P1J	WALL	24	1.7	40	Cylindrical Female	2.1mm x 5.5mm	Center Positive	90 to 264	47 to 63	CB/CUL/FCC/UL	\$18.00
2226062	MEAN WELL	SGA60U24-P1J	WALL	24	2.5	60	Cylindrical Female	2.1mm x 5.5mm	Center Positive	90 to 264	47 to 63	CB/CUL/FCC/UL	\$20.70
2121594	Jameco Reliapro	ST-241A	WALL	24	1.0	24	Screw Terminals	Screw Terminals	—	100 to 240	50 to 60	UL/CUL/CEC	\$12.49
2167613	Jameco Reliapro	ST-242A	WALL	24	2.0	48	Screw Terminals	Screw Terminals	—	100 to 240	50 to 60	UL/CUL/CUS/FCC	\$15.95
380220	MEAN WELL	GS25U28-P1J	WALL	28	0.9	25	Cylindrical Female	2.1mm x 5.5mm	Center Positive	100 to 240	50 to 60	BSMI/CB/CUL/FCC/UL	\$12.95
2230820	Condor Power Supplies Inc.	CENB1050A4803F01	TABLE-TOP	48	1.1	52.8	Locking Cylindrical Female	2.5mm x 5.5mm	Center Positive	100 to 240	50 to 60	UL/CUL	\$10.39
2271319	Jameco Reliapro	GM95-480200-F	TABLE-TOP	48	2.0	96	Cylindrical Female	2.5mm x 5.5mm	Center Positive	100 to 240	50 to 60	UL/CUL/TUV/CE/CCC	\$19.95
221585	MEAN WELL	GS40A48-P1J	TABLE-TOP	48	0.8	40	Cylindrical Female	2.1mm x 5.5mm	Center Positive	90 to 264	47 to 63	UL/CUL/TUV/CE	\$8.95
2202562	Phihong	PSA18U-480	TABLE-TOP	48	0.4	18	Cylindrical Female	2.5mm x 5.5mm	Center Positive	100 to 240	50 to 60	UL/CUL/CE/CCC	\$3.95
2273007	Li Tone Electronics (LTE)	65E-S7-1	TABLE-TOP	56	1.2	65	Cylindrical Female	2.1mm x 5.5mm	Center Positive	100 to 240	50 to 60	UL/CUL/TUV/CE/FCC	\$19.95
2230740	Jameco Reliapro	GPSN25A-13	TABLE-TOP	5, 12	2.5	30	DIN Male	4-pin DIN	—	100 to 240	50 to 60	UL/CUL/TUV/CE	\$34.95
196270	Jameco Reliapro	PSU25A-13-R	TABLE-TOP	5, 12	2.5	25	DIN Male	4-pin mini DIN	—	100 to 240	47 to 63	UL/CUL/CE	\$27.95
2229511	Ault	SC200	TABLE-TOP	5, 12	4.0	32	DIN Male	5-pin DIN	—	100 to 240	50 to 60	UL/CSA/TUV/CE	\$15.95
2250951	MEAN WELL	GP50A13D-R1B	TABLE-TOP	5, 12, -12	4.0	50	DIN Male	5-pin DIN	—	90 to 264	47 to 63	UL/CUL/TUV/CB/CE	\$39.60
221702	MEAN WELL	P50A13D-R1BU	TABLE-TOP	5, 12, -12	4.0	50	DIN Male	5-pin DIN	—	90 to 264	47 to 63	UL/CUL/TUV/CE	\$49.95