



[Click Here to Request a Large Quantity Quote](#)

**TRIMMER POTENTIOMETERS 3006 SERIES: 3/4 WATT ◦ 3/4" RECTANGULAR ◦ ±10% (.25"H)**

Jameco SKU	Mfr Name	Mfg. Series	Mfr P/N	Resistance (Ohms)	Power Rating	Tolerance (%)	Type	Number of Turns	Actuator Orientation	Price 1
241234	BI Technologies	3006P	89PR10 (3006P-1-100-VP)	10	0.75 W	10	3/4" Rectangular	20	Side	\$1.09
2287599	BI Technologies	3006P	89PR20 (3006P-1-200VP)	20	0.75 W	10	3/4" Rectangular	20	Side	\$1.09
768811	Spectrol/Vishay Corporation	3006P	43P500 (3006P-1-500)	50	0.75 W	10	3/4" Rectangular	15	Side	\$1.19
695990	BI Technologies	3006P	89PR100/43W101 (3006P-1-1	100	0.75 W	10	3/4" Rectangular	20	Side	\$1.09
2195593	BI Technologies	3006P	90PR100 (3006P-1-101)	100	0.75 W	10	3/4" Rectangular	20	Side	\$1.09
241242	BI Technologies	3006P	89PR200/43P201 (3006P-1-2	200	0.75 W	10	3/4" Rectangular	20	Side	\$1.09
2195614	BI Technologies	3006P	90PR250 (3006P-1-251)	250	0.75 W	10	3/4" Rectangular	20	Side	\$1.09
41937	Jameco Valuepro	3006P	3006P-1-501(43P501/8035EK500	500	0.75 W	10	3/4" Rectangular	15	Side	\$1.49
241269	Murata	3006P	2103P1K/3007P/3006P-1-102	1,000	0.75 W	10	3/4" Rectangular	15	Side	\$1.19
2195585	BI Technologies	3006P	90PR1K/89PR1K(3006P-1-1K)	1,000	0.75 W	10	3/4" Rectangular	20	Side	\$1.09
696052	Bourns	3006P	3006P-1-202Z (Panel mt.)	2,000	0.75 W	10	3/4" Rectangular	15	Side	\$0.99
41865	Spectrol/Vishay Corporation	3006P	43P202 (3006P-1-202)	2,000	0.75 W	10	3/4" Rectangular	15	Side	\$1.19
2198364	Bourns	3006P	3006P-1-202VP (79PR2K)	2,000	0.75 W	10	3/4" Rectangular	15	Side	\$1.49
696095	BI Technologies	3006P	89PR5K(3006P-1-502LF)	5,000	0.75 W	10	3/4" Rectangular	20	Side	\$1.09
41890	Murata	3006P	2103P5K(3006P-1-502LF)	5,000	0.75 W	10	3/4" Rectangular	15	Side	\$1.49
41822	Jameco Valuepro	3006P	3006P-1-103VP/LF	10,000	0.75 W	10	3/4" Rectangular	15	Side	\$1.49
41873	Spectrol/Vishay Corporation	3006P	3006P-1-203VP (43P203/961-20)	20,000	0.75 W	10	3/4" Rectangular	15	Side	\$1.49
2198372	BI Technologies	3006P	79PR20K (3006P-1-203)	20,000	0.75 W	10	3/4" Rectangular	20	Side	\$1.49
2195606	BI Technologies	3006P	90PR20K (3006P-1-203)	20,000	0.75 W	10	3/4" Rectangular	20	Side	\$1.09
241314	Spectrol/Vishay Corporation	3006P	43P253 (3006P-1-253)	25,000	0.75 W	10	3/4" Rectangular	15	Side	\$1.19
241323	Jameco Valuepro	3006P	3006P-1-503VP	50,000	0.75 W	10	3/4" Rectangular	15	Side	\$1.49
41849	Jameco Valuepro	3006P	3006P-1-104VP	100,000	0.75 W	10	3/4" Rectangular	15	Side	\$1.49
2198356	BI Technologies	3006P	79PR100K (3006P-1-104)	100,000	0.75 W	10	3/4" Rectangular	20	Side	\$1.49
63001	Spectrol/Vishay Corporation	3006P	43P204/89PR200 (3006P-1-)	200,000	0.75 W	10	3/4" Rectangular	15	Side	\$1.19
41953	BI Technologies	3006P	89PR500K (3006P-1-504)	500,000	0.75 W	10	3/4" Rectangular	20	Side	\$1.09
2195631	BI Technologies	3006P	90PR500K (3006P-1-504)	500,000	0.75 W	10	3/4" Rectangular	20	Side	\$1.19
241374	Jameco Valuepro	3006P	89PR1MEG/3006P-1-105VP	1,000,000	0.75 W	10	3/4" Rectangular	20	Side	\$1.09
2162901	BI Technologies	3006P	89PR2MEG/343P2M (3006P-1)	2,000,000	0.75 W	10	3/4" Rectangular	20	Side	\$1.09
2291655	Vishay	3006W	43W100 (3006W-1-100VP)	10	0.75 W	10	3/4" Rectangular	15	Side	\$1.49
2178401	Spectrol/Vishay Corporation	3006W	43W200 (3006W-1-200)	20	0.75 W	10	3/4" Rectangular	15	Side	\$1.49
2178380	BI Technologies	3006W	89WR100/43W101 (3006W-1-10	100	0.75 W	10	3/4" Rectangular	20	Side	\$1.09
2178419	Spectrol/Vishay Corporation	3006W	43W201 (3006W-1-201)	200	0.75 W	10	3/4" Rectangular	15	Side	\$1.49
2178460	Spectrol/Vishay Corporation	3006W	43W501 (3006W-1-501)	500	0.75 W	10	3/4" Rectangular	15	Side	\$1.49
2291647	Jameco Valuepro	3006W	3006W-1-102VP-LF	1,000	0.75 W	10	3/4" Rectangular	15	Side	\$1.49
2198399	BI Technologies	3006W	77PR2K (3006W-1-202)	2,000	0.75 W	10	3/4" Rectangular	20	Side	\$1.09
1967037	Bourns	3006W	3006W-1-103LF	10,000	0.75 W	10	3/4" Rectangular	15	Side	\$1.49
2178443	Spectrol/Vishay Corporation	3006W	43W253/3006W-1-253LF	25,000	0.75 W	10	3/4" Rectangular	15	Side	\$1.49
2178427	Spectrol/Vishay Corporation	3006W	43W204/89WHR200K (3006W-1	200,000	0.75 W	10	3/4" Rectangular	15	Side	\$1.49
2198381	BI Technologies	3006W	77PR1MEG (3006W-1-105)	1,000,000	0.75 W	10	3/4" Rectangular	20	Side	\$1.09
2178435	Spectrol/Vishay Corporation	3006W	43W205 (3006W-1-205)	2,000,000	0.75 W	10	3/4" Rectangular	15	Side	\$1.49
2180501	Spectrol/Vishay Corporation	3006Y	43Y500 (3006Y-1-500)	50	0.75 W	10	3/4" Rectangular	15	Side	\$1.49



[Click Here to Request a Large Quantity Quote](#)

**TRIMMER POTENTIOMETERS 3006 SERIES: 3/4 WATT ◦ 3/4" RECTANGULAR ◦ ±10% (.25"H)**

Jameco SKU	Mfr Name	Mfg. Series	Mfr P/N	Resistance (Ohms)	Power Rating	Tolerance (%)	Type	Number of Turns	Actuator Orientation	Price 1
<a href="#">2180463</a>	Spectrol/Vishay Corporation	3006Y	43Y101 (3006Y-1-101)	100	0.75 W	10	3/4" Rectangular	15	Side	\$1.49
<a href="#">2180480</a>	Spectrol/Vishay Corporation	3006Y	89XR200/43Y201 (3006Y-1-	200	0.75 W	10	3/4" Rectangular	15	Side	\$1.49
<a href="#">768853</a>	Bourns	3006Y	3006Y-1-102	1,000	0.75 W	10	3/4" Rectangular	15	Side	\$1.95
<a href="#">2180471</a>	Spectrol/Vishay Corporation	3006Y	43Y502 (3006Y-1-502)	5,000	0.75 W	10	3/4" Rectangular	15	Side	\$1.95
<a href="#">241293</a>	Spectrol/Vishay Corporation	3006Y	43Y103 (3006Y-1-103-VP)	10,000	0.75 W	10	3/4" Rectangular	15	Side	\$1.95
<a href="#">2195551</a>	BI Technologies	3006Y	89XR50K (3006Y-1-503)	50,000	0.75 W	10	3/4" Rectangular	20	Side	\$1.49
<a href="#">2180498</a>	Spectrol/Vishay Corporation	3006Y	43Y204 (3006Y-1-204)	200,000	0.75 W	10	3/4" Rectangular	15	Side	\$1.49
<a href="#">2180455</a>	Spectrol/Vishay Corporation	3006Y	43Y254 (3006Y-1-254)	250,000	0.75 W	10	3/4" Rectangular	15	Side	\$1.49
<a href="#">2180447</a>	Spectrol/Vishay Corporation	3006Y	43Y205 (3006Y-1-205)	2,000,000	0.75 W	10	3/4" Rectangular	15	Side	\$1.49