

[Click Here to Request a Large Quantity Quote](#)



TRIMMER POTENTIOMETERS 3009 SERIES: 3/4 WATT ◦ 3/4" RECTANGULAR ◦ ±10% (-55°C to +125°C) ◦ .35"H

Jameco SKU	Mfr Name	Mfg. Series	Mfr P/N	Resistance (Ohms)	Power Rating	Tolerance (%)	Type	Number of Turns	Actuator Orientation	Price 1
768861	Bourns	3009P	89PHR10 (3009P-1-101)	100	0.75 W	10	3/4" Rectangular	15	Side	\$1.49
768870	BI Technologies	3009P	89PHR2 (3009P-1-202)	2,000	0.75 W	10	3/4" Rectangular	15	Side	\$1.49
2195489	BI Technologies	3009P	89PHR20K (3009P-1-203)	20,000	0.75 W	10	3/4" Rectangular	20	Side	\$1.49
768909	BI Technologies	3009P	89PHR50K (3009P-1-503)	50,000	0.75 W	10	3/4" Rectangular	15	Side	\$1.49
696124	BI Technologies	3009P	89PHR100K (3009P-1-104)	100,000	0.75 W	10	3/4" Rectangular	15	Side	\$1.49
2178371	BI Technologies	3009W	89WHR10 (3009W-1-100)	10	0.75 W	10	3/4" Rectangular	15	Side	\$1.49
2178451	BI Technologies	3009W	89WHR50 (3009W-1-500)	50	0.75 W	10	3/4" Rectangular	15	Side	\$1.09
2195569	BI Technologies	3009W	89WHR100 (3009W-1-101)	100	0.75 W	10	3/4" Rectangular	20	Side	\$1.09
2195500	BI Technologies	3009W	89WHR1K (3009W-1-102)	1,000	0.75 W	10	3/4" Rectangular	20	Side	\$1.09
2195526	BI Technologies	3009W	89WHR50K /3009W-1-503LF	50,000	0.75 W	10	3/4" Rectangular	20	Side	\$1.09
2198401	BI Technologies	3009W	76PR100K (3009W-1-104)	100,000	0.75 W	10	3/4" Rectangular	15	Side	\$1.09
2195833	BI Technologies	3009X	89XHR100-274A (pictured)	100	0.75 W	10	3/4" Rectangular	20	.32" L Side Shaft	\$1.09
2195577	BI Technologies	3009Y	89XHR100 (3009Y-1-101)	100	0.75 W	10	3/4" Rectangular	20	Side	\$1.09
2195534	BI Technologies	3009Y	89XHR500 (3009Y-1-501)	500	0.75 W	10	3/4" Rectangular	20	Side	\$1.09