



[Click Here to Request a Large Quantity Quote](#)

**TRIMMER POTENTIOMETERS 3266 SERIES: 1/4 WATT ◦ 1/4 SQUARE ◦ ±10**

Jameco SKU	Mfr Name	Mfg. Series	Mfr P/N	Resistance (Ohms)	Power Rating	Tolerance (%)	Type	Number of Turns	Actuator Orientation	Price
<a href="#">2291663</a>	Jameco Valuepro	3266P	3266P-1-102VP/LF	1,000	0.25 W	10	1/4" Square	12	Side	\$2.95
<a href="#">2291671</a>	Jameco Valuepro	3266P	3266P-1-502VP/LF	5,000	0.25 W	10	1/4" Square	12	Side	\$2.95
<a href="#">769098</a>	Spectrol/Vishay Corporation	3266P	64PR10K (3266P-1-103LF)	10,000	0.25 W	10	1/4" Square	12	Side	\$2.95
<a href="#">1156226</a>	BI Technologies	3266P	64PR100K (3266P-1-104)	100,000	0.25 W	10	1/4" Square	12	Side	\$2.95
<a href="#">2194881</a>	BI Technologies	3266P	64PR200K (3266P-1-204VP)	200,000	0.25 W	10	1/4" Square	12	Side	\$2.95
<a href="#">2200727</a>	BI Technologies	3266W	64WR50 (3266W-1-500VP)	50	0.25 W	10	1/4" Square	12	Top	\$2.95
<a href="#">2194945</a>	BI Technologies	3266W	64WR500 (3266W-1-501)	500	0.25 W	10	1/4" Square	12	Top	\$2.95
<a href="#">696351</a>	BI Technologies	3266W	3266W-1-102LF (64WR1K)	1,000	0.25 W	10	1/4" Square	12	Top	\$2.95
<a href="#">2194929</a>	BI Technologies	3266W	3266W-1-202K(64WR2K)	2,000	0.25 W	10	1/4" Square	12	Top	\$2.95
<a href="#">254669</a>	Jameco Valuepro	3266W	3266W-1-502VP(64WR5K)	5,000	0.25 W	10	1/4" Square	12	Top	\$2.95
<a href="#">254677</a>	Jameco Valuepro	3266W	860W-1-103/3266W-1-103VP	10,000	0.25 W	10	1/4" Square	12	Top	\$2.95
<a href="#">696415</a>	BI Technologies	3266W	3266W-1-203VP(64WR20K)	20,000	0.25 W	10	1/4" Square	12	Top	\$2.95
<a href="#">254714</a>	BI Technologies	3266W	64WR100K (3266W-1-104VP)	100,000	0.25 W	10	1/4" Square	12	Top	\$2.95
<a href="#">696423</a>	BI Technologies	3266W	64WR200K (3266W-1-204)	200,000	0.25 W	10	1/4" Square	12	Top	\$2.95
<a href="#">254730</a>	BI Technologies	3266W	64WR500K (3266W-1-504)	500,000	0.25 W	10	1/4" Square	12	Top	\$2.95
<a href="#">696520</a>	BI Technologies	3266X	64XR500 (3266X-1-501VP)	500	0.25 W	10	1/4" Square	12	Side	\$2.95
<a href="#">696474</a>	BI Technologies	3266X	64XR25K/3266X-1-253VP	1,000	0.25 W	10	1/4" Square	12	Side	\$2.49
<a href="#">1156314</a>	BI Technologies	3266X	3266X-1-102VP(64XR1K)	1,000	0.25 W	10	1/4" Square	12	Side	\$2.95
<a href="#">1156381</a>	Bourns	3266X	3266X-1-502LF	5,000	0.25 W	10	1/4" Square	12	Side	\$2.95
<a href="#">1156331</a>	BI Technologies	3266X	3266X-1-103VP (64XR10)	10,000	0.25 W	10	1/4" Square	12	Side	\$2.95
<a href="#">696546</a>	BI Technologies	3266X	64XR50K (3266X-1-503)	50,000	0.25 W	10	1/4" Square	12	Side	\$2.95
<a href="#">769223</a>	BI Technologies	3266X	64XR200K (3266X-1-204)	200,000	0.25 W	10	1/4" Square	12	Side	\$2.95
<a href="#">2194953</a>	BI Technologies	3266X	64XR250K (3266X-1-254VP)	250,000	0.25 W	10	1/4" Square	12	Side	\$2.95
<a href="#">2285575</a>	Bourns	3266X	3266X-1-504LF	500,000	0.25 W	10	1/4" Square	12	Side	\$2.95
<a href="#">2194988</a>	BI Technologies	3266Y	64YR20 (3266Y-1-200)	20	0.25 W	10	1/4" Square	12	Top	\$2.95
<a href="#">2194961</a>	BI Technologies	3266Y	64YR100 (3266Y-1-101)	100	0.25 W	10	1/4" Square	12	Top	\$2.95
<a href="#">2199156</a>	BI Technologies	3266Y	64YR200 (3266Y-1-201VP)	200	0.25 W	10	1/4" Square	12	Top	\$2.95
<a href="#">2199148</a>	BI Technologies	3266Y	64YR500 (3266Y-1-501VP)	500	0.25 W	10	1/4" Square	12	Top	\$2.95
<a href="#">2194970</a>	BI Technologies	3266Y	64YR25K (3266Y-1-253VP)	25,000	0.25 W	10	1/4" Square	12	Top	\$2.95
<a href="#">1156411</a>	Bourns	3266Z	64ZR1K (3266Z-1-102)	1,000	0.25 W	10	1/4" Square	12	Side	\$2.95