



[Click Here to Request a Large Quantity Quote](#)

TRIMMER POTENTIOMETERS 3299 SERIES: 1/2 WATT ◦ 3/8" SQUARE ◦ ±10% (-55°C to +125°C)

| Jameco SKU | Mfr Name | Mfg. Series | Mfr P/N | Resistance (Ohms) | Power Rating | Tolerance (%) | Type | Number of Turns | Actuator Orientation | Price 1 |
|------------|-----------------|-------------|-------------------------------|-------------------|--------------|---------------|-------------|-----------------|----------------------|---------|
| 1157034 | BI Technologies | 3299P | 68PR100 (3299P-1-101) | 100 | 0.5 W | 10 | 3/8" Square | 20 | Side | \$2.95 |
| 2200794 | BI Technologies | 3299P | 68PR200/3299P-1-201LF | 200 | 0.5 W | 10 | 3/8" Square | 20 | Side | \$2.95 |
| 769670 | BI Technologies | 3299P | 68PR500 (3299P-1-501) | 500 | 0.5 W | 10 | 3/8" Square | 20 | Side | \$2.95 |
| 769653 | BI Technologies | 3299P | 68PR1K/3299P-1-102VP | 1,000 | 0.5 W | 10 | 3/8" Square | 20 | Side | \$2.95 |
| 854145 | BI Technologies | 3299P | 3299P-I-502(68PR5K/3102P-1-5K | 5,000 | 0.5 W | 10 | 3/8" Square | 20 | Side | \$2.95 |
| 854102 | BI Technologies | 3299P | 3299P-1-103VP (68PR10K) | 10,000 | 0.5 W | 10 | 3/8" Square | 20 | Side | \$2.95 |
| 2285607 | Bourns | 3299P | 3299P-1-504LF | 500,000 | 0.5 W | 10 | 3/8" Square | 25 | Side | \$2.95 |
| 241066 | BI Technologies | 3299W | 3299W-1-200-VP (68WR20) | 20 | 0.5 W | 10 | 3/8" Square | 20 | Top | \$2.95 |
| 241074 | BI Technologies | 3299W | 68WR50 (3299W-1-500-VP) | 50 | 0.5 W | 10 | 3/8" Square | 20 | Top | \$2.95 |
| 241082 | BI Technologies | 3299W | 3299W-1-101-VP (68WR100) | 100 | 0.5 W | 10 | 3/8" Square | 20 | Top | \$2.95 |
| 2195219 | BI Technologies | 3299W | 68WR200 (3299W-1-201) | 200 | 0.5 W | 10 | 3/8" Square | 20 | Top | \$2.95 |
| 241103 | BI Technologies | 3299W | 68WR500/3299W-1-501LF/VP) | 500 | 0.5 W | 10 | 3/8" Square | 20 | Top | \$2.95 |
| 183556 | BI Technologies | 3299W | 68WR1K (3299W-1-102) | 1,000 | 0.5 W | 10 | 3/8" Square | 25 | Top | \$2.95 |
| 241111 | BI Technologies | 3299W | 3299W-1-102-VP(68WR1K) | 1,000 | 0.5 W | 10 | 3/8" Square | 20 | Top | \$2.95 |
| 854129 | BI Technologies | 3299W | 3299W-1-202VP(68WR2K) | 2,000 | 0.5 W | 10 | 3/8" Square | 20 | Top | \$2.95 |
| 241139 | BI Technologies | 3299W | 63299W-1-502-VP(68WR5K) | 5,000 | 0.5 W | 10 | 3/8" Square | 20 | Top | \$2.95 |
| 183564 | Jameco Valuepro | 3299W | 3299W-1-103VP | 10,000 | 0.5 W | 10 | 3/8" Square | 25 | Top | \$2.95 |
| 238633 | BI Technologies | 3299W | 68WR20K(RNF32) 3299W-1-) | 20,000 | 0.5 W | 10 | 3/8" Square | 20 | Top | \$2.95 |
| 241200 | BI Technologies | 3299W | 68WR50K/3299W-1-503LP | 50,000 | 0.5 W | 10 | 3/8" Square | 20 | Top | \$2.95 |
| 241189 | Jameco Valuepro | 3299W | 3299W-1-104-VP/LF | 100,000 | 0.5 W | 10 | 3/8" Square | 25 | Top | \$2.95 |
| 854161 | BI Technologies | 3299W | 68WR200K/3299W-1-204LF | 200,000 | 0.5 W | 10 | 3/8" Square | 20 | Top | \$2.95 |
| 241197 | BI Technologies | 3299W | 68WR250K (3299W-1-254-VP) | 250,000 | 0.5 W | 10 | 3/8" Square | 20 | Top | \$2.95 |
| 238676 | Bourns | 3299W | 3299W-1-504 | 500,000 | 0.5 W | 10 | 3/8" Square | 25 | Top | \$2.95 |
| 241219 | Jameco Valuepro | 3299W | 3299W-1-105VP | 1,000,000 | 0.5 W | 10 | 3/8" Square | 25 | Top | \$2.95 |
| 769784 | BI Technologies | 3299X | 68XR500 (3299X-1-501) | 500 | 0.5 W | 10 | 3/8" Square | 20 | Side | \$2.95 |
| 854188 | BI Technologies | 3299X | 3299X-1-102VP(68XR1K) | 1,000 | 0.5 W | 10 | 3/8" Square | 20 | Side | \$2.95 |
| 854225 | BI Technologies | 3299X | 3299X-1-202 (68XR2K) | 2,000 | 0.5 W | 10 | 3/8" Square | 20 | Side | \$2.95 |
| 854268 | BI Technologies | 3299X | 68XR5K (3299X-1-502) | 5,000 | 0.5 W | 10 | 3/8" Square | 20 | Side | \$2.95 |
| 1157288 | Bourns | 3299X | 3299X-1-103LF | 10,000 | 0.5 W | 10 | 3/8" Square | 25 | Side | \$2.95 |
| 854209 | BI Technologies | 3299X | 68XR10K/3299X-1-103VP | 10,000 | 0.5 W | 10 | 3/8" Square | 20 | Side | \$1.69 |
| 1946501 | BI Technologies | 3299X | 68XR25K (3299X-1-253-VP) | 25,000 | 0.5 W | 10 | 3/8" Square | 20 | Side | \$2.95 |
| 769792 | BI Technologies | 3299X | 68XR50K (3299X-1-503) | 50,000 | 0.5 W | 10 | 3/8" Square | 20 | Side | \$2.95 |
| 769741 | BI Technologies | 3299X | 68XR100K (3299X-1-104) | 100,000 | 0.5 W | 10 | 3/8" Square | 20 | Side | \$2.95 |
| 769733 | BI Technologies | 3299X | 68XR500K (3299X-1-504) | 500,000 | 0.5 W | 10 | 3/8" Square | 20 | Side | \$2.95 |
| 1946527 | BI Technologies | 3299X | 68XR2MEG (3299X-1-205-VP) | 2,000,000 | 0.5 W | 10 | 3/8" Square | 20 | Side | \$2.95 |
| 240573 | Bourns | 3299Y | 3299Y-1-102VP | 1,000 | 0.5 W | 10 | 3/8" Square | 25 | Top | \$2.95 |
| 240581 | Bourns | 3299Y | 3299Y-1-202LF | 2,000 | 0.5 W | 10 | 3/8" Square | 25 | Top | \$2.95 |
| 240590 | Bourns | 3299Y | 3299Y-1-502VP/LF | 5,000 | 0.5 W | 10 | 3/8" Square | 25 | Top | \$2.95 |
| 240602 | Jameco Valuepro | 3299Y | 3299Y-1-103VP/LF | 10,000 | 0.5 W | 10 | 3/8" Square | 25 | Top | \$2.95 |
| 2285647 | Bourns | 3299Y | 3299Y-1-204 | 200,000 | 0.5 W | 10 | 3/8" Square | 25 | Top | \$0.99 |