



[Click Here to Request a Large Quantity Quote](#)

TRIMMER POTENTIOMETERS 3329 SERIES: 1/2 WATT ◦ 1/4" ROUND ◦ ±10% (-55°C to +150°C)

Jameco SKU	Mfr Name	Mfg. Series	Mfr P/N	Resistance (Ohms)	Power Rating	Tolerance (%)	Type	Number of Turns	Actuator Orientation	Price 1
2195850	BI Technologies	3329H	82PFR10 (3329H-1-100)	10	0.5 W	10	1/4" Round	1	Top	\$ 1.95
2195286	BI Technologies	3329H	82PFR20 (3329H-1-200)	20	0.5 W	10	1/4" Round	1	Top	\$ 1.49
1947626	BI Technologies	3329H	62PR50 (3329H-1-500)	50	0.5 W	10	1/4" Round	1	Top	\$ 1.95
770021	BI Technologies	3329H	82PR100/82MR100 (3329H-1)	100	0.5 W	10	1/4" Round	1	Top	\$ 1.95
854436	BI Technologies	3329H	62PR200/62-3-1/201(3329H)	200	0.5 W	10	1/4" Round	1	Top	\$ 1.95
2179235	Spectrol/Vishay Corporation	3329H	62-3-1/2-251 (3329H-1-251)	250	0.5 W	10	1/4" Round	1	Top	\$ 1.95
2180383	BI Technologies	3329H	62PR500 (3329H-1-501)	500	0.5 W	10	1/4" Round	1	Top	\$ 1.95
1157907	BI Technologies	3329H	82PR1K (3329H-1-102)	1,000	0.5 W	10	1/4" Round	1	Top	\$ 1.25
2179278	Spectrol/Vishay Corporation	3329H	75H102/3329H-1-102	1,000	0.5 W	10	1/4" Round	1	Top	\$ 1.49
854356	Spectrol/Vishay Corporation	3329H	62-3-1/2-102 (3329H-1-102)	1,000	0.5 W	10	1/4" Round	1	Top	\$ 1.95
1157931	BI Technologies	3329H	62PR2K (3329H-1-202)	2,000	0.5 W	10	1/4" Round	1	Top	\$ 1.49
2180391	Bourns	3329H	3329H-1-202LF	2,000	0.5 W	10	1/4" Round	1	Top	\$ 1.49
854452	Spectrol/Vishay Corporation	3329H	62-3-1/2-202 (3329H-1-202)	2,000	0.5 W	10	1/4" Round	1	Top	\$ 1.25
1157940	BI Technologies	3329H	82PFR5K/82PR5K (3329H-1-5)	5,000	0.5 W	10	1/4" Round	1	Top	\$ 1.25
854532	Vishay	3329H	3329H-1-502(62-3-1/2-502)	5,000	0.5 W	10	1/4" Round	1	Top	\$ 1.95
1157915	BI Technologies	3329H	62PR10K /3329H-1-103	10,000	0.5 W	10	1/4" Round	1	Top	\$ 1.95
2179286	Spectrol/Vishay Corporation	3329H	75H103 (3329H-1-103)	10,000	0.5 W	10	1/4" Round	1	Top	\$ 1.25
854487	BI Technologies	3329H	82PR20K/3329H-1-203LF	20,000	0.5 W	10	1/4" Round	1	Top	\$ 1.25
854399	BI Technologies	3329H	82PR50K (3329H-1-503-VP)	50,000	0.5 W	10	1/4" Round	1	Top	\$ 1.25
854567	Spectrol/Vishay Corporation	3329H	62-3-1/2-503 (3329H-1-503)	50,000	0.5 W	10	1/4" Round	1	Top	\$ 1.95
2180404	Spectrol/Vishay Corporation	3329H	75H100K (3329H-1-104)	100,000	0.5 W	10	1/4" Round	1	Top	\$ 1.25
770030	BI Technologies	3329H	62PR100K (3329H-1-104)	100,000	0.5 W	10	1/4" Round	1	Top	\$ 1.49
770056	BI Technologies	3329H	62PR200K (3329H-1-204)	200,000	0.5 W	10	1/4" Round	1	Top	\$ 1.95
2133667	Bourns	3329H	3329H-1-504LF	500,000	0.5 W	10	1/4" Round	1	Top	\$ 1.95
254561	BI Technologies	3329P	82MR20 (3329P-1-200-VP)	20	0.5 W	10	1/4" Round	1	Top	\$ 1.95
854508	Spectrol/Vishay Corporation	3329P	62-1-1/2-501 (3329P-1-501)	500	0.5 W	10	1/4" Round	1	Top	\$ 1.49
95441	Bourns	3329P	3329P-1-102LF (T7YA1K)	1,000	0.5 W	10	1/4" Round	1	Top	\$ 1.95
254502	BI Technologies	3329P	82MR2K (3329P-1-202-VP)	2,000	0.5 W	10	1/4" Round	1	Top	\$ 1.95
254511	BI Technologies	3329P	62MR5K (3329P-1-502-VP)	5,000	0.5 W	10	1/4" Round	1	Top	\$ 1.95
96719	Jameco Valuepro	3329P	3221P10K/3329P-1-103VP/LF	10,000	0.5 W	10	1/4" Round	1	Top	\$ 1.95
2179294	Spectrol/Vishay Corporation	3329P	75P203 (3329P-1-203)	20,000	0.5 W	10	1/4" Round	1	Top	\$ 1.29
254537	BI Technologies	3329P	62MR20K (3329P-1-203-VP)	20,000	0.5 W	10	1/4" Round	1	Top	\$ 1.49
770101	Bourns	3329P	3329P-1-503	50,000	0.5 W	10	1/4" Round	1	Top	\$ 1.95
95484	BI Technologies	3329P	82MR100K/3321P100K(3329P)	100,000	0.5 W	10	1/4" Round	1	Top	\$ 1.49
254570	BI Technologies	3329P	62MR200K (3329P-1-204-VP)	200,000	0.5 W	10	1/4" Round	1	Top	\$ 1.49
254538	BI Technologies	3329P	62MR250K (3329P-1-254-VP)	250,000	0.5 W	10	1/4" Round	1	Top	\$ 1.95
254588	BI Technologies	3329P	62MR500K (3329P-1-504-VP)	500,000	0.5 W	10	1/4" Round	1	Top	\$ 1.95
254596	BI Technologies	3329P	62MR1MEG (3329P-1-105-VP)	1,000,000	0.5 W	10	1/4" Round	1	Top	\$ 1.95
2195278	BI Technologies	3329U	82WR500 (3329U-1-501)	500	0.5 W	10	1/4" Round	1	Top	\$ 1.49
2195251	BI Technologies	3329U	82WFR10K (3329U-1-103)	10,000	0.5 W	10	1/4" Round	1	Top	\$ 1.25
2201851	BI Technologies	3329U	82WFR100K (3329U-1-104)	100,000	0.5 W	10	1/4" Round	1	Top	\$ 1.25
2195260	BI Technologies	3329U	82WFR250K (3329U-1-254)	250,000	0.5 W	10	1/4" Round	1	Top	\$ 1.25
770144	BI Technologies	3329W	82PAR2K (3329W-1-202)	2,000	0.5 W	10	1/4" Round	1	Top	\$ 1.95

[Click Here to Request a Large Quantity Quote](#)



TRIMMER POTENTIOMETERS 3329 SERIES: 1/2 WATT ◦ 1/4" ROUND ◦ ±10% (-55°C to +150°C)

Jameco SKU	Mfr Name	Mfg. Series	Mfr P/N	Resistance (Ohms)	Power Rating	Tolerance (%)	Type	Number of Turns	Actuator Orientation	Price 1
770136	BI Technologies	3329W	82PAR10K (3329W-1-103)	10,000	0.5 W	10	1/4" Round	1	Top	\$ 1.25
770161	BI Technologies	3329W	82PAR25K (3329W-1-253)	25,000	0.5 W	10	1/4" Round	1	Top	\$ 1.95
2180412	Spectrol/Vishay Corporation	3329X	75T102/3329X-1-102VP	1,000	0.5 W	10	1/4" Round	1	Side	\$ 1.95
2235196	Jameco Valuepro	3329X	3329-X-1-502VP	5,000	0.5 W	10	1/4" Round	1	Side	\$ 1.95
2235209	Jameco Valuepro	3329X	3329X-1-103VP	10,000	0.5 W	10	1/4" Round	1	Side	\$ 1.95