



[Click Here to Request a Large Quantity Quote](#)

TRIMMER POTENTIOMETERS 3352 SERIES: 1/2 WATT ◦ 3/8" ROUND ◦ ±20% (0°C to +125°C)

Jameco SKU	Mfr Name	Mfg. Series	Mfr P/N	Resistance (Ohms)	Power Rating	Tolerance (%)	Type	Number of Turns	Actuator Orientation	Price 1
2195729	BI Technologies	3352E	91ER500 (3352E-1-501)	500	0.5 W	20	3/8" Round	1	Top	\$0.79
2195681	BI Technologies	3352E	91ER2K (3352E-1-202)	2,000	0.5 W	20	3/8" Round	1	Top	\$0.79
2195702	BI Technologies	3352E	91ER25K (3352E-1-253)	25,000	0.5 W	20	3/8" Round	1	Top	\$0.79
2195711	BI Technologies	3352E	91ER250K (3352E-1-254)	250,000	0.5 W	20	3/8" Round	1	Top	\$0.79
2195673	BI Technologies	3352P	91BR50 (3352P-1-500)	50	0.5 W	20	3/8" Round	1	Top	\$0.79
770321	BI Technologies	3352P	91BR200 (3352P-1-201)	200	0.5 W	20	3/8" Round	1	Top	\$0.79
770339	BI Technologies	3352P	91BR500 (3352P-1-501)	500	0.5 W	20	3/8" Round	1	Top	\$0.79
2291679	Bourns	3352P	3352P-1-102 (91BR1K)	1,000	0.5 W	20	3/8" Round	1	Top	\$1.59
2200612	BI Technologies	3352P	91BR2K (3352P-1-202)	2,000	0.5 W	20	3/8" Round	1	Top	\$1.59
2281279	Bourns	3352P	3352P-1-502LF (91BR5K)	5,000	0.5 W	20	3/8" Round	1	Top	\$1.59
2291687	Bourns	3352P	3352P-1-103 (91BR10K)	10,000	0.5 W	20	3/8" Round	1	Top	\$1.59
2235372	BI Technologies	3352P	91BR50K (3352P-1-503)	50,000	0.5 W	20	3/8" Round	1	Top	\$1.59
2195665	BI Technologies	3352T	91AR10 (3352T-1-100)	10	0.5 W	20	3/8" Round	1	Top	\$1.09
2200621	BI Technologies	3352T	91AR20 (3352T-1-200)	20	0.5 W	20	3/8" Round	1	Top	\$1.09
2035805	BI Technologies	3352T	91AR50 (3352T-1-500)	50	0.5 W	20	3/8" Round	1	Top	\$1.09
2291695	Bourns	3352T	3352T-1-102 (91AR1K)	1,000	0.5 W	20	3/8" Round	1	Top	\$1.59
2195657	BI Technologies	3352T	91AR2.5K (3352T-1-252)	2,500	0.5 W	20	3/8" Round	1	Top	\$1.59
2291703	Bourns	3352T	3352T-1-103 (91AR10K)	10,000	0.5 W	20	3/8" Round	1	Top	\$1.59
350351	BI Technologies	3352T	91AR25K (3352T-1-253)	25,000	0.5 W	20	3/8" Round	1	Top	\$1.59
2291711	Bourns	3352W	3352W-1-102 (91WR1K)	1,000	0.5 W	20	3/8" Round	1	Side	\$1.59
2195753	BI Technologies	3352W	91WR2K (3352W-1-202)	2,000	0.5 W	20	3/8" Round	1	Side	\$1.09
770347	BI Technologies	3352W	91WR10K (3352W-1-103)	10,000	0.5 W	20	3/8" Round	1	Side	\$1.59
2195761	BI Technologies	3352W	91WR20K (3352W-1-203K)	20,000	0.5 W	20	3/8" Round	1	Side	\$1.59
2195745	BI Technologies	3352W	91WR100K (3352W-1-104)	100,000	0.5 W	20	3/8" Round	1	Side	\$1.59
2195737	BI Technologies	3352W	91WR1MEG (3352W-1-105)	1,000,000	0.5 W	20	3/8" Round	1	Side	\$1.59