



[Click Here to Request a Large Quantity Quote](#)

TRIMMER POTENTIOMETERS 3362 SERIES: 1/2 WATT ◦ 1/4" SQUARE ◦ ±10% (-55°C to +125°C)

Jameco SKU	Mfr Name	Mfg. Series	Mfr P/N	Resistance (Ohms)	Power Rating	Tolerance (%)	Type	Number of Turns	Actuator Orientation	Price 1
2194751	BI Technologies	3362H	25WR201 (3362H-1-201)	200	0.5 W	10	1/4" Square	1	Top	\$0.99
2291719	Bourns	3362H	3362H-1-102LF/VP	1,000	0.5 W	10	1/4" Square	1	Top	\$0.99
2194742	BI Technologies	3362H	25WR202 (3362H-1-202)	2,000	0.5 W	10	1/4" Square	1	Top	\$0.99
2291727	Bourns	3362H	3362H-1-502LF/VP	5,000	0.5 W	10	1/4" Square	1	Top	\$0.99
770371	Jameco Valuepro	3362H	3362H-1-103VP	10,000	0.5 W	10	1/4" Square	1	Top	\$0.99
2194777	BI Technologies	3362H	25WR500K (3362H-1-504)	500,000	0.5 W	10	1/4" Square	1	Top	\$0.79
2194734	BI Technologies	3362H	25WR105 (3362H-1-105)	1,000,000	0.5 W	10	1/4" Square	1	Top	\$0.99
2194697	BI Technologies	3362M	25VR101 (3362M-1-101)	100	0.5 W	10	1/4" Square	1	Side	\$0.99
2280895	Bourns	3362M	3362M-1-102LF	1,000	0.5 W	10	1/4" Square	1	Side	\$0.99
2194700	BI Technologies	3362M	25VR205 (3362M-1-205)	2,000,000	0.5 W	10	1/4" Square	1	Side	\$0.99
770419	Bourns	3362P	3362P-1-101LF	100	0.5 W	10	1/4" Square	1	Top	\$0.99
182810	Bourns	3362P	3362P-1-501VP/LF	500	0.5 W	10	1/4" Square	1	Top	\$0.99
253982	Bourns	3362P	3362P-1-102VP	1,000	0.5 W	10	1/4" Square	1	Top	\$0.99
2201586	BI Technologies	3362P	25PR202 (3362P-1-202LP)	2,000	0.5 W	10	1/4" Square	1	Top	\$0.99
182829	Bourns	3362P	3362P-1-502VP	5,000	0.5 W	10	1/4" Square	1	Top	\$0.99
182837	Jameco Valuepro	3362P	3362P-1-103VP(25PR10)	10,000	0.5 W	10	1/4" Square	1	Top	\$0.99
254002	Jameco Valuepro	3362P	25PR203/3362P-1-203VP	20,000	0.5 W	10	1/4" Square	1	Top	\$0.99
254028	Jameco Valuepro	3362P	3362P-1-503VP	50,000	0.5 W	10	1/4" Square	1	Top	\$0.99
254036	Jameco Valuepro	3362P	3362P-1-104VP/LF	100,000	0.5 W	10	1/4" Square	1	Top	\$0.99
254044	Jameco Valuepro	3362P	3362P-1-504VP/LF	500,000	0.5 W	10	1/4" Square	1	Top	\$0.99
254115	Jameco Valuepro	3362P	3362P-1-105VP	1,000,000	0.5 W	10	1/4" Square	1	Top	\$0.99
2285591	Bourns	3362R	3362R-1-102LF	1,000	0.5 W	10	1/4" Square	1	Top	\$0.99
2285599	Bourns	3362S	3362S-1-101LF	100	0.5 W	10	1/4" Square	1	Side	\$0.99
2194646	BI Technologies	3362S	25SR20K (3362S-1-203VP)	20,000	0.5 W	10	1/4" Square	1	Side	\$0.99
770540	Jameco Valuepro	3362U	25UR200/3362U-1-200VP	20	0.5 W	10	1/4" Square	1	Top	\$0.99
2133771	Philips Semiconductor	3362U	CT-6U102/3362U-1-102VP	1,000	0.5 W	10	1/4" Square	1	Top	\$0.99
770523	Bourns	3362U	3362U-1-102LF	1,000	0.5 W	10	1/4" Square	1	Top	\$0.99
2194689	BI Technologies	3362U	25UR200K (3362U-1-204)	200,000	0.5 W	10	1/4" Square	1	Top	\$0.99
2133780	Jameco Valuepro	3362U	3362U-1-105LF	1,000,000	0.5 W	10	1/4" Square	1	Top	\$0.79
2285583	Bourns	3362W	3362W-1-101LF	100	0.5 W	10	1/4" Square	1	Side	\$0.99
254166	BI Technologies	3362W	25RXR501/62-2-1 (3362W-1)	500	0.5 W	10	1/4" Square	1	Side	\$0.79
254204	Jameco Valuepro	3362W	3362W-1-103VP	10,000	0.5 W	10	1/4" Square	1	Side	\$0.99
254211	BI Technologies	3362W	25RXR20K (3362W-1-203)	20,000	0.5 W	10	1/4" Square	1	Side	\$0.99
254262	BI Technologies	3362W	25RXR500K (3362W-1-504)	500,000	0.5 W	10	1/4" Square	1	Side	\$0.99
2194785	BI Technologies	3362X	25XR500K (3362X-1-504)	500,000	0.5 W	10	1/4" Square	1	Side	\$0.99
2194620	BI Technologies	3362Z	25RSR1K (3362Z-1-102VP)	1,000	0.5 W	10	1/4" Square	1	Side	\$0.79
2194638	BI Technologies	3362Z	25RS2K (3362Z-1-202)	2,000	0.5 W	10	1/4" Square	1	Side	\$0.99