

INDEX

ATTACHMENT PLUG:

NEMA CONFIGURATION

Cat. No.	Config.	Cord AWG	Electrical A/V.	Sec	Fig.	C-UL
WS-001	5-15	18,16,14,12/3	10,13,15/125	1	1	Yes
WS-001F	5-15	18,16,14,12/3	10,13,15/125	1	1	Yes
WS-001G	5-15	18,16,14,12/3	10,13,15/125	1	1	Yes
WS-001I	6-15	14,12/3	15/250	1	4	Yes
WS-001I	5-20	14,12/3	20,18/125	1	-	Yes
WS-001I	6-20	14,12/3	18,20/250	1	-	Yes
WS-001C	6-20P	18,14,12/3	10,13,18,20/250	1	5	Yes
WS-001C	5-20P	18,14,12/3	10,18,20/125	1	-	Yes
WS-001C	6-15P	18,14,12/3	10,15,15/250	1	-	Yes
WS-001C	5-15P	18,14,12/3	10,15,15/125	1	-	Yes
WS001D(Series)	6-20P	18,16,14,12/3	10,13,18,20/250	1	-	Yes
WS001D(Series)	5-20P	18,16,14,12/3	10,13,18,20/125	1	-	Yes
WS001D(Series)	6-15P	18,16,14,12/3	10,13,15,15/250	1	-	Yes
WS001D(Series)	5-15P	18,16,14,12/3	10,13,15,15/125	1	-	Yes
WS-001H	5-15	18,16,14,12/3	10,13,15/125	1	2	Yes
WS-001H	6-15	18,16,14,12/3	10,13,15/250	1	2	Yes
WS-001H	5-20	18,16,14,12/3	10,13,20/125	1	2	Yes
WS-001H	6-20	18,16,14,12/3	10,13,20/250	1	2	Yes
WS-001H-6	5-15	18,16,14/3	10,13,15/125	1	-	Yes
WS-001H-7	5-15	18,16,14/3	10,13,15	1	26	Yes
WS-001H-8	5-15	18,16,14/3	10,13,15	1	28	Yes
WS-001H-10	5-15	18,16,14/3	-	1	29	Yes
WS-001M	5-15P	18,14,12/3	10,15,15/125	1	6	Yes
WS-001M	5-20P	18,14,12/3	10,18,20/125	1	6	Yes
WS-001M	6-15P	18,14,12/3	10,15,15/250	1	6	Yes
WS-001M	6-20P	18,14,12/3	10,18,20/250	1	6	Yes
WS-004	1-15	18,16/2	10,13/125	1	7	Yes
WS-004A	1-15	18,17,16,14/2	10,12,13,15/125	1	3	Yes
WS-004C	1-15	18,17,16,14/2	10,12,13,15/125	1	3	Yes
WS-004C-3	1-15	18,17,16,14/2	10,12,13,15/125	1	3	Yes
WS-004-L	1-15	18,17,16,14/2	10,12,13,15/125	1	22	Yes
WS-004-R	1-15	18	10/125	1	33	Yes
WS-004-S	1-15	18/2	7/125	1	34	Yes
WS-004-Q	1-15	18,16,14/2	10,13,15/125	1	35	Yes
WS-117	L5-20P	14,12,10/3	18,20,20/125	1	8	Yes
WS-117-2	L5-20P	12,10	20,20/125	1	-	Yes
WS-118	L5-15P	16,14,12,10/3	13,15,15,15/125	1	9	Yes
WS-119	L6-20P	16,14,12,10,8/3	13,18,20,20,20/250	1	9	Yes
WS-119-2	L6-20P	12,10	20,20/250	1	-	Yes
WS-120	L6-30P	16,14,12,10,8/3	13,18,25,30,30/250	1	9	Yes
WS-120-2	L6-30P	12,10	25,30/250	1	-	Yes
WS-121	L5-30P	16,14,12,10,8/3	13,18,25,30,30/125	1	9	Yes
WS-121-2	L5-30P	12,10	25,30/125	1	-	Yes
WS-122	L14-30P	16,14,12,10,8/4	10,15,20,25,30/250	1	9	Yes
WS-122-2	L14-30P	12,10	25,30/250	1	-	Yes
WS-123	L6-15P	16,14,12,10,8/3	13,15,15,15,15/250	1	9	Yes
WS-129	L14-20P	16,14,12,10,8/4	10,15,20,20,20/250	1	9	Yes
WS-129-2	L14-20P	12,10	20,20/250	1	-	Yes
WS-130	L1520PPH	16,14,12,10,8/4	10,15,20,20,20/250	1	9	Yes
WS-130-2	L15-20P	12,10	20,20/250,3-	1	-	Yes
WS-131	L15-30P	16,14,12,10,8/4	10,15,20,30,30/250	1	9	Yes
WS-131-2	L1530PPH	12,10	25,30/250,3-	1	-	Yes
WS-225	L21-30P	10	30A, 120/208 V, 3 PH	1	30	Yes
WS-226	L7-15P	18,16,14,12,10/3	10,13,15,15,15/277	1	25	Yes
WS-234	L21-20	12,10/5	20.20/208,250	1	-	Yes
WS-004E	1-15(EMI)		18/27/125	1	10	Yes

CORD CONNECTOR :

NEMA CONFIGURATION

Cat. No	Config	Cord AWG	Electrical A/V	Sec.	FIG.	C-UL
WS-022	5-15	16,14/3	13,15/125	2	3	Yes
WS-022(A.C.1)	5-15	14,12/3	15/125	2	3B	Yes
WS-022-5	5-15	18, 16, 14/3	10, 13, 15/125V	2	3A	Yes
WS-108	L5-15	14,12,10/3	15,15,15/125	2	22	Yes
WS-109	1-15	16/2	13/125	2	17	Yes
WS-111	L5-20	14,12,10/3	18,20,20/125	2	23	Yes
WS-111-2	L5-20	12, 10	20, 20/125	2		Yes
WS-113	L5-30	14,12,10/3	18,25,30/125	2	24	Yes
WS-113-2	L5-30	12, 10	25, 30/125	2		Yes
WS-116-3	5-15	18,16,14,12/3	10,13,15,15/125	2	16	Yes
WS-116-5	5-15	18,16,14,12/3	10,13,15,15/125	2	31, 32	Yes
WS-170	5-20	16,14,12/3	13,15,20/250	2	10	Yes
WS-170-1	5-20	16,14,12/3	13,15,20/125	2	11	Yes
WS-171	6-20	16,14,12/3	13,15,20/125	2	-	Yes
WS-172	6-15	16,14,12/3	13,15,15/250	2	-	Yes
WS-173	L6-15	14,12,10/3	15,15,15/250	2	25	Yes
WS-174	L6-20	14,12,10/3	18, 20, 20/250	2	18	Yes
WS-174-2	L6-20	12, 10	20, 20/250	2		Yes
WS-175	L6-30	14,12,10/3	18, 25, 30/250	2	19	Yes
WS-175-2	L6-30	12, 10	25, 30/250	2		Yes
WS-176	L14-20	14,12,10/4	15,20,20/125,250	2	20	Yes
WS-176-2	L14-20	12, 10	20, 20/125,250	2		Yes
WS-177	L14-30	14,12,10/4	15,20,30/125,250	2	21	Yes
WS-177-2	L14-30	12, 10	20, 30/125,250	2		Yes
WS-178	L15-20	14,12,10/4	18,20,20/250	2	26	Yes
WS-178-2	L15-20	12, 10	20, 20/250, 3-PH	2		Yes
WS-179	L15-30	14,12,10/4	18,25,30/250	2	27	Yes
WS-179-2	L15-30	12, 10	25, 30/250, 3-PH	2		Yes
WS-241	5-15	16,14/3	13,15/125	2	12	Yes
WS-026-1	1-15	16,14/2	13,15/125	2	13	Yes
WS-026-3	1-15	16,14/2	13,15/125	2	14	Yes
WS-026-5	1-15	16,14/2	13,15/125	2	15	Yes
WS-026-6	1-15	18, 16, 14/2	10, 13, 15/125	2	15A	Yes

IEC CONFIGURATION

Cat. No.	Config	Cord AWG	A/V	Sec.	FIG.	C-UL
WS-002	C13	18,16,14,12/3	10,13,15/125,250	2	1	Yes
WS-002-2	C13	18,16,14,12/3	10,13,15/125,250	2	1	No
WS-002A-R	C13	18,16,14/3	10,13,15/125,250	2	1	Yes
WS-002A-L	C13	18,16,14/3	10,13,15/125,250	2	1	Yes
WS-002B	C13	18,16,14/3	10,13,15/125,250	2	1	Yes
WS-002C	C15	18,16,14/3	10,13,15/125,250	2	1	Yes
WS-002C-1	C15	18,16,14/3	10,13,15/125,250	2	-	Yes
WS-002C-2	C15	18,16,14/3	10,13,15/125,250	2	-	Yes
WS-002C-5	C15	18,16,14/3	10,13,15/125,250	2	-	Yes
WS-002C-0	C15	18,16,14/3	10,13,15/125,250	2	1-1	Yes

INDEX

Construction	United States Type	Canadian Type	Section
Jacketed Cords: Thermoplastic	SVT, SVTO, <u>SVTOO</u> , SJT, SJTW <u>SJTO</u> , <u>SJTOO</u> , SJTOW, <u>SJTOOW</u> , ST, STW, STO, <u>STOO</u> , <u>STOW</u> , <u>STOOW</u>	SVT, SVTO, <u>SVTOO</u> , SJT, SJTW, SJTO, <u>SJTOO</u> , SJTOW, <u>SJTOOW</u> , ST, STW, STO, <u>STOO</u> , <u>STOW</u> , <u>STOOW</u>	1
Miscellaneous Cords:	Clock Cord	N/A	2
Parallel Cords: Thermoplastic	SPT-1, SPT-2, SPT-3, SPT-1W, SPT-2W, NISPT-1, NISPT-2	SPT-1, SPT-2, SPT-3	3
Range and Dryer Cord:	SRDT	DRT	4
N/A - Not Applicable.			

All rights reserved by Well Shin.
None of the information here may be used,
duplicated, reproduced, and changed,
either partially or completely,
without prior permission of Well Shin.

NEMA CONFIGURATION

Cat. No.	Config.	Cord AWG	Electrical A/V	Sec.	Fig.	C-UL
WS-001B9	5-15	18,16,14/3	10,13,15/125	1	14	Yes
	6-15	18,16,14/3	10,13,15/250	1	-	Yes
WS-001J	10-30	10/3	30/125,250	1	15	Yes
WS-001J-1	10-50	10/3	30/125,250	1	43	Yes
		8/2 & 10/1	40/125,250	1	-	Yes
		6/2 & 8/1	50/125,250	1	-	Yes
WS-001J-2	TT	10/3	30/125	1	30	Yes
WS-330	L7-20P	18,16,14,12,10/3	10,13,18,20,20/277	1	42	Yes

NEMA CONFIGURATION

Cat. No.	Config.	Cord AWG	Electrical A/V	Sec.	Fig.	C-UL
WS-001K	14-50P	10/4,8/2 & 10/2	30,40/125,250	1	44	Yes
	14-50P	6/2 & 8/2	50/125,250	1	-	Yes
		6/3 & 8/1	50/125,250	1	-	Yes
		6/4	50/125,250	1	-	Yes
WS-001K(A.C.)	14-50P	8/2 & 10/2, 6/2 & 8/2	40,50/125,250	1	-	Yes
WS-001L	5-50	12,10/3	20,30/125	1	-	Yes
WS-001N	6-50	12,10/3	20,30/250	1	-	Yes
WS-001O	5-30	12,10/3	20,30/125	1	45	Yes
WS-001P	14-30	10/4	30/125,250	1	16	Yes
WS-001Q	6-30P	12,10/3	20,30/250	1	-	Yes
WS-001R	7-30	12,10/3	20,30/277 ac	1	17	Yes
WS-001S	7-50	12,10/3	20,30/277 ac	1	-	Yes
WS-001T	11-30	10/3	30/250	1	-	Yes
WS-001U	11-50	10/3/1	30/250	1	46	Yes
WS-001B	5-15	18,16,14/3	10,13,15/125	1	-	Yes
WS-001B1~8	5-15	18,16,14/3	10,13,15/125	1	-	Yes
WS-001B17~24	5-15	18,16,14/3	10,13,15/125	1	-	Yes
WS-001W	7-15	18,16,14,12/3	10,13,15,15/277	1	-	Yes
WS-001X	7-20P	14,12/3	18,20/277	1	19	Yes
WS-001-3	14-20P	14,12/4	18,20,125/250	1	27	Yes
WS-001Z	5-15	18,17,16,14,12/3	10,12,13,15,15/125	1	23	Yes
WS-004B-2	1-15	18,16/2	10,13/125	1	36	Yes
WS-001B-31	5-15	14/3	15/125	1	37	Yes
WS-001-15	5-15	14,12,10/3	15,15,15/125	1	38	Yes
WS-001H-11	5-15	18,16,14,12/3	10,13,15,15/125	1	-	Yes
WS-001H-12	6-15	18,16,14,12/3	10,13,15,15/250	1	-	Yes
WS-001H-13	5-20	18,16,14,12/3	10,13,18,20/125	1	-	Yes
WS-001H-14	6-20	18,16,14,12/3	10,13,18,20/250	1	39	Yes
WS-001H-15	5-15	18,16,14,12/3	10,13,15,15/125	1	-	Yes
WS-001H-16	6-15	18,16,14,12/3	10,13,15,15/250	1	-	Yes
WS-001H-17	5-20	18,16,14,12/3	10,13,18,20/125	1	-	Yes
WS-001H-18	6-20	18,16,14,12/3	10,13,18,20/250	1	40	Yes