



MATERIAL

- Nylon 66 UL94V-0
- Poles : 1 - 40

PXHXXB1PH1	DIMENSIONS		PXHXXB1PH1	DIMENSIONS	
CONTACTS	A	B	CONTACTS	A	B
2	2.54	5.08	22	53.34	55.88
3	5.08	7.62	23	55.88	58.42
4	7.62	10.16	24	58.42	60.96
5	10.16	12.74	25	60.96	63.50
6	12.74	15.24	26	63.50	66.04
7	15.24	17.78	27	66.04	68.58
8	17.78	20.32	28	68.58	71.12
9	20.32	22.86	29	71.12	73.66
10	22.86	25.40	30	73.66	76.20
11	25.40	27.94	31	76.20	78.74
12	27.94	30.48	32	78.74	81.28
13	30.48	33.02	33	81.28	83.82
14	33.02	35.56	34	83.82	86.36
15	35.56	38.10	35	86.36	88.90
16	38.10	40.64	36	88.90	91.44
17	40.64	43.18	37	91.44	93.98
18	43.18	45.72	38	93.98	96.52
19	45.72	48.26	39	96.52	99.06
20	48.26	50.80	40	99.06	101.60
21	50.80	53.34			

UNIT: mm

CIC Components Ind Co Ltd.

繪圖 DRAWN BY
FUFU

日期 DATE
2009/03/31

核對 CHECKED BY
WENDY

比例 SCALE
1:1

PXHXXB1PH1

圖號 710-XX-80

DRAWING NO.