



GARDTEC

Part Number:

HP50-24 ("90° Plug)

Wire: **SPT1 2 conductor 105°C, 300 volts**

Lengths: **24" (610mm)**

Other options:

- **terminal connections** (any)
- **heat shrink**
- **labeling**
- **stripping**
- **tinning**
- **three conductor cords**
- **complete wire harness assemblies**
(rated at 105°C, 300 volts)
- **red tracer cords**
(all head configurations and lengths)

Listings:



UL listed (E189621, E156798)
Rated 10 AMP/125 VAC



CSA listed (LR76679-1)
Rated 7 AMP/125 VAC

