



Date	Rev.	Description




SPECIFICATIONS:

CONTACT RATING : Q:3AMPS@120V AC OR 28V DC.
1.5AMPS@250V AC.
G: 0.4VA AMPS @ 20V AC or DC
ELECTRICAL LIFE : 6,000 make-and-break cycles at full load.
CONTACT RESISTANCE : 20 mΩ max. initial @ 2-4 V DC.
100 mA, for both silver and gold plated contacts.
INSULATION RESISTANCE : 1,000 MΩ min.
DIELECTRIC STRENGTH : 1,000 V RMS @ sea level.
OPERATING TEMPERATURE : -30 °C to 130 °C



P.C. MOUNTING



Schematic

o 02 Comm.

1 • / 3 •

Model No.	Switching Position		
	ON	NONE	ON
DS-41	ON	NONE	ON
DS-42	ON	NONE	(ON)
DS-43	ON	OFF	ON
Term Comm.	2-3	OPEN	2-1

MATERIALS:

CASE : Diallyl phthalate (DAP)(UL-94V-0).
ACTUATOR : ZINC ALLOY.
BUSHING : ZINC ALLOY.
HOUSING : Stainless steel.
TERMINAL/CONTACT : Brass, with silver or gold plated.
or gold over silver
SWITCH SUPPORT : Brass, tin plated.

DCC. NO.
A4 DRAWING NO.

MATERIAL		GOLDSUN ELECTRONICS CO., LTD.			
		JAMECO NO. 106067		GOLDSUN NO.	
DRAWN: Tina		Description			Rev. 1
VERIFY PEOPLE: Chesley		UNIT: mm	SCALE:	SHEET 1 OF 1	CAS No: ERN No: