



REV.	ECN NUMBER	DATE
A	RELEASED	2012/09/21

Part No.	Color	Contact	Plating
AMJ+P060A-09	Black	Phosphor Bronze	Gold/Nickel Plated
AMJ+P060A-Y9	Yellow	Phosphor Bronze	Gold/Nickel Plated
AMJ+B060A-09	Black	Brass	Gold/Nickel Plated
AMJ+B060A-Q9	BLUE	Brass	Gold/Nickel Plated
AMJ+B060A-99	White	Brass	Gold/Nickel Plated
AMJ+B060A-R2	Red	Brass	Gold/Nickel Plated
AMJ+P060A-R2	Red	Phosphor Bronze	Gold/Nickel Plated
AMJ+P060A-59	Green(3285c)	Phosphor Bronze	Gold/Nickel Plated
AMJ+B060A-R91	Red(192U)	Brass	Gold/Nickel Plated
AMJ+B060A-Y9	Yellow	Brass	Gold/Nickel Plated
AMJ+B060A-04	Black	Brass	Tin Plated
AMJ+B060A-0I	Black	Brass	Gold(10u")/Nickel Plated
AMJ+P060A-0U	Black	Phosphor Bronze	Gold(5u")/Nickel Plated
AMJ+B060A-01	Black	Brass	Gold Plated
AMJ+P060A-01	Black	Phosphor Bronze	Gold(金)/Nickel Plated
AMJ+B060A-9T	White	Brass	Gold(3u")/Nickel Plated
AMJ+B060A-94	White	Brass	Tin Plated

NOTES

1.MATERIAL

1.1 Insulator:PBT+15%G.F(UL94V-0)

2.SPECIFICATION

2.1 Current Rating: 3 Amp

2.2 Dielectric Withstading : AC 500V/min R.M.S.

2.3 Insulator Resistance: 1000M ohms Min

2.4 Contact Resistance: 20m ohms Max

2.5 Operation Temperature: -45°C to 105°C

2.6 Contact retention force: 0.9Kgf/pin MIN.

2.7 Insertion force: 0.5Kgf/pin MAX.

2.8 Withdrawal force: 0.1Kgf/pin MIN.

GOLDSUN ELECTRONICS CO., LTD.

JAMECO NO. 112442		GOLDSUN NO.	
Description SOCKET SHORTING BLKS BLUE CLOSE (GJWCL-B)			Rev. 1
UNIT: mm	SCALE:	SHEET 1 OF 1	CAS No: ERN No: