

Distributed by:

JAMECO[®]
ELECTRONICS

www.Jameco.com ♦ 1-800-831-4242

The content and copyrights of the attached
material are the property of its owner.

Jameco Part Number 115837


MATERIALS:

PLASTIC HOUSING: ENGINEERING THERMOPLASTIC
 FLAMMABILITY RATING UL 94V-0.




CONTACTS: 0.35MM THICKNESS PHOSPHOR BRONZE

PLATING: GOLD PLATING OVER NICKEL IN CONTACT.

TIN PLATING OVER NICKEL IN SOLDER AREA.



PCB LAYOUT/TOP VIEW



- 3u" P/N 3008314000
- 8u" P/N 3008314100
- 15u" P/N 3008314200
- 30u" P/N 3008314300
- 50u" P/N 3008314400

※ 凡標記號者，為品管檢驗之尺寸

設計 DR. Vinson 93-06-07	核准 APPL Jerry 93-08-07
------------------------------	------------------------------

容許公差	TOLERANCE
.XXX	±0.10
.XX	±0.25
.X	±0.38
X	±0.50
ANG	±3°

品名 ARTICLE	GP&G W/FLANGED PCB JACK
圖號 DWG NO.	3008314000

版本說明	REVISION NOTE
------	---------------

單位 UNIT	比例 SCALE	張數 SHEET	版本 REV.
mm	4/1	1/1	A

