



Consolidated

ELECTRONIC WIRE & CABLE

Part # 818, 22 AWG (7 x 30) Stranded Tinned Copper Wire, UL Style 1007 and UL Style 1569 VW-1 80°C / 105°C 300 Volts, CSA TR-64 90°C, Consolidated Hook Up Wire

Product Construction

Conductor:

- 22 AWG (7 x 30) Stranded Tinned Copper Wire
- Stranded Tinned Copper Wire Conductor per ASTM B-33

Insulation:

- UL 1007 color coded PVC
- Temperature: -40° to +80°C
- UL 1569 color coded PVC
- Temperature: -40°C to +105°C

Applications:

- Consolidated Stranded Copper Wire UL Style 1007 / UL Style 1569 80°C / 105°C 300 Volt Hook-Up Wire
- Point to point wiring
- Internal wiring of meters, panels, electrical and electronic equipment

Industry Approvals:

- UL Style 1007
- UL

[+ more](#)



[Specifications](#) | [Other Information](#) | [Disclaimer](#)

Specifications

Gauge	22 AWG
Strands	(7 x 30) Tin Copper Wire
Nominal Insulation Wall	0.016 in.
Insulation Type	PVC
Nominal O.D.	0.062 in.
Color	0-Black/1-Brown/2-Red/3-Orange/4-Yellow/5-Green/6-Blue/7-Violet/8-Gray/9-White
Color Code Chart	Chart-Hook-Up Wire
Insulation Temperature	UL Style 1007 -40 to +80 °C UL Style 1569 -40 to +105 °C
Voltage Rating	300 V

Other Information

Approvals	CSA TR-64 90°C RoHS Compliant UL 1007, UL 1569 VW-1
------------------	--

Terms and Conditions for the Consolidated Electronic Wire and Cable Website:

Consolidated has made a very reasonable effort to ensure the accuracy of this "website" pertaining to the information, specifications and the "search" accuracy. The "website" is subject to errors and omissions. The content is subject to change without notice. This "website" is being constantly updated to correct any errors and omissions, but this does not ensure it is completely accurate. Drawings are for general reference only. Consolidated Electronic Wire & Cable is not liable for any direct, indirect, incidental or consequential damages resulting from the use of the material from this "website".

Consolidated Electronic Wire & Cable - 11044 King St., Franklin Park, Illinois 60131 | Toll Free: 800-621-4278 • Phone: 847-455-8830 • Fax: 847-455-8837 | Email: info@conwire.com