

Distributed by:

JAMECO[®]
ELECTRONICS

www.Jameco.com ♦ 1-800-831-4242

The content and copyrights of the attached
material are the property of its owner.

Jameco Part Number 139564

MATERIALS

1. CONTACT: BRASS
2. INSULATOR: PBT (UL 94V-0)
3. CONTACT PLATING: GOLD OVER NICKEL

SPECIFICATION

1. INSULATOR RESISTANCE: 5000M ohms Min
2. CURRENT RATING: 3 Amps
3. DIELECTRIC WITHSTANDING VOLTAGE: AC 500V
4. OPERATING TEMPERATURE: -45°C TO +105°C



Old Series number : 7000 Series

Part Number :

2012-254-2xXX-RG

XX : number of contacts

ROHS



TOP WILLING	TITLE	PIN HEADER PITCH=2.54mm Right Angle 雙排	SCALE		APP.	LISA	GENERAL TOLERANCE UNLESS SPECIFIED		REV
	DWG.NO.	P3-011XXX168RABG	SHEET	1 OF 1	CHK.	JACKY	LINEAR	0.0±0.30	
			UNIT	MM	DR.	DAVID	ANGLES	±1°	
8	7	6	5	4	3	2	1		