

Distributed by:

**JAMECO**<sup>®</sup>  
ELECTRONICS

**www.Jameco.com ♦ 1-800-831-4242**

The content and copyrights of the attached  
material are the property of its owner.

Jameco Part Number 141066


Date	Rev.	Description

Part No.	Size	Rating	Description	Filament Shape
141066	T1 3/4		5V 0.06A	C-2R

Test Volts	Current (mA $\pm$ 10%)			Light Output (CP $\pm$ 25%)			Life Hours
	Min.	Nom.	Max.	Min.	Nom.	Max.	
5	54	60	66	0.0375	0.05	0.0625	10,000

**DIMENSIONAL CHARACTERISTICS:**

- A. 5.84 MAX
- B. 13.2 MAX
- C. 25.4 Min
- D. 0.3



MATERIAL	<b>GOLDSUN ELECTRONICS CO., LTD.</b>		
JAMECO NO.	<b>141066</b>	GOLDSUN NO.	2200-R
DESCRIPTION	T-1 3/4 WIRE TERMINAL		Rev. 1
UNIT: mm	SCALE:	SHEET 1 OF 1	CAS No: ERN No:

DCC. NO.
A4 DRAWING NO.

DRAWN: Kiki Chen
VERIFY PEOPLE: Wendy Chen, Fanny Du